

Which professional LED work light do you need?



	Professional LED inspection lamps										MatchLine LED LED Daylight Lamps		
Light output (lumens)	100/50*	130	200/100*	145	130/70*	150	250/120*	300/120*	350/150*	330	1200/500*	2300/1200*	1500/750*
Beam	50°	40°	80°	80°	90°	120°	90°	90°	90°	120°	120°	90°	360° total illumination
Name	HDL10	Penlight Professional	PEN20	Penlight Premium	RCH6	RCH10	RCH19	RCH21S	RCH31UV	CBL10	CBH51	PJH20	MDLS CRI
Pointer		20 lm		120 lm					UV leak detector				
Power supply	AAA	AAA	Rechargeable	Rechargeable	Rechargeable	Rechargeable	Rechargeable	Rechargeable	Rechargeable	Plug	Plug, Rechargeable	Plug, Rechargeable	Rechargeable
Mounting		Lock	Lock, Hook	Lock, Hook	Lock, Hook	Lock, Hook	Lock, Hook	Lock, Hook	Lock, Hook	Lock	Lock		Lock, Hook
FindMe LED			FindMe LED		FindMe LED			FindMe LED	FindMe LED				
Robustness	IP X4	IP 54	IP 54, IK 07	IP 54, IK 07	IP 54, IK 07	IP 54, IK 07	IP 20, IK 07	IP 65, IK 08	IP 54, IK 07	IP 54, IK 07	IP 54, IK 07	IP 67, IK 09	IP 54, IK 07
Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant	Grease resistant
Order Entry	LPL29B1	LPL19B1	LPL42X1	LPL28RECHX1	LPL38X1	LPL20X1	LPL46X1	LPL47X1	LPL34UVX1	LPL35X1	LPL45X1	LPL39X1	LPL403MODX1
GOC	39360631	38819031	39631731	39220394	39607231	39060531	39823631	39841031	39419131	39421431	39732131	39609631	39627066

* Boost / Eco mode