

PHILIPS

Automotive lighting



Safety
you can **see**

Catalog 2018–2019

Countries outside of European Union

Safety you can see!

Our advanced light engine technology has been on the forefront of automotive lighting for more than 100 years. As a **leading supplier** of lamps and lighting products to the automotive industry and aftermarket, we combine technical innovations with a genuine concern for **safety** and driving comfort. Our automotive lighting is today the choice of many consumers and major automobile manufacturers. Our mission is to introduce **innovative products** that constantly improve road safety and increase workshop productivity.

Our products are designed to perform efficiently and durably for continuous **customer satisfaction**. Many garages and workshops already appreciate our new range of professional LED work lights for their outstanding light output and robustness.

High-quality lighting really does make a difference.

That's safety you can see!



Original equipment quality

We are committed to producing **best-in-class products** and services in the Original Equipment Manufacturer (OEM) market and automotive aftermarket. Our products are manufactured from **high-quality materials** and tested

to the highest specifications to maximize **safety** and driving **comfort** of our customers.

- We are the **choice** of major car manufacturers

- Our lighting equips **one in two cars** in Europe and one in three in the world
- Manufacturing processes that **exceed** current industry **specifications**

Philips anti-UV-quartz glass for optimal lighting performance

All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.

- **More powerful light**

Quartz glass high resistance allows for increased pressure inside the lamp and thus generates more powerful light.

- **Better resistance**

Philips quartz glass lamps (filament at 2 650°C and glass at 800°C) are capable of withstanding severe thermal shocks.

- **Optimal protection against ultraviolet rays**

All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.

Table of content

Introduction

2

Safety you can see

Halogen

6

12V Car lighting

Vision	10
VisionPlus	10
X-tremeVision G-force	11
LongLife EcoVision	11
ColorVision	12
WhiteVision ultra	12
CrystalVision	13
DiamondVision	13
RacingVision	15
Which lamp for which function?	16



24V bus and truck lighting

MasterDuty	47
MasterLife	48
MasterDuty BlueVision	48
Which lamp for which function?	49



36

Two-wheeler lighting

Vision moto	39
CityVision moto	39
X-tremeVision moto	40
CrystalVision ultra moto	40
Which lamp for which function?	41



56

Kits

for cars and trucks

12V spare kits	58
24V spare kits	60
Headlight restoration kit	61



Xenon

62

for cars and truck

Xenon Vision	65
Xenon X-tremeVision gen2	66
Xenon LongerLife	67
Xenon WhiteVision gen2	68
Our pro-active solution against Xenon lamp piracy	69



LED retrofit

74

for cars and trucks

Which LED lighting for which function?	78
Ultinon LED	80
X-tremeUltinon LED	80
X-tremeUltinon LED gen2	81
CANbus LED adapter	81



LED work lights

90


Find the right work light for the job	93
HDL10	96
Penlight Professional	96
PEN20	97
Penlight Premium	97
RCH5S	98
RCH6	98
RCH10	99
RCH19	99
RCH21S	100
RCH25	100
RCH31UV	101
CBL10	102
CBH51	102
PJH10	103
Philips MatchLine	104
PJH20	105
MDLS CRI	105



Annexes

108

Lighting technology explained	108
Specimen packaging	110
Understanding Philips ordering codes	111
Bases technical illustrations	112
Product index	113



Halogen



12V car lighting



Which car lamp do you need?



Experience more light



New

Up to **30%** more vision*



Vision
★★★★★



Beam performance



Light color



Lifetime**



Available in H1, H3, H4, H7, HB3, HB4, H11

Up to **60%** more vision*



VisionPlus
★★★★★




Beam performance



Light color



Lifetime**



Available in H1, H4, H7

Up to **130%** brighter light*



X-tremeVision
★★★★★



Beam performance



Light color



Lifetime**



Available in H1, H4, H7

Up to **130%** brighter light*



X-tremeVision G-force
★★★★★



Beam performance



Light color



Lifetime**




Available in H1, H4, H7***

Light that lasts


Lifetime up to **1500** hours**



LongLife EcoVision
★★★★★



Beam performance



Light color



Lifetime**



Available in H1, H3, H4, H7, H11

Images for illustration purposes only.

* Compared to the minimum legal standard

** Lifetime differs per type, indication for H7 only

*** 10 G applies to H4 and H7

**** Non-ECE homologated, for off-road only


Enjoy
your passion



Intense white
xenon effect



WhiteVision
★★★★★



Available in H1, H3, H4, H7, H8, H11, HB3, HB4

Up to **150% brighter light***



RacingVision
★★★★★




Available in H4, H7

Bright white light



CrystalVision****
★★★★★





Available in H1, H3, H4, H7, H11, HB3, HB4

Ultimate white light



DiamondVision****
★★★★★



Available in H1, H3, H4, H7, HB3, HB4

Vision

Up to **30%**
more vision*

- **Competitive price-performance ratio**
- **High-quality and ultra-resistant car lamp**

Philips Vision headlamps ensure excellent light-beam performance at a very **competitive price**.

*Compared to the minimum legal standard



Standard

Vision

Available in C1 and B1 packaging



Available in



VisionPlus

Up to **60%**
more vision*

- **Greater driving comfort with enhanced visibility**
- **High-quality and ultra-resistant car lamp**

Philips VisionPlus headlamps allow drivers to see farther for greater **safety** and **comfort**.

*Compared to the minimum legal standard



Standard

VisionPlus

Available in S2 and B1 packaging



Available in



X-tremeVision G-force

Up to **130%**
brighter light*

- Durable headlights with up to 10G vibration resistance**
- White light for higher contrast and more visibility
- Best-in-class lifetime

Philips X-tremeVision G-force car bulbs are among the **brightest** you can buy with up to 10 G vibration resistance. **See further, react faster** and **drive safer**.

*Compared to the minimum legal standard
**10 G applies to H4 and H7



Standard

X-tremeVision G-force

Available in S2 and B1 packaging



Available in



H1



H4



H7

LongLife EcoVision

Longer Lifetime,
less replacement

- Lasts significantly longer*
- High-quality and ultra-resistant car lamp

Tired of **changing** your headlamps all the time? With **longer lifetime**, Philips LongLife EcoVision is the choice for drivers seeking to **minimize maintenance** on their vehicles.

*Lifetime differs per type, indication for H7 only.



Available in



H1



H3



H4




H7



H11

Available in S2, C1 and B1 packaging



WhiteVision

Intense white xenon effect

- **Maximum visibility, premium look**
- **Maximum white light for greater contrast**
- **100% road legal**

Philips WhiteVision lamps add an intense white xenon look to your car headlights for a **premium driving experience** at night.



Safety has never been so attractive

Available in



Standard WhiteVision

Available in S2 and B1 packaging



WhiteVision ultra

Sharp white look

- **Superior white stylish look with up to 4 200 Kelvin**
- **100% road-legal performance**
- **Driving comfort with up to 60% more vision***

Philips WhiteVision ultra, featuring the latest coating formula, delivers a stunning white light of up to 4 200 Kelvin. These are the whitest road-legal halogen lights in our portfolio and the perfect choice if you're looking for a cool, stylish look.


*Compared to the minimum legal standard



Available in S2 and B1 packaging



Available in



CrystalVision

Bright white light

- Up to 4300K
- Bluish effect in the headlight
- Non-ECE homologated, for off-road only

Offering a bright white light, close to **daylight**, Philips CrystalVision produces more light than a standard headlamp and is ideal for all-purpose driving.



Standard

CrystalVision

Available in



Available in S2 and B1 packaging



DiamondVision

Ultimate white light

- Up to 5000K
- Blue-coated glass
- Non-ECE homologated, for off-road only

Philips DiamondVision produces a dazzling **white light** at up to **5000K**, offering more light output than standard headlamps. Its **styling effect** is ideal for city driving.



Standard

DiamondVision

Available in



Available in S2 and B1 packaging







RacingVision

Up to 150%* brighter light

- For a sportive drive and an increased performance
- See further, react faster
- Optimized for winter light conditions

When driving on poorly lit country roads, you rely on the performance of your headlights. Faced with an unexpected danger, reaction time is everything. Even split seconds can make a crucial difference to your safety. The superior beam performance of the Philips RacingVision headlamp helps you identify dangerous situations faster and stay in perfect control of your vehicle – whatever road conditions you're facing.

*Compared to the minimum legal standard



Standard



RacingVision

Available in S2 and B1 packaging



Available in



H4



H7

Images for illustration purposes only

Which lamp for which function?



**X-tremeVision
G-force**
New



R2 R2 Visio H1 H3 H4 H7 H9 H10 H11 H13 H15 HB3 HB4 HB5 HIR2 P13W PW16W PS19W PSX26W HiPerLCP



Low beam – high beam – Daytime Running Lights



H21W HY21W P21W PY21W PY21Wsv W21W WY21W PSY24W PSY24Wsv PWY24W PY24W PY24Wsv



W3W W5W WBT5 Bax



Front indicators



T4W H5W W5W WBT10 C5W FEST10W LED-T10 (=W5W) LED-FEST 43mm



Interior lights



W3W T4W R5W H5W W5W H6W W21/5W



Front parking lights



W3W T4W R5W W5W WY5W PCY16W



H1 H3 H4 H7 H8 H11 H16 HB3 HB4 H27W/1 H27W/2 PSX24W PS24W



Side indicators



Front fog lights

— Available in Standard





Vision

VisionPlus

X-tremeVision

LongLife
EcoVision

WhiteVision


RacingVision

CrystalVision


DiamondVision

— Available in Standard

philips.com/mylamps



Trunk lights



3rd stop light


Rear indicators



Reversing light



Glove compartment lights



Rear parking lights



License plate lights



Rear fog lights



Stop lights

*Combines stop and rear parking light function

12V car lighting

Halogen

H1 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258PRB1	12	55	P14,5s	47516930	8 711500 475169	-	8711500475176	ECE	10
12258PRC1	12	55	P14,5s	47518360	8 711500 475183	8727900363791	8711500475190	ECE	100

H1 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258VPS2	12	55	P14,5s	36322728	8 727900 363227	-	8727900363210	ECE	5
12258VPB1	12	55	P14,5s	36320330	8 727900 363203	-	8727900363197	ECE	10

H1 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258XV+S2	12	55	P14,5s	37166628	8 727900 371666	-	8727900371673	ECE	5
12258XV+B1	12	55	P14,5s	37164230	8 727900 371642	-	8727900371659	ECE	10

H1 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258XVGS2	12	55	P14,5s	35520828	8 727900 355208	-	8727900355215	ECE	5
12258XVGB1	12	55	P14,5s	35522230	8 727900 355222	-	8727900355239	ECE	10

H1 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258LLECOS2	12	55	P14,5s	36255828	8 727900 362558	-	8727900362565	ECE	5
12258LLECOB1	12	55	P14,5s	36196430	8 727900 361964	-	8727900361971	ECE	10
12258LLECO1	12	55	P14,5s	36187230	8 727900 361872	-	8727900370683	ECE	10

H1 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258WHVB1	12	55	P14,5s	37156730	8 727900 371567	-	8727900371574	ECE	10
12258WHVSM	12	55	P14,5s	78884928	8 711500 788849	-	8711500788856	ECE	5

H1 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12454RAB1	12	100	P14,5s	40722130	8 711500 407221	-	8711500407238	-	10
12454RAC1	12	100	P14,5s	69639730	8 711500 696397	-	8727900366396	-	10

H1 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258CVSM	12	55	P14,5s	48971528	8 711500 489715	-	8711500489722	-	5
12258CVB1	12	55	P14,5s	82687930	8 711500 826879	-	8711500826893	-	10

H1 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258DVS2	12	55	P14,5s	69742428	8 711500 697424	-	8711500697431	-	5
12258DVB1	12	55	P14,5s	82690930	8 711500 826909	-	8711500826916	-	10

H1 Spot



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258SPC1	12	55	P14,5s	40460230	8 711500 404602	-	8727900370690	ECE	10

H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12311C1	12	55	X511	47752130	8 711500 477521	-	8727900370782	ECE	10

H3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336PRB1	12	55	PK22s	69561130	8 711500 695611	-	8711500695628	ECE	10
12336PRC1	12	55	PK22s	69534560	8 711500 695345	8711500775696	8711500695352	ECE	100

H3 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336LLECO1	12	55	PK22s	77704130	8 711500 777041	-	8711500779366	ECE	10

H3 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336WHVB1	12	55	PK22s	77951930	8 711500 779519	-	8711500779526	ECE	10

H3 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12455RAC1	12	100	PK22s	47898630	8 711500 478986	-	8711500779373	-	10

H3 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336CVB1	12	55	PK22s	77496530	8 711500 774965	-	8711500774996	-	10

H3 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336DVS2	12	55	PK22s	69745528	8 711500 697455	-	8711500697462	-	5
12336DVB1	12	55	PK22s	77494130	8 711500 774941	-	8711500774972	-	10

H4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRB1	12	60/55	P43t-38	47480330	8 711500 474803	-	8711500474810	ECE	10
12342PRC1	12	60/55	P43t-38	49099560	8 711500 490995	8711500827807	8711500490988	ECE	100
12342PRC2	12	60/55	P43t-38	78028760	8 711500 780287	8711500780294	8711500780300	ECE	100

H4 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342VPS2	12	60/55	P43t-38	39925728	8 727900 399257	-	8727900350937	ECE	5
12342VPB1	12	60/55	P43t-38	39934930	8 727900 399349	-	8727900399332	ECE	10
12342VPC2	12	60/55	P43t-38	37435360	8 727900 374353	8727900374360	8727900374377	ECE	100

H4 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XV+S2	12	60/55	P43t-38	22109428	8 711500 221094	-	8711500221100	ECE	5
12342XV+B1	12	60/55	P43t-38	22107030	8 711500 221070	-	8711500221087	ECE	10

H4 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XVGS2	12	60/55	P43t-38	35525328	8 727900 355253	-	8727900355284	ECE	5
12342XVGB1	12	60/55	P43t-38	35529130	8 727900 355291	-	8727900355390	ECE	10

H4 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342LLECOS2	12	60/55	P43t-38	36257228	8 727900 362572	-	8727900362589	ECE	5
12342LLECOB1	12	60/55	P43t-38	36198830	8 727900 361988	-	8727900361995	ECE	10
12342LLECO1	12	60/55	P43t-38	36189630	8 727900 361896	-	8727900370836	ECE	10

H4 ColorVision Green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPGS2	12	60/55	P43t-38	36787428	8 727900 367874	-	8727900367881	ECE	5

H4 ColorVision Yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPYS2	12	60/55	P43t-38	36789828	8 727900 367898	-	8727900367904	ECE	5

H4 ColorVision Purple



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPPS2	12	60/55	P43t-38	36791128	8 727900 367911	-	8727900367928	ECE	5

H4 ColorVision Blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPBS2	12	60/55	P43t-38	36793528	8 727900 367935	-	8727900367942	ECE	5

H4 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WHVB1	12	60/55	P43t-38	22103230	8 711500 221032	-	8711500221049	ECE	10
12342WHVSM	12	60/55	P43t-38	78886328	8 711500 788863	-	8711500788870	ECE	5

H4 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WVUB1	12	60/55	P43t-38	00020028	8 727900 354898	-	8727900354881	ECE	10
12342WVUSM	12	60/55	P43t-38	00022430	8 727900 354904	-	8727900 54911	ECE	5

H4 RacingVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342RVS2	12	60/55	P43t-38	00020028	8 719018 000200	-	8719018000217	ECE	5
12342RVB1	12	60/55	P43t-38	00022430	8 719018 000224	-	8719018000231	ECE	10

H4 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12569RAB1	12	100/90	P43t-38	40728330	8 711500 407283	-	8711500407290	-	10
12569RAC1	12	100/90	P43t-38	40177930	8 711500 401779	-	8711500779441	-	10
12754C1	12	100/90	P43t-38	77438530	8 711500 774385	-	8711500779380	-	10

H4 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVSM	12	60/55	P43t-38	48981428	8 711500 489814	-	8711500489821	-	5
12342CVB1	12	60/55	P43t-38	53287630	8 727900 532876	-	8727900532883	-	10

H4 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342DVS2	12	60/55	P43t-38	69573428	8 711500 695734	-	8711500697448	-	5
12342DVB1	12	60/55	P43t-38	53289030	8 727900 532890	-	8727900532906	-	10

H7 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRB1	12	55	PX26d	40607130	8 711500 406071	-	8711500406088	ECE	10
12972PRC1	12	55	PX26d	400593760	8 711500 405937	8711500827838	8711500405944	ECE	100
12972PRC2	12	55	PX26d	37432260	8 727900 374322	8727900374339	8727900374346	ECE	100

H7 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972VPS2	12	55	PX26d	39938728	8 727900 399387	-	8727900399370	ECE	5
12972VPB1	12	55	PX26d	39936330	8 727900 399363	-	8727900399356	ECE	10
12972VPC2	12	55	PX26d	37426160	8 727900 374261	8727900374278	8727900374285	ECE	100

H7 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XV+S2	12	55	PX26d	37170328	8 727900 371703	-	8727900371710	ECE	5
12972XV+B1	12	55	PX26d	37168030	8 727900 371680	-	8727900371697	ECE	10

H7 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XVGS2	12	55	PX26d	35541328	8 727900 355413	-	8727900355789	ECE	5
12972XVGB1	12	55	PX26d	35579630	8 727900 355796	-	8727900355802	ECE	10

H7 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972LLECOS2	12	55	PX26d	36259628	8 727900 362596	-	8727900362602	ECE	5
12972LLECOB1	12	55	PX26d	36200830	8 727900 362008	-	8727900362015	ECE	10
12972LLECO1	12	55	PX26d	36192630	8 727900 361926	-	8727900371024	ECE	10

H7 ColorVision Green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPGS2	12	55	PX26d	36798028	8 727900 367980	-	8727900368017	ECE	5

H7 ColorVision Yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPYS2	12	55	PX26d	36802428	8 727900 368024	-	8727900368031	ECE	5

H7 ColorVision Purple



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPPS2	12	55	PX26d	36804828	8 727900 368048	-	8727900368055	ECE	5

H7 ColorVision Blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPBS2	12	55	PX26d	36810928	8 727900 368109	-	8727900368130	ECE	5

H7 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WHVB1	12	55	PX26d	37160430	8 727900 371604	-	8727900371611	ECE	10
12972WHVSM	12	55	PX26d	78888728	8 711500 788887	-	8711500788894	ECE	5

H7 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WVUB1	12	55	PX26d	35493530	8 727900 354935	-	8727900354928	ECE	10
12972WVUSM	12	55	PX26d	35495928	8 727900 354959	-	8727900 54942	ECE	5

H7 RacingVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972RVS2	12	55	PX26d	00024828	8 719018 000248	-	8719018000255	ECE	5
12972RVB1	12	55	PX26d	00026230	8 719018 000262	-	8719018000279	ECE	10

H7 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12035RAB1	12	80	PX26d	40732030	8 711500 407320	-	8711500407337	-	10
12035RAC1	12	80	PX26d	47208330	8 711500 472083	-	8727900371109	-	10

H7 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVSM	12	55	PX26d	48983828	8 711500 489838	-	8711500489845	-	5
12972CVB1	12	55	PX26d	53291330	8 727900 532913	-	8727900532920	-	10

H7 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972DVS2	12	55	PX26d	69747928	8 711500 697479	-	8711500697486	-	5
12972DVB1	12	55	PX26d	53293730	8 727900 532937	-	8727900532944	-	10

H8 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360WHVB1	12	35	PGJ19-1	37471130	8 727900 374711	-	8727900374728	ECE	10

H8



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360B1	12	35	PGJ19-1	82416530	8 711500 824165	-	8727900362909	ECE	10
12360C1	12	35	PGJ19-1	47582430	8 711500 475824	-	8727900371017	ECE	10

H9



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12361B1	12	65	PGJ19-5	36308130	8 727900 363081	-	8727900363098	ECE	10
12361C1	12	65	PGJ19-5	47584830	8 711500 475848	-	8727900371000	ECE	10

H10



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9145C1	12	45	PY20d	52974530	8 711559 529745	-	8727900370737	ECE	10

H11 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362PRB1	12	55	PGJ19-2	36428630	8 727900 364286	-	8727900364293	ECE	10
12362PRC1	12	55	PGJ19-2	36430930	8 727900 364309	-	8727900370751	ECE	10

H11 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362LLECOB1	12	55	PGJ19-2	36310430	8 727900 363104	-	8727900363111	ECE	10
12362LLECO1	12	55	PGJ19-2	36194030	8 727900 361940	-	8727900370744	ECE	10

H11 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362WHVB1	12	55	PGJ19-2	37469830	8 727900 374698	-	8727900374704	ECE	10

H11 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362CVSM	12	55	PGJ19-2	52646128	8 711559 526461	-	8711559526843	-	5
12362CVB1	12	55	PGJ19-2	82685530	8 711500 826855	-	8711500826862	-	10

H13



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9008C1	12	60/55	P26,4t	87798730	8 711500 877987	-	8727900370768	ECE	10

H15



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12580C1	12	55/15	PGJ23t-1	02000030	8 719018 020000	-	8719018020024	ECE	10
12580B1	12	55/15	PGJ23t-1	02001730	8 719018 020017	-	8719018020031	ECE	10

H16



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12366C1	12	19	PGJ19-3	36856730	8 727900 368567	-	8727900370775	ECE	10

HB1 9004



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9004C1	12	65/45	P29t	47074430	8 711500 470744	-	8727900370997	-	10

HB3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005PRB1	12	60	P20d	24724730	8 711500 247247	-	8711500247254	ECE	10
9005PRC1	12	60	P20d	24689930	8 711500 246899	-	8727900370980	ECE	10

HB3 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005WHVB1	12	60	P20d	37475930	8 727900 374759	-	8727900374766	ECE	10

HB3 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005CVB1	12	60	P20d	53299930	8 727900 532999	-	8727900533002	-	10

HB3 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005DVB1	12	65	P20d	53295130	8 727900 532951	-	8727900532968	-	10

HB4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006PRB1	12	51	P22d	24726130	8 711500 247261	-	8711500247278	ECE	10
9006PRC1	12	51	P22d	24687530	8 711500 246875	-	8727900370973	ECE	10

HB4 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006WHVB1	12	51	P22d	37473530	8 727900 374735	-	8727900374742	ECE	10

HB4 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006CVSM	12	60	P22d	52620128	8 711559 526201	-	8711559526454	-	5
9006CVB1	12	60	P22d	53301930	8 727900 533019	-	8727900533026	-	10

HB4 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006DVS2	12	55	P22d	53248728	8 727900 532487	-	8727900532494	-	5
9006DVB1	12	55	P22d	53297530	8 727900 532975	-	8727900532982	-	10

HB5 9007



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9007C1	12	65/55	PX29t	24550230	8 711500 245502	-	8727900370966	-	10

HIR2 LongLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9012LLC1	12	55	PX22d	35125530	8 727900 351255	-	8727900370935	ECE	10

H27W/1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12059C1	12	27	PG13	52854030	8 711559 528540	-	8727900370799	ECE	10

H27W/2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12060C1	12	27	PGJ13	52857130	8 711559 528571	-	8727900370805	ECE	10

R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12620B1	12	45/40	P45t-41	5543930	8 711500 055439	-	8711559525327	ECE	10
12620C1	12	45/40	P45t-41	40085730	8 711500 400857	-	8711500779359	ECE	10

R2 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12596(H5)C1	12	60/55	P45t-41	51226630	8 711559 512266	-	8727900370843	-	10



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12475B1	12	45/40	P45t-41	24716230	8 711500 247162	-	8711500247179	ECE	10
12475C1	12	45/40	P45t-41	40466430	8 711500 404664	-	8727900371130	ECE	10

12V signaling and interior lighting (for 12V LED retrofit lighting, please refer to page 74)

P21W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498VPB2	12	21	BA15s	36318030	8 727900 363180	-	8727900363173	ECE	10

P21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498LLECOB2	12	21	BA15s	38210530	8 727900 382105	-	8727900382112	ECE	10
12498LLECOCP	12	21	BA15s	38198628	8 727900 381986	8727900381993	8727900391695	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	5549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	200

P21/4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12594B2	12	21/4	BAZ15d	40485530	8 711500 404855	-	8711500471017	ECE	10
12594CP	12	21/4	BAZ15d	48433828	8 711500 484338	8711500484345	8727900391565	ECE	5x10

P21/5W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499VPB2	12	21/5	BAY15d	36316630	8 727900 363166	-	8727900363159	ECE	10

P21/5W LongLife Ecovision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499LLECOB2	12	21/5	BAY15d	38212930	8 727900 382129	-	8727900382136	ECE	10
12499LLECOCP	12	21/5	BAY15d	38201328	8 727900 382013	8727900382020	8727900391053	ECE	5x10

P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499B2	12	21/5	BAY15d	5545330	8 711500 055453	-	8711559520148	ECE	10
12499CP	12	21/5	BAY15d	48159773	8 711500 481597	8711500481603	8711500481610	ECE	200

PR21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12088CP	12	21	BAW15s	48531128	8 711500 485311	8711500485328	8727900391589	ECE	5x10

PR21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12495CP	12	21/5	BAW15d	48873228	8 711500 488732	8711500488749	8727900391572	ECE	5x10

PY21W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496SVB2	12	21	BAU15s	31117730	8 711500 311177	-	8711500311191	ECE	10

PY21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496LLECOCP	12	21	BAU15s	38218128	8 727900 382181	8727900382198	8727900391084	ECE	5x10

PY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496NAB2	12	21	BAU15s	52372930	8 711559 523729	-	8711559523743	ECE	10
12496NACP	12	21	BAU15s	52534173	8 711559 525341	8711559525358	8711559525365	ECE	200

Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12401CP	12	15	BA15s	87821228	8 711500 878212	8711500878229	8711500790538	-	5x10

Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12445CP	12	18	BA15s	48440628	8 711500 484406	8711500484413	8727900391602	-	5x10

R5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821LLECOB2	12	5	BA15s	38208230	8 727900 382082	-	8727900382099	ECE	10
12821LLECOCP	12	5	BA15s	38195528	8 727900 381955	8727900381962	8727900390940	ECE	5x10

R5W BA15s



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821B2	12	5	BA15s	5546030	8 711500 055460	-	8711500417701	ECE	10
12821CP	12	5	BA15s	48269373	8 711500 482693	8711500482709	8711500482716	ECE	200

R5W BA15d



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12822CP	12	5	BA15d	45407228	8 711500 454072	8711500454959	8711500790521	ECE	5x10

R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12814B2	12	10	BA15s	5547730	8 711500 055477	-	8711500417718	ECE	10
12814CP	12	10	BA15s	48341673	8 711500 483416	8711500483423	8711500483430	ECE	200

RY10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12093NACP	12	10	BAU15s	48362128	8 711500 483621	8711500483638	8727900391619	ECE	5x10

BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12829CP	12	2	BA7s	52123728	8 711559 521237	8711500401236	8727900390933	-	5x10

T2W-T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12913CP	12	2	BA9s	21997828	8 711500 219978	8711500219985	8711500220820	-	5x10
12910CP	12	3	BA9s	21949728	8 711500 219497	8711500219503	8711500220837	-	5x10

T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12929B2	12	4	BA9s	5550730	8 711500 055507	-	8711559520094	ECE	10
12929CP	12	4	BA9s	21979473	8 711500 219794	8711500219800	8711500219817	ECE	200

Miniature halogen signaling USA

H5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12023CP	12	5	BA9s	51270928	8 711559 512709	8711559512464	8727900371222	-	5x10

H6W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036B2	12	6	BAX9s	24720930	8 711500 247209	-	8711500247216	ECE	10
12036CP	12	6	BAX9s	87603428	8 711500 876034	8711500876041	8727900370676	ECE	5x10

H6W WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036WHVB2	12	6	BAX9s	37467430	8 711500 245670	-	8727900374681	ECE	10
12036BVCP	12	6	BAX9s	87609628	8 711500 876096	8711500876102	8727900370720	ECE	5x10

H10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12024CP	12	10	BA9s	52941728	8 711559 529417	8711559529424	8727900371192	-	5x10

H20W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12025CP	12	20	BA9s	87600328	8 711500 876003	8711500876010	8727900371154	-	5x10

H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12356CP	12	21	BAY9s	87989928	8 711500 879899	8711500879905	8727900371116	ECE	5x10

HY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12146CP	12	21	BAW9s	35244328	8 727900 352443	8727900352450	8727900370867	ECE	5x10

Wedge base

W1,2W - W2,3W - W2W - WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12521CP	12	1	W2x4,6d	48321828	8 711500 483218	8711500483225	8727900391671	-	5x10
12516B2	12	1.2	W2x4,6d	5554530	8 711500 055545	-	8711500417763	-	10
12516CP	12	1.2	W2x4,6d	48153573	8 711500 481535	8711500481542	8711500481559	-	200
12505CP	12	2	W2x4,6d	48327028	8 711500 483270	8711500483287	8727900391657	-	5x10
12061CP	12	2.3	W2x4,6d	48330028	8 711500 483300	8711500483317	8727900391640	ECE	5x10

W2,2W - W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12960CP	12	2.2	W2,1x9,5d	48150428	8 711500 481504	8711500481511	8727900391633	-	5x10
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10

W5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961LLECOB2	12	5	W2,1x9,5d	38204430	8 727900 382044	-	8727900382051	ECE	10
12961LLECOCP	12	5	W2,1x9,5d	38189428	8 727900 381894	8727900381900	8727900390872	ECE	5x10

W5W WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961BVB2	12	5	W2,1x9,5d	31029330	8 711500 310293	-	8711559523774	ECE	10
12961NBVB2	12	5	W2,1x9,5d	39204330	8 727900 392043	-	8727900392050	ECE	10

W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961B2	12	5	W2,1x9,5d	40421330	8 711500 404213	-	8711559520070	ECE	10
12961CP	12	5	W2,1x9,5d	49090273	8 711500 490902	8711500490919	8711500490926	ECE	200

WY5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12396NAB2	12	5	W2,1x9,5d	40058130	8 711500 400581	-	8711500400598	ECE	10
12396NACP	12	5	W2,1x9,5d	53002428	8 711559 530024	8711559530031	8727900390889	ECE	5x10

WBT10 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12040VPB2	12	6	W2,1x9,5d	52416030	8 711559 524160	-	8711559524184	-	10

W16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12067B2	12	16	W2,1x9,5d	40587630	8 711500 405876	-	8711559521053	ECE	10
12067CP	12	16	W2,1x9,5d	48272328	8 711500 482723	8711500482730	8727900391626	ECE	5x10

W21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12065B2	12	21	W3x16d	70146330	8 727900 701463	-	8727900701470	ECE	10
12065CP	12	21	W3x16d	47135228	8 711500 471352	8711500471369	8727900391107	ECE	5x10

W21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12066B2	12	21/5	W3x16q	69739130	8 727900 697391	-	8727900697407	ECE	10
12066CP	12	21/5	W3x16q	47138328	8 711500 471383	8711500471390	8727900391091	ECE	5x10

WY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12071B2	12	21	WX3x16d	69741430	8 727900 697414	-	8727900697421	ECE	10
12071CP	12	21	WX3x16d	52539628	8 711559 525396	8711559525402	8727900391688	ECE	5x10

Festoon

Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12818CP	12	3	SV6	48461128	8 711500 484611	8711500484628	8727900695632	-	5x10

Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12848CP	12	3	SV6	48467328	8 711500 484673	8711500484680	8727900391558	-	5x10

C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12844B2	12	5	SV8,5	5551430	8 711500 055514	-	8711500417749	ECE	10
12844CP	12	5	SV8,5	48156673	8 711500 481566	8711500481573	8711500481580	ECE	200

Festoon T10,5x30 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12860LLECOCP	12	10	SV8,5	38192428	8 727900 381924	8727900381931	8727900391114	-	5x10

Festoon T10,5x38



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12854CP	12	10	SV8,5	48248828	8 711500 482488	8711500482495	8727900391510	-	5x10

Festoon T10,5x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12864CP	12	5	SV8,5	48205128	8 711500 482051	8711500482075	8727900391527	-	5x10
12866B2	12	10	SV8,5	5552130	8 711500 055521	-	8711500417756	-	10
12866CP	12	10	SV8,5	48242628	8 711500 482426	8711500482433	8727900391534	-	5x10

Festoon T15x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12850CP	12	15	SV8,5	48285328	8 711500 482853	8711500482860	8727900391541	-	5x10

Bax

Bax tool box 12V



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55502GKKM	12	-	-	69717928	8 727900 697179	-	8727900697230	-	5

Bax 8,3s/1,35 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12597B2	12	1.2	B8,3s/1,35	53018530	8 711559 530185	-	8711559530192	-	10
12597CP	12	1.2	B8,3s/1,35	48365228	8 711500 483652	8711500483669	8727900390957	-	5x10

Bax 8,3s/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12602CP	12	2	B8,3s/1,5	48396628	8 711500 483966	8711500483973	8727900390995	-	5x10

Bax 8,5d/2 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12598B2	12	1.2	B8,5d/2	40588330	8 711500 405883	-	8711500405890	-	10
12598CP	12	1.2	B8,5d/2	48387428	8 711500 483874	8711500483881	8727900390964	-	5x10

Bax 8,5d/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12603CP	12	1.2	B8,5d/1,5	48399728	8 711500 483997	8711500484000	8727900391015	-	5x10

Bax 8,5d/2 green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12600CP	12	2	B8,5d/2	48393528	8 711500 483935	8711500483942	8727900390971	-	5x10

Bax 8,5d green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12604CP	12	2	B8,5d	40508128	8 711500 405081	8711500404589	8727900391022	-	5x10

Bax 8,5d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12637CP	12	1.5	B8,5d	51487128	8 711559 514871	8711500400178	8727900371048	-	5x10

Bax 10d black halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12615CP	12	5	B10d	52807628	8 711559 528076	8711500243768	8727900370911	-	5x10

Bax 10d brown halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12614CP	12	3	B10d	52805228	8 711559 528052	8711559512723	8727900370928	-	5x10

Bax 8,4d light blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12623CP	12	1.2	BX8,4d	51384328	8 711559 513843	8711500244154	8727900370904	-	5x10

Bax 8,4d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12627CP	12	1.5	BX8,4d	51414728	8 711559 514147	8711500247414	8727900370959	-	5x10
12629CP	12	1.8	BX8,4d	51488828	8 711559 514888	8711559512488	8727900371031	-	5x10

Bax 8,4d black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12625CP	12	1.2	BX8,4d	51409328	8 711559 514093	8711500244420	8727900371208	-	5x10

Bax 8,4d light green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12626CP	12	2	BX8,4d	51412328	8 711559 514123	8711500246066	8727900370942	-	5x10

Bax 8,4d olive green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12611CP	12	1.3	BX8,4d	77432328	8 711500 774323	8711500774330	8711500779397	-	5x10

Bax 8,4d orange



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12624CP	12	1.1	BX8,4d	51411628	8 711559 514116	8711500245137	8727900370898	-	5x10

Bax 8,5d white



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12638CP	12	1.12	BX8,5d	48846628	8 711500 488466	8711500488473	8727900391503	-	5x10

HiPerVision

P13W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12277C1	12	13	PG18,5d-1	69672130	8 727900 696721	-	8727900391008	ECE	10



PCY16W HiPerClick



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12271AC1	12	16	PU20d/2	38965430	8 727900 389654	-	8727900391152	ECE	10



PW16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12177C1	12	16	WP3,3x14,5/8	39623230	8 727900 396232	-	8727900396249	ECE	10



PS19W LongLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085LLC1	12	19	PG20/1	70046630	8 727900 700466	-	8727900390926	ECE	10



PS19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085C1	12	19	PG20/1	69653030	8 727900 696530	-	8727900390988	ECE	10



PSY19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12275NAC1	12	19	PG20/2	52735230	8 711559 527352	-	8727900390858	ECE	10



HiPerVision LCP



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12197HTRC1	13.5	24	HPSL 2A	39621830	8 727900 396218	-	8727900396225	-	10



PS24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12086FFC1	12	24	PG20/3	70044230	8 727900 700442	-	8727900390919	ECE	10



PSX24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12276C1	12	24	PG20/7	69676930	8 727900 696769	-	8727900390902	ECE	10



PSY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12188NAC1	12	24	PG20/4	69668430	8 727900 696684	-	8727900390834	ECE	10



PSY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12180SV+C1	12	24	PG20/4	70379530	8 727900 703795	-	8727900390841	ECE	10

PW24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12182HTRC1	12	24	WP3,3x14,5/3	39196130	8 727900 391961	-	8727900397369	ECE	10

PWY24W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174SVHTRC1	12	24	WP3,3x14,5/4	39200530	8 727900 392005	-	8727900397352	ECE	10

PWY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174NAHTRC1	12	24	WP3,3x14,5/4	39202930	8 727900 392029	-	8727900397345	ECE	10

PY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12274SV+C1	12	24	PGU20/4	69678330	8 727900 696783	-	8727900390780	ECE	10

PY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12190NAC1	12	24	PGU20/4	69690530	8 727900 696905	-	8727900390803	ECE	10

PSX26W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12278C1	12	26	PG18,5d/3	38874930	8 727900 388749	-	8727900390896	ECE	10

Halogen



Two-wheeler lighting



Which **two-wheeler lamp** do you need?



Experience more light

Up to **30%** more vision*



Vision moto



Beam performance



Light color



Lifetime**



Available in H4, H7, HS1

See and be seen



CityVision moto



Beam performance



Light color



Lifetime**



Available in H4, H7, HS1

Up to **130%** brighter light*




X-tremeVision moto



Beam performance



Light color



Lifetime**



Available in H4, H7

Enjoy your passion

Bright white light



CrystalVision ultra



Beam performance



Light color



Lifetime**



Available in H4, H7, HS1



Philips two-wheeler lighting is designed to resist extreme vibration – up to 10 G.

Images for illustration purposes only

* Compared to the minimum legal requirement

** Lifetime differs per type, indication for H7 only

Vision moto

Up to **30%**
more vision*

- Better performance*
- High-quality and ultra-resistant motorcycle lamp

Producing **up to 30% more vision*** than a standard lamp, Philips Vision moto allows riders to see farther with improved light-beam performance at a very **competitive price**.

*Compared to the minimum legal standard



Standard

Vision moto

Available in



H4

H7

HS1


CityVision moto

See and be seen

- Distinctive orange effect
- Maximum safety
- Specifically designed for city use
- Up to 40% more vision*

For maximum safety and visibility, Philips CityVision moto produces a distinctive, attention-grabbing **orange effect**. Motorcycle riders everywhere are looking for more safety, especially riders in heavy city traffic.

*Compared to the minimum legal standard



Standard

CityVision moto

Available in



H4

H7

HS1

Images for illustration purposes only **39**

X-tremeVision moto

Up to **130%**
more vision*

- Maximum brightness
- Unique gas filling for optimal lifetime and durability
- Significantly longer beam*
- Maximum comfort and safety

Philips X-tremeVision moto offers up to **130% more vision*** for riders who need to see farther for **ultimate performance** and **safety**.

*Compared to the minimum legal standard



Standard



X-tremeVision moto

Available in



H4



H7

CrystalVision ultra moto

Bright white light

- White modern look
- Customization and style on the road
- High quality and ultra-resistant headlamp

For riders seeking ultimate style, Philips CrystalVision ultra moto headlamps provide them with **bright white light**. Customize your style **with no compromise on visibility and comfort**.



Standard



CrystalVision ultra moto

Available in



H4



H7

Which lamp for which function?



Vision moto



CityVision moto



X-tremeVision moto



CrystalVision ultra moto



12258 12336 12342 12972 12361 12362 12636 9005 9006 12620 12728 12008

H1 H3 H4 H7 H9 H11 HS1 HB3 HB4 R2 S2 S3



Low beam - high beam



12961 12067 12065 12071 12396 12356

W5W W16W W21W WY21W WY5W H21W



12821 12814 12093 12498 12496 12499

R5W R10W RY10W P21W PY21W P21/5W



Front indicators



12929 12821 12814 12036

T4W R5W R10W H6W



12256 12961 12067 12913 12910

W3W W5W W16W T2W T3W



Front position light



12256 12961 12066 12929 12821 12814 12498 12499

W3W W5W W21/5W T4W R5W R10W P21W P21/5W



Rear position light



12067 12066 12498 12088 12499 12495

W16W W21/5W P21W PR21W P21/5W PR21/5W



Stop light



12256 12961 12929 12821 12814 12036 12844

W3W W5W T4W R5W R10W H6W C5W



Licence plate light



12356 12961 12067 12065 12071

W5W W16W W21W WY21W H21W



12821 12814 12093 12498 12496

R5W R10W RY10W P21W PY21W



Rear indicators

Two-wheeler lighting

Halogen

H4 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRBW	12	60/55	P43t-38	49024730	8 711500 490247	-	8711500490254	ECE	10

H4 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CTVBW	12	60/55	P43t-38	39896030	8 727900 398960	-	8727900398977	ECE	10

H4 X-tremeVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XV+BW	12	60/55	P43t-38	00056930	8 719018 000569	-	8719018000576	ECE	10

H4 CrystalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVUBW	12	60/55	P43t-38	22148330	8 711500 221483	-	8711500221490	ECE	10

H7 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRBW	12	55	PX26d	49026130	8 711500 490261	-	8711500490278	ECE	10

H7 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CTVBW	12	55	PX26d	39898430	8 727900 398984	-	8727900398991	ECE	10

H7 X-tremeVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XV+BW	12	55	PX26d	37867230	8 727900 378672	-	8727900378689	ECE	10

H7 CrystalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVUBW	12	55	PX26d	22118630	8 711500 221186	-	8711500221193	ECE	10

HS1 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636BW	12	35/35	PX43t	53035330	8 727900 530353	-	8727900530360	ECE	10
12636C1	12	35/35	PX43t	51250130	8 711559 512501	-	8727900370881	ECE	10

HS1 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636CTVBW	12	35/35	PX43t	39894630	8 727900 398946	-	8727900398953	ECE	10

HS1 CristalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636BVBW	12	35/35	PX43t	78195630	8 711500 781956	-	8711500781963	ECE	10

S2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12728BW	12	35/35	BA20d	77385230	8 711500 773852	-	8711500773869	ECE	10
12728C1	12	35/35	BA20d	77359330	8 711500 773593	-	8711500779342	ECE	10

S3



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12008BW	12	15	P26s	77381430	8 711500 773814	-	8711500773845	ECE	10
12008C1	12	15	P26s	77394430	8 711500 773944	-	8711500779335	ECE	10

Signaling lamps

W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	05549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	200

P21/5W ExtraDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499EDBW	12	21/5	BAY15d	87900430	8 711500 879004	-	8711500879035	ECE	10

Halogen



24V Bus and truck lighting



Which 24 V lamp do you need?



Safety and durability

Built to last




Best-in-class lifetime



MasterDuty



Light color
Up to 3200 K



Lifetime*
Up to 550 h



Available in
H1, H3, H4, H7, H11

MasterLife



Light color
Up to 3200 K



Lifetime*
Up to 1200 h



Available in
H1, H3, H4, H7, H11

Safety and style


Maximum xenon effect



MasterDuty BlueVision



Light color
Up to 3500 K



Lifetime*
Up to 500 h



Available in
H3, H4, H7




Heavy duty vibration resistant

Images for illustration purposes only
* Lifetime differs per type, indication for H7 only

Safety and durability

Philips 24V headlighting advantage

Combining **vibration resistance** with **high quality**, Philips truck headlamps last longer than standard lamps.



MasterDuty

Built to last

- Lasts up to 500 hours*
- Maximum vibration resistance
- Reinforced mount and base guards against shocks
- Extra robust double-coil filament

The Philips MasterDuty headlamps are designed for **maximum vibration resistance** and excellent **lifetime**. MasterDuty is the **right choice** for drivers seeking **toughness** that **lasts**.

*Lifetime differs per type, indication for H7 only



Available in B1 and C1 packaging



Available in



MasterLife

Best-in-class lifetime


- Lasts up to 1200 hours*
- Maximum vibration resistance*
- Extra-robust double-coil filament

Philips MasterLife lasts up to **1200 hours*** while withstanding extreme **stress** and **vibration**. With a **minimum failure rate** our lamps keep your fleet productive and on the move by minimizing time-consuming interruptions.

MasterLife is the smartest choice for large fleet owners!

*Lifetime differs per type, indication for H7 only

Available in C1 packaging



Available in



MasterDuty BlueVision

Maximum xenon effect

- Maximum vibration resistance*
- High-performance quartz glass with xenon-effect coating
- Distinctive blue cap, looks sharp even when turned off

For drivers seeking **ultimate style** and **performance**, Philips MasterDuty BlueVision produces a **blue xenon effect**. It combines the **durability** and **vibration resistance** of Philips MasterDuty with an additional blue xenon effect for maximum style.

*Compared to average H4 or H7 24V lamps on the market



Standard

MasterDuty BlueVision



Available in S2 and B1 packaging



Available in



Which **lamp** for which **function**?



MasterDuty



MasterLife



MasterDuty BlueVision



H1 H3 H4 H7 H11 R2 D1S/R D2S D2R

Low beam - high beam



H1 H2 H3 H4 H7 H11

Front fog lights



W5W C5W R5W T4W

Interior lights



P21W PY21W H21W

Front indicators



W3W W5W WBT5 BAX

Dashboard lights



W3W W5W R5W T4W

Front position lights



R5W R10W P21/4W P21/5W

Rear position lights



R5W R10W C5W W5W

License plate lights



W3W W5W C5W R5W R10W T4W

Running lights



W5W R5W R10W H21W

Side indicators



P21W PY21W H21W

Rear indicators



P21W P21/5W H21W P25 P22

Stop lights



P21W H21W

Rear fog lights



P21W H21W

Reversing light

24V bus and truck lighting

Halogen

— Available in Standard

H1 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MDB1	24	70	P14,5s	82585830	8 711500 825858	-	8711500825865	ECE	10
13258MDC1	24	70	P14,5s	82577360	8 711500 825773	8711500828507	8711500825780	ECE	100

H1 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MLC1	24	70	P14,5s	82569830	8 711500 825698	-	8727900370812	ECE	10

H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13311C1	24	70	X511	47751430	8 711500 477514	-	8727900371079	ECE	10

H3 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDB1	24	70	PK22s	77459030	8 711500 774590	-	8711500774613	ECE	10
13336MDC1	24	70	PK22s	77460660	8 711500 774606	8711500775313	8711500774637	ECE	100

H3 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MLC1	24	70	PK22s	77462030	8 711500 774620	-	8711500779403	ECE	10

H3 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDBVS2	24	70	PK22s	77486628	8 711500 774866	-	8711500774897	ECE	5
13336MDBVB1	24	70	PK22s	77488030	8 711500 774880	-	8711500774910	ECE	10

H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDB1	24	75/70	P43t-38	82587230	8 711500 825872	-	8711500825889	ECE	10
13342MDC1	24	75/70	P43t-38	82579760	8 711500 825797	8711500828002	8711500825803	ECE	100

H4 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MLC1	24	75/70	P43t-38	82571130	8 711500 825711	-	8727900371086	ECE	10

H4 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDBVS2	24	75/70	P43t-38	53275328	8 727900 532753	-	8727900532760	ECE	5
13342MDBVB1	24	75/70	P43t-38	53281430	8 727900 532814	-	8727900532821	ECE	10

H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDB1	24	70	PX26d	82589630	8 711500 825896	-	8711500825902	ECE	10
13972MDC1	24	70	PX26d	82581060	8 711500 825810	8711500828514	8711500825827	ECE	100

H7 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MLC1	24	70	PX26d	82573530	8 711500 825735	-	8727900371147	ECE	10

H7 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDBVS2	24	70	PX26d	53277728	8 727900 532777	-	8727900532784	ECE	5
13972MDBVB1	24	70	PX26d	53279130	8 727900 532791	-	8727900532807	ECE	10

H11 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MDC1	24	70	PGJ19-2	82583430	8 711500 825834	-	8727900371055	ECE	10

H11 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MLC1	24	70	PGJ19-2	82575930	8 711500 825759	-	8727900371062	ECE	10

R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13620C1	24	55/50	P45t-41	40087130	8 711500 400871	-	8711500779458	ECE	10

24V signaling and interior lighting (for 24V LED retrofit lighting, please refer to page 74)

P21W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MDCP	24	21	BA15s	69949473	8 727900 699494	8727900699500	8727900699517	ECE	200

P21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MLCP	24	21	BA15s	69961628	8 727900 699616	8727900699623	8727900391145	ECE	5x10

P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498B2	24	21	BA15s	40455830	8 711500 404558	-	8711500405449	ECE	10
13498CP	24	21	BA15s	48415473	8 711500 484154	8711500484161	8711500484178	ECE	200

P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13499B2	24	21/5	BAY15d	40456530	8 711500 404565	-	8711500405371	ECE	10
13499CP	24	21/5	BAY15d	48424673	8 711500 484246	8711500484253	8711500484260	ECE	200

PY21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13496MLCP	24	21	BAU15s	69964728	8 727900 699647	8727900699654	8727900391138	ECE	5x10

Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13401CP	24	15	BA15s	87826728	8 711500 878267	8711500878274	8711500790507	-	5x10
13402CP	24	15	BA15d	87836628	8 711500 878366	8711500878373	8711500790514	-	5x10

Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13445CP	24	18	BA15s	48443728	8 711500 484437	8711500484444	8727900390810	-	5x10

R5W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MDCP	24	5	BA15s	69955528	8 727900 699555	8727900699562	8727900390766	ECE	5x10

R5W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MLCP	24	5	BA15s	69970828	8 727900 699708	8727900699715	8727900390773	ECE	5x10

R5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821B2	24	5	BA15s	40453430	8 711500 404534	-	8711500405425	ECE	10
13821CP	24	5	BA15s	48338673	8 711500 483386	8711500483393	8711500483409	ECE	200
13822CP	24	5	BA15d	40904128	8 711500 409041	8711500878021	8711500790491	ECE	5x10

R10W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MDCP	24	10	BA15s	69952428	8 727900 699524	8727900699531	8727900391121	ECE	5x10

R10W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MLCP	24	10	BA15s	69967828	8 727900 699678	8727900699685	8727900390742	ECE	5x10

R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814B2	24	10	BA15s	40452730	8 711500 404527	-	8711559526409	ECE	10
13814CP	24	10	BA15s	48344773	8 711500 483447	8711500483454	8711500483461	ECE	200

BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13829CP	24	3	BA7s	52133628	8 711559 521336	8711500401274	8727900390759	-	5x10

T4W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MDCP	24	4	BA9s	69958628	8 727900 699586	8727900699593	8727900391039	ECE	5x10

T4W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MLCP	24	4	BA9s	69976028	8 727900 699760	8727900699777	8727900391046	ECE	5x10

T2W - T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13913CP	24	2	BA9s	22003528	8 711500 220035	8711500220042	8711500220844	-	5x10
13910CP	24	3	BA9s	21955828	8 711500 219558	8711500219565	8711500220851	-	5x10

T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929B2	24	4	BA9s	40454130	8 711500 404541	-	8711500405432	ECE	10
13929CP	24	4	BA9s	21985573	8 711500 219855	8711500219862	8711500219879	ECE	200

Miniature halogen signaling USA

H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24356CP	24	21	BAY9s	87615728	8 711500 876157	8711500876164	8727900371161	ECE	5x10

Wedge base

W2,5W - W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13960CP	24	2.5	W2,1x9,5d	48147428	8 711500 481474	8711500481481	8727900391275	-	5x10
13256CP	24	3	W2,1x9,5d	48141228	8 711500 481412	8711500481429	8727900391169	ECE	5x10

W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13961B2	24	5	W2,1x9,5d	52420730	8 711559 524207	-	8711559524214	ECE	10
13961CP	24	5	W2,1x9,5d	48138273	8 711500 481382	8711500481399	8711559530376	ECE	200

WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13521CP	24	1	W2x4,6d	48324928	8 711500 483249	8711500483256	8727900391176	-	5x10
13516CP	24	1.2	W2x4,6d	48306573	8 711500 483065	8711500483072	8711500483089	-	200
13974CP	24	2	W2x4,6d	48318828	8 711500 483188	8711500483195	8727900391183	-	5x10

Festoon

Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13818CP	24	3	SV6	48464228	8 711500 484642	8711500484659	8727900391251	-	5x10

Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13848CP	24	3	SV6	48470328	8 711500 484703	8711500484710	8727900391268	-	5x10

Festoon T10,5x38 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13854CP	24	10	SV8,5	48251828	8 711500 482518	8711500482525	8727900391206	-	5x10

C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13844B2	24	5	SV8,5	40463330	8 711500 404633	-	8711500405388	ECE	10
13844CP	24	5	SV8,5	48197973	8 711500 481979	8711500481986	8711500481993	ECE	200

Festoon T10,5x43 5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13864CP	24	5	SV8,5	48233428	8 711500 482334	8711500482341	8727900391213	-	5x10

Festoon T10,5x43 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13866CP	24	10	SV8,5	48245728	8 711500 482457	8711500482464	8727900391220	-	5x10

Festoon T15x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13850CP	24	15	SV8,5	48288428	8 711500 482884	8711500482891	8727900391244	-	5x10

Festoon T15x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13807CP	24	18	SV8,5	48294528	8 711500 482945	8711500482952	8727900391237	-	5x10

Bax

Bax 8,3s/1,35 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13597CP	24	1.2	B8,3s/1,35	48384328	8 711500 483843	8711500483850	8727900390797	-	5x10

Bax 8,5d/2 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13598CP	24	1.2	B8,5d/2	48390428	8 711500 483904	8711500483911	8727900390827	-	5x10

Bax 8,5d brown



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24032CP	24	1.2	B8,5d	48852728	8 711500 488527	8711500488534	8727900391077	-	5x10

Bax 8,5d/2 yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24029CP	24	1.2	B8,5d/2	48402428	8 711500 484024	8711500484031	8727900391190	-	5x10

Kits





Spare and headlight restoration **kits** for cars and trucks

For increased **safety**, it is **recommended** by most European countries that all vehicles be equipped with a **homologated spare kit**. It will not only keep drivers in **compliance** with the law, but will also keep them **safer** as they will always be prepared to **replace** a burned-out lamp.

Our **Headlight restoration kit** renovates car, truck and two-wheeler lenses to like-new condition. It's our **cost-effective alternative** to complete headlight replacement.

www.philips.com/automotive

12V spare kits

Easy Kit H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55472EKMM	12	-	-	69551928	8 727900 695519	-	8727900695533	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	-	-	1	1	1	1	1

Easy Kit H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55473EKMM	12	-	-	69555728	8 727900 695557	-	8727900695571	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	1	-	-	1	1	1	1	1

Easy Kit H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55474EKMM	12	-	-	69558828	8 727900 695588	-	8727900695601	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	-	1	-	1	1	1	1	1

Easy Kit H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55475EKMM	12	-	-	69562528	8 727900 695625	-	8727900695656	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	1	-	1	1	1	1	1

Easy Kit R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55476EKMM	12	-	-	69566328	8 727900 695663	-	8727900695687	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	-	-	1	1	1	1	1	1

Single Kit H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55008SKMM	12	-	-	52731430	8 711559 527314	-	8711559527222	-	10

Content

Lamp type	H1	H4	H7	P21W	P21/5W	PY21W	W5W	R5W	R10W	C5W	T4W	Fest. T10,5x43	Fuse 10A	Fuse15A	Fuse 20A	Fuse 30A
Quantity	1	-	-	1	1	-	-	1	-	1	1	-	-	1	1	1

Single Kit H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55005SKMM	12	-	-	52730730	8 711559 527307	-	8711559527246	-	10

Content

Lamp type	H1	H4	H7	P21W	P21/5W	PY21W	W5W	R5W	R10W	C5W	T4W	Fest. T10,5x43	Fuse 10A	Fuse15A	Fuse 20A	Fuse 30A
Quantity	-	1	-	1	1	-	-	1	-	1	1	-	-	1	1	1

Single Kit H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55007SKKM	12	-	-	52732130	8 711559 527321	-	8711559527215	-	10

Content

Lamp type	H1	H4	H7	P21W	P21/5W	PY21W	W5W	R5W	R10W	C5W	T4W	Fest. T10,5x43	Fuse 10A	Fuse15A	Fuse 20A	Fuse 30A
Quantity	-	-	1	1	1	-	-	1	-	1	1	-	-	1	1	1

Single Kit H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55010SKKM	12	-	-	30999030	8 711500 309990	-	8711500310163	-	10

Content

Lamp type	H1	H4	H7	P21W	P21/5W	PY21W	W5W	R5W	R10W	C5W	T4W	Fest. T10,5x43	Fuse 10A	Fuse15A	Fuse 20A	Fuse 30A
Quantity	1	-	1	1	-	1	1	-	1	-	-	1	2	-	1	-

Essential Box H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55717EBKM	12	-	-	70032928	8 727900 700329	-	8727900700336	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	-	-	1	1	1	1	1	1	1

Essential Box H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55718EBKM	12	-	-	70034328	8 727900 700343	-	8727900700350	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	1	-	-	1	1	1	1	1	1	1

Essential Box H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55719EBKM	12	-	-	70036728	8 727900 700367	-	8727900700374	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	-	1	-	1	1	1	1	1	1	1

Essential Box H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55720EBKM	12	-	-	70038128	8 727900 700381	-	8727900700398	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	1	-	1	1	1	1	1	1	1

Essential Box R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55721EBKM	12	-	-	70040428	8 727900 700404	-	8727900700411	-	5

Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	-	-	1	1	1	1	1	1	1	1

24V spare kits

MiniKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55554SKMDKM	24	-	-	69586130	8 727900 695861	-	8727900695885	-	10

Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	1	-	1	1	1	1	1	1	1	1

MiniKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55555SKMDKM	24	-	-	69590830	8 727900 695908	-	8727900695939	-	10

Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	-	1	1	1	1	1	1	1	1	1

MaxiKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55559LKMDKM	24	-	-	69684494	8 727900 696844	-	8727900696851	-	4

Content

Lamp type	H4	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

MaxiKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55560LKMDKM	24	-	-	69686894	8 727900 696868	-	8727900696875	-	4

Content

Lamp type	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

MaxiKit H1/H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55561LKMDKM	24	-	-	69688294	8 727900 696882	-	8727900696899	-	4

Content

Lamp type	H1	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	1	1	2	2	1	3	2	2	1	1	2	2	2	2

Headlight restoration kit

Safety

Restores headlight lenses to like-new condition!

- Less glare and up to 100% brighter lenses
- Provides safer night-time driving
- Removes haze and yellowing from harmful UV-rays and dirt
- Professional results without power tools in 30 minutes
- High-quality and economical
- 2-year UV-protection guaranteed

Removes the fading and yellowing of headlight lenses and restores them to their original state of **transparency** for **greater safety**. Headlight lenses fade and oxidize from constant exposure to the elements and become scratched due to impacts.



Before



After



Headlight restoration kit



Ordering number	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
HRK00XM	39976931	8 727900 399769	-	8727900399776	-	6

Xenon



Car and truck

lighting



Which xenon lamp do you need?



Experience more light

Ideal for replacement



Xenon Vision

Standard



Xenon Vision



Beam performance



Light color

Up to **4300 K**



Standard: 4150 K

Available in D1S, D1R, D2S, D2R, D3S, D3R, D4S, D4R, D5S

Up to **150%** more vision*



Xenon X-tremeVision gen2

Standard



Xenon X-tremeVision gen2



Beam performance



Light color

Up to **4800 K**



Standard: 4150 K

Available in D1S, D2S, D2R, D3S, D4S

Light that lasts

Peace of mind **4 + 3** years warranty



Xenon LongerLife**



4 years warranty **+3**

Beam performance



Lifetime

Up to **7 years**



Available in D1S, D2S, D2R

Enjoy your passion

Homogeneous **white** LED effect



Xenon WhiteVision gen2

Standard



Xenon WhiteVision gen2



Beam performance



Light color

Up to **5000 K**



Standard: 4150 K

Available in D1S, D2S, D2R, D3S

Images for illustration purposes only

* Compared to the minimum legal standard (except for D2R that provides up to 20% more vision)

** Not available in all countries, please contact your sales representative



Experience more light

Xenon Vision

Ideal for replacement

- **Single-lamp replacement technology:** new lamp matches color temperature of the unchanged one
- Ideal economical solution for a **single-lamp replacement**
- **Homologated 4300 K**

Philips Xenon Vision allows drivers to replace a single burned-out lamp while **matching** the **color** of the unchanged one.



Car and truck lighting



Standard



Xenon Vision

Available in C1 and S1 packaging



Available in



Images for illustration purposes only **65**

Xenon

Experience more light



Xenon X-tremeVision gen2

Our brightest xenon lamp

- Optimal light performance
- Up to 150% more vision*
- Maximum safety and visibility
- Designed for demanding drivers

Philips Xenon X-tremeVision gen2 is the latest development in **Xenon technology**. It offers the **most powerful beam** with light emission pushed to the limit. This means outstanding light performance with a unique light setting for **optimal driving comfort**.

www.philips.com/xenongen2

*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision).



Standard



Xenon X-tremeVision gen2

Available in C1 and S1 packaging



Available in



Light that lasts

4 years warranty **+3**

Xenon LongerLife

Peace of mind with the longest guarantee

Equip your car with Philips Xenon LongerLife lamps and you can drive up to 7 years without the worry of lamp failures. Philips Xenon LongerLife lamps automatically come with a **4-year warranty**. Register your purchase online and you can extend this warranty by an **extra 3 years**.

Available in C1 and S1 packaging



Available in



D1S

D2S

D2R



3 years extra warranty for free in 3 simple steps

Register online at www.philips.co.uk/xenonwarranty, within 30 days of purchase



1 Connect to www.philips.co.uk/xenonwarranty to confirm you've purchased a genuine Philips product by verifying the security code located on the certificate of authenticity sticker.



2 Fill in your personal information, indicate your point-of-purchase and provide the proof-of-purchase.



3 Print and save your 7-year warranty certificate together with your proof-of-purchase.



You can now drive safely and worry-free for 7 years!



Enjoy your passion

Xenon WhiteVision gen2

Ultimate white LED effect

- Intense homogeneous bright white light
- Perfect match with LED lighting on your car
- Up to 5000 K white light on the road
- Up to 120% more vision*
- 100% road legal

Philips Xenon WhiteVision gen2 lamps create an **intense white look** of your car and produce brighter, homogeneous white light on the road.

www.philips.com/xenongen2

*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision).



Standard

Xenon WhiteVision gen2

Available in C1 and S1 packaging



Available in



D1S

D2S

D2R

D3S

Our **pro-active solution** against xenon lamp **piracy**

COA Certificate of authenticity

Counterfeit Philips xenon lamps are becoming increasingly available through online and offline distribution channels.

These counterfeit lamps are **poor imitations** of **inferior quality**.

Buying, selling or being in possession of counterfeit products is illegal.



To **protect** our customers and all consumers from counterfeit Philips lighting products, we've created a **pro-active solution** using unique, **state-of-the-art** technology.

Philips **Certificate of Authenticity (COA)** is available on **every xenon lamp package you order**.

Using the **Security code**, professionals can verify the **authenticity** of the Philips

product on a dedicated, fully secure internet platform. Professionals can either scan the QR code or go to **www.philips.com/original**.

We are committed to helping **protect** our customers from poor imitations of inferior quality that may damage your vehicle or result in personal injury.

Always ensure that you are buying genuine Philips products.

Visual verification



Online verification

1 Connect to www.philips.com/original follow the simple instructions:

2 Type in the unique security code

3 Type in the label ID number

Retype the code again to make sure it's been entered correctly. Additional rejection of code entry may indicate this product is counterfeit.



D1S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415VIS1	85	35	PK32d-2	36489733	8 727900 364897	-	8727900364903	ECE	2
85415VIC1	85	35	PK32d-2	36473633	8 727900 364736	-	8727900364743	ECE	2

D1S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415XV2S1	85	35	PK32d-2	37697533	8 727900 376975	-	8727900376982	ECE	2
85415XV2C1	85	35	PK32d-2	37701933	8 727900 377019	-	8727900377026	ECE	2

D1S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415SYS1	85	35	PK32d-2	37246533	8 727900 372465	-	8727900372472	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37516933	8 727900 375169	-	8727900375176	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85415SYC1	85	35	PK32d-2	37250233	8 727900 372502	-	8727900372519	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37522033	8 727900 375220	-	8727900375237	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D1S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415WHV2S1	85	35	PK32d-2	36072133	8 727900 360721	-	8727900377248	ECE	2
85415WHV2C1	85	35	PK32d-2	37725533	8 727900 377255	-	8727900377262	ECE	2

D1R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85409VIC1	85	35	PK32d-3	36475033	8 727900 364750	-	8727900364767	ECE	2

D2S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122VIS1	85	35	P32d-2	36491033	8 727900 364910	-	8727900364927	ECE	2
85122VIC1	85	35	P32d-2	36477433	8 727900 364774	-	8727900364781	ECE	2

D2S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122XV2S1	85	35	P32d-2	37703333	8 727900 377033	-	8727900377040	ECE	2
85122XV2C1	85	35	P32d-2	37707133	8 727900 377071	-	8727900377088	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

D2S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122SYS1	85	35	P32d-2	37254033	8 727900 372540	-	8727900372557	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37518333	8 727900 375183	-	8727900375190	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85122SYC1	85	35	P32d-2	37244133	8 727900 372441	-	8727900372458	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37524433	8 727900 375244	-	8727900375251	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D2S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122WHV2S1	85	35	P32d-2	37727933	8 727900 377279	-	8727900377286	ECE	2
85122WHV2C1	85	35	P32d-2	37729333	8 727900 377293	-	8727900377309	ECE	2

D2R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126VIS1	85	35	P32d-3	36493433	8 727900 364934	-	8727900364941	ECE	2
85126VIC1	85	35	P32d-3	36479833	8 727900 364798	-	8727900364804	ECE	2

D2R X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126XV2S1	85	35	P32d-3	37709533	8 727900 377095	-	8727900377101	ECE	2
85126XV2C1	85	35	P32d-3	37711833	8 727900 377118	-	8727900377125	ECE	2

D2R LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126SYS1	85	35	P32d-3	37248933	8 727900 372489	-	8727900372496	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37520633	8 727900 375206	-	8727900375213	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85126SYC1	85	35	P32d-3	37252633	8 727900 372526	-	8727900372533	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37526833	8 727900 375268	-	8727900375275	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

D2R WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126WHV2S1	85	35	P32d-3	37731633	8 727900 377316	-	8727900377323	ECE	2
85126WHV2C1	85	35	P32d-3	37733033	8 727900 377330	-	8727900377347	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

D3S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403VIS1	42	35	PK32d-5	36495833	8 727900 364958	-	8727900364965	ECE	2
42403VIC1	42	35	PK32d-5	36481133	8 727900 364811	-	8727900364828	ECE	2

D3S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403XV2S1	42	35	PK32d-5	37713233	8 727900 377132	-	8727900377149	ECE	2
42403XV2C1	42	35	PK32d-5	37717033	8 727900 377170	-	8727900377187	ECE	2

D3S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403WHV2S1	42	35	PK32d-5	37735433	8 727900 377354	-	8727900377361	ECE	2
42403WHV2C1	42	35	PK32d-5	37737833	8 727900 377378	-	8727900377385	ECE	2

D3R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42306VIC1	42	35	PK32d-6	36483533	8 727900 364835	-	8727900364842	ECE	2

D4S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402VIC1	42	35	P32d-5	36485933	8 727900 364859	-	8727900364866	ECE	2

D4S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402XV2S1	42	35	P32d-5	37719433	8 727900 377194	-	8727900377200	ECE	2
42402XV2C1	42	35	P32d-5	37721733	8 727900 377217	-	8727900377224	ECE	2

D4R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42406VIC1	42	35	P32d-6	36487333	8 727900 364873	-	8727900364880	ECE	2

D5S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12410C1	12	25	PK32d-7	36981633	8 727900 369816	-	8727900369823	ECE	2



LED retrofit



Car and truck

lighting



Which **LED** lamp do you need?



The next level of white light




Ultinon LED



Beam performance



Light color



Lifetime



Available in

LED-HL [≈H4], [≈H7]
LED-FOG [≈H8/H11/H16]

Brighter. Whiter. Stronger.




X-tremeUltinon LED



Beam performance



Light color



Lifetime



Available in

LED-HL [≈H4], [≈H7], [≈HB3/HB4], [H1]**, [H11]**, [HIR2]**
LED-FOG [≈H8/H11/H16]

New

Original automotive performance in LED



LUXEON
Altilon
OEM LED


X-tremeUltinon LED gen2



Beam performance



Light color



Lifetime



Available in

LED-HL [≈H4], [≈H7]
LED-FOG [≈H8/H11/H16]

Images for illustration purposes only. * Compared to the minimum legal standard for halogen bulbs ** Coming soon



It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxemburg and Malta.



LED retrofit lighting for cars and trucks

LED

Which LED for which function?



Headlights



Front position/
parking lights



Front fog lights



Front indicators



Dashboard lights



Interior lights

X-tremeUltinon LED – Original automotive performance in LED

 LED-HL [≈H4]	 LED-HL [≈HB3/HB4]	 LED-T10 [≈W5W]	 LED-FOG [≈H8/H11/H16]	 LED-AMBER [≈PY21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	
 LED-HL [≈H7]	 LED-T20-WHITE [≈W21/5W]		 LED-AMBER [≈WY21W]	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm

Ultinon LED – The next level of white light

 LED-HL [≈H4]	 LED-T10 [≈W5W]	 LED-FOG [≈H8/H11/H16]	 LED-AMBER [≈PY21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]
 LED-HL [≈H7]	 LED-AMBER [≈WY21W]		 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm

CANbus adapter for optimal control

 CANbus LED-HL [≈H4]	 CANbus LED-HL [≈H7]	 CANbus 5W	 CANbus LED-FOG [≈H8/H11/H16]	 Smart CANbus 21W	 CANbus 5W	 CANbus 5W
-------------------------	-------------------------	---------------	----------------------------------	----------------------	---------------	---------------



It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxembourg and Malta.



Glove compartment lights



Rear position/parking lights



Rear indicators



Rear fog lights



Trunk lights



License plate lights



3rd stop light



Stop lights



Reversing light

X-tremeUltinon LED – Original automotive performance in LED

 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-AMBER [≈PY21W]	 LED-RED [≈P21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-RED [≈P21W], [≈P21/5W]	 LED-WHITE [≈P21W]
 LED-Fest 30/38/43 mm	 LED-(T20)-RED [≈P21/5W], [≈W21/5W]	 LED-AMBER [≈WY21W]	 LED-T20-RED [≈W21W]	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-T20-RED [≈W21W], [≈W21/5W]	 LED-T16-, T20-WHITE [≈W16W], [≈W21W]

Ultinon LED – The next level of white light

 LED-T10 [≈W5W]	 LED-RED [≈P21/5W]	 LED-AMBER [≈PY21W]	 LED-RED [≈P21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-RED [≈P21W], [≈P21/5W]	 LED-WHITE [≈P21W]
 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21/5W]	 LED-AMBER [≈WY21W]	 LED-T20-RED [≈W21W]	 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-T20-RED [≈W21W], [≈W21/5W]	 LED-T20-WHITE [≈W21W]	

CANbus adapter for optimal control

 CANbus 5W	 CANbus 5W	 Smart CANbus 21W	 CANbus 21W	 CANbus 5W	 CANbus 5W	 CANbus 21W	 CANbus 21W	 CANbus 21W
---------------	---------------	----------------------	----------------	---------------	---------------	----------------	----------------	----------------

*LED CANbus adapter 21W included in the pack

LED retrofit lighting for cars and trucks

LED

Ultinon LED

The next level of white light

- Get up to **+160%** brighter light* for superior visibility
- Up to **6 200 K** color temperature for **pure white light**
- **Philips SafeBeam** technology for glare-free driving
- Up to **8-year lifetime**.

*Compared to the minimum legal standard for halogen bulbs



Standard halogen



Ultinon LED

Available in X2 packaging



Available in



LED-HL [≈H4]



LED-HL [≈H7]



LED-FOG [≈H8/H11/H16]

X-tremeUltinon LED

Brighter. Whiter. Stronger.

- Up to **+200%** brighter light* for superior visibility
- Up to **6 500 K** color temperature for **arctic white light**
- Philips heat management technologies: **AirCool, AirFlux, Ceralight****
- **Philips SafeBeam** technology for glare-free driving
- Up to **12-year lifetime**.

*Compared to the minimum legal standard for halogen bulbs

****AirFlux**: for LED-HL [H4] and LED-HL [H8/H11/H16] only.

AirCool: for LED-HL [H7] only. **Ceralight**: cooling system for LED-T10 using ceramic material for enhanced heat and vibration resistance



Standard halogen



X-tremeUltinon LED

Available in X2 packaging



Available in



LED-HL [≈H4]



LED-HL [≈H7]



LED-HL [≈HB3/HB4]



LED-FOG [≈H8/H11/H16]

X-tremeUltinon LED gen2

Unique with automotive OEM LED

- **Exclusive** automotive LED technology
- Up to 250% brighter **homogeneous** light*
- Up to **5 800 K** color temperature for **cool white light**
- **Optimal spectrum** for best road sign visibility
- **IP65:** dust tight and water resistant
- **Philips SafeBeam** technology for glare-free driving
- Up to **12-year lifetime**.

*Compared to the minimum legal standard for halogen bulbs



Standard halogen



X-tremeUltinon LED gen2

Available in X2 packaging



Available in



LED-HL [H4]



LED-HL [H7]



LED-FOG [H8/H11/H16]


CANbus LED adapter

Better fit for LED retrofit bulbs

- **Prevent inaccurate dashboard warnings**
- **Easy installation**
- No flickering effect
- Fully functional high beam indicator*

In the installation and operation of LED retrofit bulbs, users can run across challenges. Philips CANbus LED adapters ensure a better fit for their peace of mind.

*For H4 only




Available in X2 packaging



Available in



LED-CANBUS for LED-HL [H4] LED-HL [H7] LED-HL [H8/H11/H18]



LED-CANBUS [H4/H7]



Smart CANBUS [H4/H7]

LED retrofit lighting for cars and trucks

LED

12V LED retrofit headlighting

LED-HL [≈H4] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342XUWX2	12	22	P43t-38	06012931	8 719018 060129	-	8719018060136	-	6

LED-HL [≈H4] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12901HPX2	12	23	P43t-38	39737631	8 727900 397376	-	8727900397383	-	6

LED-HL [≈H4] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342ULWX2	12	15	P43t-38	39859531	8 727900 398595	-	8727900398601	-	6

LED-HL [≈H7] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972XUWX2	12	25	PX26d	06014331	8 719018 060143	-	8 719 018 060 150	-	6

LED-HL [≈H7] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12985BWX2	12	25	PX26d	39817531	8 727900 398175	-	8727900398182	-	6

LED-HL [≈H7] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972ULWX2	12	14	PX26d	39861831	8 727900 398618	-	8727900398625	-	6

LED-FOG [≈H8/H11/H16] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366XUWX2	12	15.5	PGJ19-1/2/3	06016731	8 719018 060167	-	8 719 018 060 174	-	6

LED-FOG [≈H8/H11/H16] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12794UNIX2	12	19	PGJ19-1/2/3	39739031	8 727900 397390	-	8727900397406	-	6

LED-FOG [≈H8/H11/H16] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366ULWX2	12	10	PGJ19-1/2/3	39863231	8 727900 398632	-	8727900398649	-	6

LED-HL [≈HB3/HB4] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005XUWX2	12	25	P20d/P22d	39875531	8 727900 398755	-	8727900398762	-	6

12V LED retrofit signaling and interior lighting

LED-FEST 30 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129404000KX1	12	1	SV8,5-8	39714730	8 727900 397147	-	8727900397154	-	10

LED-FEST 30 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129416000KX1	12	1	SV8,5-8	39716130	8 727900 387223	-	8727900387230	-	10

LED-FEST 30 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11860ULWX1	12	0.6	SV8,5-8	05037330	8 719018 050373	-	8719018050380	-	10

LED-FEST 38 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
128584000KX1	12	1	SV8,5-8	39706230	8 727900 703412	-	8727900703405	-	10

LED-FEST 38 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
128596000KX1	12	1	SV8,5-8	39708630	8 727900 703399	-	8727900703382	-	10

LED-FEST 38 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854ULWX1	12	0.6	SV8,5-8	05039730	8 719018 050397	-	8719018050403	-	10

LED-FEST 43 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129454000KX1	12	1	SV8,5-8	39710930	8 727900 397109	-	8727900397116	-	10

LED-FEST 43 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129466000KX1	12	1	SV8,5-8	39712330	8 727900 383416	-	8727900383423	-	10

LED-FEST 43 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11864ULWX1	12	0.6	SV8,5-8	05041030	8 719018 050410	-	8719018050427	-	10

It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxemburg and Malta.

LED-T10 [≈W5W] 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127994000KX2	12	0.9	W2,1x9,5d	39594530	8 727900 395945	-	8727900395952	-	10

LED-T10 [≈W5W] 4000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961ULW4X2	12	0.6	W2,1x9,5d	5083030	8 719018 050830	-	8719018050847	-	10

LED-T10 [≈W5W] 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127996000KX2	12	0.9	W2,1x9,5d	39596930	8 727900 395969	-	8727900395976	-	10

LED-T10 [≈W5W] 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961ULWX2	12	0.6	W2,1x9,5d	05031130	8 719018 050311	-	8719018050328	-	10

LED-T10 [≈W5W] 8000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127998000KX2	12	0.9	W2,1x9,5d	39598330	8 727900 395983	-	8727900395990	-	10

12V LED retrofit interior lighting

The following LED interior lighting ordering codes are valid in Cyprus, Germany, Greece, Luxemburg, Malta, Netherlands and Spain.

LED-T10 [≈W5W] 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12799160X2	12	0.9	W2,1x9,5d	39792530	8 727900 397925	-	8727900397932	-	10

LED-T10 [≈W5W] 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961ULWIX2	12	0.6	W2,1x9,5d	05060130	8 719018 050601	-	8719018050618	-	10

LED-T10 [≈W5W] 8000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12799180X2	12	0.9	W2,1x9,5d	39794930	8 727900 397949	-	8727900397956	-	10

LED-FEST 30 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12941160X1	12	1	SV8,5-8	39804530	8 727900 398045	-	8727900398052	-	10

LED-FEST 38 mm 6000K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12859160X1	12	1	SV8,5-8	39800730	8 727900 398007	-	8727900398014	-	10

LED-FEST 38 mm 6000K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854ULWIX1	12	0.6	SV8,5-8	05058830	8 719018 050588	-	8719018050595	-	10

LED-FEST 43 mm 6000K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12946160X1	12	1	SV8,5-8	39802130	8 727900 398021	-	8727900398038	-	10

12V LED retrofit signaling lighting

LED-RED [≈P21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499XURX2	12/24	0.3/2.2	BAY15d	05151630	8 719018 051516	-	8719018051523	-	10

LED-RED [≈P21/5W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499ULRX2	12	2.7	BAY15d	05025030	8 719018 050250	-	8719018050267	-	10

LED-RED [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XURX2	12/24	2.3	BA15s	05157830	8 719018 051578	-	8719018051585	-	10

LED-RED [≈P21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULRX2	12	2.7	BA15s	05023630	8 719018 050236	-	8719018050243	-	10

LED-WHITE [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUWX2	12/24	2.7	BA15S	05145530	8 719018 051455	-	8719018051486	-	10



It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxemburg and Malta.

LED-WHITE [≈P21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULWX2	12	1.95	BA15s	05035930	8 719018 050359	-	8719018050366	-	10

LED-T16-WHITE [≈W16W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11067XUWX2	12	TBC	W2,1x9,5d	05184430	8 719018 051462	-	8719018051851	-	10

LED-T20-WHITE [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUWX2	12/24	1.7	W3x16d	05146230	8 719018 050830	-	8719018051479	-	10

LED-T20-WHITE [≈W21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULWX2	12	1.95	W3x16d	05033530	8 719018 050335	-	8719018050342	-	10

LED-T20-WHITE [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XUWX2	12/24	0.3/1.8	w3x16q	05149330	8 719018 051493	-	8719018051509	-	10

LED-T20-RED [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XURX2	12V/24V	2.1	W3x16d	05153030	8 719018 051530	-	8719018051547	-	10

LED-T20-RED [≈W21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULRX2	12	2.7	W3x16d	05027430	8 719018 050274	-	8719018050281	-	10

LED-T20-RED [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XURX2	12/24	0.3/2.2	W3x16q	05155430	8 719018 051554	-	8719018051561	-	10

LED-T20-RED [≈W21/5W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066ULRX2	12	2.7	W3x16q	05029830	8 719018 050298	-	8719018050304	-	10

LED-T20-AMBER [≈WY21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUAXM	12	1.8	W3x16d	05161530	8 719018 051615	-	8719018051622	-	10

LED-T20-AMBER [≈WY21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULAX2	12	0.75	W3x16d	05075530	8 719018 050755	-	8719018050762	-	10

LED-AMBER [≈PY21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUAXM	12	1.8	BAU15s	05159230	8 719018 051592	-	8719018051608	-	10

LED-AMBER [≈PY21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULAX2	12	0.75	BAU15s	05073130	8 719018 050731	-	8719018050748	-	10

CANbus LED adapter

LED-CANBUS [≈5W]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12956X2	12	5	-	39722230	8 727900 397222	-	8727900397239	-	10

LED-CANBUS [≈21W]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18957X2	12	21	-	39587730	8 727900 395877	-	8727900395884	-	10

LED-CANBUS for LED-HL [≈H4]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18960C2	12	10	-	39809030	8 727900 398090	-	8727900398106	-	10

LED-CANBUS for LED-HL [≈H7]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18952C2	12	10	-	05064930	8 719018 050649	-	8719018050656	-	10

LED-CANBUS for LED-FOG [≈H8/H11/H16]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18954C2	12	10	-	05066330	8 719018 050663	-	8719018050670	-	10

LED connector rings for LED-HL

Type B



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172BX2	-	-	-	05121930	8 719018 051219	-	8719018051226	-	10

Type C



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172CX2	-	-	-	05123330	8 719018 051233	-	8719018051240	-	10



It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxemburg and Malta.

24V LED retrofit interior and signaling lighting

LED-FEST 38 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
249446000KX1	24	1	SV8,5	39718530	8 727900 384185	-	8727900384192	-	10

LED-FEST 43 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
249466000KX1	24	1	SV8,5	39720830	8 727900 397208	-	8727900397215	-	10

LED-WHITE [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUWX2	12/24	2.7	BA15S	05145530	8 719018 051455	-	8719018051486	-	10

LED-T20-WHITE [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUWX2	12/24	1.7	W3x16d	05146230	8 719018 051462	-	8719018051479	-	10

LED-T20-WHITE [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XUWX2	12/24	0.3/1.8	W3x16q	05149330	8 719018 051493	-	8719018051509	-	10

LED-RED [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XURX2	12/24	2.3	BA15s	05157830	8 719018 051578	-	8719018051585	-	10

LED-RED [≈P21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499XURX2	12/24	0.3/2.2	BAY15d	05151630	8 719018 051516	-	8719018051523	-	10

LED-T20-RED [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XURX2	12V/24V	2.1	W3x16d	05153030	8 719018 051530	-	8719018051547	-	10

LED-T20-RED [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XURX2	12/24	0.3/2.2	W3x16q	05155430	8 719018 051554	-	8719018051561	-	10



It is your own responsibility that the use of the LED retrofit lights complies with applicable legal requirements. Lumileds cannot accept any responsibility and/or liability. The LED retrofit headlights and exterior signaling lighting cannot be sold in Germany, Spain, Cyprus, Netherlands, Greece, Luxemburg and Malta.



LED retrofit lighting for cars and trucks

LED

LED



Professional

LED work lights





Find
the right
work light
for the job

HDL10	Penlight Professional	PEN20	Penlight Premium
			
			
Boost light   100 lm <10 h	Boost light   130 lm <11 h	Boost light   200 lm <2 h	Boost light   145 lm <6 h
Eco light   50 lm <10 h		Eco light   100 lm <4.5 h	Eco light  
Angle/flexibility   50° 90°	Angle/flexibility  40°	Angle/flexibility  80°	Angle/flexibility  80°
	Features  20 lm spot light	Features  FindMe	Features   120 lm FindMe
Fixture  Headband	Fixture  Clip	Fixture   Clip Magnet	Fixture   80° clip Magnet
Robustness  IPX4	Robustness  IP54	Robustness   IP54 IK07	Robustness   IP54 IK07
Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof
Power supply  3x AAA	Power supply  3x AAA	Power supply   <2 h	Power supply   2 h
		Charging features   Micro USB 1500x	Charging features  Micro USB
Order entry LPL29B1 GOC 39360631	Order entry LPL19B1 GOC 38819031	Order entry LPL42X1 GOC 39631731	Order entry LPL28RECHX1 GOC 39220394

New		New			
RCH5S	RCH6	RCH10	RCH19	RCH21S	RCH25
Boost light 300 lm <1.5 h	Boost light 130 lm 2 h	Boost light 150 lm <5 h	Boost light 250 lm 4 h	Boost light 300 lm 3.5 h	Boost light 500 lm <3.5 h
Dimmed light 30 lm <12 h	Eco light 70 lm 4 h		Eco light 120 lm 7 h	Eco light 120 lm 6 h	Dimmed light 50 lm <10 h
Angle/flexibility 120° 180°	Angle/flexibility 90° 90°	Angle/flexibility 120°	Angle/flexibility 90° 180°	Angle/flexibility 90° 90°	Angle/flexibility 120° 180°
Features Dimming 120 lm	Features Headband FindMe			Features FindMe	Features Dimming 300 lm
Fixture 360° Magnet	Fixture Clip Magnet	Fixture 360° Magnet	Fixture 360° Magnet	Fixture 360° Magnet	Fixture 360° Magnet
Robustness IP68 IK09	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP20 IK07	Robustness IP65 IK08	Robustness IP68 IK09
Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof
Power supply <2.5 h	Power supply 1 h	Power supply 4 h	Power supply <3 h	Power supply <2 h	Power supply <3.5 h
Charging features Docking station	Charging features Micro USB 1500x		Charging features Micro USB	Charging features Docking station 1500x	Charging features Docking station
Order entry LPL62X1 GOC 05163931	Order entry LPL38X1 GOC 39607231	Order entry LPL20X1 GOC 39060531	Order entry LPL46X1 GOC 39823631	Order entry LPL47X1 GOC 39841031	Order entry LPL63X1 GOC 05165331

RCH31UV	CBL10	CBH51	New PJH10	PJH20	MDLS CRI
					
					
Boost light  350 lm  3.5 h	Boost light  330 lm	Boost light  1200 lm  3 h	Boost light  1000 lm  <3 h	Boost light  2300 lm  2 h	Boost light  1500 lm  1 h
Eco light  150 lm  <8 h		Eco light  500 lm  5.5 h	Dimmed light  100 lm  <12 h	Eco light  1200 lm  4 h	Eco light  750 lm  2.5 h
Angle/flexibility  90°  90°	Angle/flexibility  120°	Angle/flexibility  120°  360°	Angle/flexibility  90°  180°	Angle/flexibility  90°  180°	Angle/flexibility  360°  90°
Features  UV light  FindMe			Features  Dimming	Features  CRI 92  Matte filter	Features  CRI 92  Matte filter
Fixture  360°  Magnet	Fixture  360° hook	Fixture  1.1 – 1.8 m holder	Fixture  Magnet		Fixture  Clamp  Magnet
Robustness  IP54  IK07	Robustness  IP54  IK07	Robustness  IP54  IK07	Robustness  IP68  IK09	Robustness  IP67  IK09	Robustness  IP54  IK07
Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof	Grease resistance  Garage proof
Power supply  2.5 h	Power supply  100-240 V  5 m	Power supply  100-240 V  5 m	Power supply  <4.5 h	Power supply  100-240 V  5 m	Power supply  1.1 h  3.2 h
Charging features  Docking station		Charging features  2 h	Charging features  Micro USB	Charging features  3.5 h  Power bank	Charging features  Docking station
Order entry LPL34UVX1 GOC 39419131	Order entry LPL35X1 GOC 39421431	Order entry LPL45X1 GOC 39732131	Order entry LPL64X1 GOC 05167731	Order entry LPL39X1 GOC 39609631	Order entry LPL403MODX1 GOC 39627066

LPL29B1

100/50lm
Boost/eco mode

HDL10

50° beam angle

Quality finish

- 90° pivoting lamp head
- Adjustable headband
- Water resistant
- Powered with 3 Philips AAA batteries

Precise beam angle

- 50° beam angle
- Long-lasting LED

Dual light mode

- 100lm boost LED light for high-precision tasks
- 50lm eco LED light for a quick inspection

Philips high-power LED head lamp is a perfect tool for hands-free repairs. With the 90° orientable head you can easily direct your light wherever you need to see. The eco and boost light modes as well as its wide beam angle offer superior illumination of your work space.



LPL19B1

130lm

Penlight Professional

The portable inspection tool

Intense white light for optimal vision

- High-quality LEDs with 130lm light output
- Natural white light of 6000K

Accesses very narrow spaces

- LED pointer on top 20lm
- Small and compact

Up to every inspection job

- Water, dust and solvent protection: IP54
- 11-hour battery autonomy

Philips Penlight Professional is a durable and reliable inspection tool, featuring six long-lasting and powerful LEDs producing 130lm of bright, natural white light for precise inspection of any area.



LPL42X1

200/100 lm
Boost/eco mode

PEN20

Powerful rechargeable LED light, fits in your pocket

High-quality white LED light

- Defeat darkness with bright, soft natural light
- High-quality LUXEON® LED light up to 200 lm
- Lights a large work area with 80° wide-beam angle

Ultra-durable battery

- New battery lasts 5x longer than most rechargeable batteries
- Increased autonomy and ultra-fast USB recharge
- Battery run time: 2h/4.5h
- Battery charging time: up to 2 hours

High resistance

- Strong impact resistance: IK07
- Water, dust and solvent protection: IP54

Hands-free lighting

- Work hands-free with built-in 80° swivel hook and magnet



LPL28RECHX1

145 lm

Penlight Premium

Compact, USB-rechargeable

See what remains hidden to others

- Defeat darkness
- High-quality LUXEON LED: 145 lm light output
Focus light: 120 lm light output
- Wide 80° beam angle

High resistance

- Strong impact resistance: IK07
- Water and dust-protected: IP54
- Resistant to chemicals

Ultra-durable battery

- New battery lasts 5x longer than most rechargeable batteries
- Increased autonomy and ultra-fast USB recharge



LPL62X1

300/30 lm

RCH5S

Pocket inspection lamp

High-quality white LED light

- Unique dimming function for comfort, including memory function
- Boost mode, up to 300 lumen
- Spot light, up to 120 lumen
- Wide 120° beam angle
- Bright natural light of 6 000 K

Enhanced robustness

- Very strong impact resistance: IK09
- High water and dust protection: IP68
- Chemical and workshop solvents resistance

Durable battery

- Shared docking station with Philips RCH25
- Long autonomy - up to 12 hours (dimmed light)
- Super-fast recharge – less than 2.5 hours

Versatility

- 180° rotating lighting module
- Hands-free: 360° retractable hooks and strong magnet



New



LPL38X1

130/70 lm
Boost/eco mode

RCH6

Pocket and head compact LED light

Pocket and head - dual function lighting

- Multipurpose lighting, slim design
- 90° pivoting head lamp
- Powerful magnet and headband
- FindMe feature

Superior bright light

- Defeats darkness
- High-quality 130 lm LUXEON LED
- Wide 90° beam angle

Ultra-durable and fast charging battery

- 5x longer lifetime with new, advanced technology battery
- Long autonomy and ultra-fast recharge

High resistance

- Strong impact resistance: IK07
- Water, dust and solvent protection: IP54



LPL20X1

150 lm

RCH10

New easy-open cap with magnet

More light output

- White LED light 150 lm

High resistance

- Strong impact resistance: IK07
- Water, dust and solvent protection: IP54

Hands-free lighting

- Cordless, with rotatable hook and magnet on the bottom

The compact rechargeable LED work lamp is ideal for quick inspection and longer repair operations. It eliminates all shadows with its strong 120° light beam while its 360° rotatable hook provides a hands-free working environment.



LPL46X1

250/120 lm
Boost/eco mode

RCH19

Ultra-slim rechargeable lamp

Ultra-slim and versatile lamp

- 180° rotating lighting module
- Hands-free: 360° retractable hook and strong magnet
- Up to 7 hours autonomy in eco mode
- Fast charging: 3 hours

Superior bright light

- Boost mode light output: up to 250 lumen
- 90° wide beam angle
- Bright natural light: 6000 K

Robust design for workshop environment

- Strong impact resistance: IK07
- Chemical and workshop solvent resistance



LPL47X1

300/120 lm
Boost/eco mode

RCH21S

Robust rechargeable lamp with docking station

Improved robustness with unbreakable design

- Robust housing and rubber grip for strong impact resistance: IK08
- High water, dust and solvent protection: IP65
- Chemical and workshop solvents resistance

High-quality white LED light

- High-quality LUXEON® LED light: 300 lm Boost and 120 lm eco
- 90° wide beam angle
- Natural white light: 6 000 K

Ultra-durable lithium battery

- 5x longer lifetime than standard lithium battery, up to 1500 charge cycles (a standard charging cycle-count in the market is 300).
- Long autonomy: up to 6 hours in eco mode
- Super-fast recharge within less than 2 hours

Handy and versatile

- 90° rotating lighting module
- Rubber grips for easy pick-up
- Hands-free: 360° retractable hook and strong magnet
- FindMe red light when in stand-by mode



LPL63X1

500/50 lm

RCH25

Hand inspection lamp

High-quality white LED light

- Unique dimming function for comfort, including memory function
- Boost mode, up to 500 lumen
- Spot light, up to 300 lumen
- 120° wide beam angle
- Bright natural light of 6 000 K

Enhanced robustness

- Very strong impact resistance: IK09
- High water and dust protection: IP68
- Chemical and workshop solvents resistance

Durable battery

- Shared docking station with Philips RCH5S
- Long autonomy: up to 10 hours (dimmed light)
- Fast recharge: less than 3.5 hours

Versatility

- 180° rotating lighting module
- Hands-free: 360° retractable hooks and strong magnet

New





LPL34UVX1

350/150lm
Boost/eco mode

RCH31UV

Rechargeable compact
LED work lamp with UV

High-quality white LUXEON® LED light and UV leak detector

- High-power LED light: 350 lm boost and 150 lm eco
- Wide beam angle - 90°
- UV-light leak detector

High resistance

- Strong impact resistance: IK07
- Water, dust and solvent protection: IP54

Ultra-durable battery

- New battery with 5x longer lifetime
- Long autonomy and ultra-fast recharge

Handy and versatile

- 90° flexible light module
- Hands-free: 360° retractable hook
and powerful magnet
- Red FindMe indicator while in stand-by mode



LPL35X1

330 lm

CBL10

Cabled and compact LED work lamp

High-power white LED light

- Defeat darkness
- High-quality 330 lumen LED light
- Wide-beam 120° angle

High resistance

- Resistant to chemical and workshop solvents
- Strong impact resistance: IK07
- Water and dust-protected: IP54

Compact and hands-free lighting

- Powerful light in a compact design
- 360° adjustable and retractable hook

Our LED CBL10 inspection lamp features powerful LEDs for an intense white light and a bright wide beam to defeat darkness. Designed to optimize clarity and vision quality, the 6000K white light also improves visual comfort for fatigue-free work.



LPL45X1

1200/500 lm
Boost/eco mode

CBH51

Hybrid LED bonnet lamp

Versatility


- Cable or cordless use
- Integrated telescopic mounting, stretched from 1.1 to 1.8 meters
- 360° hooks with foam pads
- 5.5 hours / 3 hours autonomy

High-quality white LED light

- Boost mode, up to 1200lm
- 120° wide beam angle
- Bright natural light of 6000K

Enhanced robustness

- Strong impact resistance: IK07
- Water and dust-protected: IP54
- Chemical and workshop solvent resistance
- 5-meter robust cable for tough workshop environments



LPL64X1

1000/100lm

PJH10

Small hand projector

High-quality white LED light

- Unique dimming function for working comfort, including memory function
- Boost mode, up to 1 000 lumen
- 90° beam angle
- Bright natural light of 6 000 K

Enhanced robustness

- Very strong impact resistance: IK09
- High water and dust protection: IP68
- Chemical and workshop solvents resistance

Durable battery

- Long autonomy: up to 12 hours (dimmed light)
- Micro USB charger
- Recharge: less than 4.5 hours

Versatility

- 180° rotating lighting module
- Hands-free: strong magnet and third foot including a clip

New



True color match lighting solution



True white daylight

Philips MatchLine

True color match, designed for professionals

Featuring the latest Lumileds, LUXEON® SMD LED technology, Philips MatchLine offers you the true white daylight (6 000 K) working experience. You can prepare, paint, polish and clean, as if you were working outdoors on a bright sunny day.

www.philips.com/matchline

Control light and banish shadows with our new MatchLine color match lamp



Without filter



Color rendering with conventional lamp



Reasonable CRI



With filter



Color rendering with MatchLine



Good CRI



Excellent CRI



LPL39X1

PJH20

2300/1200 lm
Two-step light output

Rechargeable LED projector for paint shops

Superior and convenient bright light

- Easily match colors as if you were working in daylight
- High Color Rendering Index (CRI 92) reveals true color
- Multipurpose, two-step light output (2300/1200 lm)
- 90° wide-beam angle to light your entire work area
- Matte filter reduces glare for your working comfort

Versatile

- Dual battery and cable power: easily switch between rechargeable and cabled power source
- Flexibility with 5-meter cable
- With a handy tripod mount (to be ordered separately), simply position for the most efficient lighting

High resistance

- Ultra-strong impact resistance: IK09
- High water, dust and solvent protection: IP67



1500/750 lm
Two-step light output

LPL403MODX1

MDLS CRI

3-module multidirectional LED lamps for paint shops

Powerful light that eliminates shadows

- Easily match colors as if you were working in daylight
- High Color Rendering Index (CRI 92) reveals true color
- Eliminates shadows with 360° full light coverage
- High-quality, two-step light output (1500/750 lm)
- Matte filter reduces glare for your working comfort

Versatile

- Work hands-free while easily controlling light direction
- New, advanced battery technology provides 5x longer work time

High resistance

- Strong impact resistance: IK07
- Water, dust and solvent protection: IP54

Note: single spare module can be ordered separately



HDL10



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL29B1	4.5	1.6	-	39360631	8 727900 393606	-	8727900393699	-	6

Penlight Professional



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL19B1	4.5	1.6	-	38819031	8 727900 388190	-	8727900388206	-	6

PEN20



Ordering number	V	W	plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL42X1	100-240	1.8	-	39631731	8 727900 396317	-	8727900396324	-	6

Penlight Premium



Ordering number	V	W	plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL28RECHX1	100-240	2	EU	39220394	8 727900 392203	-	8727900392210	-	4

RCH5S



Ordering number	V	W	plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL62X1	100-240	3	EU	05163931	8 719018 051639	-	8719018051646	-	6

RCH6



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL38X1	100-240	2	EU	39607231	8 727900 396072	-	8727900396089	-	6

RCH10



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL20X1	100-240	2.5	EU	39060531	8 727900 390605	-	8727900390612	-	6

RCH19



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL46X1	100-240	2	EU	39823631	8 727900 398236	-	8727900398243	-	6

RCH21S



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL47X1	100-240	3	EU	39841031	8 727900 398410	-	8727900398427	-	6

RCH25



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL63X1	100-240	5	EU	05165331	8 719018 051653	-	8719018051660	-	6

RCH31UV



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL34UVX1	100-240	3	EU	39419131	8 727900 394191	-	8727900394207	-	6

CBL10



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL35X1	100-240	3.5	EU	39421431	8 727900 394214	-	8727900394221	-	6

CBH51



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL45X1	100-240	10	EU	39732131	8 727900 397321	-	8727900397338	-	6

PJH10



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL64X1	100-240	10	EU	05167731	8 719018 051677	-	8719018051684	-	6

PJH20



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL39X1	100-240	20	EU	39609631	8 727900 396096	-	8727900396102	-	6

PJH20 Tripod



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL43X1	-	-	-	39634833	8 727900 396348	-	8727900396355	-	2

MDLS CRI Multidirectional lighting system



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL403MODX1	100-240	15	EU&UK	39627066	8 727900 396270	-	8727900396287	-	1

MDLS CRI Multidirectional lighting system - spare module



Ordering number	V	W	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
LPL41SPAREX1	100-240	5	-	39629433	8 727900 396294	-	8727900396300	-	2

Universal USB car charger



Ordering number	V	Plug	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
DLP2357/10	10.5-18	-	61448985	4 895185 614489	-	-	-	36

Lighting technology explained

www.philips.com/automotive

■ AirCool technology

Smart cooling system that diverts heat away from the light's critical components (active cooling with a fan).

■ AirFlux technology

Optimal thermal management resulting in longer lifetime (passive cooling using heat sink).

■ Asymmetrical beam pattern

An offset beam pattern for low-beam applications. Provides a longer beam in the lane of traffic, which avoids blinding oncoming traffic.

■ Automotive Grade Quality

The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards.

■ Ballast

The electronic driver that controls a xenon HID bulb.

■ Base

Bottom part of the bulb which ensures a proper mechanical and electrical connection with the lamp unit of the car. Its precision is important for a correct beam pattern.

■ Board voltage

Electrical voltage in the board net of the vehicle. In cars, the operational voltage at the bulb connector typically varies between 13 and 14 volts (V). The official test voltage for halogen headlight bulbs is 13.2V according to ECE R37. For trucks with a 24V board net the test voltage is 28V. The board voltage has a significant impact on filament bulb lifetime. In general, a 5% voltage increase reduces the lifetime by 50%.

■ Burner

Burner is the glass part of a halogen or xenon HID bulb in which the light emission is generated. It consists of hard or quartz glass and contains the filament and the two electrodes.

■ Candela (cd)

Unit of luminous intensity that measures the amount of luminous power emitted by a light source in a particular direction.

■ CeraLight

Cooling system using ceramic material for enhanced heat and vibration resistance.

■ Color temperature

Thermal measure for light color. Derived from the color emitted by a "black body" which is heated up to a certain temperature (see also Kelvin).

■ Cut-off zone

The line between the bright and dark zones of low beam light. Above the cut-off zone the amount of light is limited in order to avoid blinding oncoming traffic.

■ D(...)

Nomenclature for xenon HID bulbs where **D** stands for "discharge." Available technical types: **D1S, D1R, D2S, D2R, D3S, D3R, D4S, D4R** and **D5S**.

D1 and **D2** First bulbs introduced in 1991

D3 and **D4** Mercury-free bulbs that replace D1 and D2

For D1 and D3, the electronic high-voltage starter is already integrated in the bulb base. The **S** type is used with projector (lens) systems. Version **R** is used in open reflectors and features an additional coating on the outer tube (pinstripe) which blocks out some areas to avoid glare. The **D5S** is a 25-watt bulb with integrated starter and integrated ballast.

■ Discharge bulb

The correct, technical term of the so-called xenon bulb is **high-intensity discharge** bulb. The light is emitted by an electric arc which is produced between two electrodes. **See also** HID and xenon light.

■ DOT

The United States Department of Transportation which oversees federal highway, air, railroad, maritime and other transportation administration functions. It fulfills a role similar to the Economic Commission for Europe (ECE).

■ DRL

Daytime Running Lights.

■ ECE

Economic Commission for Europe. One of five regional commissions of the United Nations (UN) based in Geneva that contributes to enhancing the effectiveness of the UN through the regional implementation of outcomes of global UN Conferences and Summits. The ECE is responsible for harmonizing technical specifications for vehicles whose regulations are also mandatory in many countries outside Europe.

■ ECE R

This stands for the ECE Regulation.

Examples for vehicle lighting:

R37 Filament lamps

R99 Gas-discharge light sources

R48 Installation of lighting and light-signaling devices

■ Electric arc

The connecting luminous discharge between the two electrodes of a xenon HID bulb. This is similar in principle to a bolt of lightning. The electric arc is created by the high-voltage starter and stabilized and controlled by the ballast.

■ Electrodes

Electrical conductors which are positioned opposite each other in the vessel of a xenon gas-discharge bulb. The electric arc, which emits light, is produced between the electrodes.

■ EMI conform

Automotive standards of electromagnetic interference.

■ E-mark

The ECE mark of approval. The digit following the "E" indicates in which country the approval has been granted. For example: E1 indicates Germany and E2 indicates France. An approval granted by one ECE member is valid for all member states and is typically adopted by national regulations. Single minor deviations are possible.

■ Festoon

A tube-shaped bulb with contacts at each end such as C5W, which is commonly used for interior and license plate lighting.

■ Filament

A coiled tungsten wire that emits light.

■ H(...)

Nomenclature for halogen bulbs. H = halogen.

The bulbs are numbered consecutively.

The most common types are:

H1 First halogen bulb (single filament).

H4 Double filament for both low beam and high beam application in one headlamp unit.

H7 Most common halogen bulb in Europe for low beam, high beam, and fog lighting.

■ Halogen

A gas that is used to create the halogen cycle process in a light bulb. During operation the tungsten molecules evaporate from the tungsten. In the cycle process they combine with the halogen molecules and fall back to the wire. This extends the lifetime of a bulb and allows operation at a higher intensity. Halogen bulbs contain a high-pressure halogen filling. Non-halogen incandescent bulbs often use a vacuum.

■ HB(...)

ECE name of original North American bulb types which were approved for use in Europe as well. For example:

HB3 refers to 9005 and HB4 refers to 9006.

■ Hg

Symbol for mercury (Latin: hydrargyrum). Xenon bulb types D1 and D2 still contain approximately one third of the amount of mercury as a normal domestic energy-saving bulb. D3, D4 und D5 are completely mercury free.

■ HID

High Intensity Discharge. Correct technical name for a so-called xenon bulb.

See also gas-discharge bulb, xenon light, xenon system.

■ High-voltage starter

Creates high-voltage pulses of approximately 20 000 volts to ignite the electric arc in a xenon HID bulb.

■ HiPerVision

Very compact signaling-bulb range with high-precision filaments and a long lifetime. For use in signaling lights, fog lamps, rear and daytime running lights.

■ Illuminance (lux)

Contrary to luminous flux (lumen), which is a measure of the total amount of light emitted by a light source, illuminance describes the amount of luminous flux per unit area, such as on the road. This is measured with a lux meter.

■ IP65 certification

Dust ingress and splash water protection improving durability.

■ Kelvin (K)

A unit of measure of temperature based upon an absolute scale whereby zero (minus 273° C) represents the point where all thermal motion ceases. In lighting, however, this is a measure of color temperature. The higher the color temperature, the whiter and cooler the light appears.

■ LED

Light Emitting Diode.

■ Lifetime

Statistical data that indicate the failure rate of a percentage of bulbs operated at a specific voltage over a certain period of time. Common lifetime data indication:

B3 Time when statistically 3% of the test samples have failed

TC Time when 63% of the test samples have failed.

■ Luminance

The intensity of light emitted from a surface per unit area in a given direction from, for example, the filament or the electric arc of a xenon HID bulb. An important indicator of the amount of light a headlamp unit provides on the road. The unit is candela/m² (cd/m²).

■ Lumen (lm)

Unit of luminous flux.

■ Luminous flux (lumen)

The total amount of light that is emitted by a light source in all directions.

■ Lux (lx)

Unit of illuminance. 1 Lux = 1 lm/m².

See also Illuminance.

■ Lux meter

Illuminance measuring device.

■ LUXEON

Lumileds LED chips technology.

■ Pb

Symbol for lead (Latin: plumbum).

All Philips automotive bulbs are **lead-free**.

■ Quartz glass

Temperature and pressure resistant glass for halogen and xenon HID bulbs. The glass also has a special coating to block out harmful ultraviolet (UV) light.

■ SafeBeam technology

Technology that projects the light exactly where you need it on the road.

■ Tungsten

Filament and electrode material.

■ UV-block

Ultraviolet (UV) rays blocking glass absorbs the UV light created by the filament or the electric arc. UV block is mandatory for all ECE complying car bulbs because UV light can damage the plastic cover of the headlamp.

See also Quartz glass.

■ Wedge base

Bulb with a glass base, such as W5W. Mainly used for position lights, side indicators and interior lighting.

■ Xenon (Xe)

One of the noble gases. Commonly used to refer to HID bulbs.

■ Xenon light

Headlights with HID bulbs.

See also D(...), Discharge bulb, HID.

■ Xenon system

A complete xenon system consists of the HID bulb, the high-voltage starter and the electronic ballast which controls the electric arc.

Specimen packaging

Discover the perfect anti-theft solution for your store.



VP VisionPlus



LLECO LongLife EcoVision



XV X-tremeVision



WHV WhiteVision



CVP ColorVision



RV RacingVision



VI Xenon Vision



XV2 Xenon X-tremeVision gen2



WHV2 Xenon WhiteVision gen2



SY Xenon LongerLife

Ordering information

Description	Ordering number	GOC	EAN1	EAN3
12V halogen				
H1 VP SF	56252SF	39991228	8727900399912	8727900399929
H4 VP SF	56293SF	39010028	8727900390100	8727900390117
H7 VP SF	56295SF	39012428	8727900390124	8727900390131
H1 VP BF	56279BF	26949730	8718696269497	8718696269503
H4 VP BF	56278BF	26947330	8718696269473	8718696269480
H7 VP BF	56277BF	26945930	8718696269459	8718696269466
H1 LLECO SF	56261SF	26909128	8718696269091	8718696269107
H4 LLECO SF	56292SF	39002528	8727900390025	8727900390032
H7 LLECO SF	56294SF	39004928	8727900390049	8727900390056
H1 LLECO BF	56273BF	26939830	8718696269398	8718696269404
H4 LLECO BF	56270BF	26933630	8718696269336	8718696269343
H7 LLECO BF	56268BF	26927530	8718696269275	8718696269282
H1 XV+ SF	56400SF	26957230	8718696269572	8718696269589
H4 XV+ SF	56399SF	26955830	8718696269558	8718696269565
H7 XV+ SF	56364SF	26953430	8718696269534	8718696269541
H1 XV+ BF	56406BF	26969530	8718696269695	8718696269701
H4 XV+ BF	56405BF	26967130	8718696269671	8718696269688
H7 XV+ BF	56404BF	26965730	8718696269657	8718696269664
H1 WHV SF	56403SF	26963328	8718696269633	8718696269640
H4 WHV SF	56402SF	26962628	8718696269626	8718696269619
H7 WHV SF	56401SF	26959628	8718696269596	8718696269602
H1 WHV BF	56409BF	26975630	8718696269756	8718696269763
H4 WHV BF	56408BF	26973230	8718696269732	8718696269749
H7 WHV BF	56407BF	26971830	8718696269718	8718696269725
H4 ColorVision Green SF	56262SF	26911428	8718696269114	8718696269121

Description	Ordering number	GOC	EAN1	EAN3
H4 ColorVision Yellow SF	56255SF	39997428	8727900399974	8727900399981
H4 ColorVision Purple SF	56257SF	26900828	8718696269008	8718696269015
H4 ColorVision Blue SF	56258SF	26902228	8718696269022	8718696269039
H7 ColorVision Green SF	56259SF	26904628	8718696269046	8718696269053
H7 ColorVision Yellow SF	56248SF	39983728	8727900399837	8727900399844
H7 ColorVision Purple SF	56249SF	39985128	8727900399851	8727900399868
H7 ColorVision Blue SF	56250SF	39987528	8727900399875	8727900399882
H4 RV SF	56648SF	27010330	8718696270103	8718696270110
H4 RV BF	56649BF	27012730	8718696270127	8718696270134
H7 RV SF	56650SF	27014130	8718696270141	8718696270158
H7 RV BF	56651BF	27016530	8718696270165	8718696270172

Xenon


D1S Vision S1	85415VISF	36504733	8727900365047	8727900365054
D2S Vision S1	85122VISF	36507833	8727900365078	8727900365085
D2R Vision S1	85126VISF	36511533	8727900365115	8727900365122
D3S Vision S1	42403VISF	36515333	8727900365153	8727900365160
D1S XV2 SF	56643SF	39655333	8727900396553	8727900396560
D2S XV2 SF	56644SF	39657733	8727900396577	8727900396584
D2R XV2 SF	56645SF	39659133	8727900396591	8727900396607
D3S XV2 SF	56646SF	39661433	8727900396614	8727900396621
D4S XV2 SF	56647SF	39663833	8727900396638	8727900396645
D1S WHV2 SF	56640SF	39649233	8727900396492	8727900396508
D2S WHV2 SF	56641SF	39651533	8727900396515	8727900396522
D3S WHV2 SF	56642SF	39653933	8727900396539	8727900396546

Understanding Philips ordering codes

All our automotive lighting products can be ordered using **Philips Order Entry**.

With Philips Order Entry you can identify the **lamp type**, the **product range** and the **packaging type**.

Example: **12972XVB1**, H7 X-tremeVision, single blister



3/ Packaging type



Commercial pack
Material carton
Contents **C1** 1 lamp
Contents **CP** 10 lamps
Packaging type **C1/CP**



Single blister
Material carton/plastic
Contents 1 lamp
Packaging type **B1**



Double blister
Material carton/plastic
Contents 2 lamps
Packaging type **B2**

1/ Lamp type

Every **lamp type** is designated by Philips with a unique number called lamp type.

- All 12V lamps start with 12 (for example: 12972 for H7 12V)
- All 24V lamps starting with 13 (for example: 13972 for H7 24V)

2/ Range type

Most lamp types are available in different product **ranges**. These are indicated by a **color code**. The color code is used on ordering code pages and on Which lamp for which function pages of each section, to indicate the availability of a lamp in a specific product range.

Color code

	Vision Up to 30% more vision	Range type PR
	VisionPlus Up to 60% more vision	Range type VP
	X-tremeVision Up to 130% brighter light	Range type XV+
	X-tremeVision G-force Up to 130% brighter light	Range type XVG
	LongLife EcoVision Lifetime up to 1500 hours	Range type LLECO
	ColorVision Add a touch of color	Range type CVP
	WhiteVision Intense white xenon effect	Range type WHV or BVU
	WhiteVision ultra Sharp white look	Range type WVU



Special pack
Material plastic
Contents **S2** 2 lamps
Contents **SM** 4 lamps
(2 headlamps,
2 position lamps)
Packaging type **S2/SM**



Xenon single blister
Material carton/plastic
Contents 1 lamp
Packaging type **S1**



LED X1/X2 blister
Material carton/plastic
Contents **X1** 1 lamp
Contents **X2** 2 lamps
Packaging types **X1/X2**

	RacingVision Up to 150% brighter light	Range type RV
	CrystalVision Bright white light	Range type CV
	DiamondVision Ultimate white light	Range type DV
	Standard	Range type STD
	Ultinon LED The next level of white light	Range type UL
	X-tremeUltinon LED Brighter. Whiter. Stronger.	Range type XU
	X-tremeUltinon LED gen2 Unique with automotive OEM LED	Range type XU2

Technical illustrations Bases



SV6
IEC 7004-5



SV8,5-8
IEC 7004-81



W2x4,6d
IEC 7004-94



W2,1x9,5d
IEC 7004-91




W3x16d
IEC 7004-105



W3x16q
IEC 7004-106




WX3x16d
IEC 7004-105



BAX 9s
IEC 7004-8



BAY 9s
IEC 7004-9



BA 7s



BA 9s
IEC 7004-14



BA 15s
IEC 7004-11A




BA 15d
IEC 7004-11A



BAU 15s
IEC 7004-11A



BAY 15d
IEC 7004-11B



BAW 9s
IEC 7004-149-1



BAW 15d
IEC 7004-11E-1




BAW 15s
IEC 7004-11E11



BAZ 15d
IEC 7004-11C




BA20d
IEC 7004-12




P43t-38
IEC 7004-39



P45t-41
IEC 7004-95




P20d-PY20d
IEC 7004-31




P22d
IEC 7004-32




PX22d



PG13
IEC 7004-107




PGJ13
IEC 7004-107




HPSL HTR




PG18,5d
IEC 7004-147



PG20
IEC 7004-127



PGU20



PU20d




PGJ19-1/2
IEC 7004-110




PGJ19-3
IEC 7004-110




PGJ19-5
IEC 7004-110




PGJ23t-1



P14,5s
IEC 7004-46




X511
IEC 7004-99



P26s




PX26d,4t
IEC 7004-128-2




PX26d
IEC 7004-5




P29t-PX29t
IEC 7004-66




P32d
IEC 7004-111




P32d-2
IEC 7004-111




P32d-3
IEC 7004-111




P32d-5
IEC 7004-111



P32d-6
IEC 7004-111




PK32d-2
IEC 7004-111




PK32d-3/5/6
IEC 7004-111




PK32d-7
IEC 7004-111




PK22s
IEC 7004-47




W3x16d
IEC 7004-105-1




W3x16q
IEC 7004-106-1




W2,1x9,5d



WP3,3x14,5/3




Bax 8,3s




Bax 8,4d



Bax 8,5d/1



Bax 8,5d/2



Bax 10d

Product **index** by ordering number

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12023CP	H5W	Standard	12	5	BA9s	51270928	8711559512709	8711559512464	8727900371222	28
12024CP	H10W	Standard	12	10	BA9s	52941728	8711559529417	8711559529424	8727900371192	29
12025CP	H20W	Standard	12	20	BA9s	87600328	8711500876003	8711500876010	8727900371154	29
12035RAB1	H7	Rally	12	80	PX26d	40732030	8711500407320	-	8711500407337	23
12035RAC1	H7	Rally	12	80	PX26d	47208330	8711500472083	-	8727900371109	23
12036B2	H6W	Standard	12	6	BAX9s	24720930	8711500247209	-	8711500247216	28
12036BVCP	H6W	WhiteVision	12	6	BAX9s	87609628	8711500876096	8711500876102	8727900370720	28
12036CP	H6W	Standard	12	6	BAX9s	87603428	8711500876034	8711500876041	8727900370676	28
12036WHVB2	H6W	WhiteVision	12	6	BAX9s	37467430	8711500245670	-	8727900374681	28
12040VPB2	WBT10	VisionPlus	12	6	W2.1x9,5d	52416030	8711559524160	-	8711559524184	30
12059C1	H27W/1	Standard	12	27	PG13	52854030	8711559528540	-	8727900370799	25
12060C1	H27W/2	Standard	12	27	PGJ13	52857130	8711559528571	-	8727900370805	25
12061CP	W2.3W	Standard	12	2.3	W2x4,6d	48330028	8711500483300	8711500483317	8727900391640	29
12065B2	W21W	Standard	12	21	W3x16d	70146330	8727900701463	-	8727900701470	30
12065CP	W21W	Standard	12	21	W3x16d	47135228	8711500471352	8711500471369	8727900391107	30
12066B2	W21/5W	Standard	12	21/5	W3x16q	69739130	8727900697391	-	8727900697407	30
12066CP	W21/5W	Standard	12	21/5	W3x16q	47138328	8711500471383	8711500471390	8727900391091	30
12067B2	W16W	Standard	12	16	W2.1x9,5d	40587630	8711500405876	-	8711559521053	30
12067CP	W16W	Standard	12	16	W2.1x9,5d	48272328	8711500482723	8711500482730	8727900391626	30
12071B2	WY21W	Standard	12	21	WX3x16d	69741430	8727900697414	-	8727900697421	30
12071CP	WY21W	Standard	12	21	WX3x16d	52539628	8711559525396	8711559525402	8727900391688	30
12085C1	PS19W	Standard	12	19	PG20/1	69653030	8727900696530	-	8727900390988	34
12085LLC1	PS19W	LongLife	12	19	PG20/1	70046630	8727900700466	-	8727900390926	34
12086FFC1	PS24W	Standard	12	24	PG20/3	70044230	8727900700442	-	8727900390919	34
12088CP	PR21W	Standard	12	21	BAW15s	48531128	8711500485311	8711500485328	8727900391589	27
12093NACP	RY10W	Standard	12	10	BAU15s	48362128	8711500483621	8711500483638	8727900391619	28
12146CP	HY21W	Standard	12	21	BAW9s	35244328	8727900352443	8727900352450	8727900370867	29
12174NAHTRC1	PWY24W	Standard	12	24	WP3,3x14,5/4	39202930	8727900392029	-	8727900397345	35
12174SVHTRC1	PWY24W	SilverVision+	12	24	WP3,3x14,5/4	39200530	8727900392005	-	8727900397352	35
12177C1	PW16W	Standard	12	16	WP3,3x14,5/8	39623230	8727900396232	-	8727900396249	34
12180SV+C1	PSY24W	SilverVision+	12	24	PG20/4	70379530	8727900703795	-	8727900390841	35
12182HTRC1	PW24W	Standard	12	24	WP3,3x14,5/3	39196130	8727900391961	-	8727900397369	35
12188NAC1	PSY24W	Standard	12	24	PG20/4	69668430	8727900696684	-	8727900390834	34
12190NAC1	PY24W	Standard	12	24	PGU20/4	69690530	8727900696905	-	8727900390803	35
12197HTRC1	HiPerVision LCP	Standard	13.5	24	HPSL 2A	39621830	8727900396218	-	8727900396225	34
12256B2	W3W	Standard	12	3	W2.1x9,5d	52410830	8711559524108	-	8711559524122	43
12256CP	W3W	Standard	12	3	W2.1x9,5d	48144328	8711500481443	8711500481450	8727900391664	43
12258CVB1	H1	CrystalVision	12	55	P14,5s	82687930	8711500826879	-	8711500826893	18
12258CVSM	H1	CrystalVision	12	55	P14,5s	48971528	8711500489715	-	8711500489722	18
12258DVB1	H1	DiamondVision	12	55	P14,5s	82690930	8711500826909	-	8711500826916	19
12258DVS2	H1	DiamondVision	12	55	P14,5s	69742428	8711500697424	-	8711500697431	19
12258LLEC0B1	H1	LongLife EcoVision	12	55	P14,5s	36196430	8727900361964	-	8727900361971	18
12258LLEC0C1	H1	LongLife EcoVision	12	55	P14,5s	36187230	8727900361872	-	8727900370683	18
12258LLEC0S2	H1	LongLife EcoVision	12	55	P14,5s	36255828	8727900362558	-	8727900362565	18
12258PRB1	H1	Vision	12	55	P14,5s	47516930	8711500475169	-	8711500475176	18
12258PRC1	H1	Vision	12	55	P14,5s	47518360	8711500475183	8727900363791	8711500475190	18
12258SPC1	H1	Spot	12	55	P14,5s	40460230	8711500404602	-	8727900370690	19
12258VPB1	H1	VisionPlus	12	55	P14,5s	36320330	8727900363203	-	8727900363197	18
12258VPS2	H1	VisionPlus	12	55	P14,5s	36322728	8727900363227	-	8727900363210	18
12258WHVB1	H1	WhiteVision	12	55	P14,5s	37156730	8727900371567	-	8727900371574	18
12258WHVSM	H1	WhiteVision	12	55	P14,5s	78884928	8711500788849	-	8711500788856	18
12258XV+B1	H1	X-tremeVision	12	55	P14,5s	37164230	8727900371642	-	8727900371659	18
12258XV+S2	H1	X-tremeVision	12	55	P14,5s	37166628	8727900371666	-	8727900371673	18
12271AC1	PCY16W	HiPerClick	12	16	PU20d/2	38965430	8727900389654	-	8727900391152	34
12274SV+C1	PY24	SilverVision+	12	24	PGU20/4	69678330	8727900696783	-	8727900390780	35
12275NAC1	PSY19W	Standard	12	19	PG20/2	52735230	8711559527352	-	8727900390858	34
12276C1	PSX24W	Standard	12	24	PG20/7	69676930	8727900696769	-	8727900390902	34
12277C1	P13W	Standard	12	13	PG18,5d-1	69672130	8727900696721	-	8727900391008	34
12278C1	PSX26W	Standard	12	26	PG18,5d/3	38874930	8727900388749	-	8727900390896	35
12311C1	H2	Standard	12	55	X511	47752130	8711500477521	-	8727900370782	19
12336CVB1	H3	CrystalVision	12	55	PK22s	77496530	8711500774965	-	8711500774996	19
12336DVB1	H3	DiamondVision	12	55	PK22s	77494130	8711500774941	-	8711500774972	19

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12336DVS2	H3	DiamondVision	12	55	PK22s	69745528	8711500697455	-	8711500697462	19
12336LLECO1	H3	LongLife EcoVision	12	55	PK22s	77704130	8711500777041	-	8711500779366	19
12336PRB1	H3	Vision	12	55	PK22s	69561130	8711500695611	-	8711500695628	19
12336PRC1	H3	Vision	12	55	PK22s	69534560	8711500695345	8711500775696	8711500695352	19
12336WHVB1	H3	WhiteVision	12	55	PK22s	77951930	8711500779519	-	8711500779526	19
12342CVPBS2	H4	ColorVision Blue	12	60/55	P43t-38	36793528	8727900367935	-	8727900367942	20
12342CVPGS2	H4	ColorVision Green	12	60/55	P43t-38	36787428	8727900367874	-	8727900367881	20
12342CVPPS2	H4	ColorVision Purple	12	60/55	P43t-38	36791128	8727900367911	-	8727900367928	20
12342CVPYS2	H4	ColorVision Yellow	12	60/55	P43t-38	36789828	8727900367898	-	8727900367904	20
12342CVSM	H4	CrystalVision	12	60/55	P43t-38	48981428	8711500489814	-	8711500489821	21
12342DVB1	H4	DiamondVision	12	60/55	P43t-38	53289030	8727900532890	-	8727900532906	21
12342DVS2	H4	DiamondVision	12	60/55	P43t-38	69573428	8711500695734	-	8711500697448	21
12342LLECOB1	H4	LongLife EcoVision	12	60/55	P43t-38	36198830	8727900361988	-	8727900361995	20
12342LLECO1	H4	LongLife EcoVision	12	60/55	P43t-38	36189630	8727900361896	-	8727900370836	20
12342LLECOS2	H4	LongLife EcoVision	12	60/55	P43t-38	36257228	8727900362572	-	8727900362589	20
12342PRB1	H4	Vision	12	60/55	P43t-38	47480330	8711500474803	-	8711500474810	20
12342PRC1	H4	Vision	12	60/55	P43t-38	49099560	8711500490995	8711500827807	8711500490988	20
12342PRC2	H4	Vision	12	60/55	P43t-38	78028760	8711500780287	8711500780294	8711500780300	20
12342RVB1	H4	RacingVision	12	60/55	P43t-38	00022430	8719018000224	-	8719018000231	21
12342RVS2	H4	RacingVision	12	60/55	P43t-38	00020028	8719018000200	-	8719018000217	21
12342VPB1	H4	VisionPlus	12	60/55	P43t-38	39934930	8727900399349	-	8727900399332	20
12342VPC2	H4	VisionPlus	12	60/55	P43t-38	37435360	8727900374353	8727900374360	8727900374377	20
12342VPS2	H4	VisionPlus	12	60/55	P43t-38	39925728	8727900399257	-	8727900350937	20
12342WHVB1	H4	WhiteVision	12	60/55	P43t-38	22103230	8711500221032	-	8711500221049	21
12342WHVSM	H4	WhiteVision	12	60/55	P43t-38	78886328	8711500788863	-	8711500788870	21
12342XV+B1	H4	X-tremeVision	12	60/55	P43t-38	22107030	8711500221070	-	8711500221087	20
12342XV+S2	H4	X-tremeVision	12	60/55	P43t-38	22109428	8711500221094	-	8711500221100	20
12356CP	H21W	Standard	12	21	BAY9s	87989928	8711500879899	8711500879905	8727900371116	29
12360B1	H8	Standard	12	35	PGJ19-1	82416530	8711500824165	-	8727900362909	23
12360C1	H8	Standard	12	35	PGJ19-1	47582430	8711500475824	-	8727900371017	23
12360WHVB1	H8	WhiteVision	12	35	PGJ19-1	37471130	8727900374711	-	8727900374728	23
12361B1	H9	Standard	12	65	PGJ19-5	36308130	8727900363081	-	8727900363098	23
12361C1	H9	Standard	12	65	PGJ19-5	47584830	8711500475848	-	8727900371000	23
12362CVB1	H11	CrystalVision	12	55	PGJ19-2	82685530	8711500826855	-	8711500826862	24
12362CVSM	H11	CrystalVision	12	55	PGJ19-2	52646128	8711559526461	-	8711559526843	24
12362LLECOB1	H11	LongLife EcoVision	12	55	PGJ19-2	36310430	8727900363104	-	8727900363111	24
12362LLECO1	H11	LongLife EcoVision	12	55	PGJ19-2	36194030	8727900361940	-	8727900370744	24
12362PRB1	H11	Vision	12	55	PGJ19-2	36428630	8727900364286	-	8727900364293	24
12362PRC1	H11	Vision	12	55	PGJ19-2	36430930	8727900364309	-	8727900370751	24
12362WHVB1	H11	WhiteVision	12	55	PGJ19-2	37469830	8727900374698	-	8727900374704	24
12366C1	H16	Standard	12	19	PGJ19-3	36856730	8727900368567	-	8727900370775	24
12396NAB2	WY5W	Standard	12	5	W2.1x9.5d	40058130	8711500400581	-	8711500400598	30
12396NACP	WY5W	Standard	12	5	W2.1x9.5d	53002428	8711559530024	8711559530031	8727900390889	30
12401CP	Stop P22	Standard	12	15	BA15s	87821228	8711500878212	8711500878229	8711500790538	27
12445CP	Stop P25	Standard	12	18	BA15s	48440628	8711500484406	8711500484413	8727900391602	27
12454RAB1	H1	Rally	12	100	P14.5s	40722130	8711500407221	-	8711500407238	18
12454RAC1	H1	Rally	12	100	P14.5s	69639730	8711500696397	-	8727900366396	18
12455RAC1	H3	Rally	12	100	PK22s	47898630	8711500478986	-	8711500779373	19
12475B1	R2	R2 Visio	12	45/40	P45t-41	24716230	8711500247162	-	8711500247179	26
12475C1	R2	R2 Visio	12	45/40	P45t-41	40466430	8711500404664	-	8727900371130	26
12495CP	PR21/5W	Standard	12	21/5	BAW15d	48873228	8711500488732	8711500488749	8727900391572	27
12496LLECOCP	PY21W	LongLife EcoVision	12	21	BAU15s	38218128	8727900382181	8727900382198	8727900391084	27
12496NAB2	PY21W	Standard	12	21	BAU15s	52372930	8711559523729	-	8711559523743	27
12496NACP	PY21W	Standard	12	21	BAU15s	52534173	8711559525341	8711559525358	8711559525365	27
12496SVB2	PY21W	SilverVision	12	21	BAU15s	31117730	8711500311177	-	8711500311191	27
12498B2	P21W	Standard	12	21	BA15s	5549130	8711500055491	-	8711559520131	26
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	26
12498LLECOB2	P21W	LongLife EcoVision	12	21	BA15s	38210530	8727900382105	-	8727900382112	26
12498LLECO1	P21W	LongLife EcoVision	12	21	BA15s	38198628	8727900381986	8727900381993	8727900391695	26
12498VPB2	P21W	VisionPlus	12	21	BA15s	36318030	8727900363180	-	8727900363173	26
12499B2	P21/5W	Standard	12	21/5	BAY15d	5545330	8711500055453	-	8711559520148	26
12499CP	P21/5W	Standard	12	21/5	BAY15d	48159773	8711500481597	8711500481603	8711500481610	26
12499LLECOB2	P21/5W	LongLife EcoVision	12	21/5	BAY15d	38212930	8727900382129	-	8727900382136	26
12499LLECO1	P21/5W	LongLife EcoVision	12	21/5	BAY15d	38201328	8727900382013	8727900382020	8727900391053	26
12499VPB2	P21/5W	VisionPlus	12	21/5	BAY15d	36316630	8727900363166	-	8727900363159	26

Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12972CVPPS2	H7	ColorVision Purple	12	55	PX26d	36804828	8727900368048	-	8727900368055	22
12972CVPYS2	H7	ColorVision Yellow	12	55	PX26d	36802428	8727900368024	-	8727900368031	22
12972CVSM	H7	CrystalVision	12	55	PX26d	48983828	8711500489838	-	8711500489845	23
12972DVB1	H7	DiamondVision	12	55	PX26d	53293730	8727900532937	-	8727900532944	23
12972DVS2	H7	DiamondVision	12	55	PX26d	69747928	8711500697479	-	8711500697486	23
12972LLECOB1	H7	LongLife EcoVision	12	55	PX26d	36200830	8727900362008	-	8727900362015	22
12972LLECOB1	H7	LongLife EcoVision	12	55	PX26d	36192630	8727900361926	-	8727900371024	22
12972LLECOS2	H7	LongLife EcoVision	12	55	PX26d	36259628	8727900362596	-	8727900362602	22
12972PRB1	H7	Vision	12	55	PX26d	40607130	8711500406071	-	8711500406088	21
12972PRC1	H7	Vision	12	55	PX26d	40593760	8711500405937	8711500827838	8711500405944	21
12972PRC2	H7	Vision	12	55	PX26d	37432260	8727900374322	8727900374339	8727900374346	21
12972RVB1	H7	RacingVision	12	55	PX26d	00026230	8719018000262	-	8719018000279	23
12972RVS2	H7	RacingVision	12	55	PX26d	00024828	8719018000248	-	8719018000255	23
12972VPB1	H7	VisionPlus	12	55	PX26d	39936330	8727900399363	-	8727900399356	21
12972VPC2	H7	VisionPlus	12	55	PX26d	37426160	8727900374261	8727900374278	8727900374285	21
12972VPS2	H7	VisionPlus	12	55	PX26d	39938728	8727900399387	-	8727900399370	21
12972WHVB1	H7	WhiteVision	12	55	PX26d	37160430	8727900371604	-	8727900371611	23
12972WHVSM	H7	WhiteVision	12	55	PX26d	78888728	8711500788887	-	8711500788894	23
12972XV+B1	H7	X-tremeVision	12	55	PX26d	37168030	8727900371680	-	8727900371697	22
12972XV+S2	H7	X-tremeVision	12	55	PX26d	37170328	8727900371703	-	8727900371710	18
55502GKKM	Bax Tool Box 12V	Standard	12	-	-	69717928	8727900697179	-	8727900697230	32
9004C1	HB1	Standard	12	65/45	P29t	47074430	8711500470744	-	8727900370997	24
9005CVB1	HB3	CrystalVision	12	60	P20d	53299930	8727900532999	-	8727900533002	24
9005DVB1	HB3	DiamondVision	12	65	P20d	53295130	8727900532951	-	8727900532968	25
9005PRB1	HB3	Vision	12	60	P20d	24724730	8711500247247	-	8711500247254	24
9005PRC1	HB3	Vision	12	60	P20d	24689930	8711500246899	-	8727900370980	24
9005WHVB1	HB3	WhiteVision	12	60	P20d	37475930	8727900374759	-	8727900374766	24
9006CVB1	HB4	CrystalVision	12	60	P22d	53301930	8727900533019	-	8727900533026	24
9006CVSM	HB4	CrystalVision	12	60	P22d	52620128	8711559526201	-	8711559526454	24
9006DVB1	HB4	DiamondVision	12	55	P22d	53297530	8727900532975	-	8727900532982	25
9006DVS2	HB4	DiamondVision	12	55	P22d	53248728	8727900532487	-	8727900532494	25
9006PRB1	HB4	Vision	12	51	P22d	24726130	8711500247261	-	8711500247278	25
9006PRC1	HB4	Vision	12	51	P22d	24687530	8711500246875	-	8727900370973	25
9006WHVB1	HB4	WhiteVision	12	51	P22d	37473530	8727900374735	-	8727900374742	25
9007C1	HB5	Standard	12	65/55	PX29t	24550230	8711500245502	-	8727900370966	25
9008C1	H13	Standard	12	60/55	P26.4t	87798730	8711500877987	-	8727900370768	24
9012LLC1	HIR2	LongLife	12	55	PX22d	35125530	8727900351255	-	8727900370935	25
9145C1	H10	Standard	12	45	PY20d	52974530	8711559529745	-	8727900370737	24
12972WVUB1	H7	WhiteVision ultra	12	55	PX26d	35493530	8727900354935	-	8727900354928	22
12972WVUSM	H7	WhiteVision ultra	12	55	PX26d	35495928	8727900354959	-	8727900354942	22
12258XVGS2	H1	X-tremeVision G-force	12	55	P14.5s	35520828	8727900355208	-	8727900355215	18
12258XVGB1	H1	X-tremeVision G-force	12	55	P14.5s	35522230	8727900355222	-	8727900355239	18
12342XVGS2	H4	X-tremeVision G-force	12	60/55	P43t-38	35525328	8727900355253	-	8727900355284	20
12342XVGB1	H4	X-tremeVision G-force	12	60/55	P43t-38	35529130	8727900355291	-	8727900355390	20
12972XVGS2	H7	X-tremeVision G-force	12	55	PX26d	35541328	8727900355413	-	8727900355789	22
12972XVGB1	H7	X-tremeVision G-force	12	55	PX26d	35579630	8727900355796	-	8727900355802	22

Halogen two-wheeler lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12008BW	S3	Standard	12	15	P26s	77381430	8711500773814	-	8711500773845	43
12008C1	S3	Standard	12	15	P26s	77394430	8711500773944	-	8711500779335	43
12256B2	W3W	Standard	12	3	W2.1x9.5d	52410830	8711559524108	-	8711559524122	43
12256CP	W3W	Standard	12	3	W2.1x9.5d	48144328	8711500481443	8711500481450	8727900391664	43
12342CTVBW	H4	CityVision moto	12	60/55	P43t-38	39896030	8727900398960	-	8727900398977	42
12342PRBW	H4	Vision moto	12	60/55	P43t-38	49024730	8711500490247	-	8711500490254	42
12498B2	P21W	Standard	12	21	BA15s	05549130	8711500055491	-	8711559520131	43
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	43
12499EDBW	P21/5W	ExtraDuty	12	21/5	BAY15d	87900430	8711500879004	-	8711500879035	43
12636BW	HS1	Vision moto	12	35/35	PX43t	53035330	8727900530353	-	8727900530360	42
12636C1	HS1	Vision moto	12	35/35	PX43t	51250130	8711559512501	-	8727900370881	42
12636CTVBW	HS1	CityVision moto	12	35/35	PX43t	39894630	8727900398946	-	8727900398953	43
12728BW	S2	Standard	12	35/35	BA20d	77385230	8711500773852	-	8711500773869	43
12728C1	S2	Standard	12	35/35	BA20d	77359330	8711500773593	-	8711500779342	43
12972CTVBW	H7	CityVision moto	12	55	PX26d	39898430	8727900398984	-	8727900398991	42
12972PRBW	H7	Vision moto	12	55	PX26d	49026130	8711500490261	-	8711500490278	42

Kits

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
13961CP	W5W	Standard	24	5	W2,1x9,5d	48138273	8711500481382	8711500481399	8711559530376	54
13972MDB1	H7	MasterDuty	24	70	PX26d	82589630	8711500825896	-	8711500825902	51
13972MDBVB1	H7	MasterDuty BlueVision	24	70	PX26d	53279130	8727900532791	-	8727900532807	51
13972MDBVS2	H7	MasterDuty BlueVision	24	70	PX26d	53277728	8727900532777	-	8727900532784	51
13972MDC1	H7	MasterDuty	24	70	PX26d	82581060	8711500825810	8711500828514	8711500825827	51
13972MLC1	H7	MasterLife	24	70	PX26d	82573530	8711500825735	-	8727900371147	51
13974CP	WBT5	Standard	24	2	W2x4,6d	48318828	8711500483188	8711500483195	8727900391183	54
24029CP	Bax 8,5d/2 yellow	Standard	24	1.2	B8,5d/2	48402428	8711500484024	8711500484031	8727900391190	55
24032CP	Bax 8,5d brown	Standard	24	1.2	B8,5d	48852728	8711500488527	8711500488534	8727900391077	55
24356CP	H21W	Standard	24	21	BAY9s	87615728	8711500876157	8711500876164	8727900371161	53
24362MDC1	H11	MasterDuty	24	70	PGJ19-2	82583430	8711500825834	-	8727900371055	51
24362MLC1	H11	MasterLife	24	70	PGJ19-2	82575930	8711500825759	-	8727900371062	51

Kits

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12V Spare kits										
55005SKKM	H4	Single Kit	12	-	-	52730730	8711559527307	-	8711559527246	58
55007SKKM	H7	Single Kit	12	-	-	52732130	8711559527321	-	8711559527215	59
55008SKKM	H1	Single Kit	12	-	-	52731430	8711559527314	-	8711559527222	58
55010SKKM	H1/H7	Single Kit	12	-	-	30999030	8711500309990	-	8711500310163	59
55472EKKM	H1	Easy Kit	12	-	-	69551928	8727900695519	-	8727900695533	58
55473EKKM	H4	Easy Kit	12	-	-	69555728	8727900695557	-	8727900695571	58
55474EKKM	H7	Easy Kit	12	-	-	69558828	8727900695588	-	8727900695601	58
55475EKKM	H1/H7	Easy Kit	12	-	-	69562528	8727900695625	-	8727900695656	58
55476EKKM	R2	Easy Kit	12	-	-	69566328	8727900695663	-	8727900695687	58
55717EBKM	H1	Essential Box	12	-	-	70032928	8727900700329	-	8727900700336	59
55718EBKM	H4	Essential Box	12	-	-	70034328	8727900700343	-	8727900700350	59
55719EBKM	H7	Essential Box	12	-	-	70036728	8727900700367	-	8727900700374	59
55720EBKM	H1/H7	Essential Box	12	-	-	70038128	8727900700381	-	8727900700398	59
55721EBKM	R2	Essential Box	12	-	-	70040428	8727900700404	-	8727900700411	59
24V Spare kits										
55554SKMDKM	MiniKit H4	MasterDuty	24	-	-	69586130	8727900695861	-	8727900695885	60
55555SKMDKM	MiniKit H7	MasterDuty	24	-	-	69590830	8727900695908	-	8727900695939	60
55559LKMDKM	MaxiKit H4	MasterDuty	24	-	-	69684494	8727900696844	-	8727900696851	60
55560LKMDKM	MaxiKit H7	MasterDuty	24	-	-	69686894	8727900696868	-	8727900696875	60
55561LKMDKM	MaxiKit H1/H7	MasterDuty	24	-	-	69688294	8727900696882	-	8727900696899	60
Headlight restoration kit										
HRK00XM	-	-	-	-	-	39976931	8727900399769	-	8727900399776	61

Xenon lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12410C1	D5S	Vision	12	25	PK32d-7	36981633	8727900369816	-	8727900369823	72
42306VIC1	D3R	Vision	42	35	PK32d-6	36483533	8727900364835	-	8727900364842	72
42402VIC1	D4S	Vision	42	35	P32d-5	36485933	8727900364859	-	8727900364866	72
42402XV2C1	D4S	X-tremeVision gen2	42	35	P32d-5	37721733	8727900377217	-	8727900377224	72
42402XV2S1	D4S	X-tremeVision gen2	42	35	P32d-5	37719433	8727900377194	-	8727900377200	72
42403VIC1	D3S	Vision	42	35	PK32d-5	36481133	8727900364811	-	8727900364828	72
42403VIS1	D3S	Vision	42	35	PK32d-5	36495833	8727900364958	-	8727900364965	72
42403WHV2C1	D3S	WhiteVision gen2	42	35	PK32d-5	37737833	8727900377378	-	8727900377385	72
42403WHV2S1	D3S	WhiteVision gen2	42	35	PK32d-5	37735433	8727900377354	-	8727900377361	72
42403XV2C1	D3S	X-tremeVision gen2	42	35	PK32d-5	37717033	8727900377170	-	8727900377187	72
42403XV2S1	D3S	X-tremeVision gen2	42	35	PK32d-5	37713233	8727900377132	-	8727900377149	72
42406VIC1	D4R	Vision	42	35	P32d-6	36487333	8727900364873	-	8727900364880	72
85122SYC1	D2S	LongerLife	85	35	P32d-2	37518333	8727900375183	-	8727900375190	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37244133	8727900372441	-	8727900372458	71
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37524433	8727900375244	-	8727900375251	71
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85122SYS1	D2S	LongerLife	85	35	P32d-2	37254033	8727900372540	-	8727900372557	71
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122VIC1	D2S	Vision	85	35	P32d-2	36477433	8727900364774	-	8727900364781	70
85122VIS1	D2S	Vision	85	35	P32d-2	36491033	8727900364910	-	8727900364927	70
85122WHV2C1	D2S	WhiteVision gen2	85	35	P32d-2	37729333	8727900377293	-	8727900377309	71
85122WHV2S1	D2S	WhiteVision gen2	85	35	P32d-2	37727933	8727900377279	-	8727900377286	71
85122XV2C1	D2S	X-tremeVision gen2	85	35	P32d-2	37707133	8727900377071	-	8727900377088	70
85122XV2S1	D2S	X-tremeVision gen2	85	35	P32d-2	37703333	8727900377033	-	8727900377040	70
85126SYC1	D2R	LongerLife	85	35	P32d-3	37520633	8727900375206	-	8727900375213	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37252633	8727900372526	-	8727900372533	71
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37526833	8727900375268	-	8727900375275	71
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85126SYS1	D2R	LongerLife	85	35	P32d-3	37248933	8727900372489	-	8727900372496	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126VIC1	D2R	Vision	85	35	P32d-3	36479833	8727900364798	-	8727900364804	71
85126VIS1	D2R	Vision	85	35	P32d-3	36493433	8727900364934	-	8727900364941	71
85126WHV2C1	D2R	WhiteVision gen2	85	35	P32d-3	37733033	8727900377330	-	8727900377347	71
85126WHV2S1	D2R	WhiteVision gen2	85	35	P32d-3	37731633	8727900377316	-	8727900377323	71
85126XV2C1	D2R	X-tremeVision gen2	85	35	P32d-3	37711833	8727900377118	-	8727900377125	71
85126XV2S1	D2R	X-tremeVision gen2	85	35	P32d-3	37709533	8727900377095	-	8727900377101	71
85409VIC1	D1R	Vision	85	35	PK32d-3	36475033	8727900364750	-	8727900364767	70
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37516933	8727900375169	-	8727900375176	70
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37250233	8727900372502	-	8727900372519	70
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37522033	8727900375220	-	8727900375237	70
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85415SYS1	D1S	LongerLife	85	35	PK32d-2	37246533	8727900372465	-	8727900372472	70
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415VIC1	D1S	Vision	85	35	PK32d-2	36473633	8727900364736	-	8727900364743	70
85415VIS1	D1S	Vision	85	35	PK32d-2	36489733	8727900364897	-	8727900364903	70
85415WHV2C1	D1S	WhiteVision gen2	85	35	PK32d-2	37725533	8727900377255	-	8727900377262	70
85415WHV2S1	D1S	WhiteVision gen2	85	35	PK32d-2	36072133	8727900360721	-	8727900377248	70
85415XV2C1	D1S	X-tremeVision gen2	85	35	PK32d-2	37701933	8727900377019	-	8727900377026	70
85415XV2S1	D1S	X-tremeVision gen2	85	35	PK32d-2	37697533	8727900376975	-	8727900376982	70

LED Professional work lights

Ordering number	Type	V	W	Plug	GOC	EAN1	EAN2	EAN3	Page
LPL19B1	Penlight Professional	4.5	1.6	-	38819031	8727900388190	-	8727900388206	96
LPL20X1	RCH10	100-240	2.5	EU	39060531	8727900390605	-	8727900390612	99
LPL28RECHX1	Penlight Premium	100-240	2	EU	39220394	8727900392203	-	8727900392210	97
LPL29B1	HDL10	4.5	1.6	-	39360631	8727900393606	-	8727900393699	96
LPL34UVX1	RCH31UV	100-240	3	EU	39419131	8727900394191	-	8727900394207	101
LPL35X1	CBL10	100-240	3.5	EU	39421431	8727900394214	-	8727900394221	102
LPL38X1	RCH6	100-240	2	EU	39607231	8727900396072	-	8727900396089	100
LPL39X1	PJH20	100-240	20	EU	39609631	8727900396096	-	8727900396102	105
LPL403MODX1	MDLS CRI	100-240	15	EU/UK	39627066	8727900396270	-	8727900396287	105
LPL41SPAREX1	MDLS CRI spare module	100-240	5	-	39629433	8727900396294	-	8727900396300	105
LPL42X1	PEN20	100-240	1.8	-	39631731	8727900396317	-	8727900396324	97
LPL43X1	PJH20 Tripod	-	-	-	39634833	8727900396348	-	8727900396355	108
LPL45X1	CBH51	100-240	10	EU	39732131	8727900397321	-	8727900397338	102
LPL46X1	RCH19	100-240	2	EU	39823631	8727900398236	-	8727900398243	99
LPL47X1	RCH21S	100-240	3	EU	39841031	8727900398410	-	8727900398427	100
LPL62X1	RCH5S	100-240	3	EU	05163931	8719018051639	-	8719018051646	98
LPL63X1	RCH25	100-240	5	EU	05165331	8719018051653	-	8719018051660	100
LPL64X1	PJH10	100-240	10	EU	05167731	8719018051677	-	8719018051684	103
P357/10	Universal USB car charger	10.5 -18	-	-	61448985	4895185614489	-	-	107

A series of horizontal dotted lines for writing.





2018 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

www.philips.com/automotive