

PHILIPS

SmartBright 2.0
LED Luminaire

26W



Cost-effective indoor commercial lighting

When you need an affordable, energy efficient replacement for TL and T5 troffers, the Philips SmartBright 2.0 LED Luminaire is the perfect solution.

The elegant design blends seamlessly into any commercial décor and the 25,000 hour lifetime makes it a true fit and forget solution.

Features and benefits

- The cost-effective entry level alternative to conventional troffers
- High quality light output that's easy on the eye
- Elegant linear design is suitable for a range of commercial applications

Product data




Key specification

	RC098V	RC098V
Lumen/Watt	LED22S – 26W/2200lm	LED22S – 26W/2200lm
Correlated Colour Temperature (CCT)	4000K	4000K
Colour Rendering Index (CRI)	80	80
Flex and plug	Yes	Yes
Lifetime	25,000hrs L70 @ 25°C*	25,000hrs L70 @ 25°C*
Unified Glare Ratio (UGR)	UGR22	UGR23
Optics	PS optical diffuser	PS optical diffuser
Driver	Integrated fixed driver	Integrated fixed driver
Dimmable	No	No
Installation	T-Bar recessed, Plaster recessed (supplied with plaster clips)	T-Bar recessed, Plaster recessed (supplied with plaster clips)
IP rating	IP20	IP20
Dimension/Weight	Square – 597x597x32/ 2.5kg	Rectangle – 1197x297x32/ 2.3kg
Colour of housing	White	White
Applications	Supermarkets, Open Plan Offices, Public Indoor Areas and General Commercial Lighting	

*When the fitting reaches 70% of full potential (new)

Dimensions (mm)



Model	W	L	H	Weight (kg)	Cut-Out
RC098V – Rectangle	297	1197	32	2.3	260x1100 (+/- 2mm)
RC098V – Square	597	597	32	2.5	560x560 (+/-2mm)

Model	Run Current	Start (Inrush) Current	Start Current Duration	Earth Leakage Current	MCB Type	Max # of luminaire
RC098V	0.4A	8.4A	42us	0.7mA _{pk}	16A Type B	≤60 pcs

Order Placement Information

Commercial Code	12NC	Description
RC098V26W4KFSQP	824110141901	RC098V LED22S/840 W60L60 PCV GM CAU AD
RC098V26W4KFREP	824110141891	RC098V LED22S/840 W30L120 PCV GM CAU AD

