



PHILIPS

hue personal
wireless
lighting








**Bring your
home to life**
with smart lighting



Philips Hue welcomes you home and lets you remotely control your lights from your bedroom to your backyard.





-  **Set your lights** for when you are not at home
-  **Wakes you up** with light
-  **Wireless** dimming
-  **Light to relax**, read, concentrate and energise
-  **Be creative** with 16 million colours

Easy to install

- 1 Turn on your lighting**
Install all lamps and turn on the light switches.
- 2 Connect the bridge to the router**
And turn power on.
- 3 Download the Hue app**
Follow the instructions to install Hue.
- 4 Expand**
Add more lights and accessories to complete your Hue experience.

White

Control your smart lights



2700 Kelvin

Warm white

White ambiance

Customise your daily routines



2200 - 6500 Kelvin

◀ Warm white Cool daylight ▶

White & colour ambiance

Create extraordinary experiences



2000 - 6500 Kelvin

◀ Warm white Cool daylight ▶

◀ 16 million colours ▶

Hue white ambience Aphelion downlight



Features and Benefits

- 9W white recessed downlight
- Away from home control
- Control via your smart device
- Dimmable

Design and finishing

- Material: aluminium
- Colour: white

Product dimensions & weight

- Length: 13.6 cm
- Width: 5.3 cm
- Net weight: 0.344 kg
- Recessed distance: 10 cm
- Cut out length: 12.5 cm
- Cut out width: 12.5 cm

Packaging dimensions & weight

- Height: 14.3 cm
- Length: 17.1 cm
- Width: 10.1 cm
- Weight: 0.464 kg

Technical specifications

- Mains power: 230 V
- IC rating: IC – Abutted and Covered
- Hue White Ambience: Tunable White
- Total lumen output fixture: 600 lm
- Fixture dimmable
- LED
- Built in LED
- Lifetime up to: 20,000 hrs
- IP code: IP44 from the front, suitable for bathroom. IP20 from the back, protection against objects bigger than 12.5mm

Miscellaneous

- Especially designed for living room and bedroom
- Style: Functional
- Type: Recessed spot light

Service

- Warranty: 1 year

Order Placement Information

Order Code	Barcode	Description
HUEWADL	6947830431380	Aphelion Hue downlight

Hue white ambience Muscari ceiling light



Features and Benefits

- From warm white to cool daylight
- Away from home control
- Control via your smart device
- Dimmable
- Free Hue dimmer switch

Design and finishing

- Material: metal, synthetics
- Colour: aluminium

Product dimensions & weight

- Height: 10.9 cm
- Length: 53.5 cm
- Width: 53.5 cm
- Net weight: 3.400 kg

Packaging dimensions & weight

- Height: 17 cm
- Length: 60 cm
- Width: 60 cm
- Weight: 6.500 kg

What's in the box

- Muscari Ceiling light: 1
- Dimmer Switch: 1

Miscellaneous

- Especially designed for living room and bedroom
- Style: Contemporary
- Type: Ceiling light

Technical specifications

- Mains power: Range 100 V - 240 V, 50-60 Hz
- Bulb technology: LED, 24 V
- Hue White Ambience: Tunable White
- Wattage bulb included: 40 W
- Maximum wattage replacement bulb: 45 W
- Light colour: cool white
- Total lumen output fixture: 2200 lm
- Fixture dimmable
- LED
- Built in LED
- Lifetime up to: 30,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Battery type: CR - Button cell
- Light source equivalent to traditional bulb of: 216 W

Service

- Warranty: 1 year

Order Placement Information

Order Code	Barcode	Description
HUEMUSCARICL	6947830430086	Muscari ceiling light

Hue white ambience Muscari pendant light



Features and Benefits

- Pendant light
- Dimmable
- Warm white to cool daylight
- Away from home control
- Control via your smart device
- Free Hue dimmer switch

Design and finishing

- Material: metal, synthetics
- Colour: aluminium

Product dimensions & weight

- Height: 150 cm
- Length: 53.5 cm
- Width: 53.5 cm
- Net weight: 3.400 kg

Packaging dimensions & weight

- Height: 17 cm
- Length: 60 cm
- Width: 60 cm
- Weight: 6.500 kg

What's in the box

- Muscari Pendant light: 1
- Dimmer Switch: 1

Miscellaneous

- Especially designed for living and bedroom
- Style: Contemporary
- Type: Pendant light

Technical specifications

- Mains power: Range 100 V - 240 V, 50-60 Hz
- Bulb technology: LED, 24 V
- Hue White Ambience: Tunable White
- Wattage bulb included: 40 W
- Maximum wattage replacement bulb: 45 W
- Light colour: cool white
- Total lumen output fixture: 2200 lm
- Fixture dimmable
- LED
- Built in LED
- Lifetime up to: 30,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II - double insulated
- Battery type: CR - Button cell
- Light source equivalent to traditional bulb of: 216 W

Service

- Warranty: 1 year

Order Placement Information

Order Code	Barcode	Description
HUEMUSCARIPD	6947830430420	Muscari pendant light

LightStrip Plus

base



Features and Benefits

- Ultimate flexibility: shape, bend and extend
- Extendible up to 10 metres
- High light output: 1600 lumen
- Requires a Philips Hue bridge

Design and finishing

- Material: synthetics
- Colour: multi colour

Extra feature/accessory incl.

- Dimmable
- LED integrated
- Colour changing (LED)
- Power adapter included
- ZigBee Light Link
- Diffused light effect
- Universal Plug

Product dimensions & weight

- Height: 0.5 cm
- Length: 200 cm
- Width: 1.5 cm
- Net weight: 0.337 kg

Technical specifications

- Mains power: Range 220 V – 240 V, 50–60 Hz
- Number of bulbs: 1
- Wattage bulb included: bulb not included
- Total lumen output fixture: 1600 lm
- Fixture dimmable
- LED
- Lifetime up to: 20,000 hrs
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: II – double insulated

Packaging dimensions & weight

- Height: 5.2 cm
- Length: 21 cm
- Width: 21 cm
- Weight: 0.510 kg

Miscellaneous

- Especially designed for living room, bedroom, home office and study
- Type: Indirect light

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUESTRIP	8718696150405	LightStrip Plus APR base

LightStrip Plus

extension

Features and Benefits

- Extend your Lightstrip Plus with 1 metre extensions
- Extendible up to 10 metres
- Ultimate flexibility: shape, bend and extend
- Requires a Philips Hue bridge



Design and finishing

- Material: synthetics
- Colour: multi colour

Extra feature/accessory incl.

- Dimmable
- LED integrated
- Colour changing (LED)
- Power adapter included
- Diffused light effect
- ZigBee Light Link
- Universal Plug

Product dimensions & weight

- Height: 0.5 cm
- Length: 100 cm
- Width: 1.5 cm
- Net weight: 0.053 kg

Packaging dimensions & weight

- Height: 5.1 cm
- Length: 21 cm
- Width: 10.5 cm
- Weight: 0.160 kg

Miscellaneous

- Especially designed for living room, bedroom, home office and study
- Type: Indirect light

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUESTRIPEXT	8718696150412	LightStrip Plus APR Extension

Hue bulbs

E27/B22



Features and Benefits

- White and colour ambience
- White ambience
- Warm white

The bulb

- Form factor: A60
- Lifetime: 25000 hour(s)
- Wattage: 10 W
- Input voltage: 220V-240V
- Lumen output: 806 lm
- Software upgradeable
- Start up: Instant 100% light output
- Height: 110 mm
- Max. standby power: 0,2 W
- Diameter: 62 mm
- White and colour ambience: 16 million colours
- White ambience: Tunable white 2200K to 6500K
- Warm white: 2700K

Service

- Warranty: 2 years

The bridge

- Height: 26 mm
- Frequency band: 2400-2483,5 MHz
- Max. number of accessories: 12
- Max. number of bulbs: 50
- Power adapter: 100-240 V AC / 50-60Hz

Environmental

- Operational humidity: 5% < H < 95% (non condensing)
- Operational temperature: -10°C – 45°C

Order Placement Information

Order Code	Barcode	Description
HUECOLOURE27	8718696725580	Hue white and color ambience E27 bulb (16mil colours)
HUECOLOURB22	8718696725665	Hue white and color ambience B22 bulb (16mil colours)
HUEWAE27	8718696670385	Hue white ambience E27 bulb (2200K-6500K)
HUEWAB22	8718696672884	Hue white ambience B22 bulb (2200K-6500K)
HUEWHITEB22	8718696449691	Hue white E27 bulb (2700K)
HUEWHITEE27	8718696554951	Hue white B22 bulb (2700K)

Hue white and color ambience bulb

GU10

Features and Benefits

- Single bulb GU10
- White and colour ambience
- Relax, read, concentrate and energize with light recipes
- Smart control, home and away



The bulb

- Fitting: GU10
- Form factor: GU10
- Lifetime: 25,000 hour(s)
- Wattage: 6.5 W
- Light output: 16 million colours, Functional white light, All shades of white, From warm to cold white colour, Dimmable via smart device only, Beam angle - 160° +- 20°
- Lumen output: 145 lm @ 2000K, 210 lm @ 3,000K, 250 lm @ 4,000K, 230 lm @ 6500K, 38 lm/W efficacy @4,000K, Default start-up 195lm @ 2700K, >80 CRI from 2000–4000K
- Software upgradeable
- Start up: Instant 100% light output
- Height: 71 mm
- Width: 50 mm

What's in the box

- Hue bulbs: 1

Environmental

- Operational humidity: 0%<H <80% (non condensing)
- Operational temperature: 0°C - 40°C

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUECOLOURGU10	8718696554913	White and color GU10

Motion sensor



Features and Benefits

- Turn your Hue lights on and off automatically
- Integrated daylight sensor
- Day and night setting
- Requires a Philips Hue bridge

The switch

- IP rating: IP42
- Minimal battery lifetime: 2 year(s)
- Mounting options: freestanding
- Software upgradeable: when connected to Hue bridge
- Sensor depth: 20 mm
- Sensor height: 55 mm
- Sensor width: 55 mm
- Zigbee Light link: protocol IEEE 802.15.4

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUEMOTION	8718696769881	Hue motion sensor

Hue dimmer switch

Features and Benefits

- Dim your Philips Hue lights
- Use as a remote control
- No wires – battery powered
- Switch between scenes
- Requires a Philips Hue bridge



The switch

- Batteries included: 1 x CR2450
- Frequency band: 2400 – 2483.5 MHz
- Lifetime: 50,000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 3 year(s)
- Minimal range indoor: 500 inch
- Software upgradeable: when connected to Hue bridge
- Switch depth: 11 mm
- Switch height: 92 mm
- Switch width: 35 mm
- Weight of switch: 37 g
- Wall plate depth: 14 mm
- Wall plate height: 115 mm
- Wall plate width: 70 mm
- Weight including wall plate: 67 g
- Zigbee Light link: protocol IEEE 802.15.4

Environmental

- Operational humidity: 5% < H < 95% (non condensing)
- Operational temperature: -10°C – 45°C

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUEDIMMER	8718696752029	Hue dimmer switch

Hue tap switch

Features and Benefits

- Recall your favourite Philips Hue scenes
- Use as a remote control
- Powered by your touch - no batteries
- Requires a Philips Hue bridge



Technical specifications

- Diameter: 75 mm
- Height: 25 mm
- Lifetime: 50,000 clicks
- Number of configurable buttons: 4
- Weight: 90 gr

Order Placement Information

Order Code	Barcode	Description
HUETAP	8718696752005	Hue tap switch

Hue bridge

Features and Benefits

- The heart of your Philips Hue system
- Add up to 50 Philips Hue lights
- Smart control, home and away
- Control with your voice



The bridge

- Diameter: 88 mm
- Height: 26 mm
- Frequency band: 2400–2483.5 MHz
- Max. number of accessories: 10
- Max. number of bulbs: 50
- Mounting options: Desktop, Wall
- Power adapter: 100–240 V AC / 50–60Hz, Output voltage: 5 V DC 600mA, Standby power: 0.1 W max
- Power consumption: 250mA max

What's in the box

- Bridge: 1
- Ethernet network cable: 1
- Power adapter: 1

What's in the box

- Operational humidity: 0%<H <80% (non condensing)
- Operational temperature: 0°C - 40°C

What's supported

- iOS: 8 or later
- HomeKit compatible: iOS 9 or later
- iPad: 2, 3rd and 4th generation
- iPad Air: 1, 2
- iPad Mini: 1, 2, 3
- Phone: 4, 4S, 5, 5S, 6, 6 Plus
- iPod Touch: 5th generation

Also tested on

- Android: 2.3 or later
- Google Nexus: 5, 7
- HTC: One
- Motorola Nexus: 6
- Note: Note, Note 2, Note 3, Note 4
- OnePlus: One
- Samsung Galaxy: S2, S3, S4, S5
- Sony: Xperia Z3

Service

- Warranty: 2 years

Order Placement Information

Order Code	Barcode	Description
HUEBRIDGE	8718696555057	Hue bridge



Philips Lighting Australia

65 Epping Road,

North Ryde 2113, Australia

Tel: 1300 304 404

www.philips.com.au/lighting

Email: clubblueau@philips.com

©2018 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent – or other industrial or intellectual property rights.