

**PHILIPS**

*Badkamer/Salle de bain*





1.



3.



2.

1. **Hotstone 34049 11 16**  
H67 L146 D147  
LED - 2x 2,5W incl. - 350lm  
15.000 hrs - Class II - IP44  
metal - synthetics

2. **Hotstone 34050 11 16**  
H59 L346 D144  
LED - 4x 2,5W incl. - 2x 350lm  
15.000 hrs - Class II - IP44  
metal - synthetics

3. **Care 34107 11 16**  
H180 L91 D134  
E14 - 1x 12W incl. - 737lm  
Class II - IP44  
glass - metal



1.



2.



3.



4.

1. **Fit 34058 11 16**  
 H63 L333 D64  
 LED - 2x 2,5W incl. - 350lm  
 15.000 hrs - Class II - IP44  
 metal - synthetics



2. **Fit 34059 11 16**  
 H63 L483 D67  
 LED - 3x 2,5W incl. - 520lm  
 15.000 hrs - Class II - IP44  
 metal - synthetics



3. **Vitalise 34093 11 16**  
 H60 L388 D77  
 G5 - 1x 8W incl. - 470lm  
 Class II - IP44  
 glass - metal



4. **Vitalise 34094 11 16**  
 H60 L616 D77  
 G5 - 1x 13W incl. - 1000lm  
 Class II - IP44  
 glass - metal





1.



2.



3.

- 
1. **Salts ceiling lamp 32010 17 16**  
 H100 D315  
 E27 - 1x 20 W incl.  
 Class I - IP44  
 mat chrome - metal

2. **Fountain ceiling lamp 32020 67 16**  
 H95 D350  
 E27 - 1x 20 W incl.  
 Class I - IP21  
 mat glass - glass

- 
3. **Pool ceiling lamp 32081 31 16**  
 H110 D270  
 E27 - 1x 20 W incl.  
 Class II - IP44  
 white - glass

1.



2.



---

1. **Baume 32053 31 16**  
H71 L262 D262  
LED - 3x 2,5W incl. - 530lm  
15.000 hrs - Class II - IP44  
synthetics

---

2. **Cool 32063 31 16**  
H78 L352 D352  
LED - 3x 4W incl. - 820lm  
15.000 hrs - Class II - IP44  
metal - synthetics

---

3. **Seru 32065 31 16**  
H66 L364 D340  
LED - 3x 4,7W incl. - 1060lm  
15.000 hrs - Class II - IP44  
metal - synthetics



1.



2.

---

1. **Beach 32070 17 16**  
H55 L360 D360  
2GX13 - 1x 40W incl. - 3300lm  
Class I - IP44  
synthetics - metal

---

2. **Thermen 32082 87 16**  
H65 L400 D400  
2GX13 - 1x 40W incl. - 3300lm  
Class I - IP44  
glass - metal



1.

- 
1. **Spa 32005 31 16**  
H120 L260 D260  
E27 - 1x 20W incl. - 1250lm  
Class II - IP44  
glass



1.



2.

---

1. **Roots recessed 59902 17 16**

H39 D100  
GU10 - 3x 35W incl.  
Class II - IP23  
mat chrome - metal

---

2. **Roots recessed 59902 11 16**

H39 D100  
GU10 - 3x 35 W incl.  
Class II - IP23  
chrome - metal






1.



2.



3.



2.

1. **Wash 59905 11 16**  
 L105 D105 R150 C90 x90  
 GU10 - 1x 35W incl.  
 Class II - IP44  
 metal



2. **Wash 59905 17 16**  
 L105 D105 R150 C90 x90  
 GU10 - 1x 35W incl. -  
 Class II - IP44  
 metal



3. **Tub 59925 17 16**  
 L92 D92 R57 C80 x80  
 Power LED - 1x 7,5W incl. - 350lm  
 Class III - IP65  
 glass



