

**PHILIPS**

Outdoor lighting

Iridium gen3



Product guide

# The first intelligent 'plug and play' road luminaire



# Contents

<b>The Iridium gen3 family</b>	<b>3</b>
The first intelligent ‘plug and play’ road luminaire	3
<b>Family range</b>	<b>4</b>
<b>Lighting performance</b>	<b>5</b>
Light distribution	5
<b>Applications</b>	<b>6</b>
<b>Application examples</b>	<b>7</b>
<b>Luminaire features</b>	<b>8</b>
Tilt adjustments	8
Spigot arrangement	8
Easy ‘plug and play’ installation in just three steps	9
<b>Iridium gen3 in control</b>	<b>10</b>
CityTouch Ready	10
Starsense Wireless with RF antenna	11
LumiStep	11
DynaDimmer	11
<b>Iridium gen3 in perspective</b>	<b>12</b>
<b>Iridium gen3 complete sets</b>	<b>13</b>
Féroé bracket	13
Mayotte bracket	13
KC bracket	14
Aloa/Accante pole	14
<b>Main specifications</b>	<b>16</b>
<b>Specification table</b>	<b>17</b>

# The Iridium gen3 family

## The first intelligent ‘plug and play’ road luminaire

Iridium gen3 is the first intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it directly from a distance through CityTouch lighting management platform. Remote light management made easy!

The new ‘plug and play’ concept has been designed to ensure safe and easy installation in just three steps:

1. Install the spigot
2. Plug in the mains
3. Tilt and close the luminaire

The luminaire’s high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications on roads and in residential areas. The luminaire’s neo-classical design guarantees a consistent look and feel for your surroundings.



- ✓ Seamless connection from luminaire to CityTouch software without commissioning: CityTouch Ready
- ✓ ‘Plug and play’ installation in just three steps
- ✓ High efficiency, ensuring fast payback and low Total Cost of Ownership

## Family range

The neo-classical design of the new Iridium gen3 family ensures smooth integration of the luminaire in residential areas as well as on main roads. Inspired by the round shape of Iridium, the new Iridium gen3 provides the best of new LED technology while still echoing the legacy designs.



Iridium gen3 Mini



Iridium gen3 Medium



Iridium gen3 Large




# Lighting performance

## Light distribution

The Iridium gen3 family comes with a wide choice of optics and lumen packages. It suits applications ranging from residential streets to main roads, with the guarantee of high performance up to 131 lm/W.


### Iridium gen3 Mini

**MSO** Medium Street Optic




CE and S class for street and path lighting

**WSO** Wide Street Optic



CE and S class for street and path lighting


**DK** Distribution Medium for wet road conditions



MEW class for road lighting


### Iridium gen3 Medium and Large

**A** Distribution Asymmetrical




S class for area square lighting

**DC** Distribution Medium for comfort




ME1-2 class for road lighting (T1<10)

**DK** Distribution Medium for wet road conditions




MEW class for road lighting

**DM** Distribution Medium




ME3 (to ME6) and CE class for road and street lighting

**DW** Distribution Wide




ME3 (to ME6) and CE class for road and street lighting

### Different LED optics for different applications



# Applications


The Iridium gen3 family's neo-classical round design, together with its wide range of optics and lumen packages, makes it the perfect luminaire to light residential areas, urban roads as well as provincial roads and highways.



Iridium gen3 is part of our functional lighting solutions portfolio and incorporate primarily traffic functions that offer guidance and orientation, in a way that traffic safety for all participants is secured, mainly by having perfect glare control, white color rendering and uniformity quality up to all relevant standards. At the same time maximization of pole spacings is targeted by designing high performance optics, to match various lighting classes and road geometries for traffic routes in and around cities.

# Application examples


## Pedestrian/cycle path




S3 class

### Iridium gen3 Mini

Light distribution: WSO  
 Source: GRN25/830  
 (2,300 lm)  
 Spacing: 29 m  
 System power: 20 W  
 Glare Index class: G3



## Minor road




ME3a class

-1 m 7 m

### Iridium gen3 Medium

Light distribution: DM  
 Source: GRN115/740  
 (9,000 lm)  
 Spacing: 34 m  
 System power: 86 W



## Residential wide street




S2 class


12 m

### Iridium gen3 Large

Light distribution: DW  
 Source: GRN120/830  
 (10,000 lm)  
 Spacing: 41 m  
 System power: 95 W



## Highway




ME3b class

7 m 2 m 7 m

### Iridium gen3 Large

Light distribution: DM  
 Source: GRN185/740  
 (15,500 lm)  
 Spacing: 71 m  
 System power: 138 W



# Luminaire features

## Tilt adjustments

The Iridium gen3 new and innovative separated spigot makes it possible to have post-top mounting in three positions  $-0^\circ$ ,  $+5^\circ$ ,  $+10^\circ$ , while with side-entry the spigot provides negative tilt to fit existing brackets  $-0^\circ$ ,  $-5^\circ$ ,  $-10^\circ$ .



Post-top:  $0^\circ$ ,  $+5^\circ$ ,  $+10^\circ$



Side-entry:  $0^\circ$ ,  $-5^\circ$ ,  $-10^\circ$



Easy tilt setting

## Spigot arrangement

One common spigot is used in the three sizes of the Iridium gen3 family.



Post-top  $\varnothing$  60/76 mm  
Side-entry  $\varnothing$  42/60 mm



# Luminaire features

## Easy 'plug and play' installation in just three steps



Install spigot on the pole  
(post-top or side-entry)



Position the luminaire  
on the spigot



Connect the connector to the luminaire,  
close and tilt



Optimized side-entry installation with  
bubble level indicator



- ✓ CityTouch Ready
- ✓ Automatic connection
- ✓ Automatic location
- ✓ Automatic commissioning
- ✓ Automatic asset data import into CityTouch lighting management platform



No segment controller



No router



No outdoor luminaire  
controller



No cabinet

# Iridium gen3 in control

Philips offers you a complete connected public lighting system to help you overcome all the challenges you face in terms of an evolving urban environment, the movement of traffic, etc., as well as the need for flexible lighting and reduced costs.



**READY**

## CityTouch Ready

Iridium can be seamlessly connected with CityTouch via integration of all the intelligence into the luminaire without any additional hardware needed. The communication runs directly via the public mobile network. As a positive side effect, no own maintenance effort is required. In addition, the whole connectivity management is part of our service which keeps any hassle away from you as a customer. Once connected to the power supply a light point automatically appears on the CityTouch map at the right location – with all lighting assets imported into the system and ready to be remotely controlled by CityTouch LightWave.

CityTouch LightWave is an intelligent, interactive remote management solution for your street lighting. It brings your city lighting to life and provides you with flexibility, knowledge and accuracy.

Flexibility means that you will be easily able to act or react according to expected and unexpected situations by dimming or brightening all areas within your city to ensure safety and well-being. Knowledge implies that you are always informed about the current status of every single luminaire – for better maintenance and faster repairs. Accuracy stands for precise energy metering which gives you a perfect overview on real non-estimated energy consumption.

### CityTouch LightWave key features



#### Control of each individual light point

You get the flexibility to adapt every single luminaire to changing situations or demands of the city at any time. To adjust calendars to the individual needs you are free to change the “switching points” of every dimming profile simply via drag and drop.



#### Fault detection & notification

A quicker and better knowledge of the current status of the lighting infrastructure enables you to manage faster maintenance and improve the maintenance service level.



#### Accurate energy metering

With accurate energy metering down to the level of each single luminaire it is possible to verify your energy bills and identify new potential savings.

# Iridium gen3 in control

Philips offers you a complete range of lighting controls to maximize your energy consumption by dimming and reduced light nuisance.

## Starsense Wireless with RF antenna




A system to control and monitor remotely light points, that works independently with practically any light source. It is not limited in available power scenarios. Starsense allows to have feedback from the installation, which supports easy maintenance. This solution can generate up to 70% energy savings and 40% on maintenance costs.

## LumiStep






An integrated stand-alone control system which lowers the flux of the light source and power consumed over a period of 6, 8 or 10 hours (3 pre-programmed versions). The potential energy savings (on power system) is up to 25%, depending on the luminaires and light source used.



## DynaDimmer




An integrated stand-alone control system included in each light point - operated on electronic equipment and can be integrated into the luminaire. It can apply 5 levels of power, (re)definable on the level and duration, per chosen light point. For example, an average energy saving of approximately 50% per year can be realized.



## Iridium gen3 in perspective

The Iridium gen3 range has been designed to offer perfect solutions, including in terms of the proportion of the luminaire to its mounting height or a specific environment.


- Iridium gen3 Mini is suitable for mounting heights from 3 to 6 m, for instance on residential streets.
- Iridium gen3 Medium is suitable for mounting heights from 6 to 12 m, for instance on main residential streets or urban traffic roads.
- Iridium gen3 Large is suitable for mounting heights from 6 to 16 m, for instance on main urban traffic roads or highways.



# Iridium gen3 complete sets


## Féroé bracket

1. Iridium gen3 Large + Féroé bracket + Aloa/Accante pole + Féroé rear bracket + Iridium gen3 Mini
- 2,4. Iridium gen3 Medium + Féroé bracket + Aloa/Accante pole
- 3,6. Iridium gen3 Large + Féroé bracket + Aloa/Accante pole
- 5,7. Iridium gen3 Mini + Féroé bracket + Aloa/Accante pole



## Mayotte bracket


- 1,4. Iridium gen3 Large + Mayotte bracket + Aloa/Accante pole
- 2,3. Iridium gen3 Mini + Mayotte bracket + Aloa/Accante pole
- 5,6. Iridium gen3 Medium + Mayotte bracket + Aloa/Accante pole
7. Iridium gen3 Large + Mayotte bracket + Aloa/Accante pole + Mayotte rear bracket + Iridium gen3 Mini



# Iridium gen3 complete sets

## KC bracket

- 1,7,12. Iridium gen3 Large + KC bracket + Aloa/Accante pole
- 2,5,8,10,11. Iridium gen3 Medium + KC bracket + Aloa/Accante pole
- 3,4,6,9. Iridium gen3 Mini + KC bracket + Aloa/Accante pole



## Aloa/Accante pole

- 1. Iridium gen3 Mini + Aloa/Accante pole
- 2. Iridium gen3 Medium + Aloa/Accante pole
- 3. Iridium gen3 Large + Aloa/Accante pole





# Main specifications

## Iridium gen3

Product features	Iridium gen3 Mini	Iridium gen3 Medium	Iridium gen3 Large
<b>Type</b>	BGP381	BGP382	BGP383
<b>Light source</b>	Integral LED-module	Integral LED-module	Integral LED-module
<b>Color temperature</b>	<ul style="list-style-type: none"> <li>• 3000 K (warm white)</li> <li>• 4000 K (neutral white)</li> </ul>	<ul style="list-style-type: none"> <li>• 3000 K (warm white)</li> <li>• 4000 K (neutral white)</li> </ul>	<ul style="list-style-type: none"> <li>• 3000 K (warm white)</li> <li>• 4000 K (neutral white)</li> </ul>
<b>Color Rendering Index</b>	<ul style="list-style-type: none"> <li>• ≥ 80 (warm white)</li> <li>• ≥ 70 (neutral white)</li> </ul>	<ul style="list-style-type: none"> <li>• ≥ 80 (warm white)</li> <li>• ≥ 70 (neutral white)</li> </ul>	<ul style="list-style-type: none"> <li>• ≥ 80 (warm white)</li> <li>• ≥ 70 (neutral white)</li> </ul>
<b>Luminous flux</b>	1,021 to 4,024 lm	4,616 to 9,951 lm	7,372 to 15,553 lm
<b>Power</b>	9 to 36 W depending on LED configuration	38 to 86 W depending on LED configuration	60 to 138 W depending on LED configuration
<b>Luminaire efficacy</b>	100 to 126 lm/W	105 to 129 lm/W	103 to 131 lm/W
<b>Lumen maintenance</b>	100,000 hours at L80F10	100,000 hours at L80F10	100,000 hours at L80F10
<b>Optic</b>	<ul style="list-style-type: none"> <li>• Medium street optic (MSO)</li> <li>• Wide Street Optic (WSO)</li> <li>• Distribution Medium for wet road conditions (DK)</li> </ul>	<ul style="list-style-type: none"> <li>• Distribution Asymmetrical (DA)</li> <li>• Distribution Medium (DM)</li> <li>• Distribution Wide (DW)</li> <li>• Distribution Medium for comfort (DC)</li> <li>• Distribution Medium for wet road conditions (DK)</li> </ul>	<ul style="list-style-type: none"> <li>• Distribution Asymmetrical (DA)</li> <li>• Distribution Medium (DM)</li> <li>• Distribution Wide (DW)</li> <li>• Distribution Medium for comfort (DC)</li> <li>• Distribution Medium for wet road conditions (DK)</li> </ul>
<b>Installation</b>	<ul style="list-style-type: none"> <li>• Post-top: 60 or 76 mm</li> <li>• Side-entry: 42 or 60 mm</li> <li>• Recommended mounting height: 4 m</li> <li>• Standard tilt angle post-top: 0, 5 and 10°</li> <li>• Adjustable tilt angle: 0, -5 and -10°</li> </ul>	<ul style="list-style-type: none"> <li>• Post-top: 60 or 76 mm</li> <li>• Side-entry: 42 or 60 mm</li> <li>• Recommended mounting height: 8 m</li> <li>• Standard tilt angle post-top: 0, 5 and 10°</li> <li>• Adjustable tilt angle: 0, -5 and -10°</li> </ul>	<ul style="list-style-type: none"> <li>• Post-top: 60 or 76 mm</li> <li>• Side-entry: 42 or 60 mm</li> <li>• Recommended mounting height: 10 m</li> <li>• Standard tilt angle post-top: 0, 5 and 10°</li> <li>• Adjustable tilt angle: 0, -5 and -10°</li> </ul>
<b>Driver</b>	Built-in (self ballasted LED-module)	Built-in (self ballasted LED-module)	Built-in (self ballasted LED-module)
<b>Inrush current driver</b>	27 A / 150 µs	80 A / 150 µs	105 A / 150 µs
<b>Mains voltage</b>	220-240 V / 50-60 Hz	220-240 V / 50-60 Hz	220-240 V / 50-60 Hz
<b>Material</b>	<ul style="list-style-type: none"> <li>• Housing: high pressure die-cast aluminum</li> <li>• Cover: polycarbonate, flat</li> </ul>	<ul style="list-style-type: none"> <li>• Housing: high pressure die-cast aluminum</li> <li>• Cover: polycarbonate, flat</li> </ul>	<ul style="list-style-type: none"> <li>• Housing: high pressure die-cast aluminum</li> <li>• Cover: polycarbonate, flat</li> </ul>
<b>Color</b>	<ul style="list-style-type: none"> <li>• Aluminum or grey</li> <li>• Other RAL or AKZO colors available on request</li> </ul>	<ul style="list-style-type: none"> <li>• Aluminum or grey</li> <li>• Other RAL or AKZO colors available on request</li> </ul>	<ul style="list-style-type: none"> <li>• Aluminum or grey</li> <li>• Other RAL or AKZO colors available on request</li> </ul>
<b>IP</b>	IP66	IP66	IP66
<b>IK</b>	IK09	IK09	IK09
<b>Weight</b>	6,5 kg	10,5 kg	14,2 kg
<b>Electrical connection</b>	Push-in connector with 3 to 5 poles	Push-in connector with 3 to 5 poles	Push-in connector with 3 to 5 poles
<b>Operating temperature range</b>	-30 to +35 °C	-30 to +35 °C	-30 to +35 °C
<b>Options</b>	<ul style="list-style-type: none"> <li>• Nema socket</li> <li>• Photocell: mini cell 35, 55, 75 Lux</li> <li>• Fuse</li> <li>• Cable: 3, 4, 5, 6 m</li> </ul>	<ul style="list-style-type: none"> <li>• Nema socket</li> <li>• Photocell: mini cell 35, 55, 75 Lux</li> <li>• Fuse</li> <li>• Cable: 6, 8, 9, 10, 11, 12 m</li> </ul>	<ul style="list-style-type: none"> <li>• Nema socket</li> <li>• Photocell: mini cell 35, 55, 75 Lux</li> <li>• Fuse</li> <li>• Cable: 6, 8, 9, 10, 11, 12, 16 m</li> </ul>
<b>Dimming</b>	<ul style="list-style-type: none"> <li>• LumiStep 6, 8 or 10 hours • DynaDimmer</li> <li>• Constant Light Output (CLO) • SDU • 1-10 V</li> <li>• DALI • RF regulation • Controls system output • CityTouch Ready</li> </ul>	<ul style="list-style-type: none"> <li>• LumiStep 6, 8 or 10 hours • DynaDimmer</li> <li>• Constant Light Output (CLO) • SDU • 1-10 V</li> <li>• DALI • RF regulation • Controls system output • CityTouch Ready</li> </ul>	<ul style="list-style-type: none"> <li>• LumiStep 6, 8 or 10 hours • DynaDimmer</li> <li>• Constant Light Output (CLO) • SDU • 1-10 V</li> <li>• DALI • RF regulation • Controls system output • CityTouch Ready</li> </ul>
<b>Maintenance</b>	Can be opened via screw to replace driver and LED module	Can be opened via screw to replace driver and LED module	Can be opened via screw to replace driver and LED module
<b>Dimensions</b>	530 x 270 x 147 mm	643 x 328 x 157 mm	748 x 354 x 154 mm
<b>Surge protection</b>	4 kV standard (Optional: 10 kV)	4 kV standard (Optional: 10 kV)	4 kV standard (Optional: 10 kV)
<b>Effective Projective Area</b>	SCx 0,024 M <sup>2</sup> max	SCx 0,031 M <sup>2</sup> max	SCx 0,039 M <sup>2</sup> max



# Specification table

Luminaire version	Product family code	Line	Color	System flux (lm)	System power (W)	System efficacy (lm/W)
-------------------	---------------------	------	-------	------------------	------------------	------------------------

## Iridium gen3 Mini

Iridium gen3 Mini	BGP381	GRN11/740	NW	1,021	9	115
Iridium gen3 Mini	BGP381	GRN13/740	NW	1,214	11	115
Iridium gen3 Mini	BGP381	GRN15/740	NW	1,404	13	112
Iridium gen3 Mini	BGP381	GRN17/740	NW	1,591	14	112
Iridium gen3 Mini	BGP381	GRN19/740	NW	1,815	14	126
Iridium gen3 Mini	BGP381	GRN20/740	NW	1,859	17	110
Iridium gen3 Mini	BGP381	GRN22/740	NW	2,029	16	124
Iridium gen3 Mini	BGP381	GRN25/740	NW	2,295	19	123
Iridium gen3 Mini	BGP381	GRN30/740	NW	2,765	23	119
Iridium gen3 Mini	BGP381	GRN35/740	NW	3,176	27	117
Iridium gen3 Mini	BGP381	GRN40/740	NW	3,630	32	114
Iridium gen3 Mini	BGP381	GRN45/740	NW	4,024	36	113
Iridium gen3 Mini	BGP381	GRN11/830	WW	1,025	10	104
Iridium gen3 Mini	BGP381	GRN13/830	WW	1,215	12	105
Iridium gen3 Mini	BGP381	GRN15/830	WW	1,384	13	103
Iridium gen3 Mini	BGP381	GRN17/830	WW	1,568	16	101
Iridium gen3 Mini	BGP381	GRN19/830	WW	1,765	16	114
Iridium gen3 Mini	BGP381	GRN20/830	WW	1,846	19	100
Iridium gen3 Mini	BGP381	GRN22/830	WW	2,035	18	113
Iridium gen3 Mini	BGP381	GRN25/830	WW	2,296	21	111
Iridium gen3 Mini	BGP381	GRN30/830	WW	2,724	25	108
Iridium gen3 Mini	BGP381	GRN35/830	WW	3,188	30	106
Iridium gen3 Mini	BGP381	GRN40/830	WW	3,594	35	103

## Iridium gen3 Medium




Iridium gen3 Medium	BGP382	GRN55/740	NW	5,027	38	132
Iridium gen3 Medium	BGP382	GRN65/740	NW	5,936	46	129
Iridium gen3 Medium	BGP382	GRN75/740	NW	6,827	55	125
Iridium gen3 Medium	BGP382	GRN85/740	NW	7,637	63	122
Iridium gen3 Medium	BGP382	GRN95/740	NW	8,429	71	119
Iridium gen3 Medium	BGP382	GRN105/740	NW	9,259	79	117
Iridium gen3 Medium	BGP382	GRN115/740	NW	9,951	86	115
Iridium gen3 Medium	BGP382	GRN50/830	WW	4,616	38	122
Iridium gen3 Medium	BGP382	GRN60/830	WW	5,445	46	118
Iridium gen3 Medium	BGP382	GRN70/830	WW	6,373	56	114
Iridium gen3 Medium	BGP382	GRN80/830	WW	7,165	65	111
Iridium gen3 Medium	BGP382	GRN90/830	WW	7,937	73	109
Iridium gen3 Medium	BGP382	GRN100/830	WW	8,793	83	106

# Specification table

Luminaire version	Product family code	Line	Color	System flux (lm)	System power (W)	System efficacy (lm/W)
-------------------	---------------------	------	-------	------------------	------------------	------------------------

## Iridium gen3 Large

Iridium gen3 Large	BGP383	GRN96/740	NW	8,666	66	131
Iridium gen3 Large	BGP383	GRN106/740	NW	9,573	75	128
Iridium gen3 Large	BGP383	GRN116/740	NW	10,366	82	126
Iridium gen3 Large	BGP383	GRN125/740	NW	11,147	90	124
Iridium gen3 Large	BGP383	GRN135/740	NW	11,915	98	122
Iridium gen3 Large	BGP383	GRN145/740	NW	12,669	106	120
Iridium gen3 Large	BGP383	GRN155/740	NW	13,500	115	118
Iridium gen3 Large	BGP383	GRN165/740	NW	14,222	123	116
Iridium gen3 Large	BGP383	GRN175/740	NW	14,928	131	114
Iridium gen3 Large	BGP383	GRN185/740	NW	15,533	138	113
Iridium gen3 Large	BGP383	GRN81/830	WW	7,372	61	122
Iridium gen3 Large	BGP383	GRN91/830	WW	8,199	69	119
Iridium gen3 Large	BGP383	GRN101/830	WW	9,012	78	116
Iridium gen3 Large	BGP383	GRN110/830	WW	9,721	85	114
Iridium gen3 Large	BGP383	GRN120/830	WW	10,589	95	112
Iridium gen3 Large	BGP383	GRN130/830	WW	11,352	104	110
Iridium gen3 Large	BGP383	GRN140/830	WW	12,096	113	107
Iridium gen3 Large	BGP383	GRN150/830	WW	12,820	122	105
Iridium gen3 Large	BGP383	GRN160/830	WW	13,524	131	103





© 2014 Royal Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication there of does not convey nor imply any license under patent or other industrial or intellectual property rights.

Document order number: 3222 635 69508  
07/2014

Data subject to change.

[www.philips.com/catalog](http://www.philips.com/catalog)