

PHILIPS

Lighting

Gemakkelijk overstappen van conventionele verlichting naar CoreLine of Ledinaire LED-armaturen



CoreLine



Ledinaire

Conventionele armaturen

Uitgefaseerd		Voor elke ruimte een oplossing		Eenvoud voor een scherpe prijs	
Type	Omschrijving	Omschrijving	EOC	Omschrijving	EOC
Inbouwarmatuur	Impala TBS160 2X36W TLD M2	CoreLine Inbouw RC120B LED37S/830 PSU W30L120	26812300		
Inbouwarmatuur	Impala TBS160 2X36W TLD M6	CoreLine Inbouw RC120B LED34S/830 PSD W30L120 VAR-PC	26658700		
Inbouwarmatuur	Impala TBS160 4X18W TLD M2	CoreLine Inbouw RC120B LED37S/830 PSU W60L60	89755100	Ledinaire Panel RC065B LED32S/840 PSU 60x60	7328599
Inbouwarmatuur	Impala TBS160 4X18W TLD M6	CoreLine Inbouw RC120B LED34S/830 PSD W60L60 VAR-PC	26656300		
Inbouwarmatuur	TBS260 2X28W TL5 M2	CoreLine Inbouw RC120B LED37S/830 PSU W30L120	26812300		
Inbouwarmatuur	TBS260 2X28W TL5 D6/M6	CoreLine Inbouw RC120B LED34S/830 PSD W30L120 VAR-PC	26658700		
Inbouwarmatuur	TBS260 4X14W TL5 M2	CoreLine Inbouw RC120B LED37S/830 PSU W60L60	89755100	Ledinaire Panel RC065B LED32S/840 PSU 60x60	7328599
Inbouwarmatuur	TBS260 4X14W TL5 D6/M6	CoreLine Inbouw RC120B LED34S/830 PSD W60L60 VAR-PC	26656300		
Inbouwarmatuur	TBS330 2X36W TLD M2	CoreLine Inbouw RC120B LED37S/830 PSU W30L120	26812300		
Inbouwarmatuur	TBS330 2X36W TLD M6	CoreLine Inbouw RC120B LED34S/830 PSD W30L120 VAR-PC	26658700		
Inbouwarmatuur	TBS330 4X18W TLD M2	CoreLine Inbouw RC120B LED37S/830 PSU W60L60	89755100	Ledinaire Panel RC065B LED32S/840 PSU 60x60	7328599
Inbouwarmatuur	TBS330 4X18W TLD M6	CoreLine Inbouw RC120B LED34S/830 PSD W60L60 VAR-PC	26656300		
Downlight	Europa 2 FBH099/FBS120 1X18W	CoreLine Downlight DN131B LED10S/830 PSU PI6 ALU	85226200	Ledinaire Downlight DN060 LED8S/840 PSU	30664399
Downlight	Europa 2 FBH099/FBS120 2X18W	CoreLine Downlight DN131B LED20S/830 PSU PI6 ALU	85228600	Ledinaire Downlight DN060 LED18S/840 PSU	30663699
Downlight	Europa 2 FBH099/FBS120 1X26W	CoreLine Downlight DN131B LED10S/830 PSU PI6 ALU	85226200	Ledinaire Downlight DN060 LED8S/840 PSU	30664399
Downlight	Europa 2 FBH099/FBS120 2X26W	CoreLine Downlight DN131B LED20S/830 PSU PI6 ALU	85228600	Ledinaire Downlight DN060 LED18S/840 PSU	30663699
Waterdicht	Pacific TCW216 1xTL5-28W HFS PI	CoreLine Waterdicht WT120C LED40S/840 PSU L1200	84048000	Ledinaire waterproof WT060C LED36S/840 PSU L1200	38011399
Waterdicht	Pacific TCW216 1xTL5-35W HFS PI	CoreLine Waterdicht WT120C LED40S/840 PSU L1200	84048000	Ledinaire waterproof WT060C LED36S/840 PSU L1200	38011399
Waterdicht	Pacific TCW216 1xTL5-49W HFS PI	CoreLine Waterdicht WT120C LED60S/840 PSU L1500	84049700	Ledinaire waterproof WT060C LED56S/840 PSU L1500	38013799
Waterdicht	Pacific TCW216 1xTL-D36W HFS PI	CoreLine Waterdicht WT120C LED40S/840 PSU L1200	84048000	Ledinaire waterproof WT060C LED36S/840 PSU L1200	38011399
Waterdicht	Pacific TCW216 1xTL-D58W HFS PI	CoreLine Waterdicht WT120C LED60S/840 PSU L1500	84049700	Ledinaire waterproof WT060C LED56S/840 PSU L1500	38013799
Batten/balk	TMX204 1xTL5-28W HFP	CoreLine Batten BN124 LED41S/840 PSU TW1	07474999		
Batten/balk	TMX204 1xTL5-35W HFP	CoreLine Batten BN124 LED64S/840 PSU TW1	38001499		
Batten/balk	TMX204 1xTL5-49W HFP	CoreLine Batten BN124 LED64S/840 PSU TW1	38001499		
Batten/balk	TMX204 1xTL-D36W HFP	CoreLine Batten BN124 LED41S/840 PSU TW1	07474999		
Batten/balk	TMX204 1xTL-D58W HFP	CoreLine Batten BN124 LED64S/840 PSU TW1	38001499		
Inbouwspot	Zadora QBS570 1XHAL MR50 45W	CoreLine Inbouwspot RS141B LED6-32/827 PSR WH	06903599	Ledinaire ClearAccent Spot RS060B LED5-36830 PSR	7268499
Inbouwspot	Zadora QBS570 1XHAL MR50 50W	CoreLine Inbouwspot RS141B LED6-32/827 PSR WH	06903599	Ledinaire ClearAccent Spot RS060B LED5-36830 PSR	7268499
Inbouwspot	Zadora LED RS049B adjustable	CoreLine Inbouwspot RS141B LED6-32/827 PSR WH	06903599	Ledinaire ClearAccent Spot RS060B LED5-36830 PSR	7268499
Beveiligingsarmatuur	FWC120	CoreLine FWC LED WC120 LED18-/830 PSU II WH	85193699		
Wand-Plafond opbouw	Gondola FWG200 1X PL-C 18W	CoreLine Wand & plafond-armatuur WL120V LED12S/840 PSR WH	06635599		
Wand-Plafond opbouw	Gondola FWG200 2X PL-C 18W	CoreLine Wand & plafond-armatuur WL120V LED16S/840 PSR WH	06633199		
Schijnwerper	Tempo 2/3	CoreLine Tempo BVP110 LED42/NW S	30636000		
Highbay	Cabana BY150P 1XHPI-P250W-BU IC IP65	CoreLine Highbay BY121P G3 LED205S/840 PSD WB GR	30147100		
Highbay	Cabana BY150P 1XHPI-P400W-BU IC IP65	CoreLine Highbay BY120P G2 LED105S/840 PSU WB GR	30144000		