



**PHILIPS**

LED

InstantFit lamps

---

# This is **real compatibility**

Other lamps claim compatibility, but only InstantFit has been proven to work with 50% more ballasts<sup>1</sup> delivering even light output, proven energy savings and a long average lifetime. That's true compatibility.

- **InstantFit works with over 200 ballasts** — more than any other lamp — so you know it's going to perform as expected and keep you from having to redo any jobs
- **Proven over 40% energy savings<sup>2</sup>** over fluorescent means a satisfied customer and no time wasted going back to a job
- **Lifetime delivered** — average life rating of 50,000 hours<sup>3</sup>, with up to 70,000<sup>3</sup> in the portfolio, means satisfied customers
- **Improved profit** and more time growing business instead of doing rework
- **Light quality and performance predictability**— consistent light output and no flicker means satisfied happy customers and no wasted time redoing a job.
- **Proven product history** and a company with a long history of innovation and reliability in the lighting industry.



# Philips InstantFit LED lamps

## Philips InstantFit LED T8 lamps

### Ordering, electrical and technical data (Subject to change without notice)

Product Number	Model Number(s)	DLC Product ID <sup>5</sup>	Ordering Code	Volts (Depending on Ballast)	Base	CRI	Color Temp. (K)	Pkg Qty	LED Lifetime <sup>4</sup>	MOL (In.)	Beam Angle
<b>InstantFit LED T8 - 4'</b>											
46826-4	9290011239C	Not DLC Certified	10T8/48-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	48	160°
46827-2	9290011240D / 9290011240C	PCY5A5J7	10T8/48-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	48	160°
46828-0	9290011241D / 9290011241C	PES681F4	10T8/48-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	48	160°
46829-8	9290011242D / 9290011242C	PICQAFXR	10T8/48-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	48	160°
• 46956-9	9290011239C	Not DLC Certified	10T8/48-3000 IF 10/1 TAA/NAFTA	120-277, 347	G13	82	3000	10	50,000	48	160°
• 46957-7	9290011240C	PCY5A5J7	10T8/48-3500 IF 10/1 TAA/NAFTA	120-277, 347	G13	82	3500	10	50,000	48	160°
• 46958-5	9290011241C	PES681F4	10T8/48-4000 IF 10/1 TAA/NAFTA	120-277, 347	G13	82	4000	10	50,000	48	160°
• 46959-3	9290011242C	PICQAFXR	10T8/48-5000 IF 10/1 TAA/NAFTA	120-277, 347	G13	82	5000	10	50,000	48	160°
<b>InstantFit LED T8 - 4' dimmable high output</b>											
46830-6	9290011585C	PIGG4T6Q	14T8/48-3000 IF 10/1 DIM	120-277, 347	G13	82	3000	10	50,000	48	160°
46831-4	9290011586C	P5R4PGPD	14T8/48-3500 IF 10/1 DIM	120-277, 347	G13	82	3500	10	50,000	48	160°
46832-2	9290011587C	PFWPMJNV	14T8/48-4000 IF 10/1 DIM	120-277, 347	G13	82	4000	10	50,000	48	160°
46833-0	9290011588C	P9RG41WJ	14T8/48-5000 IF 10/1 DIM	120-277, 347	G13	82	5000	10	50,000	48	160°
• 46960-1	9290011585C	PIGG4T6Q	14T8/48-3000 IF 10/1 DIM TAA/NAFTA	120-277, 347	G13	82	3000	10	50,000	48	160°
• 46961-9	9290011586C	P5R4PGPD	14T8/48-3500 IF 10/1 DIM TAA/NAFTA	120-277, 347	G13	82	3500	10	50,000	48	160°
• 46962-7	9290011587C	PFWPMJNV	14T8/48-4000 IF 10/1 DIM TAA/NAFTA	120-277, 347	G13	82	4000	10	50,000	48	160°
• 46963-5	9290011588C	P9RG41WJ	14T8/48-5000 IF 10/1 DIM TAA/NAFTA	120-277, 347	G13	82	5000	10	50,000	48	160°
<b>InstantFit LED T8 - 4' high output glass</b>											
47009-6	9290013430	Pending	14T8 PRO LED/48-3000 IF G 10/1	120-277, 347	G13	82	3000	10	50,000	48	240°
47010-4	9290013431	PV2NCRIM	14T8 PRO LED/48-3500 IF G 10/1	120-277, 347	G13	82	3500	10	50,000	48	240°
47011-2	9290013432	PUQ8ZEAH	14T8 PRO LED/48-4000 IF G 10/1	120-277, 347	G13	82	4000	10	50,000	48	240°
47012-0	9290013433	P8HU6SVS	14T8 PRO LED/48-5000 IF G 10/1	120-277, 347	G13	82	5000	10	50,000	48	240°
<b>InstantFit LED T8 - 4' ultra high output</b>											
46313-3	9290012267	PNGUXZUY	16.5T8 LED/48-3500 IF 10/1 UHO	120-277, 347	G13	82	3500	10	70,000	48	160°
46314-1	9290012268	PZ5C8FWR	16.5T8 LED/48-4000 IF 10/1 UHO	120-277, 347	G13	82	4000	10	70,000	48	160°
46315-8	9290012269	PS8REP3K	16.5T8 LED/48-5000 IF 10/1 UHO	120-277, 347	G13	82	5000	10	70,000	48	160°
<b>InstantFit LED T8 - 4' glass</b>											
45656-6	9290011511	Not DLC Certified	17T8/48-4000 IFG 10/1	120-277, 347	G13	82	4000	10	36,000	48	240°
45657-4	9290011512	Not DLC Certified	17T8/48-5000 IFG 10/1	120-277, 347	G13	82	5000	10	36,000	48	240°
<b>InstantFit LED T8 - 3'</b>											
46932-0	9290013113	No DLC Category	9T8 LED/36-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	36	160°
46933-8	9290013114	No DLC Category	9T8 LED/36-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	36	160°
46934-6	9290013115	No DLC Category	9T8 LED/36-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	36	160°
46935-3	9290013116	No DLC Category	9T8 LED/36-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	36	160°
<b>InstantFit LED T8 - 2' high output</b>											
46927-0	9290013108	Not DLC Certified	7T8 LED/24-3000 IF 10/1	120-277, 347	G13	82	3000	10	50,000	24	160°
46928-8	9290013109	PM745MKV	7T8 LED/24-3500 IF 10/1	120-277, 347	G13	82	3500	10	50,000	24	160°
46929-6	9290013110	PKTG4YER	7T8 LED/24-4000 IF 10/1	120-277, 347	G13	82	4000	10	50,000	24	160°
46930-4	9290013111	PW99TC5B	7T8 LED/24-5000 IF 10/1	120-277, 347	G13	82	5000	10	50,000	24	160°
<b>InstantFit LED T8/T12 - 8'</b>											
46923-9	9290013077	No DLC Category	35T8/96-3000 IF FA8 10/1	120-277, 347	FA8	82	3000	10	50,000	96	160°
46924-7	9290013078	No DLC Category	35T8/96-3500 IF FA8 10/1	120-277, 347	FA8	82	3500	10	50,000	96	160°
46925-4	9290013146	No DLC Category	35T8/96-4000 IF FA8 10/1	120-277, 347	FA8	82	4000	10	50,000	96	160°
46926-2	9290013147	No DLC Category	35T8/96-6500 IF FA8 10/1	120-277, 347	FA8	82	6500	10	50,000	96	160°
<b>InstantFit LED T5 high output</b>											
46712-6	9290012837	Not DLC Certified	24T5 LED/HO/48-3000 IF 10/1	120-277, 347-480V	G5	82	3000	10	50,000	46	160°
46713-4	9290012838	PR7H998W	24T5 LED/HO/48-3500 IF 10/1	120-277, 347-480V	G5	82	3500	10	50,000	46	160°
46714-2	9290012839	PUFNVUMP	24T5 LED/HO/48-4000 IF 10/1	120-277, 347-480V	G5	82	4000	10	50,000	46	160°
46715-9	9290012840	PJHYX3QV	24T5 LED/HO/48-5000 IF 10/1	120-277, 347-480V	G5	82	5000	10	50,000	46	160°
<b>InstantFit LED T8 U-Bent - 6" high output</b>											
46937-9	9290013118	PTESWFZT	13T8 LED/24-3000 IF-6U 10/1	120-277, 347	G13	82	3000	10	50,000	24	160°
46938-7	9290013119	P14MK6P7	13T8 LED/24-3500 IF-6U 10/1	120-277, 347	G13	82	3500	10	50,000	24	160°
46939-5	9290013120	P3WDMMYN	13T8 LED/24-4000 IF-6U 10/1	120-277, 347	G13	82	4000	10	50,000	24	160°
46940-3	9290013121	PSR46S6R	13T8 LED/24-5000 IF-6U 10/1	120-277, 347	G13	82	5000	10	50,000	24	160°
<b>LED InstantFit - 4' rotatable high output</b>											
46865-2	9290013033	PIZ3VUZP	14T8/48-3000 IF 10/1 ROT	120-277, 347	G13	82	3000	10	50,000	48	160°
46866-0	9290013034	PMRXKRUT	14T8/48-3500 IF 10/1 ROT	120-277, 347	G13	82	3500	10	50,000	48	160°
46867-8	9290013035	P2R73QWZ	14T8/48-4000 IF 10/1 ROT	120-277, 347	G13	82	4000	10	50,000	48	160°
46868-6	9290013036	PQ2TMYAQ	14T8/48-5000 IF 10/1 ROT	120-277, 347	G13	82	5000	10	50,000	48	160°

Please refer to [www.philips.com/instantfit](http://www.philips.com/instantfit) for instant start ballasts details and the latest ballast compatibility guide<sup>5</sup>.

For more information on Philips' limited warranty please visit [www.philips.com/warranties](http://www.philips.com/warranties).

# Philips InstantFit LED lamps

## Philips InstantFit LED T8 lamps

### Ballast technical data (Subject to change without notice)

Product Number	Bare Lamp Watts (W)	Average System Watts (W)			Initial Lumens <sup>6</sup>		
		Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)	Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)
<b>InstantFit LED T8 - 4'</b>							
46826-4	10.0	11.0	13.0	16.0	1300	1500	1700
46827-2	10.0	11.0	13.0	16.0	1300	1500	1800
46828-0	10.0	11.0	13.0	16.0	1400	1600	1850
46829-8	10.0	11.0	13.0	16.0	1400	1600	1850
46956-9	10.0	11.0	13.0	16.0	1300	1500	1700
46957-7	10.0	11.0	13.0	16.0	1300	1500	1800
46958-5	10.0	11.0	13.0	16.0	1400	1600	1850
46959-3	10.0	11.0	13.0	16.0	1400	1600	1850
<b>InstantFit LED T8 - 4' dimmable high output</b>							
46830-6	14.0	15.0	17.0	23.0	1800	2000	2700
46831-4	14.0	15.0	17.0	23.0	1800	2000	2700
46832-2	14.0	15.0	17.0	23.0	1900	2100	2800
46833-0	14.0	15.0	17.0	23.0	1900	2100	2800
46960-1	14.0	15.0	17.0	23.0	1800	2000	2700
46961-9	14.0	15.0	17.0	23.0	1800	2000	2700
46962-7	14.0	15.0	17.0	23.0	1900	2100	2800
46963-5	14.0	15.0	17.0	23.0	1900	2100	2800
<b>InstantFit LED T8 - 4' high output glass</b>							
47009-6	14.0	15.0	17.0	23.0	1750	2000	2350
47010-4	14.0	15.0	17.0	23.0	1750	2000	2350
47011-2	14.0	15.0	17.0	23.0	1850	2100	2450
47012-0	14.0	15.0	17.0	23.0	1850	2100	2450s
<b>InstantFit LED T8 - 4' ultra high output</b>							
46313-3	16.5	18.0	20.0	27.0	2200	2400	2950
46314-1	16.5	18.0	20.0	27.0	2250	2500	3050
46315-8	16.5	18.0	20.0	27.0	2250	2500	3050
<b>InstantFit LED T8 - 4' glass</b>							
45656-6	17.0	18.0	20.0	26.5	1850	2100	2450
45657-4	17.0	18.0	20.0	26.5	1850	2100	2450
<b>InstantFit LED T8 - 3'</b>							
46932-0	9.0	10.5	11.5	15.5	950	1100	1300
46933-8	9.0	10.5	11.5	15.5	950	1100	1300
46934-6	9.0	10.5	11.5	15.5	1050	1200	1400
46935-3	9.0	10.5	11.5	15.5	1050	1200	1400
<b>InstantFit LED - 2' high output</b>							
46927-0	7.0	8.5	9.5	13.5	950	1050	1200
46928-8	7.0	8.5	9.5	13.5	950	1050	1200
46929-6	7.0	8.5	9.5	13.5	1050	1150	1300
46930-4	7.0	8.5	9.5	13.5	1050	1150	1300
<b>InstantFit LED T8/T12 - 8'</b>							
46923-9	35.0	N/A	41.0	N/A	N/A	4000	N/A
46924-7	35.0	N/A	41.0	N/A	N/A	4000	N/A
46925-4	35.0	N/A	41.0	N/A	N/A	4200	N/A
46926-2	35.0	N/A	41.0	N/A	N/A	4200	N/A
<b>InstantFit LED T5 high output</b>							
46712-6	24.0	N/A	28.0	N/A	N/A	3300	N/A
46713-4	24.0	N/A	28.0	N/A	N/A	3300	N/A
46714-2	24.0	N/A	28.0	N/A	N/A	3500	N/A
46715-9	24.0	N/A	28.0	N/A	N/A	3500	N/A
<b>InstantFit LED T8 U-Bent - 6" high output</b>							
46937-9	13.0	14.0	16.0	21.0	1800	2000	2700
46938-7	13.0	14.0	16.0	21.0	1800	2000	2700
46939-5	13.0	14.0	16.0	21.0	1900	2100	2800
46940-3	13.0	14.0	16.0	21.0	1900	2100	2800
<b>LED InstantFit - 4' dimmable rotatable high output</b>							
46865-2	14.0	15.0	17.0	23.0	1800	2000	2700
46866-0	14.0	15.0	17.0	23.0	1800	2000	2700
46867-8	14.0	15.0	17.0	23.0	1900	2100	2800
46868-6	14.0	15.0	17.0	23.0	1900	2100	2800

# Philips InstantFit LED lamps

## Philips InstantFit LED T8 electro magnetic compatible lamps

### Ordering, electrical and technical data (Subject to change without notice)

Product No.	Model No.	Ordering Code	Volts (Depending on Ballast)	Base	CRI	Color Temp. (K)	LED Lifetime (hrs.) <sup>4</sup>	MOL (In.)	Beam Angle
<b>InstantFit LED T8 EM compatible<sup>5</sup> – 4' glass</b>									
46311-7	9290012265	20T12 EM LED/48-4000 IF G	120-277	G13	83	4000	36,000	48	240°
46312-5	9290012266	20T12 EM LED/48-6500 IF G	120-277	G13	83	6500	36,000	48	240°

### Ballast technical data (Subject to change without notice)

Product No.	Bare Lamp Watts (W)	Average System Watts (W)			Initial Lumens <sup>4</sup>		
		Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)	Low Ballast Factor (0.78)	Normal Ballast Factor (0.88)	High Ballast Factor (1.18)
<b>InstantFit LED T8 EM compatible – 4' glass</b>							
46311-7	20	20	23	31	1850	2100	2800
46312-5	20	20	23	31	1850	2100	2800

Suitable for use in fixtures where ambient temperature is between -4°F (-20°C) and 113°F (45°C).

## System wattage of the Philips InstantFit T8 vs a comparable linear T12<sup>7</sup>

Ballast Model No.	Manufacturer	System Voltage	No. of Lamps	System Power (W) T12 Fluorescent	System Power (W) T8 LED	Energy Savings (%) <sup>9</sup>
R-140-1-TP	Philips Advance	120	1	52.1	26.1	50.0%
RL-140-TP	Philips Advance	120	1	32.8	25.6	21.7%
R-2S40-1-TP	Philips Advance	120	2	88.9	47.1	47.0%
XQM-2S40-TP	Philips Advance	220	2	95.5	51.9	45.6%
V-2S40-1-TP	Philips Advance	277	2	90.2	45.3	49.8%
RQM-2S40-3-TP	Philips Advance	120	2	86.9	46.4	46.6%
R-2S34-TP-5	Philips Advance	120	2	81.1	41.5	48.8%
V-2S34-TP	Philips Advance	277	2	79.2	42.6	46.3%
RM-2S35-TP	Philips Advance	120	2	60.9	41.2	32.4%

# Philips InstantFit LED lamps

## Philips InstantFit LED T8 lamps

### Shipping data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	Lamps/ SKU	SKUs per Layer	Layers High	SKU Dimensions (L x W x H) (In.)	Case Dimensions (L x W x H) (In.)	Pallet Dimensions (L x W x H) (In.)
<b>InstantFit LED T8 - 4'</b>												
46826-4	47219-1	46826-7	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46827-2	47220-7	46827-4	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46828-0	47221-4	46828-1	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46829-8	47222-1	46829-8	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46956-9	47260-3	46956-1	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46957-7	47261-0	46957-8	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46958-5	47262-7	46958-5	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46959-3	47263-4	46959-2	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
<b>InstantFit LED T8 - 4' dimmable high output</b>												
46830-6	47223-8	46830-4	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46831-4	47224-5	46831-1	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46832-2	47225-2	46832-8	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46833-0	47226-9	46833-5	10	6.2	0.42	1120	1	70	16	48.0 x 1.1 x 1.1	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46960-1	47264-1	46960-8	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46961-9	47265-8	46961-5	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46962-7	47266-5	46962-2	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46963-5	47267-2	46963-9	10	9.7	0.60	600	1	60	10	48.0 x 1.1 x 1.1	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
<b>InstantFit LED T8 - 4' high output glass</b>												
47009-6	45240-7	47009-3	10	6.2	0.42	550	1	50	16	48.0 x 1.1 x 1.1	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3
47010-4	45275-9	47010-9	10	6.2	0.42	550	1	50	16	48.0 x 1.1 x 1.1	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3
47011-2	45325-1	47011-6	10	6.2	0.42	550	1	50	16	48.0 x 1.1 x 1.1	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3
47012-0	45248-3	47012-3	10	6.2	0.42	550	1	50	16	48.0 x 1.1 x 1.1	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3
<b>InstantFit LED T8 - 4' ultra high output</b>												
46313-3	46313-7	46313-2	10	9.7	0.59	600	1	60	10	1.1 x 1.1 x 48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46314-1	46314-4	46314-9	10	9.7	0.59	600	1	60	10	1.1 x 1.1 x 48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
46315-8	46315-1	46315-6	10	9.7	0.59	600	1	60	10	1.1 x 1.1 x 48.0	48.8 x 6.0 x 3.5	49.2 x 39.4 x 40.9
<b>InstantFit LED T8 - 4' glass</b>												
45656-6	45656-6	45656-1	10	9.7	1.06	360	1	40	10	1.1 x 1.1 x 48.0	49.8 x 8.8 x 4.2	51.2 x 39.4 x 43.4
45657-4	45657-3	45657-8	10	9.7	1.06	360	1	40	10	1.1 x 1.1 x 48.0	49.8 x 8.8 x 4.2	51.2 x 39.4 x 43.4
<b>InstantFit LED T8 - 3'</b>												
46932-0	47231-3	46932-5	10	4.5	0.31	1440	1	90	16	35.7 x 1.0 x 1.0	37.1 x 5.4 x 2.7	50.6 x 39.4 x 48.6
46933-8	47232-0	46933-2	10	4.5	0.31	1440	1	90	16	35.7 x 1.0 x 1.0	37.1 x 5.4 x 2.7	50.6 x 39.4 x 48.6
46934-6	47233-7	46934-9	10	4.5	0.31	1440	1	90	16	35.7 x 1.0 x 1.0	37.1 x 5.4 x 2.7	50.6 x 39.4 x 48.6
46935-3	47234-4	46935-6	10	4.5	0.31	1440	1	90	16	35.7 x 1.0 x 1.0	37.1 x 5.4 x 2.7	50.6 x 39.4 x 48.6
<b>InstantFit LED T8 - 2' high output</b>												
46927-0	47227-6	46927-1	10	2.6	0.23	2240	1	140	16	23.7 x 1.0 x 1.0	25.3 x 5.8 x 2.7	51.1 x 39.4 x 48.6
46928-8	47228-3	46928-8	10	2.6	0.23	2240	1	140	16	23.7 x 1.0 x 1.0	25.3 x 5.8 x 2.7	51.1 x 39.4 x 48.6
46929-6	47229-0	46929-5	10	2.6	0.23	2240	1	140	16	23.7 x 1.0 x 1.0	25.3 x 5.8 x 2.7	51.1 x 39.4 x 48.6
46930-4	47230-6	46930-1	10	2.6	0.23	2240	1	140	16	23.7 x 1.0 x 1.0	25.3 x 5.8 x 2.7	51.1 x 39.4 x 48.6
<b>InstantFit LED T8/T12 - 8'</b>												
46923-9	46923-8	46923-3	10	16.7	2.06	300	1	30	10	0.0 x 0.0 x 0.0	95.9 x 9.4 x 3.9	96.4 x 29.9 x 45.2
46924-7	46052-5	46052-0	10	16.7	2.06	300	1	30	10	0.0 x 0.0 x 0.0	95.9 x 9.4 x 3.9	96.4 x 29.9 x 45.2
46925-4	46925-2	46925-7	10	16.7	2.06	300	1	30	10	0.0 x 0.0 x 0.0	95.9 x 9.4 x 3.9	96.4 x 29.9 x 45.2
46926-2	46926-9	46926-4	10	16.7	2.06	300	1	30	10	0.0 x 0.0 x 0.0	95.9 x 9.4 x 3.9	96.4 x 29.9 x 45.2
<b>InstantFit LED T5 high output</b>												
46712-6	46712-8	46712-3	10	4.7	0.22	2000	1	100	20	0.0 x 0.0 x 0.0	46.3 x 4.0 x 2.1	47.2 x 40.6 x 47.6
46713-4	46713-5	46713-0	10	4.7	0.22	2000	1	100	20	0.0 x 0.0 x 0.0	46.3 x 4.0 x 2.1	47.2 x 40.6 x 47.6
46714-2	46714-2	46714-7	10	4.7	0.22	2000	1	100	20	0.0 x 0.0 x 0.0	46.3 x 4.0 x 2.1	47.2 x 40.6 x 47.6
46715-9	46715-9	46715-4	10	4.7	0.22	2000	1	100	20	0.0 x 0.0 x 0.0	46.3 x 4.0 x 2.1	47.2 x 40.6 x 47.6
<b>InstantFit LED U-Bent - 6" high output</b>												
46937-9	47235-1	46937-0	10	8.2	1.20	300	1	100	3	22.4 x 7.1 x 1.1	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
46938-7	47236-8	46938-7	10	8.2	1.20	300	1	100	3	22.4 x 7.1 x 1.1	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
46939-5	47237-5	46939-4	10	8.2	1.20	300	1	100	3	22.4 x 7.1 x 1.1	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
46940-3	47238-2	46940-0	10	8.2	1.20	300	1	100	3	22.4 x 7.1 x 1.1	23.1 x 7.5 x 11.9	47.2 x 39.4 x 41.4
<b>LED InstantFit - 4' rotatable high output</b>												
46865-2	47268-9	46865-6	10	6.2	0.42	1120	1	70	16	0.0 x 0.0 x 0.0	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46866-0	47269-6	46866-3	10	6.2	0.42	1120	1	70	16	0.0 x 0.0 x 0.0	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46867-8	47270-2	46867-0	10	6.2	0.42	1120	1	70	16	0.0 x 0.0 x 0.0	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7
46868-6	47271-9	46868-7	10	6.2	0.42	1120	1	70	16	0.0 x 0.0 x 0.0	49.3 x 5.5 x 2.7	50.4 x 39.4 x 48.7

# Philips InstantFit LED lamps


## Philips InstantFit LED T8 electro magnetic compatible lamps

### Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	Lamps/SKU	SKUs per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
<b>InstantFit LED T8 EM compatible - 4' glass</b>												
46311-7	46311-3	46311-8	10	6.26	1.06	360	1	40	9	1.1 x 1.1 x 48.0	49.8 x 8.8 x 4.2	51.2 x 39.4 x 43.4
46312-5	46312-0	46312-5	10	6.26	1.06	360	1	40	9	1.1 x 1.1 x 48.0	49.8 x 8.8 x 4.2	51.2 x 39.4 x 43.4

### Relative Light Output vs. Ambient Temperature

#### 4' T8 Lamps - 0.88 BF Ballast



Suitable for use in fixtures where ambient temperature is between -4°F (-20°C) and 113°F (45°C).

**Warning:** Philips LED T8 InstantFit lamps will only operate properly on compatible Instant-start and Programmed-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit [www.philips.com/instantfit](http://www.philips.com/instantfit)

**FCC Note:** This device complies with Part 18 of the FCC Rules.

1. Based on the next leading competitor and their number of compatible ballasts at time of printing.
2. Savings based on comparison to F32T8 electronic instant start systems.
3. Tested to B50 L70 requirement with a ballast factor < 0.88.
4. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Testing with a ballast whose ballast factor is ≤ 0.88
5. Compatibility subject to change as additional ballasts are tested. If you do not see your ballast on the compatibility list please contact your local Philips Lighting representative.
6. Photometric testing consistent with IES LM-79.
7. Measured data provided as a reference. System power may vary depending on ballast manufacturer and ballast age. Please refer to [www.philips.com/instantfit](http://www.philips.com/instantfit) for the latest ballast compatibility guide.
8. DLC Product ID list is for UL Type A only. The product may also be DLC certified as UL Type C. To verify search the DLC QPL using the model number.
- Products offered under the Trade Agreements Act (TAA).  
For more information, visit <http://www.va.gov/oal/business/fss/taa.asp>

Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at [www.designlights.org/search](http://www.designlights.org/search).



© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008