

**PHILIPS  
LUMEC**

Roadway

RoadFocus

145, 180, 215 and 241W RFL



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

The Philips Lumece RoadFocus LED Cobra Head luminaires feature a sleek design that provides seamless replacement of existing HID luminaires. RoadFocus is available in three sizes, offers multiple lumen packages, and a complete array of optical distributions, making it an outstanding solution for all types of roadway applications.

**Ordering guide**

**Example:** RFL-145W64LED4K-T-R2S-UNIV-DMG-OTL-RCD7-SP2-WC10-GY3

Luminaire	LED Module	Optical System	Voltage	Driver and Dimming	Wattage Switch	Twist-Lock Receptacle	Surge Protection	Warranty	Finish
<input type="text" value="RFL"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text" value="WC10"/>	<input type="text"/>
RFL RoadFocus Large	145W64LED4K-T or 180W80LED4K-T or 215W96LED4K-T or 241W112LED4K-T	R2S Type II Short R2M Type II Medium R3S Type III Short R3M Type III Medium 5 Type V	UNIV 120-277VAC HVU 347-480VAC	<b>Standard:</b> DMG <sup>1,6</sup> Dimmable driver 0-10V <b>Optional:</b> AMPD <sup>2,4,5,6</sup> Amplight Dimming DynaDimmer Economy Profile CDMGE25 <sup>2,4,5,6</sup> CDMGE50 <sup>2,4,5,6</sup> CDMGE75 <sup>2,4,5,6</sup> DynaDimmer Median Profile CDMGM25 <sup>2,4,5,6</sup> CDMGM50 <sup>2,4,5,6</sup> CDMGM75 <sup>2,4,5,6</sup> DynaDimmer Safety Profile CDMGS25 <sup>2,4,5,6</sup> CDMGS50 <sup>2,4,5,6</sup> CDMGS75 <sup>2,4,5,6</sup> DALI <sup>2,4,5,6</sup> Digitally Addressable Lighting Interface DMG-AST <sup>*2,4</sup> Adjustable Startup Time DMG-CLO <sup>*2,4,5</sup> Constant Light Output DMG-OTL <sup>*2,4</sup> Over The Life <i>*Includes 0-10v Dimming</i>	FAWS <sup>5</sup> Field Adjustable Wattage Selector (optional)	<b>Standard:</b> RCD <sup>1,3,7</sup> Receptacle for twist-lock photocell or shorting cap, 5-pin (standard) <b>Optional:</b> RCD7 <sup>3,7</sup> Receptacle for twist-lock photocell or shorting cap, 7-pin (optional)	SP2 <sup>8</sup> 20kV / 20kA Surge Protector (optional)	WC10 <sup>1</sup> 10-year limited warranty (standard)	BK Black Finish BR Bronze Finish GY3 Gray Finish WH White Finish

1. Please note these integrated features come standard with RoadFocus luminaires.

2. Denotes programmable driver option. Not available with HVU (347-480volt).

3. Use of photoelectric cell or shorting cap is required to ensure proper illumination.

4. Not available with HVU (347-480volt).

5. FAWS not available with AMPD, CDMG options, DALI or CLO.

6. Dimming choices: Select either DMG or AMPD or one of the CDMG options or DALI.

7. When RCD7 option is selected you will get 7-pin instead of standard RCD 5-pin.

8. When SP2 option is selected you will get SP2 instead of standard SP1.



# RFL RoadFocus LED Cobrahead, Large

145, 180, 215, and 241W

**Accessories** (must be ordered as separate line items – quickly and easily installed in the field)

<p><b>ACC-RFS-RFM-RFL-PH9<sup>9</sup></b> Shorting cap</p> <p><b>ACC-RFS-RFM-RFL-HS</b> House side shield, 1 per 16 LED light engine.</p> <p><b>ACC-RFS-RFM-RFL-UNIV-PH8<sup>9</sup></b> Twist-lock Photoelectric Cell, UNIV (120-277VAC).</p> <p><b>ACC-RFM-RFL-PH8/347<sup>9</sup></b> Twist-lock Photoelectric Cell, HVU 347VAC.</p> <p><b>ACC-RFM-RFL-PH8/480<sup>9</sup></b> Twist-lock Photoelectric Cell, HVU 480VAC.</p> <p><b>ACC-RFS-RFM-RFL-UNIV-PH8XL<sup>9</sup></b> Twist-lock Photoelectric Cell, extended life, UNIV (120-277VAC).</p>	<p><b>ACC-RFS-RFM-RFL-UNIV-SPC<sup>9,10</sup></b> Starsense twist-lock photoelectric cell &amp; antenna node, UNIV (120-277VAC).</p> <p><b>ACC-RFM-RFL-HVU-SPC<sup>9,10</sup></b> Starsense twist-lock photoelectric cell &amp; antenna node, HVU (347-480VAC).</p> <p><b>ACC-RFS-RFM-RFL-UNIV-SPCD<sup>9,10</sup></b> Starsense dimmable twist-lock photoelectric cell &amp; antenna node, UNIV (120-277VAC).</p>
--	--

9. Use of photoelectric cell or shorting cap is required to ensure proper illumination.

10. Please note that more hardware as well as software are required – please contact the quotations department for help with putting together the entire control system.

## LED Wattage and Lumen Values

LED = Philips Lumileds LUXEON T, CRI = 70, CCT = 4000K (+/- 350K)

System (LED + driver) rated life = 100,000 hrs<sup>11</sup>

LED Module	Typical Delivered Lumens	Typical System Wattage (W) <sup>12</sup>	LED Current (mA)	Typical System Current (A) @						Efficacy (Lm/W)	BUG Rating
				120V	208V	240V	277V	347V	480V		
145W64LED4K-T-R2S	16,349	137	700	1.15	0.66	0.58	0.51	0.41	0.31	119	B3-U0-G2
145W64LED4K-T-R2M	16,046	137	700	1.15	0.66	0.58	0.51	0.41	0.31	117	B3-U0-G3
145W64LED4K-T-R3S	15,763	137	700	1.15	0.66	0.58	0.51	0.41	0.31	115	B2-U0-G3
145W64LED4K-T-R3M	15,697	137	700	1.15	0.66	0.58	0.51	0.41	0.31	115	B3-U0-G2
180W80LED4K-T-R2S	20,444	174	700	1.46	0.86	0.76	0.69	0.52	0.39	117	B3-U0-G2
180W80LED4K-T-R2M	20,065	174	700	1.46	0.86	0.76	0.69	0.52	0.39	115	B3-U0-G3
180W80LED4K-T-R3S	19,711	174	700	1.46	0.86	0.76	0.69	0.52	0.39	113	B2-U0-G3
180W80LED4K-T-R3M	19,628	174	700	1.46	0.86	0.76	0.69	0.52	0.39	113	B3-U0-G3
215W96LED4K-T-R2S	24,538	207	700	1.74	1.01	0.89	0.80	0.62	0.46	119	B3-U0-G2
215W96LED4K-T-R2M	24,084	207	700	1.74	1.01	0.89	0.80	0.62	0.46	116	B3-U0-G3
215W96LED4K-T-R3S	23,658	207	700	1.74	1.01	0.89	0.80	0.62	0.46	114	B3-U0-G4
215W96LED4K-T-R3M	23,559	207	700	1.74	1.01	0.89	0.80	0.62	0.46	114	B3-U0-G3
241W112LED4K-T-R2S	28,633	248	700	2.03	1.17	1.02	0.91	0.72	0.53	115	B4-U0-G3
241W112LED4K-T-R2M	28,102	248	700	2.03	1.17	1.02	0.91	0.72	0.53	114	B3-U0-G4
241W112LED4K-T-R3S	27,606	244	700	2.03	1.17	1.02	0.91	0.72	0.53	113	B3-U0-G4
241W112LED4K-T-R3M	27,490	244	700	2.03	1.17	1.02	0.91	0.72	0.53	113	B3-U0-G4

Type V (5) IES files for all LED modules pending.

11. L<sub>70</sub> >100,000 hrs (at ambient temperature = 25°C).

12. System wattage or total luminaire wattage includes the LED module and the LED driver.

Note: Due to rapid and continuous advances in LED technology, LED luminaire data is subject to change without notice and at the discretion of Philips.


# RFL RoadFocus LED Cobrahead, Large

145, 180, 215, and 241W

## Field Adjustable Wattage (FAWS) Multiplier Chart

FAWS Position	Typical Delivered Lumens Multiplier	Typical System wattage and typical current
1	0.37	0.29
2	0.55	0.50
3	0.62	0.58
4	0.71	0.69
5	0.77	0.75
6	0.81	0.81
7	0.84	0.87
8	0.94	0.91
9	0.98	0.96
10	1.00	1.00

## Dimensions



Weight: 27.3 Lbs  
EPA: 0.92 sq. ft.

## Predicted Lumen Depreciation Data<sup>14,15,16</sup>

Ambient Temperature °C	Driver mA	Calculated L <sub>70</sub> Hours	L <sub>70</sub> per TM-21	Lumen Maintenance % at 60,000 hrs
25°C	700 mA	>100,000 hours	>60,000 hours	>94%

14. Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions.

15. L<sub>70</sub> is the predicted time when LED performance depreciates to 70% of initial lumen output.

16. Calculated per IESNA TM21-11. Published L<sub>70</sub> hours limited to 6 times actual LED test hours

## Specifications

### Housing

Made of a low copper die cast Aluminum alloy (A360), 0.100" (2.5mm) minimum thickness. Fits on a 1.66" (42mm) O.D. (1.25" NPS), 1.9" (48mm) O.D. (1.5" NPS) or 2 3/8" (60mm) O.D. (2" NPS) by 5 1/2" (140mm) minimum long tenon. Comes with a zinc plated clamp fixed by 2 zinc plated hexagonal bolts 3/8 16 UNC for ease of installation. Provides an easy step adjustment of +/- 5° tilt in 2.5° increments. Includes integral bubble level standard (always included). A quick release, tool less entry, single latch, hinged, removable door opens downward to provide access to electronic components and to a terminal block. Door is secured to prevent accidental dropping or disengagement. A clearance of 13" (330mm) at the rear is required in order to remove the door. Complete with a bird guard protecting against birds and similar intruders and an ANSI label to identify wattage and source (both included in box). Housing (including electrical compartment) rated IP54 per ANSI C136.37.

### Light Engine

Composed of 4 main components: LED Module / Optical System / Heat Sink / Driver

Electrical components are RoHS compliant, IP66 sealed light engine equipped with Philips Lumileds LUXEON T LEDs. LEDs tested by ISO 17025-2005 accredited lab in accordance with IESNA LM-80 guidelines in compliance with EPA ENERGY STAR, extrapolations in accordance with IESNA TM-21. Metal core board ensures greater heat transfer and longer lifespan.

**LED Module** (Included), LED type Philips Lumileds LUXEON T. Composed of high performance white LEDs. Color temperature as per ANSI bin 4000 Kelvin nominal (3985K +/- 275K), CRI 70 Min. 75 Typical.

**Optical System:** Composed of high performance optical grade polymer refractor lenses to achieve desired distribution optimized to get maximum spacing, target lumens and a superior lighting uniformity. System is rated IP66. Performance shall be tested per LM-63, LM-79 and TM-15 (IESNA) certifying its photometric performance. Dark Sky compliant with 0% uplight and U0 per IESNA TM-15.

**Heat Sink:** Built in the housing, designed to ensure high efficacy and superior cooling by natural vertical convection air flow pattern always close to LEDs and driver optimising their efficiency and life. Product does not use any cooling device with moving parts (only passive cooling). Wide openings enable natural cleaning and removal of dirt and debris. Entire luminaire is rated for operation in ambient temperature of -40°C / -40°F up to +40°C / +104°F.

# RFL RoadFocus LED Cobrahead, Large

145, 180, 215, and 241W

## Specifications (continued)

**Driver:** High power factor of 90% min. Electronic driver, operating range 50/60 Hz. Auto adjusting universal voltage input from 120 to 277 or 347 to 480 VAC rated for both application line to line or line to neutral, Class I, THD of 20% max.

**(DMG), Dimming compatible 0-10 volts.** The current supplying the LEDs will be reduced by the driver if the driver experiences internal overheating as a protection to the LEDs and the electrical components. Output is protected from short circuits, voltage overload and current overload. Automatic recovery after correction. Standard built in driver surge protection of 2.5kV (min).

### Integrated Features

**DMG:** Dimmable driver 0-10V.

**RCD\*:** Receptacle with 5 pins enabling dimming, can be used with a twist lock Starsense or photoelectric cell or a shorting cap.

**WC10:** 10-year limited warranty from defects in material and workmanship in its intended use, as well as coverage for finish. Visit website for more details.

**SP1:** Surge protection device tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line-Ground, Line-Neutral and Neutral-Ground, and in accordance with DOE MSSLC Model Specification for LED Roadway Luminaires Appendix D Electrical Immunity High test level 10kV/10kA.

*Please note that these integrated features always come with RoadFocus luminaire.*

*\* Use of photoelectric cell or shorting cap is required to ensure proper illumination.*

### Driver and Luminaire Options

**AMPD\*:** Driver pre-programmed for compatibility with Amplit control system.

**AST\*:** Pre-set driver for progressive start-up of the LED module(s) to optimize energy management and enhance visual comfort at start-up.

**CLO\*:** Pre-set driver to manage the lumen depreciation by adjusting the power given to the LEDs offering the same lighting intensity during the entire lifespan of the LED module.

**DALI\*:** Pre-set driver compatible with the DALI control system.

**OTL\*:** Pre-set driver to signal end of life of the LED module(s) for better fixture management.

**CDMG\*:** Dynamimmer standard dimming functionalities including pre-programmed scenarios to suit many applications and needs from safety to maximum energy savings

### Safety Mode:

CDMG525: 4 hours, 25% power dimming

CDMG550: 4 hours 50% power dimming

CDMG575: 4 hours 75% power dimming

### Median Mode:

CDMG25: 6 hours 25% power dimming

CDMG50: 6 hours 50% power dimming

CDMG75: 6 hours 75% power dimming

### Economy Mode:

CDMG25: 8 hours 25% power dimming

CDMG50: 8 hours 50% power dimming

CDMG75: 8 hours 75% power dimming

*\*Not available with HVU (347-480V)*

**FAWS:** Field Adjustable Wattage Selector, pre-set to the highest position, can be easily switched in the field to the required position. This reduces total luminaire wattage consumption and reduces the light level – see the FAWS multiplier chart for more details. **NOTE:** When using FAWS with dimming, set the switch to position 10 (maximum output) to enable dimming.

**SP2:** 20kV / 20kA surge protection device that provides extra protection beyond the SP1 10kV/10kA level.

**RCD7\*:** Receptacle with 7 pins enabling dimming and additional functionality (to be determined), can be used with a twist lock Starsense node or photoelectric cell or a shorting cap.

*Please note: Additional hardware will be required to utilize the additional 2 pins on this receptacle.*

*\* Use of photoelectric cell or shorting cap is required to ensure proper illumination.*

### Luminaire Useful Life

Refer to IES files for energy consumption and delivered lumens for each option. Based on ISTMT in situ thermal testing in accordance with UL1598 and UL8750, Philips System Reliability Tool, Philips Advance data and Philips Lumileds LM-80/TM-21 data, expected to reach 100,000 + hours (72W32LED and 108W48LED at 700mA) or 94,500 hours (108W32LED and 160W48LED at 1050mA) with >L70 lumen maintenance @ 25°C. Luminaire Useful Life accounts for LED lumen maintenance AND all of these additional factors including: LED life, driver life, PCB substrate, solder joints, on/off cycles, burning hours and corrosion.

### Wiring

The connection of the luminaire is done using a terminal block connector 600V, 85A for use with #2 14 AWG. wires from the primary circuit, located inside the housing. Due to the inrush current that occurs with electronic drivers, recommend using a time delay or slow blow fuse to avoid unnecessary and unwanted fuse blowing that can occur with fast acting fuses.

### Hardware

All exposed screws shall be stainless steel with Ceramic primer seal basecoat to reduce seizing of the parts. All seals and sealing devices are made and/or lined with EPDM and/or silicone and/or rubber.

### Finish

Color in accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with  $\pm$  1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard. The surface treatment achieves a minimum of 2000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard.

### LED products manufacturing standard

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with IEC61340-5-1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.

### Vibration Resistance

The RFL meets the ANSI C136.31, American National Standard for Roadway Luminaire Vibration specifications for Bridge/overpass applications. (Tested for 3G over 100,000 cycles by an independent lab)

### Certifications and Compliance

cULus Listed for Canada and USA. Luminaire meets DOE and MSSLC Model Specification for LED Roadway Luminaires. RoadFocus LED Cobrahead luminaires are DesignLights Consortium qualified.

### Limited Warranty

10-year limited warranty. See philips.com/luminaires for details and restrictions.

### Brackets/Arms

For brackets / arms available with this luminaire, see Lumec 3D for details.

