

Revolutionize linear lighting with LED


FLUXSTREAM LED LINEAR

The Philips Day-Brite / Philips CFI FluxStream LED Linear is a new, high performing luminaire delivering smooth diffuse light ideal for light industrial, commercial, and residential applications with the unparalleled energy efficiency of Philips LED light engines.

Benefits

- Exceptional long life up to 5x longer than linear fluorescent¹.
- Ideal for use in cold temperatures.
- Even distribution in continuous row mount applications.
- Up to 33% energy savings compared to linear fluorescent².
- Fluxstream luminaires are Designlights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).




^{1,2} see footnotes on back



PHILIPS
Day-Brite

PHILIPS
CFI

FLUXSTREAM LED LINEAR



Note: 7/8" KO's in each end of luminaire.

Features

- Sleek, compact design for tight spaces
- 50,000hr Rated System Life
100,000hr (L70) LED lumen maintenance
- 80+ CRI
- Enclosed lens enhances visual comfort and protects LED board.
- Individual or continuous row mountable
- Up to 4100 lm per unit
- Acrylic lens shields LED from view
- Dimming & motion sensor options available

FluxStream LED is a new, high performing linear luminaire delivering smooth diffuse light ideal for light industrial, commercial, and residential applications with the unparalleled energy efficiency of Philips LED lighting. Exceptional efficiency, longevity, and aesthetic appeal make it the ideal choice for many applications such as utility, aisle merchandising, back of house, and cold storage.

Ordering guide

example: LF8FR3940USZT

Series	Length	Lens	Lumens ³	Color	Voltage	Driver	Options
<input type="checkbox"/> LF	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
LF FluxStream	4 4' length 8 8' length (nominal)	FR 100% Frost 10 10% Frost	31 3100 lumens ⁴ 39 3900 lumens ⁴ 41 4100 lumens ⁵ (nominal)	40 4000K 35 3500K	U Universal 120/277v 3 347v	LAG LED driver DZT 0-10v dimming SZT Step dimming (100-40)	Refer to spec sheet

1. FluxStream L₇₀ lumen maintenance of 100,000 hours compared to 700 series linear fluorescent at 20,000 hours.
2. LF43940 FluxStream input power is 40.1W compared to a 2xT8T5 strip drawing 63W.
3. Lumen package per 4' nominal length.
4. Only available with **(FR)** 100% frost lens option.
5. Only available with **(10)** 10% frost lens option.



© 2014 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/luminaires

PDb-1301BN 06/14

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
a division of Philips Electronics Ltd.
281 Hillmount Rd,
Markham, ON Canada L6C 2S3
Tel. 800-668-9008