

PHILIPS

Fortimo

LED

Fortimo LED Line 2ft
2200lm 8xx 1R LV4



Datasheet

Fortimo LED Line Gen4

Fortimo LED Line is designed to produce pure white light for general lighting applications with high efficiency levels. The Fortimo LED Line portfolio consists of 2 main ranges of products, which have been differentiated by the number of rows of LEDs on the module. Both ranges feature a variety of different length modules, lumen packages and color temperatures for all the different types of linear luminaires.

Key features and benefits

- State-of-the-art LED module efficiency of up to 186 lm/W
- Long life-time: >50,000 hours
- High color rendering (CRI >80 and >90)
- Excellent color consistency of 3 SDCM
- Choice of color temperatures (3000, 4000 and 5000 K)
- Two module lengths: 1 ft/280 mm or 2 ft/560 mm
- Three lumen packages: 650, 1100, and 2000 lm per foot/280 mm
- LED module range with 1 or 3 rows of LEDs
- Tunable lumen output, efficacy and lifetime
- Push-in connectors enabling automated wiring
- Wide temperature (Tc) range from -40 °C up to +90 °C
- Five year system warranty

May 2017

 Zhaga

Ordering data

Commercial product name	EOC	12NC	Box quantity
Fortimo LED Line 2ft 2200lm 830 1R LV4	8718696 686829 00	9290 015 43306	180
Fortimo LED Line 2ft 2200lm 840 1R LV4	8718696 901601 00	9290 015 43506	180
Fortimo LED Line 2ft 2200lm 850 1R LV4	8718696 901618 00	9290 015 43606	180

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED Line 2ft 2200lm 8xx 1R LV4	408	600	700	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	45	80	80	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)


Fortimo LED Line 2ft 2200lm 830 1R LV4

Parameter	Min	Typ	Max	Unit
Luminous flux	1933	2090	2247	lm
Module efficacy	148	164	180	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.433, 0.400)		-
Color consistency			3	SDCM
CRI	80			
Radiation angle		120		deg
Photobiological safety			RG1	
Energy efficiency label		A++		
$\Delta u'v'$ at 6000 hours			0.007	

R9=7

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	830	lm	lm/W
80% I-nom 326mA	Tc 25 °C	1735	172
	Tc-nom 45 °C	1696	169
	Tc-life 80 °C	1620	163
I-nom 408mA	Tc 25 °C	2139	167
	Tc-nom 45 °C	2090	164
	Tc-life 80 °C	1996	158
I-life 600mA	Tc 25 °C	3047	157
	Tc-nom 45 °C	2977	154
	Tc-life 80 °C	2840	149




Fortimo LED Line 2ft 2200lm 840 1R LV4

Parameter	Min	Typ	Max	Unit
Luminous flux	2035	2200	2365	lm
Module efficacy	155	173	190	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.383, 0.375)		-
Color consistency			3	SDCM
CRI	80			
Radiation angle		120		deg
Photobiological safety			RG1	
Energy efficiency label		A++		
$\Delta u'v'$ at 6000 hours			0.007	

R9=6

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	840	lm	lm/W
80% I-nom 326mA	Tc 25 °C	1826	181
	Tc-nom 45 °C	1785	178
	Tc-life 80 °C	1705	172
I-nom 408mA	Tc 25 °C	2251	176
	Tc-nom 45 °C	2200	173
	Tc-life 80 °C	2101	167
I-life 600mA	Tc 25 °C	3208	165
	Tc-nom 45 °C	3134	162
	Tc-life 80 °C	2991	157




Fortimo LED Line 2ft 2200lm 850 1R LV4

Parameter	Min	Typ	Max	Unit
Luminous flux	2055	2222	2389	lm
Module efficacy	157	174	192	lm/W
Correlated color temperature (CCT)		5000		K
Color coordinates (CIEx, CIEy)		(0.345, 0.352)		-
Color consistency			3	SDCM
CRI	80			
Radiation angle		120		deg
Photobiological safety			RG1	
Energy efficiency label		A++		
$\Delta u'v'$ at 6000 hours			0.007	

R9=8


Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	850	lm	lm/W
80% I-nom 326mA	Tc 25 °C	1844	182
	Tc-nom 45 °C	1803	179
	Tc-life 80 °C	1722	173
I-nom 408mA	Tc 25 °C	2274	177
	Tc-nom 45 °C	2222	174
	Tc-life 80 °C	2122	168
I-life 600mA	Tc 25 °C	3241	167
	Tc-nom 45 °C	3166	164
	Tc-life 80 °C	3022	158



Beam shape

The Philips LED module generates a Lambertian beam shape, which is a pragmatic starting point for OEMs wishing to design secondary optics.



Electrical characteristics

[Fortimo LED Line 2ft 2200lm 830 1R LV4](#)
[Fortimo LED Line 2ft 2200lm 840 1R LV4](#)
[Fortimo LED Line 2ft 2200lm 850 1R LV4](#)


Parameter	Min	Typ	Max	Unit
Forward voltage	30.2	31.2	32.2	V
Power consumption	12.3	12.7	13.2	W
Number of modules in parallel per chain			2	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%
 Specifications stated at Tc-nom and I-nom
 Bins D and I

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
600	143	94
490	118	97
408	100	100
367	91	101
326	81	103
285	72	105
245	62	106
204	52	108



Flux and efficacy versus temperature at Tc (at I nominal)

Tcase [°C]	Flux [%]	Efficacy [%]
80	96	97
45	100	100
25	102	102
0	105	103



Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% I-nom 326mA	Tc 25°C	>70	>70	>70	>70	>70	>70	36	35	34
	Tc-nom 45°C	>70	>70	>70	64	63	61	30	29	29
	Tc-life 80°C	70	70	68	45	43	42	21	21	20
I-nom 408mA	Tc 25°C	>70	>70	>70	>70	70	69	34	33	32
	Tc-nom 45°C	>70	>70	>70	61	58	57	28	28	27
	Tc-life 80°C	68	65	64	42	41	40	20	19	19
I-life 600mA	Tc 25°C	>70	>70	>70	66	64	62	31	30	29
	Tc-nom 45°C	>70	>70	>70	55	53	52	26	25	25
	Tc-life 80°C	61	59	58	35	37	36	18	17	17

Values in the table are based on available LM80 LED data (12000 hours). Lumen maintenance will be updated once additional measurement data becomes available.


Thermal switching table

Calculated number of switches at which the survival rate of the population $\geq 90\%$, at a given ambient temperature and delta T with respect to Tc (where $T_c = T_{\text{ambient}} + \Delta T$)


		Tambient [°C]											
		-40	-30	-20	-10	0	10	20	30	40	50	60	70
delta T [°C] (delta T = Tc - Tambient)	10	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k
	20	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	X
	30	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	X	X	X
	40	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	> 100 k	X	X	X	X
	50	57 k	57 k	57 k	57 k	57 k	57 k	57 k	X	X	X	X	X
	60	28 k	28 k	28 k	28 k	28 k	28 k	X	X	X	X	X	X
	70	16 k	16 k	16 k	16 k	16 k	X	X	X	X	X	X	X
	80	10 k	10 k	10 k	10 k	X	X	X	X	X	X	X	X
	90	6 k	6 k	6 k	X	X	X	X	X	X	X	X	X
	100	4 k	4 k	X	X	X	X	X	X	X	X	X	X

Lumen maintenance graphs

Lumen maintenance at I-life and Tc-life conditions




Lumen maintenance for B50 at current I-life conditions



Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.33...0.5	mm ²	stranded wire
	20...22	AWG	stranded wire
Input wire strip length	7.5...8.5	mm	
Input wire cross-section	0.33...0.75	mm ²	solid, fused, stranded
	18...22	AWG	solid, fused, stranded
Input wire strip length	7.5...8.5	mm	




More information in the design-in guide of LED Linear modules.

Mechanical characteristics

Fortimo LED Line 2ft 2200lm 830 1R LV4
 Fortimo LED Line 2ft 2200lm 840 1R LV4
 Fortimo LED Line 2ft 2200lm 850 1R LV4

Parameter	Min	Typ	Max	Unit
Length	560.2	560.7	561.2	mm
Width	39.5	40	40.5	mm
Height excl. connector	4.19	4.29	4.39	mm
Height incl. connector	5.6	5.8	6	mm
Warpage (IPC-TM-650)			0.75	%



Absolute ratings

Parameter	Min	Typ	Max	Unit
Current through the LED module (I-max)			700	mA
Case temperature (Tc-max)			80	°C
Power at rated Vf-max and I-max			24.2	W
ESD (direct contact)			8	kV
ESD (air)			15	kV
Working voltage			120	V _{dc}
Voltage strength	1240			V _{ac}
Ambient temperature	-40			°C

Application information

Certificates and Standards

IEC/TR 62278:2014

IEC 62384

IEC 62031:2008 (First Edition) + A1:2012 + A2:2014

Relevant clauses of EN 62471:2008 (With IEC/TR 62471-2: 2009 and IEC/TR 62778: 2014)

UL 8750

ENEC+

CE

ENEC

Zhaga

Compliant*

*L56W4

Application

IP rating	No IP-rating
Overheating protection	No protection
Luminaire class	IEC Class I and IEC Class II
Dimming	Yes



© 2017 Philips Lighting Holding B.V. All rights reserved.

This document contains information relating to the Philips Lighting portfolio, intended for companies who may be interested in developing their product offering. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

www.philips.com/technology

05/2017