


DTC602 Timeclock Astronomical 365 day timeclock

The DTC602 timeclock is used to automate programmed tasks and events on a DyNet network. The DTC602 is suitable for, but not limited to, North American, South American, Australian and New Zealand markets

- Advanced clock controls Features sunrise/ sunset tracking and automatic adjustment for daylight saving.
- Performs as an energy management controller — Uses powerful macro and conditional logic functions to perform full automation of large commercial projects, where automatic lighting events are required at predetermined times.
- Sets the operating mode of other devices on the network — Can be used to set the operating mode of multifunction sensors, giving priority to IR, PIR or PE facilities, depending on the time of day or day of the week.
- Local or remote operation Programming and operation is possible either locally, utilizing the front panel LCD display and keypad, or remotely via a PC.
- PIN protected Prevent unauthorized system changes through use of PIN password protection.
- Used as a system programmer The timeclock can be used to program system changes, guiding the user step-by-step through the programing task. Channel, area and preset scene names are automatically uploaded from the network.



For detailed product information, please refer to the product information pages at www.philips.com/lightingcontrolsna.



Specifications

Due to continuous improvements and innovations, specifications may change without notice.

ltem	Specification	Details
Hardware	DyNet DC Supply	24 V @ 35 mA (max.) /12V @ 50mA from the DyNet network
	Control Inputs/Outputs	One RS-485 DyNet serial port
	User Controls	One 122 x 32 pixel rear lit LCD display One 12 button LCD transport keys One 12 button numeric keypad
	Clock	365 day clock Battery backup Sunrise/sunset tracking Automatic daylight saving adjustment 250 timed events 64 tasks
	Memory	All data stored in 100 year life EEPROM
Physical	Dimensions $(H \times W \times D)$	4.4" x 6.4" x 0.9" (133 mm x 162 mm x 24 mm)
	Packed Weight	0.5 lbs (0.2 kg)
	Construction	0.06" (1.6 mm) stainless steel faceplate/body
	Operating Conditions	Temperature: 32 to 122° F (0 to 50° C) ambient Humdity: 10 to 90% non-condensing
	Storage & Transport	Temperature: -13 to 140° F (-25 to 60° C) ambient Humidity: 0 to 90% non-condensing
Certification	Certification	FCC, ICES, RoHS Compliant
Options & Ordering	Standard Product CAT5/CAT6 Wiring Adapter	DTC602 (Philips 12NC - 913703074109) DRJ45ADAPT
		FC



Philips Lighting North America 200 Franklin Square Dr Somerset, NJ, United States Tel: 1-800-526-2731 Email: controls.support@philips.com Web: www.philips.com/lightingcontrolsna

Philips Lighting Canada 281 Hillmount Road Markham, Ontario L6C 2S3 Canada Specifications subject to change without notice. ©WMGD Pty Ltd Trading as Dynalite. Unit 6, 691 Gardeners Road Mascot 2020 Australia. ABN 33 097 246 921. All rights reserved. Dynalite, DyNet and associated logos are the registered trademarks of WMGD Pty Ltd. Not to be reproduced without permission.