



Page 1 of 2 Basic Wall Washer





#### **Ordering Information**

Catalog No.	Mountings	Finish	Lamps
6310	All Lytespan Track Systems	Matte White	100W R30
			75W PAR30

#### **Features**

- 1. Lytespan Attachment Fitting: die-cast zinc alloy.
- 2. Lever: locks attachment fitting electrically and mechanically anywhere
- 3. Housing: .040" aluminum.
- 4. Reflector: embossed texture; anodic processed aluminum.
- 5. Movable Brass Contact: extends for connection to 2nd circuit in Advent
- 6. Polarity Keyway
- 7. Swivel: die-cast zinc alloy. 90° vertical x 350° horizontal adjustment.

### **Options & Accessories**

Porcelain socket, medium base, nickel plated screw shell. No. 18 braided SF-1 leads.

#### **Finish**

All painted finishes baked enamel.

#### Labels

UL, I.B.E.W.

Job Information	Туре:
Job Name:	
Cat. No.:	
Lamp(s):	
Volts/Ballast:	

Lightolier a Genlyte company www.lightolier.com 631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710 We reserve the right to change details of design, materials and finish. © 2005 Genlyte Group LLC • B1005


Page 2 of 2 Basic Wall Washer

# **Lighting Data**

**EXAMPLE:** With multiple 75 watt R30 FL units located 2" from wall, 2" on center and aimed 60° from horizontal, the illumination on the wall 3" down from the ceiling is 52 footcandles beneath fixtures and 49 footcandles between fixtures.

Footcandles are average and rounded off and are based on a minum of five units.

For 100W R30 FL, multiply footcandles by



# Footcandles on Wall from Multiple Units ñ 75W R30 FL TRACK 2 FEET FROM WALL

		<b>←</b> 2" <b>→</b>	<b>──</b> 2" <b>──</b>		3"──				
		60°	Ċ		Ů	Ů		Ò	
Distance From Ceiling	1"		79	71	79	65	35	65	
	2"		78	65	78	60	37	60	
	3"		52	49	52	38	29	38	
	4"		29	31	29	21	21	21	
	5"		17	17	17	11	12	11	
	6"		12	13	12	8	8	8	
	7"		7	7	7	4	5	4	
Dis	8"		5	5	5	3	3	3	
	9"		4	5	4	3	3	3	

## TRACK 3 FEET FROM WALL

	<b>←</b> 3" <b>→</b>	<b>──</b> 3" <b>──</b>			<b>◄</b> —4"——		
	60°	Ů		Ů	Ď	Ů	
1"		34	32	34	29 17 2	<u> 29</u>	
2"		36	30	36	29 25 2	29	
3"		34	26	34	27 21 2	27	
4"		24	22	24	19 17 1	19	
5"		17	16	17	14 11 1	14	
6"		11	10	11	8 7	8	
7"		8	8	8	5 5	5	
8"		5	6	5	4 5	4	
9"		5	6	5	4 3	4	
	I				I		

Job Information

Type:

Lightolier a Genlyte company www.lightolier.com
631 Airport Road, Fall River, MA 02720 ◆ (508) 679-8131 ◆ Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
© 2005 Genlyte Group LLC ◆ B1005