
PHILIPS ADVANCE

LED Driver

Xitanium SR

150W 120-277V 0.7A SR XI150C070V235VSF1



The Philips Advance Xitanium SR LED driver can help reduce complexity and cost of


light fixtures used in wireless connected lighting systems. It features a standard digital interface to enable direct connection to SR-certified components. Functionality that ordinarily would require additional auxiliary components is integrated into the driver. The result is a simple, cost-effective light fixture that can enable every fixture to become a wireless node.

Specifications

				Efficiency@	Max.			Inrush			Surge		
Input	Output	Output	Output	Max. Load	Case	Input	Max. Input	Current		Power	Protection		Envir.
Voltage	Power	Voltage	Current	and 70°C	Temp.	Current	Power	(Apk/10%-	THD @	Factor @	Common/	Weight	Protection
(Vrms)	(W)	(V)	(A)	Case	(°C)	(Arms)	(W) ¹	μs)	Max. Load	Max. Load	Diff (KV)	(Lbs/kgs)	Rating
120	150	78-235	0.07-0.70	91	80	1.5	180	54 / 280	<10%	>0.95	6/6	2.1/0.95	UL damp
277	150	70-233	0.07-0.70	93	180	0.65	100	133 / 270	10%	70.93	0,0	2.1/0.93	& dry


Enclosure

	In. (mm)
Case Length	8.38 (211.1)
Case Width	2.35 (59.1)
Case Height	1.49 (37.6)
Mounting Length	9.0 (226.2)
Mounting Width	1.7 (42.9)
Overall Length	9 54 (240 5)



Based on 1W load from SR power supply and 6.2W load from auxiliary power supply.

Wiring Diagram



Input and output use lead-wires.

Lead-wires are 18AWG 105C/600V solid copper per UL1452.

Lead length outside enclosure: 270 mm (±30mm) on all wires.

Dimming	Dimming Range	Minimum Output Current (A)	
DALI	10% ~ 100%	0.070	

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Features

- · Compatible with SR-certified devices
- Standard digital interface including integral power supply
- 24VDC auxiliary power supply for higher power device requirements
- · Accurate power metering
- Logic signal input
- Drive current setting via SimpleSet
- 5-year limited warranty¹

Benefits

- Enables interoperability with multiple sensor/network system vendors
- Reduces cost and complexity of outdoor connected lighting systems²
- Eliminates need for high-voltage relays to increase system reliability
- 2% metering accuracy meets proposed ANSI standard C136.52
- Can be used with standard motion sensors for local control to complement network control

Application

- Area
- · Roadway
- · Parking garages
- Floodlights

Product Data

Ordering Information	
Order Code	XI150C070V235VSF1
Full Product Code	XI150C070V235VSF1M (Mid-pack, 10pcs/box)
Full Product Name	XITANIUM 150W 0.7A 120-277V SR
Net Weight Per Piece	0.95 KG / 2.1 lbs
Input Information	
Inrush Current	Per NEMA 410
Line Voltage (AC operation)	120-277VAC +/- 10%
Line Current	1.50A @ 120V, 0.65A @ 277V
Line Frequency	50/60Hz
Surge Protection	Refer to table
Output Information	
Output Voltage Range	78VDC to 235VDC
Output Current Range	0.07A to 0.70A
Output Current Ripple	<15% at max. lout (ripple = pk-avg/avg) Low frequency (<120 Hz) content <1%
Output Current Tolerance	±5% at max. output current
Open Circuit Voltage	310VDC max.
Protections	Short Circuit and Open Circuit Protection for LED + and LED-
Features	
AOC (adjustable output current)	0.07A to 0.70A via SimpleSet programming (refer to graphs and notes)
Life @ TC 80°C	50000 hr [nom] (refer to graphs)
Suitable for Outdoor Use?	Yes
Interfaces	AOC via SimpleSet or SR using MultiOne, SR, Logic Signal Input (LSI), Auxiliary Power Supply
Min. Ambient Temp	-40°C
Max. Case Temperature (Tcase)	80°C
Input Over-voltage	Can survive input over-voltage stress of 320VAC for 48 hours and 350VAC for 2 hours
Earth Leakage Current	0.75 mA [max.]
THD Total	Refer to graph

^{1.} View limited warranty at www.philips.com/warranties for details and restrictions.

^{2.} Functionality that ordinarily would require additional auxiliary components is integrated into the driver.

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


Product Data (continued)

Power Factor	Refer to graph				
Efficiency	Refer to table				
Power Reporting Accuracy	± 2% in performance window and under nominal operating conditions				
SR Interface					
Digital Protocol	Detailed specifications available to SR-Certified Partners				
SR Power Supply	Detailed specifications available to SR-Certified Partners				
Auxiliary Power Supply					
Power	3W continuous, 10.5W peak for 1.2ms				
Voltage	24V+/-10%				
Ripple	300mV peak-peak for resistive load				
Protection	Overload and short circuit protected				
Last Gasp Energy	200mJ typ.				
Logic Signal Input (LSI)					
Dry Contact Input	Yes				
Logic Low	<3V or open				
Logic High	>7V				
Max. Current Draw	2mA				
Environment & Approbation					
Agency Approbations	UL8750, UL1310, UL935, CSA-C22.2 No. 250.13-12, CSA C22.2 No. 223				
Audible Noise	<24dB Class A				
Isolation Between Output and Input	Refer to table				
Isolation of Controls	Refer to table				
EMC (electromagnetic compliance)	Meets FCC 47 Part 15 Class A				
Envir. Protection Rating	UL Dry & Damp				

Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Logic Signal Input (LSI) Characteristics (Typical)




Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Operating Window

The driver current cutback feature provides for an increased output voltage with a reduced output current during abnormal LED operation, such as cold weather starting. Output tolerance +/-5%.




Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.

Dimming Characteristics


Dimming is accomplished through the two-wire SR connection to the sensor. DALI standard IEC62386_207 Edition 1 defines the linear dimming curve, as well as the command for switching between logarithmic and linear curves. Only a linear dimming curve is utilized.




Performance Characteristics

Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification. Data below at 70°C Tcase.

Efficiency Vs. Output Voltage @ 120VAC




Efficiency Vs. Output Voltage @ 277VAC




Performance Characteristics

Based on measurements on a typical sample. The accuracy of the measurements is within the tolerance of the measurement instruments. The graphs are meant to be a guideline and not a specification. Data below at 70°C Tcase.

Power Factor Vs. Output Power




Total Harmonic Distortion Vs. Output Power




Electrical Specifications

All the specifications are typical and at 25°C Tcase unless specified otherwise.


Output Current Vs. Driver Case Temperature



Driver Lifetime Vs. Driver Case Temperature



Inrush Current Info



Vin	Ipeak	T (@ 10% of Ipeak)	
120 Vac	54A	280µs	
277 Vac	133A	270µs	

Inrush current is measured at peak of the corresponding line voltage, source impedance per NEMA 410.

Lightning Surge Info

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)
1.2/50µs Combination	6kV	6kV
Wave (w/t 2Ω)		

Isolation

Isolation	Input Leads	Output Leads	SR Leads (SR+, SR-/ SGND, AUX, and LSI), Class 2 Only	Enclosure
Input Leads	NA	2xU+1kV	2xU+1kV	2xU+1kV
Output Leads	2xU+1kV	NA	2xU+1kV	2xU+1kV
SR Leads (SR+, SR-/SGND, AUX, and LSI), Class 2 Only	2xU+1kV	2xU+1kV	NA	2xU+1kV
Enclosure	2xU+1kV	2xU+1kV	2xU+1kV	NA

U = Max. input voltage





Philips Lighting North America Corporation 10275 W. Higgins Road, Rosemont IL 60018 Tel: 800-322-2086 Fax: 888-423-1882 Customer/Technical Service: 800-372-3331 OEM Support: 866-915-5886