



PHILIPS

RESPIRONICS

DreamStation

CPAP

Designed to **empower patients** and facilitate CPAP therapy adoption

DreamStation CPAP features

- Fixed CPAP therapy mode
- C-Flex
- **NEW** - Smart Ramp : 0 to 45 min
- **NEW** - Performance Check
- Mask fit check
- On-board memory
- **NEW** - remote monitoring solution via Bluetooth®
- Oximetry module (optional) to monitor therapy efficacy

Humidification

- Active humidification controlled by the room environment
- Pre-heat humidifier capable
- Heated tube (optional)

DreamStation CPAP Pro benefits

- **Daily Progress Feedback** displays a simple trend of patients' nightly use to help track progress on the path to adherence.
- **Connectivity** and remote monitoring options including a standard integrated Bluetooth module
- **Performance Check** simplifies in-home device evaluation for easy remote troubleshooting
- **Patient' data management** through detailed compliance reports

DreamStation CPAP Pro specifications

Part number	Description
INX200S15	DreamStation CPAP with SD card
INX200H15	DreamStation CPAP with humidifier and SD card
INX200T15	DreamStation CPAP with humidifier, heated tube and SD card

Specifications

Therapy modes	CPAP
Therapy features	C-Flex
Flex pressure relief	0 to 3
Pressure range	4-20 cm H ₂ O
Smart Ramp time	0 to 45 min (5-min increments)
Starting ramp pressure	Patient adjustable
Humidification	Heated humidification: fixed, adaptive, heated tube modes Heated tube (optional)
Device controls	Color LCD/control wheel/push button
LCD backlight control	Ambient light sensor
Filters	Reusable pollen and disposable ultra-fine
Data storage capacity (minimum)	Display: compliance 1 day, 7-day, 30-day averages SD card > 1 year On-board: up to 6 months
Altitude compensation	Automatic
Warranty	2 years
Dimensions	15,7 (L) x 19,3 (W) x 8,4 cm (H) (without humidifier) 29,7 (L) x 19,3 (W) x 8,4 cm (H) (with humidifier)
Weight	1,33 kg (without humidifier), 1,98kg (with humidifier) but including power supply
Power supply	80W/12V/6,67A
Electrical requirements	100-240 VAC, 50/60 Hz, 2.0-1.0 A

Sleep therapy accessories

Humidification	Part number
DreamStation heated humidifier	EUXH
Water chamber	1122520

Tubing	Part number
Heated tube (15mm)	HT15
Standard tube (15mm)	PR15

Filters	Part number
Pollen (foam) filter, reusable (1/pack)	1122446
Ultra-fine filter, disposable (1/pack)	1122447
Ultra-fine filter, disposable (2/pack)	1122518
Ultra-fine filter, disposable (6/pack)	1122519

Accessories	Part number
DreamStation carrying case	1121162
DreamStation link module	1120293
DreamStation SpO ₂ module	1121694
Reuseable finger sensor (clip)	936
Oximetry finger sensor, Adult, Flex	953
Flexiwrap, sens tape, Adult (25/pack)	954A
Reuseable finger sensor (soft), medium	1062050
Reuseable finger sensor (soft), small	1062051
DreamStation, 80W power supply	1118499

