

European Union September 2018

Phase out of halogen bulbs and candles

The process of gradual phase out of inefficient, energy-consuming electrical devices has been continuing in Europe for a few years already. Lighting is a part of it, and many halogen lamp types are gradually being phased out from the European market. However, not every type of halogen lamp is being banned from the European market at the same time.

The changes in EU lighting legislation are being implemented gradually, so that sufficient choice of energy saving alternative products is available.





What does it mean for **halogen products** from September 2018 onwards

On 1st September 2018, mains voltage halogen non-directional lamps (bulbs and candles) will not fulfil EU eco-design requirements.* This means that they can no longer be produced or imported for resale into the EU. Any remaining halogen bulbs and candles on commercial stock can still be sold out after this date.

* Stage 6 DIM1 (Commission Regulation (EU) 2015/1428 of 25 August 2015 amending Commission Regulation (EC) No 244/2009 with regard to ecodesign requirements for non-directional household lamps)

Is this a reason for concern? Absolutely not!


Philips offers a compelling range of LED alternatives to replace the banned 230–240 V halogen bulb and candle lamps. LED bulbs and candles come in a wide variety of shapes, finishes, colors and price points acceptable by local markets. Moreover, most LED bulbs and candles come in both a dimmable and non-dimmable version, and with a choice of packaging types.

In this leaflet you will find our recommended LED replacements for the halogen bulbs and candles.

Some types of halogen lamps: like capsules, linear, low voltage reflectors lamps - will still be available and can be sold in EU.

See also the overview below.

Legislation overview for Halogen lamps



All impacted lamps are being upgraded to comply

Below lamps are impacted by the third stage of the ErP legislation. Here you will find our recommended, efficient and cost-effective upgrades and / or LED replacements for the impacted lamps.

E27 A55



Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

18 W - A55

18W E27 230V A55 1CT/15 SRP	8718291701163	871829170116301
-----------------------------	---------------	-----------------

28 W - A55

28W E27 230V A55 1CT/15 SRP	8727900252774	872790025277405
28W E27 240V A55 1CT/15 SRP	8727900252835	872790025283501

42 W - A55

42W E27 230V A55 1CT/15 SRP	8727900251715	872790025171506
-----------------------------	---------------	-----------------

53 W - A55

53W E27 230V A55 1CT/15 SRP	8727900251722	872790025172205
-----------------------------	---------------	-----------------

70 W - A55

70W E27 230V A55 1CT/15 SRP	8727900252255	872790025225506
-----------------------------	---------------	-----------------

105 W - A55

105W E27 230V A55 1CT/15 SRP	8727900252262	872790025226200
------------------------------	---------------	-----------------

140 W - A55

140W E27 230V A55 1CT/15 SRP	8727900252552	872790025255200
------------------------------	---------------	-----------------

LED bulb



CLA LED bulb 40W	CLA LED bulb 60W	CLA LED bulb 75W	CLA LED bulb 100W	CorePro LED bulb 120W	CorePro LED bulb 150W
------------------	------------------	------------------	-------------------	-----------------------	-----------------------

CLA LED bulb 40W	CLA LED bulb 40W	CLA LED bulb 60W	CLA LED bulb 60W	MAS LEDbulb	CLA LED bulb 100W
------------------	------------------	------------------	------------------	-------------	-------------------

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

No LED alternative available

CLA LED bulb

ND 4.3-40W E27 827 A60 CL	929001890002	871869680867200
---------------------------	--------------	-----------------

CLA LED bulb

ND 7-60W E27 WW A60 CL	929001387302	871869674273000
------------------------	--------------	-----------------

CLA LED bulb

ND 8-75W E27 827 A60 CL	929001888902	871869680951800
-------------------------	--------------	-----------------

CLA LED bulb

ND 11-100W E27 827 A67 CL	929001889202	871869680959400
---------------------------	--------------	-----------------

CorePro LED bulb

ND 18.5-120W E27 827 A67	929001313202	871869670167600
--------------------------	--------------	-----------------

CorePro LED bulb

ND 19.5-150W A67E27 827	929001892402	871869681385000
-------------------------	--------------	-----------------

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

No LED alternative available

CLA LED bulb

DT 5.5-40W A60 E27 CL	929001893902	871869681075000
D 5.5-40W A60 E27 827 CL	929001331002	871869670940500

CLA LED bulb

DT 8.5-60W A60 E27 CL	929001894102	871869681079800
D 8-60W A60 E27 827 CL	929001331202	871869670944300

MAS LEDbulb

DT 11-75W A67 E27 827 FR	929001200502	871869655551400
--------------------------	--------------	-----------------

MAS LEDbulb

DT 15-100W A67 E27 827 FR	929001184402	871869655555200
DT 15.5-100W E27 927-922 A67FR	929001868702	871869682620100

CLA LED bulb

D 12-100W A67 E27 827 CL	929001882902	871869680631900
--------------------------	--------------	-----------------

Dimmable not available. Select a non dimmable offer.

Dimmable not available. Select a non dimmable offer.

LED bulb alternatives

B22 A55



Halogen

Phase out GPC (12nc) EOC

28 W - A55

28W B22 230V A55 CL 2BC/10 8718291202820 871829120282000

42 W - A55

42W B22 230V A55 1CT/15 SRP 8727900942644 872790094264403

53 W - A55

53W B22 230V A55 1CT/15 SRP 8727900942668 872790094266801

70 W - A55

70W B22 240V A55 1CT/15 SRP 8727900251890 872790025189002

LED bulb



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED bulb

ND 4.3-40W B22 827 A60 CL 929001890102 871869680869600

CLA LED bulb

ND 7-60W B22 WW A60 CL 929001387402 871869674277800

Non dimmable not available. Select a dimmable offer.

Non dimmable not available. Select a dimmable offer.



Dimmable

LED recommendation GPC (12nc) EOC

CLA LED bulb

D 5-40W A60 B22 827 CL 929001331102 871869670942900

CLA LED bulb

D 8-60W A60 B22 827 CL 929001331302 871869670946700

MAS LEDbulb

DT 11-75W A67 B22 827 FR 929001200402 871869655553800

MAS LEDbulb

DT 15-100W A67 B22 827 FR 929001200302 871869655557600

E27 G95



Halogen

Phase out GPC (12nc) EOC

42 W - G95

42W E27 230V G95 CL 1CT/6 SRP 8727900921007 872790092100701

LED bulb



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED bulb

ND 7-60W E27 WW G93 CL 929001387902 871869674271600



Dimmable

LED recommendation GPC (12nc) EOC

CLA LED bulb

D 8-60W G93 E27 827 CL 929001895702 871869681431400

LED candle alternatives

B15 B35



CLA LED candle 25W

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

18 W - B35

18W B15 240V B35 1CT/15 SRP	8718291219453	871829121945301
-----------------------------	---------------	-----------------

LED candle



CLA LED candle 25W

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CLA LED candle

ND 2-25W B35 B15 827 CL	929001815502	871869676688000
-------------------------	--------------	-----------------

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

Dimmable not available. Select a non dimmable offer.

E14 B35



B35

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

18 W - B35

18W E14 230V B35 1CT/15 SRP	8727900820546	872790082054604
-----------------------------	---------------	-----------------

28 W - B35

28W E14 230V B35 1CT/15 SRP	8727900252651	872790025265106
-----------------------------	---------------	-----------------

28W E14 240V B35 1CT/15 SRP	8727900252712	872790025271203
-----------------------------	---------------	-----------------

42 W - B35

42W E14 230V B35 1CT/15 SRP	8727900820584	872790082058402
-----------------------------	---------------	-----------------

LED candle



CLA LED candle 25W



CLA LED candle 40W

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CLA LED candle

ND 2-25W B35 E14 827 CL	929001238302	871869657407200
-------------------------	--------------	-----------------

CLA LED candle

ND 4.3-40W E14 827 B35 CL	929001889702	871869680853500
---------------------------	--------------	-----------------

Non dimmable not available. Select a dimmable offer.



MAS LEDcandle 25W-40W

CLA LED candle 40W

MAS LEDcandle 60W

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

MAS LEDcandle

DT 4-25W E14 B38 CL	929001139802	871869645368100
---------------------	--------------	-----------------

MAS LEDcandle

DT 6-40W E14 B38 CL	929001140402	871869645350600
---------------------	--------------	-----------------

CLA LED candle

D 5-40W B35 E14 827 CL	929001332102	871869670982500
------------------------	--------------	-----------------

MAS LEDcandle

DT 8-60W B40 E14 827 CL	929001211702	871869655599600
-------------------------	--------------	-----------------

LED candle alternatives

B22 B35



Halogen

Phase out GPC (12nc) EOC

18 W - B35

18W B22 240V B35 1CT/15 SRP 8727900862645 872790086264502

28 W - B35

28W B22 230V B35 CL 2BC/10 8718291202868 871829120286800

LED candle



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED candle

ND 2-25W B35 B22 827 CL 929001815602 871869676690300

CLA LED candle

ND 4.3-40W B22 827 B35 CL 929001889902 871869680857300



Dimmable

LED recommendation GPC (12nc) EOC

MAS LEDcandle

DT 4-25W B22 B38 CL 929001140202 871869670065500

MAS LEDcandle

DT 6-40W B22 B38 CL 929001140802 871869645362900

E14 BW35




Halogen

Phase out GPC (12nc) EOC

18 W - BW35

18W E14 230V BW35 1CT/15 SRP 8727900820669 872790082066901

LED candle



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED candle

ND 2-25W ST35 E14 827 CL 929001238502 871869657411900

Dimmable

LED recommendation GPC (12nc) EOC

Dimmable not available. Select a non dimmable offer.

E14 BXS35



Halogen

Phase out GPC (12nc) EOC

18 W - BXS35

18W E14 230V BXS35 1CT/10 SRP 8718291204435 871829120443501

28 W - BXS35

28W E14 230V BXS35 1CT/10 SRP 8727900925067 872790092506701

LED candle



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED candle

ND 2-25W BA35 E14 827 CL 929001238402 871869657409600

Non dimmable not available. Select a dimmable offer.



Dimmable

LED recommendation GPC (12nc) EOC

MAS LEDcandle

DT 4-25W E14 BA38 CL 929001139902 871869645376600

MAS LEDcandle

DT 6-40W E14 BA38 CL 929001140502 871869645354400

LED lustre alternatives

E14 P45



Halogen

Phase out GPC (12nc) EOC

18 W - P45

18W E14 230V P45 1CT/15 SRP 8727900831443 872790083144304

28 W - P45

28W E14 230V P45 1CT/15 SRP 8727900831467 872790083146704

28W E14 240V P45 1CT/15 SRP 8727900835793 872790083579304

42 W - P45

42W E14 230V P45 1CT/15 SRP 8727900831481 872790083148101

LED lustre



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED lustre

ND 2-25W P45 E14 827 CL 929001238602 871869657413300

CLA LED lustre

ND 4.3-40W E14 827 P45 CL 929001890402 871869680971600

Non dimmable not available. Select a dimmable offer.



Dimmable

LED recommendation GPC (12nc) EOC

MAS LEDlustre

DT 4-25W E14 P48 CL 929001140002 871869645378000

CLA LED lustre

D 2.7-25W P45 E14 827 CL 929001332302 871869670986300

MAS LEDlustre

DT 6-40W E14 P48 CL 929001140602 871869645358200

CLA LED lustre

D 5-40W P45 E14 827 CL 929001332502 871869670990000

MAS LEDlustre

DT 8-60W P50 E14 827 CL 929001211902 871869658067700

E27 P45



Halogen

Phase out GPC (12nc) EOC

18 W - P45

18W E27 230V P45 1CT/15 SRP 8727900831382 872790083138204

28 W - P45

28W E27 230V P45 1CT/15 SRP 8727900831405 872790083140504

28W E27 240V P45 1CT/15 SRP 8727900863000 872790086300004

42 W - P45

42W E27 230V P45 1CT/15 SRP 8727900831429 872790083142901

LED lustre



Non dimmable

LED recommendation GPC (12nc) EOC

CLA LED lustre

ND 2-25W P45 E27 827 CL 929001238702 871869657415700

CLA LED lustre

ND 4.3-40W E27 827 P45 CL 929001890502 871869680973000

No LED alternative available



Dimmable

LED recommendation GPC (12nc) EOC

MAS LEDlustre

DT 4-25W E27 P48 CL 929001140202 871869670065500

CLA LED lustre

D 2.7-25W P45 E27 827 CL 929001332402 871869670988700

MAS LEDlustre

DT 6-40W E27 P48 CL 929001140702 871869645360500

CLA LED lustre

D 5-40W P45 E27 827 CL 929001332602 871869670992400

No LED alternative available

LED lustre alternatives

P45

▶ LED lustre



Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

18 W - P45

18W B22 230V P45 CL 2BC/10	8718291691013	871829169101301
----------------------------	---------------	-----------------

42 W - P45

42W B22 240V P45 1CT/15 SRP	8727900862980	872790086298002
-----------------------------	---------------	-----------------



CLA LED
lustre 25W

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CLA LED lustre

ND 2-25W P45 B22 827 CL	929001815902	871869676696500
-------------------------	--------------	-----------------

No LED alternative available



CLA LED
lustre 25W

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CLA LED lustre

ND 2-25W P45 B22 827 CL	929001815902	871869676696500
-------------------------	--------------	-----------------

No LED alternative available

LED bulb alternatives

T25



Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

18 W - T25

18W E14 230V T25L1CT/20 SRP	8718291223030	871829122303001
-----------------------------	---------------	-----------------

28 W - T25

CH 28W E14 230V T25L1CT/20 SRP	8718291223481	871829122348104
--------------------------------	---------------	-----------------

▶ LED bulb



Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

LED

3.2-25 T25 E14 WW FR ND SRT4	929001325801	871869670313700
------------------------------	--------------	-----------------

▶ No LED alternative available

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

▶ Dimmable not available. Select a non dimmable offer.

▶ No LED alternative available

LED spot alternatives

Spot



Hal-Twist 2y

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

25 W - Hal-Twist 2y

25W GU10 230V 25D 1CT/10x5F	924887044213	871150065239365
25W GU10 240V 25D 1CT/50	924881545502	871150065246165

35 W - Hal-Twist 2y

35W GU10 230V 20D 1CT/50	924887144255	871150065275165
35W GU10 230V 20D CL 1CT/50	924887144245	871150065228765
35W GU10 230V 40D 1CT/50	924713444245	871150065236265
35W GU10 230V 40D 1CT/50	924713444255	871150065283665

50 W - Hal-Twist 2y

50W GU10 230V 20D 1CT/10X5F	924887244225	871150042847960
50W GU10 240V 20D 1CT/10X5F	924887245525	871150042850960
50W GU10 230V 40D 1CT/10X5F	924713544225	871150042853060
50W GU10 240V 40D 1CT/10X5F	924713545525	871150042856160
50W GU10 230V 40D 1CT/10X5F	924713544235	871150041258460
50W GU10 240V 40D 1CT/10X5F	924713545535	871150041261460

DimTone offers color change from 2700K to 2200K while dimming the light.

LED spot MV



CorePro LED spot MV



LED spot classic MV



MASTER LEDspot MV



LED spot classic D MV

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV		
3.2-25W GU10 827 36D	929001219802	871869656322900
LED spot classic MV		
ND 3.1-25W GU10 827 36D	929001217502	871869658769000

CorePro LED spot MV		
3.5-35W GU10 827 36D	929001220102	871869648594100
LED spot classic MV		
ND 3.5-35W GU10 827 36D	929001217802	871869659992100

CorePro LED spot MV		
5-50W GU10 827 36D	929001220402	871869648598900
LED spot classic MV		
ND 4.6-50W GU10 827 36D	929001215202	871869659994500
ND 5.3-50W GU10 827 36D	929001188702	871869655118900

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

MASTER LEDspot MV		
VLE D 4-25W GU10 827 40D	929001215402	871869656296300

MASTER LEDspot MV		
VLE D 3.5-35W GU10 827 40D	929001215502	871869656298700
LED spot classic MV		
D 4.4-35W GU10 827 36D	929001218602	871869656558200
DimTone 4.5-35W GU10 36D	929001278502	871868666764400

MASTER LEDspot MV		
VLE D 4.3-50W GU10 827 40D	929001216102	871869656310600
LED spot classic MV		
D 5.5-50W GU10 827 36D	929001218802	871869656560500
DimTone 5-50W GU10 36D	929001278602	871868666762000

Spot



Tw Alu 3000h



EcoHalo Tw

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

50 W - Tw Alu 3000 hour

50W GU10 230V 25D 1CT/10X5F	924880644264	871150064932460
50W GU10 230V 50D 1CT/10X5F	924880744269	871150064935560

35 W - EcoHalo Tw / 50W EcoHalo Tw

35W GU10 230V 40D 1CT/10X5F	925641044205	872790086404500
-----------------------------	--------------	-----------------

LEDs pot MV



CorePro LED spot MV



LED spot classic MV



MASTER LEDspot MV



LED spot classic D MV

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV		
5-50W GU10 827 36D	929001220402	871869648598900
LED spot classic MV		
ND 4.6-50W GU10 827 36D	929001215202	871869659994500

CorePro LED spot MV		
5-50W GU10 827 36D	929001220402	871869648598900
LED spot classic MV		
ND 4.6-50W GU10 827 36D	929001215202	871869659994500

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

MASTER LEDspot MV		
VLE D 4.3-50W GU10 827 40D	929001216102	871869656310600
LED spot classic MV		
D 5.5-50W GU10 827 36D	929001218802	871869656560500
DimTone 5-50W GU10 36D	929001278602	871868666762000

MASTER LEDspot MV		
VLE D 4.3-50W GU10 827 40D	929001216102	871869656310600
LED spot classic MV		
D 5.5-50W GU10 827 36D	929001218802	871869656560500
DimTone 5-50W GU10 36D	929001278602	871868666762000

DimTone offers color change from 2700K to 2200K while dimming the light.

LED spot MV PAR alternatives

HalogenA PAR

▶ LED spot MV PAR R50



Halogen

Phase out GPC (12nc) EOC

HalogenA PAR16

40W E14 230V 25D 1CT/15 924526644213 871150049753620

Non dimmable

LED recommendation GPC (12nc) EOC

CorePro LED spot MV

ND 2.9-40W 827 R50 36D 929001235902 871869657851300

Dimmable

LED recommendation GPC (12nc) EOC

CorePro LED spot MV

D 5-60W 827 R50 36D 929001236002 871869657853700

HalogenA PAR

▶ LED spot MV PAR



Halogen

Phase out GPC (12nc) EOC

50 W - HalogenA PAR20

50W E27 230V 25D 1CT/15 924713344204 871150049489420

75 W - HalogenA PAR30S

75W E27 230V 10D 1CT/15 924710944204 871150050441820

75W E27 230V 30D 1CT/15 924710844204 871150050439520

100 W - HalogenA PAR30S

100W E27 230V 30D 1CT/15 924541744204 871150051881120

100 W - HalogenA PAR38

100W E27 230V 30D 1CT/15 924890544201 871150065521920

Non dimmable

LED recommendation

Non dimmable not available. Select a dimmable offer.

Non dimmable not available. Select a dimmable offer.

Non dimmable not available. Select a dimmable offer.

Non dimmable not available. Select a dimmable offer.

Dimmable

LED recommendation GPC (12nc) EOC

MASTER LEDspot

D 5.5-50W 2700K PAR20 25D 929001145302 871869646063400

MASTER LEDspot

D 8.5-75W 827 WW PAR30S 25D SO 929001244102 871869657805600

MASTER LEDspot

D 9.5-90W 827 WW PAR30S 25D SO 929001198702 871869655080900

MASTER LEDspot

D 13-100W 827 WW PAR38 25D 929001142802 871869646043600

LED spot MV PAR alternatives

PAR38



Incandescent

Phase out	GPC (12nc)	EOC
60 W / 80W - PAR38		
60W E27 230V FL 30D 1CT/12	923810444214	871150038063015
80W E27 220-240V FL 1CT/15	923810544279	871150090003620
80W E27 220-240V SP 1CT/15	923810244295	871150060037020
80W E27 230V FL 30D 1BL/10	923810544230	871150002123600
80W E27 230V FL 30D 1CT/12	923810544229	871150038066115
80W E27 230V FL 30D 1CT/12	923810544233	871150060040015
80W E27 230V SP 12D 1CT/12	923810244212	871150038075315
80W E27 240V PAR38 Flood 1CT/6	923810545580	871150001856497

120 W - PAR38		
120W E27 230V FL 30D 1CT/12	923810644229	871150038061615
120W E27 230V SP 12D 1CT/12	923810344210	871150038071515
120W E27 240V FL 1CT/6	923815645594	871016317089300

▶ LED spot MV PAR



Non dimmable

LED recommendation
Non dimmable not available. Select a dimmable offer.

Non dimmable not available. Select a dimmable offer.
--

Dimmable

LED recommendation	GPC (12nc)	EOC
MASTER LEDspot		
D 6-60W 827WW PAR38 25D	929001239302	871869657829200

D 13-100W 827 WW PAR38 25D	92900142802	871869646043600
----------------------------	-------------	-----------------

LED spot alternatives

E14 EcoClassic



EcoClassic R39



EcoClassic R50

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

28 W - EcoClassic R39

28W E14 R39 45D 1CT/10 SRP	925719044204	871829175721401
----------------------------	--------------	-----------------

18 W - EcoClassic R50

18W E14 230V NR50 1CT/10 SRP	925645244210	872790082042304
------------------------------	--------------	-----------------

28 W - EcoClassic R50

28W E14 230V NR50 1CT/10 SRP	925640044235	872790025274304
------------------------------	--------------	-----------------

28W E14 230V NR50 30D 1CT/10	925640044236	871869646636000
------------------------------	--------------	-----------------

28W E14 240V NR50 1CT/10 SRP	925640045504	872790025276701
------------------------------	--------------	-----------------

42 W - EcoClassic R50

42W E14 230V NR50 1CT/10 SRP	925714044205	871829168435001
------------------------------	--------------	-----------------

LED spot MV



CorePro LED spot MV R50

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV

ND 2.2-30W 827 R39 36D	929001235502	871869658404000
------------------------	--------------	-----------------

CorePro LED spot MV

ND 1.7-25W 827 R50 36D	929001235802	871869657849000
------------------------	--------------	-----------------



CorePro LED spot MV R39



CorePro LED spot MV R50

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV

Dimmable not available. Select a non dimmable offer.

CorePro LED spot MV

D 5-60W 827 R50 36D	929001236002	871869657853700
---------------------	--------------	-----------------

CorePro LED spot MV

D 5-60W 827 R50 36D	929001236002	871869657853700
---------------------	--------------	-----------------

E27 EcoClassic



EcoClassic NR63



EcoClassic R80

Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

28 W - EcoClassic NR63

28W E27 230V NR63 1CT/10 SRP	925645344213	872790082046104
------------------------------	--------------	-----------------

28W E27 240V NR63 1CT/10 SRP	925645345504	872790082048502
------------------------------	--------------	-----------------

42 W - EcoClassic NR63

42W E27 230V NR63 1CT/10 SRP	925636044223	872790025195104
------------------------------	--------------	-----------------

42W E27 240V NR63 1CT/10 SRP	925636045505	872790025196801
------------------------------	--------------	-----------------

42 W - EcoClassic NR80

42W E27 R80 55D 1CT/10 SRP	925718944203	871829177096101
----------------------------	--------------	-----------------

42W E27 R80 25D 1CT/10 SRP	925645444208	872790083530401
----------------------------	--------------	-----------------

70 W - EcoClassic NR80

70W E27 R80 25D 1CT/10 SRP	925645544205	872790083534201
----------------------------	--------------	-----------------

LED spot MV



CorePro LEDspot R63



CorePro LEDspot R80

Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV

ND 2.7-40W 827 R63 36D	929001233602	871869657859900
------------------------	--------------	-----------------

CorePro LED spot MV

ND 3.7-60W 827 R80 40D	929001235602	871869658406400
------------------------	--------------	-----------------

CorePro LED spot MV

ND 7-100W 827 R80 40D	929001235702	871869658408800
-----------------------	--------------	-----------------



CorePro LEDspot R63



CorePro LEDspot R80

Dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

CorePro LED spot MV

D 5.7-60W 827 R63 36D	929001114402	871869658958800
-----------------------	--------------	-----------------

CorePro LED spot MV

Dimmable not available. Select a non dimmable offer.

CorePro LED spot MV

Dimmable not available. Select a non dimmable offer.

Lamps with no direct LED replacement

We're currently unable to offer a direct LED replacement for the lamps featured below, but we can recommend suitable alternatives.

ReflCM



Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

ReflCM
25W E14 230V P45 SI-CL 1CT/4X5F 920437244205 871150001254838
40W E14 230V P45 SI-CL 1CT/4X5F 920438744206 871150001255538

▶ ReflCM



Non dimmable

LED recommendation	GPC (12nc)	EOC
--------------------	------------	-----

LED classic CM
P45 35W WW E14 CL ND SRT4 929001395101 871869675082700

Dimmable

LED recommendation

Dimmable not available. Select a non dimmable offer.

ReflCM



Halogen

Phase out	GPC (12nc)	EOC
-----------	------------	-----

ReflCM
25W E14 230V P45 SI-CL 1CT/4X5F 920437244205 871150001254838
40W E14 230V P45 SI-CL 1CT/4X5F 920438744206 871150001255538


▶ ReflCM



Non dimmable

LED recommendation

LED classic CM
A60 30W WW E27 CL ND SRT4 929001276458 871869666867201
A60 48W WW E27 CL ND RF 929001276517 871869666869602



Dimmable

LED recommendation

LED classic CM
48W A60 E27 WW CL D SRT4 929001333501 871869670926900



©2018 Philips Lighting Holding B.V. All rights reserved. This document contains information relating to Philips Lighting product portfolio. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Trademarks are the property of Koninklijke Philips N.V., Philips Lighting Holding B.V. or their respective owners.

04/2018
Data subject to change.

www.philips.com