


SL- HYDRUS-350

► Photometric Data


Color Temperature:6710K
Total Power: 500W
AC Input: 230V



WASH MODE


Beam Angle: 10deg(Narrow) Lumen Output: 3,440lm

Distance	Field Diameter	Center Beam(lx)
5m	0.9m	17,000
10m	1.76m	4,250
15m	2.64m	1,888
20m	3.52m	1,063
25m	4.41m	680



Beam Angle: 20deg(Mid) Lumen Output: 4,750lm

Distance	Field Diameter	Center Beam(lx)
5m	1.6m	3,000
10m	3.5m	750
15m	5.4m	333
20m	7.2m	188
25m	9.1m	120



Beam Angle: 40deg(Wide) Lumen Output: 5,440lm

Distance	Field Diameter	Center Beam(lx)
5m	3.5m	1,000
10m	8.3m	250
15m	12.5m	111
20m	16.7m	62
25m	20.9m	40

SPOT MODE

Beam Angle: 5deg(Narrow) Lumen Output: 8,900lm

Distance	Field Diameter	Center Beam(lx)
5m	0.46m	85,000
10m	0.87m	21,250
15m	1.31m	9,444
20m	1.74m	5,312
25m	2.18m	3,400

Beam Angle: 12.5deg(Mid) Lumen Output: 10,600lm

Distance	Field Diameter	Center Beam(lx)
5m	1.1m	16,000
10m	2.2m	4,000
15m	3.3m	1,777
20m	4.4m	1,000
25m	5.5m	640

Beam Angle: 28deg(Wide) Lumen Output: 11,000lm

Distance	Field Diameter	Center Beam(lx)
5m	2.47m	3,440
10m	5.21m	860
15m	7.93m	382
20m	10.6m	215
25m	13.3m	138

BEAM MODE

Beam Angle: 2.8deg(Narrow) Lumen Output: 10,712lm

Distance	Field Diameter	Center Beam(lx)
5m	0.24m	1,343,693
10m	0.48m	335,923
15m	0.73m	149,299
20m	0.97m	83,980
25m	1.22m	53,747

Beam Angle: 10deg(Mid) Lumen Output:14,000lm

Distance	Field Diameter	Center Beam(lx)
5m	0.87m	200,000
10m	1.76m	50,000
15m	2.64m	22,222
20m	3.52m	12,500
25m	4.41m	8,000

Beam Angle: 22deg(Wide) Lumen Output: 15,000lm

Distance	Field Diameter	Center Beam(lx)
5m	1.94m	152,000
10m	4.04m	38,000
15m	6.06m	16,888
20m	8.09m	9,500
25m	10.1m	6,080

** All rights reserved. Improvement and changes to specifications, design and all contents in this catalog, may be made at any time without prior notice.