


SL LED SPOT 300

Photometric Data

Color Temperature: 6500k

Total Power : 400 w

AC Input: 230 v



Beam Angle	10° (Narrow)	Lumen Output	10,593lm	Beam Angle	21° (Mid)	Lumen Output	11,261lm	Beam Angle	45° (Wide)	Lumen Output	11,500lm
Distance (M)	Field Diameter (m)	Centre of Beam (Lx)	Distance (M)	Field Diameter (m)	Centre of Beam (Lx)	Distance (M)	Field Diameter (m)	Centre of Beam (Lx)	Distance (M)	Field Diameter (m)	Centre of Beam (Lx)
5	0.9	17120	5	1.86	4407	5	4.1	1050			
10	1.81	4280	10	3.72	1102	10	8.2	263			
15	2.7	1902	15	5.58	490	15	12.3	117			
20	3.62	1070	20	7.44	275	20	16.4	66			
25	4.5	685	25	9.3	176	25	20.5	42			

** All rights reserved. Improvement and changes to specifications, design and all contents in this catalog, may be made at any time without prior notice.

PHILIPS