



PHILIPS

LEDlamps

LEDtube High Output

The right LEDtube for **high light output** with the best lm/W

Whatever your lighting application, the Philips MASTER LEDtube portfolio has the right LEDtube for you.



With a high lumen output of 2100 lm to 3100 lm, our High Output LEDtubes provide brilliant light quality with the best lumen per watt. A simple switch that comes in a choice of two lengths and colour temperatures, with the option of rotating end-caps.

The right choice for the high street, supermarkets, DIY and industrial applications.



Product data

MASTER LEDtube High Output



Product type	LED	Traditional	Rotable endcap	Lumen output	Operation	Beam angle	CRI	Colour temperature	EOC 1 pcs (C)
MASTER LEDtube	Wattage	Equivalent		Lumen		°		K	
1200mm ROT	20 W	36 W	Yes	1900 lm	EM & Mains	160°	83	3000	871869642198700
1200mm ROT	20 W	36 W	Yes	2100 lm	EM & Mains	160°	83	4000	871869642200700
1200mm ROT	20 W	36 W	Yes	2100 lm	EM & Mains	160°	83	6500	871869642202100
1500mm ROT	23 W	58 W	Yes	2900 lm	EM & Mains	160°	83	3000	871829178956700
1500mm ROT	23 W	58 W	Yes	3100 lm	EM & Mains	160°	83	4000	871829178958100
1500mm ROT	23 W	58 W	Yes	3100 lm	EM & Mains	160°	83	6500	871829178960400
1200mm ROT InstantFit	18 W	36 W	Yes	2100 lm	HF	160°	83	4000	871869647125800
1200mm ROT InstantFit	18 W	36 W	Yes	2100 lm	HF	160°	83	6500	871869647127200
1500mm ROT InstantFit	25 W	58 W	Yes	3100 lm	HF	160°	83	4000	871869640886500
1500mm ROT InstantFit	25 W	58 W	Yes	3100 lm	HF	160°	83	6500	871869640888900

