

The Philips logo is displayed in a white rounded rectangle on a blue background. The background of the entire advertisement is a blurred photograph of a construction site with a worker on a ladder and a Philips LED spot lamp in the foreground.

MASTER LEDspot

Value



Quality, **value** and lifetime

You've got it in one with the new range of MASTER LEDspot Value lamps. They offer high quality at an affordable price with a 25, 36 and 40 degree beam angle for general lighting applications. As a 20 W, 35 W or 50 W equivalent, with a choice of three colour temperatures, dimmable options and a 25,000 and 35,000 hour lifetime, these lamps are everything you value in LED.



MASTER LEDspot MV Value



Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Color temperature	EOC
MASTER LEDspot MV 3,5-35W	W	W	lm	lm/W	cd	°		K	8718696
VLE D 3.5-35W GU10 827 25D	3.5	35	260	74	1000	25	80	2700	43832900
VLE D 3.5-35W GU10 830 25D	3.5	35	270	77	1000	25	80	3000	43834300
VLE D 3.5-35W GU10 840 25D	3.5	35	290	83	1000	25	80	4000	43836700
VLE D 3.5-35W GU10 827 40D	3.5	35	260	74	600	40	80	2700	45703000
VLE D 3.5-35W GU10 830 40D	3.5	35	270	77	600	40	80	3000	45705400
VLE D 3.5-35W GU10 840 40D	3.5	35	290	83	600	40	80	4000	45707800
MASTER LEDspot MV 4,3-50W	W	W	lm	lm/W	cd	°		K	8718696
VLE D 4.3-50W GU10 827 25D	4.3	50	355	83	1400	25	80	2700	43838100
VLE D 4.3-50W GU10 830 25D	4.3	50	365	85	1400	25	80	3000	43844200
VLE D 4.3-50W GU10 840 25D	4.3	50	390	91	1400	25	80	4000	43846600
VLE D 4.3-50W GU10 827 40D	4.3	50	355	83	800	40	80	2700	45709200
VLE D 4.3-50W GU10 830 40D	4.3	50	365	85	800	40	80	3000	45711500
VLE D 4.3-50W GU10 840 40D	4.3	50	390	91	800	40	80	4000	45713900



MASTER LEDspot LV Value



Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Color temperature	EOC
MASTER LEDspot LV 3,4-20W	W	W	lm	lm/W	cd	°		K	8718696
VLE 3.4-20W 827 MR16 24D	3.4	20	220	65	1000	24	80	2700	47570600
VLE 3.4-20W 830 MR16 24D	3.4	20	225	66	1000	24	80	3000	47576800
VLE 3.4-20W 827 MR16 36D	3.4	20	220	65	550	36	80	2700	47572000
VLE 3.4-20W 830 MR16 36D	3.4	20	225	66	600	36	80	3000	47574400

Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Color temperature	EOC North Europe	EOC South Europe
MASTER LEDspot LV-6,3-35W*	W	W	lm	lm/W	cd	°		K	8718696	
D 6.3-35W 2700K MR16 24D	6.3	35	380	60	1800	24	80	2700	49021100	871869644217300
D 6.3-35W 3000K MR16 24D	6.3	35	395	63	1800	24	80	3000	49023500	871869644219700
D 6.3-35W 4000K MR16 24D	6.3	35	410	65	1800	24	80	4000	49025900	871869644221000
D 6.3-35W 2700K MR16 36D	6.3	35	380	60	980	36	80	2700	49027300	871829177533100
D 6.3-35W 3000K MR16 36D	6.3	35	395	63	1000	36	80	3000	49029700	871829178543900
D 6.3-35W 4000K MR16 36D	6.3	35	410	65	1000	36	80	4000	49031000	871829178545300

* Complete 6,3-35W range includes AirFlux technology

