

## SL PUNCHLITE 220



The SL PUNCHLITE 220 is a high performance luminaire, delivering a powerful blended beam. Rated for outdoor use, the PUNCHLITE is ideal for large outdoor stages and permanent outdoor applications.


The innovative and large motorized zoom range of 8-40 degrees delivers flexibility to your lighting design. Highlight performers, objects or building elements with a narrow shaft of light, or flood a wide area with a powerful wash of colour.

Configure the PUNCHLITE remotely via RDM, or locally through the comprehensive Showline LCD menu system. The robust split yoke allows quick setup in any orientation, and the optional accessory holder allows the use of third party accessories to shape and control the beam.

### Features:

- Rugged Construction
- 18pcs High Quality LEDs for exceptional output and colour
- IP65 for wet locations and outdoor use
- Motorized optical system, featuring unmatched zoom range (8° - 40°) and delivering fully blended even light
- HSIC( Hue, Saturation, Intensity, Colour Temperature) operation mode
- 8 or 16 bit DMX-512A operation for smooth stepless fades
- On-board LCD Menu System for addressing and setup
- Remote configuration available via RDM
- 5pin DMX-512A(RDM) IN and THRU connections

### Drawing Diagram:



## Technical Specifications:

<b>Version:</b> SL PUNCHLITE 220, IP65	<b>Features:</b> Double yoke for floor standing or hanging Silent passive cooling Harmonize color calibration IP65 Power and DMX IN/THRU connections
<b>Optics:</b> 8-40 degree beam angle 18 high power RGBW LEDs	
<b>Controls:</b> DMX-512A(RDM) Local LCD control Master/Slave	<b>Physical:</b> 100 - 240VAC, 230W 320mm x 254mm x 252mm / 12.6" x 10" x 9.9" 10.4 kgs / 23.01 lbs CE/C-Tick/cETL
<b>Modes:</b> HSIC RGBW 8 bit RBGW 16 bit	<b>Luminance:</b> 3500 lumens CRI/CQS: 90 (RGBW)

## Ordering Information:

**88-095-6092-36**

SL Punchlite 220 Color Par RGBW, IP65

**SLPUNCHLITE220**

**89-020-6090-00**

Accessory Mounting Kit for Four Leaf Barndoor (20BDSF2020)

**28-002-1450-00**

SL Punchlite 220 Top Hat

**17-017-0756-00**

1 metre mains input cable, IP connector to bare end

**17-017-0755-00**

1 metre mains output cable, IP connector to bare end

**17-003-0113-00**

1 metre mains input cable, IP connector to UL3 plug

**17-017-0754-00**

1 metre mains output cable, IP connector to UL3 socket

**17-017-0729-00**

1 metre DMX input cable, IP Connector to female 5 pin XLR

**17-017-0753-00**

1 metre DMX output cable, IP Connector to male 5 pin XLR

## Harmonize Color Calibration Technology

At the heart of all Showline products is Philips Harmonize Calibration technology. Harmonize is a proprietary, advanced LED color matching system, consisting of 3 correction modules: RGB, RGBW and CoolWhite/Warm White. Every Showline fixture undergoes rigorous testing to provide you with consistent control of color and intensity as well as output of the highest quality.

Philips Group 2014. All rights reserved.

The Company reserves the right to make any variation in design or construction to the equipment described. E&OE. Philips Entertainment delivers fully integrated lighting solutions; from simple lamps to complete systems designed with the specific needs of the entertainment and specialized display lighting markets.

[www.philips.com/showline](http://www.philips.com/showline)

