
# Sh⊕wline SL STRIP 400





The SL STRIP 400 LED luminaire is a compact linear wash luminaire delivering a bright narrow beam.


A wide choice of options makes the SL STRIP 400 suitable for a diverse variety of lighting desgn applications. Choose the RGBW LED option for washes of colour, or choose the Tunable White option for selective grazing and uplighting. For wet applications and outdoor environments, select the IP65 models.

Mounting brackets feature secure lock off and a tight profile to insure close placement to insure smooth beam spreads. The SL STRIP 400 Luminaire is fully RDM capable, ensuring fast convenient remote comissioning - ideal for installations where access to the luminaires is difficult.

### Features :

- Rugged Construction
- Philips LumiLeds RGBW LED's for exceptional output and color
- Built-in color presets, effects and chases
- HSIC (Hue Saturation Intensity Color temperature) operation mode
- 8 or 16-bit DMX-512A operation for smooth stepless fades
- On-board LCD Menu System for addressing and setup
- Remote configuration available via RDM
- PowerCon in and thru power connections
- 5-pin DMX-512A(RDM) in and thru connections

## **Drawing Diagram**:



# **Shewline Technical Specifications :**

Version: SL STRIP 400 RGBW, IP20 or IP65

**Optics:** 10 degree beam angle 36 high power LEDs

Controls: DMX-512A(RDM) Local LCD control Master/slave

Features: Color Gel filter preset Chase - Strobe + Duration Effect Engine LED & Tungsten Curves selection

Modes: HSIC 8 bit RGBW 16 bit RGBW

### Physical:

90-240VAC, 90W 1000mm x 92mm x 140mm, 6kg CE


Luminance: 2350 lumens CRI/COS: >90 (RGBW)

# **Ordering Information :**

SLSTRIP400RGBWIP20 SL STRIP 400 RGBW IP20 88-095-4264-31 SLSTRIP400RGBWIP65 SL STRIP 400 RGBW IP65 88-095-4174-31 SLSTRIP400TWIP20 SL STRIP 400 Tunable White IP20 88-095-4264-71 SLSTRIP400TWIP65 SL STRIP 400 Tunable White IP65 88-095-4174-71

# Harmonize Color Calibration Technology

At the heart of all Showline products is Philips Harmonize Calibration technology. Harmonize is a proprietary, advanced LED color matching system, consisting of 3 correction modules: RGB, RGBW and Cool White/Warm White. Every Showline fixture undergoes rigorous testing to provide you with consistent control of color and intensity as well as output of the highest quality.



#### Philips Group 2012. All rights reserved.

The Company reserves the right to make any variation in design or construction to the equipment described. E&OE. Philips Entertainment delivers fully integrated lighting solutions; from simple lamps to complete systems designed with the specific needs of the entertainment and specialized display lighting markets.

Dallas, TX 75238 USA Tel: +1 214647 7880 Fax: +1 214647 8030

Philips Entertainment Philips Entertainment Lighting Asia U.S. 10911 Petal Street Limited Unit C, 14/F, Roxy Industry Centre No. 41 - 49 Kwai Cheong Road Kwai Chung, N.T. Hong Kong Tel: +852 27969786 Fax: +852 27986546

Philips Entertainment Group Europe Rondweg Zuid 85 Winterswijk 7102 JD Netherlands Tel: +31 543-542343 Fax: +31 53 4500425

Philips Entertainment New Zealand 19 - 21 Kawana Street, Northcote Auckland 0627, New Zealand Tel: +64 9481 0100 Fax: +64 9481 0101

