

SL-Estrip-10-RGBW-IP65

► Photometric Data

Light source specifications

Optics: /
 Beam angle: 25 degree
 Light distribution: symmetric direct illumination
 CRI: /


Illuminance

DISTANCE	1m	2m	3m	5m
COLOR	Lux	Lux	Lux	Lux
RGBW	5597	1399	622	224


Light output

COLOR	Total (lumens)	Power(watts)	Efficacy(lm / W)
RGBW	1906	132.6	14.3

Full intensity in RGBW




Light distribution



IES file is also available

Isolux diagram



At 1m distance
 — 3% 166.7lx — 10% 555.7lx
 — 5% 277.9lx — 30% 1667lx
 — 50% 2779lx