

SL-Estrip-10-RGBW-IP65

► Photometric Data

Light source specifications

Optics: /
 Beam angle: 11X38degree
 Light distribution: symmetric direct illumination
 CRI: /


Illuminance

DISTANCE	1m	2m	3m	5m
COLOR	Lux	Lux	Lux	Lux
RGBW	7291	1823	818	292


Light output

COLOR	Total (lumens)	Power(watts)	Efficacy(lm / W)
RGBW	1884	132.6	14.2

Full intensity in RGBW



Light distribution



IES file is also available

Isolux diagram

