

The advertisement features a top section with a wooden background showing three Philips LEDtube lamps. Two are upright, labeled 'PHILIPS LEDtube' and 'EMC/AMV High Output', while one is lying on its side. A dark blue overlay on the left contains the Philips logo and product information. The middle section has a white background with a large headline. The bottom section also has a white background with descriptive text and a small image of two LEDtubes in the bottom right corner.

PHILIPS

LEDlamps

LEDtube High Output

The right LEDtube for **high light output** with the best lm/W

Whatever your lighting application, the Philips MASTER LEDtube portfolio has the right LEDtube for you.

With a high lumen output of 2100 lm to 3100 lm, our High Output LEDtubes provide brilliant light quality with the best lumen per watt. A simple switch that comes in a choice of two lengths and colour temperatures, with the option of rotating end-caps.


The right choice for the high street, supermarkets, DIY and industrial applications.



Product data

MASTER LEDtube High Output

							
3000/4000/6500	G13	ROTABLE (ROT)	NON-DIMMABLE	50,000 H	EEL	BEAM ANGLE	DIMENSIONS



Product type	LED	Traditional	Rotable endcap	Lumen output	Operation	Beam angle	CRI	Colour temperature	EOC 1 pcs (C)
MASTER LEDtube	Wattage	Equivalent		Lumen		°		K	
1200mm ROT	18 W	36 W	Yes	1900 lm	EM & Mains	160°	83	3000	871869642198700
1200mm ROT	18 W	36 W	Yes	2100 lm	EM & Mains	160°	83	4000	871869642200700
1200mm ROT	18 W	36 W	Yes	2100 lm	EM & Mains	160°	83	6500	871869642202100
1500mm ROT	23 W	58 W	Yes	2900 lm	EM & Mains	160°	83	3000	871829178956700
1500mm ROT	23 W	58 W	Yes	3100 lm	EM & Mains	160°	83	4000	871829178958100
1500mm ROT	23 W	58 W	Yes	3100 lm	EM & Mains	160°	83	6500	871829178960400
1200mm ROT InstantFit	18 W	36 W	Yes	2000 lm	HF	160°	83	3000	871869651456600
1200mm ROT InstantFit	18 W	36 W	Yes	2100 lm	HF	160°	83	4000	871869647125800
1200mm ROT InstantFit	18 W	36 W	Yes	2100 lm	HF	160°	83	6500	871869647127200
1500mm ROT InstantFit	25 W	58 W	Yes	2900 lm	HF	160°	83	3000	871869651458000
1500mm ROT InstantFit	25 W	58 W	Yes	3100 lm	HF	160°	83	4000	871869640886500
1500mm ROT InstantFit	25 W	58 W	Yes	3100 lm	HF	160°	83	6500	871869640888900

