



**PHILIPS**

LEDlamps

LEDtube Standard Output

# The right LEDtube for best energy efficiency

Whatever your lighting application, the Philips MASTER LEDtube portfolio has the right LEDtube for you.

With an output of 1600 lm to 2000 lm, our Standard Output LEDtubes offer the best energy efficiency with the shortest payback time. A simple switch that comes in a choice of two lengths and colour temperatures, with the option of rotating end-caps.

The right choice for car parks, public transport and warehouses.



# Product data

## MASTER LEDtube Standard Output



4000/6500



G13



ROTABLE  
(ROT)



NON-  
DIMMABLE



50,000 H



EEL




160°  
BEAM ANGLE




27.3  
DIMENSIONS

1198 1498



EM



HF

Product type	LED	Traditional	Rotable endcap	Lumen output	Operation	Beam angle	CRI	Colour temperature	EOC 1 pcs (C)*
MASTER LEDtube	Wattage	Equivalent		Lumen		°		K	
1200mm	14.5 W	36 W	Yes	1600 lm	EM & Mains	160°	83	4000	871829179308300
1200mm	14.5 W	36 W	Yes	1600 lm	EM & Mains	160°	83	6500	871829179310600
1500mm	20 W	58 W	Yes	2000 lm	EM & Mains	160°	83	4000	871829173451200
1500mm	20 W	58 W	Yes	2000 lm	EM & Mains	160°	83	6500	871829173453600
1200mm InstantFit	16.5 W	36 W	Yes	1600 lm	HF	160°	83	4000	871829172885600
1200mm InstantFit	16.5 W	36 W	Yes	1600 lm	HF	160°	83	6500	871829172887000
1500mm InstantFit	22 W	58 W	Yes	2000 lm	HF	160°	83	4000	871869640078400
1500mm InstantFit	22 W	58 W	Yes	2000 lm	HF	160°	83	6500	871869640080700

