

# Razor-sharp, pure Platinum

Its razor-sharp light beams have revolutionized the industry in a relatively short amount of time since the first innovative MSD Platinum 5 R was launched in 2010.

Successful productions are the result of close teamwork, as is getting the right lighting solution. Philips has been working with leading fixture makers for years, jointly developing innovative solutions for high performance fixtures in the entertainment market. The Philips Platinum range is one of the products of this close industry cooperation: Platinum lamps provide powerful, compact, brilliant and intense lighting for every type of event.

### Platinum technology

Philips MSD/MSR Platinum lamps are the original, brightest, and most compact short arc lamps on the market, enabling the design of small flexible, and extremely efficient fixtures. The very short arc produces a sparkling, bright light that eliminates shadows and reproduces vivid colors perfectly. The Platinum system is compact and lightweight too, so it can be used anywhere. In short, more light output, more design possibilities, and less energy consumption.

## **Quality assured**

Since Philips Platinum lamps are technologically advanced, close cooperation is required during the design-in to ensure optimum performance of the entertainment fixture. We therefore advise to always replace end-of-life lamps with the original Philips Platinum types.













# New high-end reflector lamp for DJ/club lighting

Most top clubs want powerful intense lighting from compact moving heads.



The new Philips MSD Platinum 2 R is a powerful high-end reflector lamp and is ideal for scanners and fast-moving effect lights. Leading manufacturers have already started implementing this lamp in their entertainment fixtures successfully.

### **Design-ins**

See page seven for a list of initial design-ins.

### **Amazing characteristics**

Philips MSD Platinum 2 R produces a sparkling, bright light that eliminates shadows and reproduces brilliant and vivid colors. Being the most compact reflector lamp system available today means that small, lightweight fixtures can be developed, offering more design possibilities. The high precision reflector and innovative burner-filling result in a bright and efficient light beam: the light output is equivalent to a MSD lamp of 300W, yet energy consumption is halved. Moreover, these benefits can be enjoyed over the 6,000 hours lifetime of the lamp system, which is twice as long as of other MSD lamps.



MSD Platinum 2 R

Specifications								
Туре	Lamp wattage	Arc size	Lumen	Colour	CRI	Max allowable	Average lamp life	Burning position
	(W)	(mm)	output (lm)	temp (K)		pinch temp (°C)	(h)	
Dhiline MSD Dlatinum 2 D	137	<b>Λ Q</b>	5150	8000	75	350	6000	Λην





News, interviews, innovations, technical information, interactive, behind the scenes, discounts and events.

Become a member now, sign up at www.philips.com/onstage

Today, stage lighting is all about creating impact and powerful effects. High brightness and high-contrast beams are needed, using compact luminaire and fixture designs that improve creative choice and flexibility.

The Philips MSR Platinum 35, MSD Platinum 5 R, 14 R, 15 R, 16 R, 17 RA, 20 R and the new 11 R, have all been developed to deliver just this balance. These compact, lightweight lamp systems provide the freedom to create smaller, lighter luminaires – for use at any location on stage.

Fixtures incorporating this range of lamps have been released by leading manufacturers, with the latest being for the new Platinum 11 R that offer extreme brightness for increased impact.

## **Design-ins**

See page seven for a list of initial design-ins.

## Choosing the right lamp

Philips Platinum lamps for touring and stage lighting fixtures serve three main categories:

- Philips MSD Platinum 5 R for laser effects with beam fixtures in less demanding applications. Combines high beam intensity with outstanding color reproduction and a long life.
- Philips MSD Platinum 11 R, 14 R, 15 R, 16 R,
  17 RA and 20 R for follow-spots, profile fixtures and beam fixtures. The 17 RA and
  20 R produce a powerful and brilliant intense light for every type of event.
- Philips MSR Platinum 35 for smaller high power lighting fixtures. This extremely bright lamp is a replacement for MSR Gold 1200W and offers added flexibility and enables small fixture building.



MSD Platinum 5 R MSD Platinum 14 R



MSD Platinum 15 R MSD Platinum 16 R



**NEW** MSD Platinum 11 R MSD Platinum 17 RA



MSD Platinum 20 R



MSR Platinum 35

### **Specifications**

Туре	Lamp wattage (W)	Arc size (mm)	Lumen output (lm)	Colour temp (K)	CRI	Max allowable pinch temp (°C)	Average lamp life (h)	Burning position
Philips MSD Platinum 5 R	190	1.0	7950	8000	75	350	3000	Any
Philips MSD Platinum 11 R	250	0.8	12000	7800	81	350	2000	Any
Philips MSD Platinum 14 R	280	0.8	12000	7800	80	350	2000	Any
Philips MSD Platinum 15 R	300	1.3	13500	8000	75	350	2000	Any
Philips MSD Platinum 16 R	330	1.3	16000	8000	75	350	1500	Any
Philips MSD Platinum 17 RA	350	1.0	> 20000	7000	85	350	1500	Any
Philips MSD Platinum 20 R	470	1.2	> 23000	8000	80	400	1500	Any
Philips MSR Platinum 35*	800	3.0	57800	7750	> 75	450	1000	Any

<sup>\*</sup> Cap base: PGJX36

# Purpose-built for Film/Studio lighting

As every stage director knows, color purity and evenly distributed light are essential ingredients for any production, whether in a theater or on a movie set. This is especially true for accurate reproduction of skin tones.



35 ST has been especially developed for Studio/ Theater lighting fixtures to ensure consistent high quality light output with the right level of brightness, color rendering and color temperature – in any burning position. The result is true natural colors on stage, attractive and accurately exposed pictures for film and video.

These ingredients ensure that the 35 ST is found in several fixtures, greatly extending the application areas for the Platinum fixtures.

# **Design-ins**

See page seven for a list of initial design-ins.

### The best choice in Studio/Theatre

Platinum 35 ST has a color temperature of 6000 Kelvin. All colors are faithfully reproduced thanks to the high color rendering and a better balanced spectrum, where the red content of the spectrum has been improved.

With this level of unrivalled brightness from such a compact light source, the Platinum 35 ST enables even more compact fixture designs.



MSR Platinum 35 ST

### **Specifications**

Type	Lamp wattage	Arc size	Lumen	Colour	CRI	Max allowable	Average lamp life	Burning position
	(W)	(mm)	output (lm)	temp (K)		pinch temp (°C)	(h)	
Philips MSR Platinum 35 ST*	800	3	57800	6000	80	450	750	Any

# Design-in overview

Company	Fixture model	Philips lamp type
Acme	AE-275B / AE-275R / AE-710Beam	Philips MSD Platinum 2 R
merican DJ	Vizi Roller Beam 2R / Vizi Beam Hybrid 2R	Philips MSD Platinum 2 R
ation	Rayzor Beam 2 R / Sniper 2 R	Philips MSD Platinum 2 R
lly	X-SMART BEAM	Philips MSD Platinum 2 R
rbly	LS-2R / LBM-2R / VDH-2R	Philips MSD Platinum 2 R
ton Blue	2R-BEAM	Philips MSD Platinum 2 R
me	XP-5R BEAM	Philips MSD Platinum 5 R
nerican DJ	Vizi Beam 5R / Vizi Spot 5R	Philips MSD Platinum 5 R
ay Paky	Sharpy	Philips MSD Platinum 5 R
S	Jack	Philips MSD Platinum 5 R
rgeiz	Cobalt Plus 5R / Cobalt Plus Beam 5R / Cobalt Plus Spot 5R	Philips MSD Platinum 5 R
ation	Platinum Beam 5 R / Platinum Beam 5 R Extreme / Platinum Spot 5 R Pro	Philips MSD Platinum 5 R
turelight	PLB-5R / PLS-5R	Philips MSD Platinum 5 R
ly	X-BEAM 5R / X-SPOT 5R	Philips MSD Platinum 5 R
Lighting	XR 200 Beam	Philips MSD Platinum 5 R
bly	PT160 Pro / JT160-E / JT160B / PT160B / PT160B Pro	Philips MSD Platinum 5 R
on Blue	5R-BEAM / 5R-SPOT	Philips MSD Platinum 5 R
me	XP-280 BS	Philips MSD Platinum 14 R
ation	Platinum HFX	Philips MSD Platinum 14 R
bly	PT280B / PT280 Hybrid	Philips MSD Platinum 14 R
me	XP-15R SPOT	Philips MSD Platinum 15 R
rgeiz	Cobalt X-Beam 15R	Philips MSD Platinum 15 R
tion	Platinum Beam 15 R / Platinum Spot 15 R / Platinum Spot 15 R Pro	Philips MSD Platinum 15 R
ie Art		
	Fine 300 beam / Fine 300 wash	Philips MSD Platinum 15 R
turelight	PLB-15R / PLS-15R	Philips MSD Platinum 15 R
IVEN	Graphite 2000	Philips MSD Platinum 15 R
ly	X-BEAM 15R	Philips MSD Platinum 15 R
Lighting	XR 300 Beam	Philips MSD Platinum 15 R
bly	Pt 320S spot / PT322S spot basic/ Pt 320B beam	Philips MSD Platinum 15 R
ton Blue	15R SPOT / 15R BEAM / 15R FOLLOWSPOT	Philips MSD Platinum 15 R
me	XP-16R BSW / XP-16R Spot / XP-16R Beam	Philips MSD Platinum 16 R
ay Paky	Sharpy Wash 330	Philips MSD Platinum 16 R
S	Max	Philips MSD Platinum 16 R
ation	Platinum Wash 16 R Pro	Philips MSD Platinum 16 R
ne Art	Fine 330 wash / Fine 330 spot	Philips MSD Platinum 16 R
lly	X-SUPER BEAM	Philips MSD Platinum 16 R
rbly	PT330W	Philips MSD Platinum 16 R
ition	Platinum BX / Platinum SBX	Philips MSD Platinum 17 RA
e Art	Fine 350BSW	Philips MSD Platinum 17 RA
Lighting	PR2362 BWS	Philips MSD Platinum 17 RA
bly	G10B / G10 Hybrid	Philips MSD Platinum 17 RA
me	XP-20R BEAM / XP-20R BSW	Philips MSD Platinum 20 R
ay Paky	Supersharpy / Mythos	Philips MSD Platinum 20 R
ition	Platinum FLX	Philips MSD Platinum 20 R
e Art	Fine 470BEAM / Fine 470BSW	Philips MSD Platinum 20 R
bly	G12WB / G12 Hybrid MKII	Philips MSD Platinum 20 R
y Paky	Alpha Profile 800 ST / Alpha Spot QWO ST	Philips MSR Platinum 35 + Philips MSR Platinum 35 ST
tion	Platinum Profile 35 Pro / Platinum Spot 35 Pro	Philips MSR Platinum 35 + Philips MSR Platinum 35 ST
e Art	Fine 800SF	Philips MSR Platinum 35 ST
ilips Vari*Lite	VL880	Philips MSR Platinum 35
≀ Lighting	XR 800 Spot	Philips MSR Platinum 35 + Philips MSR Platinum 35 ST
be	MMX Spot / MMX Wash Beam	Philips MSR Platinum 35 + Philips MSR Platinum 35 ST
bly	FS800M	Philips MSR Platinum 35 ST
rbly	PT800S / PT800P	Philips MSR Platinum 35 + Philips MSR Platinum 35 ST

