## **Showline**



## **About the SL HYDRUS 350**

The SL HYDRUS 350 is a hybrid BEAM/SPOT/WASH moving luminaire designed for special event, television, and concert lighting applictions. Powered by the PHILIPS Platinum 17RA Lamp, the luminaire delivers powerful output, great colour control and a comprehensive beam effects system in a compact sized luminaire.

## **Preliminary Features:**

Colour System: One fixed colour wheel with 10 colours and one open slot. Colour system

allows for split colour mode and color scroll effects.

Gobos / Effects: One fixed gobo / beam aperture wheel containing 12 beam effect images.

One indexable / rotating gobo wheel with images from the VARI\*LITE Library. Includes a unique coloured gobo which is multi layered and has multiple focal

layers in its projection.

Animation wheel: One animation wheel with Fire Breakup effect

Prisms: Two Prisms (a) 4 facet linear (b) 8 facet circular

Beam angles: Beam MODE: 2°-20°

Spot MODE : 2.3°-23° Wash MODE : 10°-40°

Source: 350W Platinum 17RA

Power Consumption: 450 Watts

Movement: Pan 630° @ 42RPM

Tilt 270° @ 42RPM

AC Input: 100 to 240 VAC

Copyright Philips Entertainment 2016, all rights reserved. The information contained herein is preliminary and subject to change without prior notice.

