

**PHILIPS**

Cinema lamps

Cross reference

# Philips Digital Cinema Xenon Lamps

| Projector Manufacturer                                     | Projector Model                                    | Philips   | Christie/Ushio   | Osram   |
|--|--|---|--|---|
| Sony   | SRX-R220/R320                                      | XDC 4200S<br>XDC 4200SL<br>XDC 3000S<br>XDC 2000S                                       | DXL-40SRX<br>DXL-40SRX/LL<br>DXL-30SRX<br>DXL-20SRX            | XBO 4200 W/HPS<br>XBO 4200 W/HPS LL<br>XBO 3000 W/HPS<br>XBO 2000 W/HPS       |
| NEC  | NC2500S/3200S/3240S                                | XDC 7000N <b>NEW!</b><br>XDC 6000NL<br>XDC 6000N<br>XDC 4500NL <b>NEW!</b><br>XDC 4500N | DXL-70SN<br>DXL-60SN/L<br>DXL-60SN<br>DXL-45SN/L<br>DXL-45SN   | -<br>XBO 6000 W/HPN L<br>XBO 6000 W/HPN<br>XBO 4500 W/HPN L<br>XBO 4500 W/HPN |
|  | NC2000C/NC1600C/NC1200C                            | XDC 2000N   | DXL-20SN3  | XBO 2000 W/HPN  |
|  | NC2000C/1600C                                      | XDC 4000NL <b>NEW!</b><br>XDC 4000N<br>XDC 4001N<br>XDC 4002N<br>XDC 3000NL <b>NEW!</b> | DXL-40SN/L<br>DXL-40SN<br>DXL-40SCN<br>DXL-40SN2<br>DXL-30SN/L | -<br>XBO 4000 W/HPN<br>-<br>XBO 4000 W/HPN L<br>XBO 3000 W/HPN                |
| Barco  | DP4K-32B/DP2K-32B                                  | XDC 6500BL <b>NEW!</b><br>XDC 6500B   | -<br>DXL-65BA2   | -<br>XBO 6500 W/DHP   |
|  | DP-90/100/3000                                     | XDC 6000B<br>XDC 4500B<br>XDC 3001B   | DXL-60BA2/L<br>DXL-45BA/L<br>DXL-30BA/L                        | XBO 6000 W/DHP<br>XBO 4500 W/DHP<br>XBO 3000 W/DHS                            |
|  | DP2K-20C/23B/DP-1500/2000                          | XDC 4000BL <b>NEW!</b><br>XDC 4000B   | DXL-40BAF/L<br>DXL-40BAF                                       | XBO 4000 W/DHP L<br>XBO 4000 W/DHP  |
|  | DP2K-15C/19B/20C/23B/DP-1500/2000                  | XDC 3000BL <b>NEW!</b><br>XDC 3000B   | DXL-30BAF/L<br>DXL-30BAF                                       | XBO 3000 W/DHP L<br>XBO 3000 W/DHP  |
|  | DP2K-10S/12C/15C/19B/20C/23B/DP4K-23B/DP-1500/2000 | XDC 2200B<br>XDC 2000B  | DXL-22BAF/L<br>DXL-20BAF/L                                     | XBO 2200 W/DHP<br>XBO 2000 W/DHP  |
| DP2K-8S/10S/12C/15C/19B/20C/23B/DP4K-23B/DP-1200/1500/2000 | XDC 1200B  | DXL-12BAF   | XBO 1200 W/DHP   |   |
| Christie   | CP2210/2215/CP2000-M                               | XDC 2001C   | CDXL-20SD  | XBO 2000 W/DTS  |
|  | CP2230/4230<br>CP2000-SB/XB                        | XDC 6000C<br>XDC 4500CL <b>NEW!</b><br>XDC 4500C  | CDXL-60<br>CDXL-45SP<br>CDXL-45                                | XBO 6000 W/DTP<br>XBO 4500 W/DTP L<br>XBO 4500 W/DTP                          |
|  | CP2220/4220  | XDC 3001C   | CDXL-30SD  | XBO 3000 W/DTS  |
|  | CP2220/2230/4220/4230<br>CP2000-SB/XB/ZX           | XDC 3000C<br>XDC 2000C  | CDXL-30<br>CDXL-20   | XBO 3000 W/DTP<br>XBO 2000 W/DTP  |
| IMAX   | Gen III (Barco)                                    | XDC 6500BI  | DXL-65BA2  | -   |

# The right Philips Digital Cinema Xenon lamp for each projector model

## Philips lamp types

## Barco projector models

| Ordering code | Product description             | DP2K-8S | DP2K-10Sz | DP2K-12C | DP2K-15C | DP2K-19B | DP2K-20C | DP2K-23B | DP4K-23B | DP2K-32B | DP4K-32B | DP-90 | DP-100 | DP-1200 | DP-1500 | DP-2000 | DP-3000 |
|---------------|---------------------------------|---------|-----------|----------|----------|----------|----------|----------|----------|----------|----------|-------|--------|---------|---------|---------|---------|
| 928418506301  | Philips XDC 1200 B              | ✓       |           |          |          |          |          |          |          |          |          |       |        |         |         |         |         |
| 928415306301  | Philips XDC 2000 B              |         | ✓         | ✓        | ✓        | ✓        | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928418406301  | Philips XDC 2200 B              |         | ✓         | ✓        | ✓        | ✓        | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928419206301  | Philips XDC 3000 BL <b>NEW!</b> |         |           | ✓        | ✓        | ✓        | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928415206301  | Philips XDC 3000 B              |         |           |          | ✓        | ✓        | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928419106301  | Philips XDC 4000 BL <b>NEW!</b> |         |           |          |          | ✓        | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928417006301  | Philips XDC 4000 B              |         |           |          |          |          | ✓        | ✓        | ✓        |          |          |       |        |         |         |         |         |
| 928417806301  | Philips XDC 3001 B              |         |           |          |          |          |          | ✓        | ✓        |          |          |       |        |         | ✓       | ✓       | ✓       |
| 928417706301  | Philips XDC 4500 B              |         |           |          |          |          |          |          |          | ✓        | ✓        |       |        |         |         |         |         |
| 928417606301  | Philips XDC 6000 B              |         |           |          |          |          |          |          |          | ✓        | ✓        |       |        |         |         |         |         |
| 928415006301  | Philips XDC 6500 B              |         |           |          |          |          |          |          |          | ✓        | ✓        |       |        |         |         |         |         |
| 928418706301  | Philips XDC 6500 BL <b>NEW!</b> |         |           |          |          |          |          |          |          | ✓        | ✓        |       |        |         |         |         |         |

## Philips lamp types

## NEC projector models

| Ordering code | Product description             | NC1200C | NC1600C | NC2000C | NC2500S | NC3200S | NC3240S |
|---------------|---------------------------------|---------|---------|---------|---------|---------|---------|
| 928418806301  | Philips XDC 2000N               | ✓       |         |         |         |         |         |
| 928419606301  | Philips XDC 3000 NL <b>NEW!</b> |         | ✓       | ✓       | ✓       | ✓       | ✓       |
| 928419706301  | Philips XDC 4000 NL <b>NEW!</b> |         | ✓       | ✓       | ✓       | ✓       | ✓       |
| 928415406301  | Philips XDC 4000 N              |         | ✓       | ✓       | ✓       | ✓       | ✓       |
| 928415506301  | Philips XDC 4001 N              |         | ✓       | ✓       | ✓       | ✓       | ✓       |
| 928418006301  | Philips XDC 4002 N              |         | ✓       | ✓       | ✓       | ✓       | ✓       |
| 928419806301  | Philips XDC 4500 NL <b>NEW!</b> |         |         |         | ✓       | ✓       | ✓       |
| 928415406201  | Philips XDC 4500 N              |         |         |         | ✓       | ✓       | ✓       |
| 928419906301  | Philips XDC 6000 NL <b>NEW!</b> |         |         |         | ✓       | ✓       | ✓       |
| 928416806201  | Philips XDC 6000 N              |         |         |         | ✓       | ✓       | ✓       |
| 928420006301  | Philips XDC 7000 N <b>NEW!</b>  |         |         |         | ✓       | ✓       | ✓       |

## Philips lamp types

## Sony projector models

| Ordering code | Product description | SRX-R220 | SRX-R320 |
|---------------|---------------------|----------|----------|
| 928413406301  | Philips XDC 2000 S  | ✓        | ✓        |
| 928411806201  | Philips XDC 3000 S  | ✓        | ✓        |
| 928417506301  | Philips XDC 4200 SL | ✓        | ✓        |
| 928414606201  | Philips XDC 4200 S  | ✓        | ✓        |

## Philips lamp types

## Christie projector models

| Ordering code | Product description             | CP2210 | CP2215 | CP2220 | CP2230 | CP4220 | CP4230 | CP2000-M | CP2000-SB | CP2000-XB | CP2000-ZX |
|---------------|---------------------------------|--------|--------|--------|--------|--------|--------|----------|-----------|-----------|-----------|
| 928413306301  | Philips XDC 2000 C              |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |
| 928418906301  | Philips XDC 2001 C              | ✓      | ✓      |        |        |        |        |          |           |           |           |
| 928411706201  | Philips XDC 3000 C              |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |
| 928418306301  | Philips XDC 3001 C              |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |
| 928419506301  | Philips XDC 4500 CL <b>NEW!</b> |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |
| 928415306201  | Philips XDC 4500 C              |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |
| 928416706201  | Philips XDC 6000 C              |        |        | ✓      | ✓      | ✓      | ✓      | ✓        | ✓         | ✓         | ✓         |

## Philips lamp types

## IMAX projector models

| Ordering code | Product description | Gen III |
|---------------|---------------------|---------|
| 928418606301  | Philips XDC 6500 BI | ✓       |

✓ This lamp fits in this projector

