

The Philips logo is displayed in a bold, blue, sans-serif font. It is positioned within a white rectangular area that has a curved bottom edge, which is set against a dark red background.

Trade lighting

# Every light the office needs

Whether it's LED, conventional  
luminaires or controls, we've got the  
right installation solution for offices.



Find the right light  
**for every  
kind of office**



Today's offices are bright, flexible spaces that offer more exciting lighting possibilities than ever before. With light you can connect the whole office environment. From open plan offices that energize and inspire, to corridors, restrooms and parking areas that feel safe and secure.

But office lighting isn't just about providing the right light levels to perform tasks safely and effectively. Your customers will also be looking for ways to reduce their energy and maintenance bills, as well as the cost of the lighting installation itself.

Our solutions let you approach office lighting from four different angles. From high quality conventional solutions to sophisticated controls that are smart, sustainable and ultra-efficient. So with Philips, you have every light the office needs.



Relamping

Option

## Conventional lamp

With fluorescent tri-phosphor technology, our conventional lamp **upgrades** offer high quality light and a long to extremely long and reliable lifetime.

Option

## LED lamp

You can improve existing luminaire installations quickly and simply by **replacing** conventional lamps with energy-efficient LEDs.



Renovation

Option

## LED luminaire

For **renovations** or new installations, our one-to-one replacements are an energy-saving alternative to existing luminaires.

Option

## Lighting control

Add lighting controls to LED luminaires and you can create a **smarter lighting** solution.

# Choosing the right light

We've made it easy to compare different lighting solutions depending on when and where they'll be used in the office. So whether they need an upgrade, replacement, renovation or smart solution, you can offer your customers the right office light every time.



**Open plan office**



**Corridor**



**Restroom**



**Parking**

## Conventional

## LED lamp



MASTER TL5 High Efficiency



MASTER LEDtube 600-1200-1500 mm



MASTER PL-C



CorePro LED PLC



LED spot classic



MASTER TL-D Xtreme



CorePro LEDtube

## LED luminaire

## Lighting control



CoreLine Panel OC



OccuSwitch Presence Detector LRM1011



CoreLine SlimDownlight



OccuSwitch Presence Detector LRM1011



CoreLine Recessed Spot



OccuSwitch Movement Detector LRM1032



CoreLine Waterproof



OccuSwitch Movement Detector LRM1040





# Open plan office





Option

## Conventional lamp

### MASTER TL5 High Efficiency

- › Lamp efficacies up to 104 lm/W
- › Low energy consumption
- › Constant lumen level, excellent lumen maintenance
- › Good color rendering
- › Choice out of 6 color temperatures



Option

## LED lamp

### MASTER LEDtube Ultra Output T8 1200 and 1500 mm

- › Fluorescent TL-D replacement
- › Ultra output of 2300 lm up to 3700 lm
- › High quality light with outstanding lamp efficiency of 148 lm/W
- › High light output designed for ergonomic norms
- › Available in 1200 and 1500 mm lengths
- › One blue stripe for EM & Mains control gear
- › Two blue stripes for HF control gear

### MASTER LEDtube 600 mm

- › Up to 1050 lumens light output
- › Choice of color temperatures: 3000K, 4000K, 6500K
- › One blue stripe for EM & Mains control gear
- › Two blue stripes for HF control gear



new





## Option LED luminaire

### CoreLine Panel OC

- › Surface-of-light panel design
- › 50,000 hours lifetime
- › 3400 lumens light output
- › Unified Glare Rating (UGR) =18 (square design); UGR<19 (rectangular)
- › Saves up to 40% energy compared to functional TL-D luminaires






Option

## Lighting control

### OccuSwitch Presence Detector LRM1011

- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m<sup>2</sup>
- › Detachable mains connector
- › Separate Weiland cable for hassle-free installation



Application bundle

Save up to  
**30%**

more energy -  
add a presence  
detector to your  
luminaires





LR image  
169dpi

# Corridor





Option

## Conventional lamp

### MASTER PL-C

- › Efficient, compact fluorescent lamp
- › Optimum light performance
- › Choice out of 4 color temperatures
- › 2 pin with instant starter for electromagnetic gear
- › 4 pin for HF control gear
- › 4 pins enables dimming down to 10%
- › 600, 900, 1200 and 1800 lumen at 10, 13, 18 and 26W



Option

## LED lamp

### CorePro LED PLC

- › Retrofit LED upgrade for downlighting
- › Incredible energy savings
- › 30,000 hours lifetime, less maintenance
- › Fits neatly into existing fixtures
- › Similar PLC form-factor - no building or modification work
- › The range includes both 2-pin (EM) and 4-pin (HF) lamps options.



new



Option

## LED luminaire

### CoreLine SlimDownlight

- › Ultra-thin, recessed LED downlight
- › One-to-one replacement for conventional luminaires
- › Saves up to 40% energy compared to functional TL-D luminaires
- › 50,000 hours lifetime
- › 'Surface of light' for a high-end look
- › Extremely small build-in depth (<50 mm) fits more ceiling types





Option

## Lighting control

### OccuSwitch Presence Detector LRM1011

- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m<sup>2</sup>
- › Detachable mains connector
- › Separate Weiland cable for hassle-free installation





# Restroom



## Option LED lamp

### LED spot classic G10 and MR16

- › Long-lasting replacement for non-dimmable and dimmable spots
- › Iconic glass spot with single optic, no shades in the beam
- › LED replacement for halogens phased out by ErP
- › Dimmable versions: GU10 3.2-35W and 5.3-50W
- › 15,000 hours lifetime





Option  
LED luminaire



**CoreLine Recessed Spot**

- › Designed to replace halogen luminaires
- › Saves 80% energy compared with halogen
- › 50,000 hours lifetime, 15x halogen
- › Slim design (60mm) fits in most types of ceiling
- › Compatible with almost all wall-mounted dimmers

Fast fit  
with push-in  
connectors



Option  
Lighting control

**OccuSwitch Movement Detector LRM1032**


- › Light switch with built-in movement detector
- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m2
- › Detachable mains connector
- › Separate Wieland cable for hassle-free installation



Application bundle  
Save up to  
**50%**  
more energy -  
add a movement  
detector to your  
luminaires



# Parking







Option

## Conventional lamp

### MASTER TL-D Xtreme

- › Extremely long lifetime up to 90.000 hrs - 10 years of operation
- › Lower maintenance costs
- › Fewer early failures
- › Less waste and disposal costs
- › Easy switch from spot to group replacement



Option

## LED lamp

### MASTER LEDtube High Output EM/HF

- › An affordable LED solution
- › Minimizes overall lighting costs
- › Retrofit replacement on EM and HF ballast (Instant Fit) installations
- › Available in 1200 mm and 1500 mm lengths for EM and HF gear



### CorePro LEDtube EM

- › An affordable LED solution
- › Minimizes overall lighting costs
- › Retrofit replacement on electromagnetic (EM) ballast installations
- › Available in 1200 mm and 1500 mm lengths
- › Beam angle of 240°



NEW



✓ Uniform light spread for car parks, storage rooms, warehouses

✗ Not for high lux applications like offices or industry



## Option LED luminaire

### CoreLine Waterproof

- › Direct replacement for conventional waterproof luminaires (18 to 58 W TL-D)
- › Same light performance, installation flexibility and length
- › Reliable integrated LED technology
- › 50,000 hours lifetime
- › Maintenance-free installation



Saves  
**50%**  
energy  
compared  
with TL-D



Option

## Lighting control

### Movement detector LRM1040

- › Designed for outdoor or indoor use (IP54)
- › Adjustable light sensor prevents switch on in daylight
- › Wall, corner or ceiling mounting
- › Cover 12m range over 240°



Application bundle

Save up to


**70%**

more energy -  
add a movement  
detector to your  
luminaires



For a longer  
lifetime, turn  
lighting off when  
not required

# Calculate **Total Cost of Ownership**



Every business is keen to reduce energy, maintenance and operating costs to meet tight budgets and environmental targets. Understanding the total costs of a lighting installation over its whole life time can help to sell the right lighting choice. Our quick comparison tool includes energy consumption, maintenance costs and carbon footprint. So you can instantly see the Total Cost of Ownership (TCO) and show your clients how much they can save.

**Just follow these four simple steps:**

- 1** Go to the link for the product TCO calculator  
LEDlamps  
[www.philips.com/masterledlamps](http://www.philips.com/masterledlamps)  
[www.philips.com/coreproledlamps](http://www.philips.com/coreproledlamps)  
LEDtubes  
[www.philips.com/LEDtube](http://www.philips.com/LEDtube)  
Coreline  
[www.philips.com/coreline](http://www.philips.com/coreline)  
Application bundles  
[www.philips.com/applicationbundles](http://www.philips.com/applicationbundles)
- 2** Follow the steps on screen
- 3** Complete your project details
- 4** The online tool automatically calculates the TCO

# Specifications

## Open plan office

### MASTER TL5 High Efficiency



  
2700/3000/3500/  
4000/5000/6500



G5



DIMMABLE



24,000 H



EEL

| Product description       | Wattage | Lamp lumen output | Color temp | CRI | EOC      |
|---------------------------|---------|-------------------|------------|-----|----------|
|                           | W       | lm                | K          |     | 8711500  |
| MASTER TL5 14W/827 1SL/40 | 13.7    | 1350              | 2700       | 82  | 64102155 |
| MASTER TL5 14W/830 UNP/40 | 13.7    | 1350              | 3000       | 82  | 61063855 |
| MASTER TL5 14W/830 1SL/40 | 13.7    | 1350              | 3000       | 82  | 63938755 |
| MASTER TL5 14W/830 1SL/20 | 13.7    | 1350              | 3000       | 82  | 63938705 |
| MASTER TL5 14W/835 1SL/40 | 13.7    | 1350              | 3500       | 82  | 70765955 |
| MASTER TL5 14W/840 UNP/40 | 13.7    | 1350              | 4000       | 82  | 61066955 |
| MASTER TL5 14W/840 1SL/40 | 13.7    | 1350              | 4000       | 82  | 63940055 |
| MASTER TL5 14W/840 1SL/20 | 13.7    | 1350              | 4000       | 82  | 63940005 |
| MASTER TL5 14W/865 UNP/40 | 13.7    | 1250              | 6500       | 82  | 61068355 |
| MASTER TL5 14W/865 1SL/40 | 13.7    | 1250              | 6500       | 82  | 71009355 |
| MASTER TL5 21W/827 1SL/40 | 20.7    | 2100              | 2700       | 82  | 64320955 |
| MASTER TL5 21W/830 UNP/40 | 20.7    | 2100              | 3000       | 82  | 61070655 |
| MASTER TL5 21W/830 1SL/40 | 20.7    | 2100              | 3000       | 82  | 63942455 |
| MASTER TL5 21W/830 1SL/20 | 20.7    | 2100              | 3000       | 82  | 63942405 |
| MASTER TL5 21W/840 UNP/40 | 20.7    | 2100              | 4000       | 82  | 61072055 |
| MASTER TL5 21W/840 1SL/40 | 20.7    | 2100              | 4000       | 82  | 63944855 |
| MASTER TL5 21W/840 1SL/20 | 20.7    | 2100              | 4000       | 82  | 63944805 |
| MASTER TL5 21W/865 UNP/40 | 20.7    | 1950              | 6500       | 82  | 61077555 |
| MASTER TL5 21W/865 1SL/40 | 20.7    | 1950              | 6500       | 82  | 71011655 |
| MASTER TL5 28W/827 1SL/40 | 27.8    | 2900              | 2700       | 82  | 64322355 |
| MASTER TL5 28W/830 UNP/40 | 27.8    | 2900              | 3000       | 82  | 61081255 |
| MASTER TL5 28W/830 1SL/40 | 27.8    | 2900              | 3000       | 82  | 63946255 |
| MASTER TL5 28W/830 1SL/20 | 27.8    | 2900              | 3000       | 82  | 63946205 |
| MASTER TL5 28W/835 1SL/40 | 27.8    | 2900              | 3500       | 82  | 71004855 |
| MASTER TL5 28W/840 UNP/40 | 27.8    | 2900              | 4000       | 82  | 61090455 |
| MASTER TL5 28W/840 1SL/40 | 27.8    | 2900              | 4000       | 82  | 63948655 |
| MASTER TL5 28W/840 1SL/20 | 27.8    | 2900              | 4000       | 82  | 63948605 |
| MASTER TL5 28W/850 1SL/40 | 27.8    | 2775              | 5000       | 82  | 26020855 |
| MASTER TL5 28W/865 UNP/40 | 27.8    | 2700              | 6500       | 82  | 61092855 |
| MASTER TL5 28W/865 1SL/40 | 27.8    | 2700              | 6500       | 82  | 71015455 |
| MASTER TL5 35W/827 1SL/40 | 34.7    | 3650              | 2700       | 82  | 64324755 |
| MASTER TL5 35W/830 UNP/40 | 34.7    | 3650              | 3000       | 82  | 61103155 |
| MASTER TL5 35W/830 1SL/40 | 34.7    | 3650              | 3000       | 82  | 63950955 |
| MASTER TL5 35W/830 1SL/20 | 34.7    | 3650              | 3000       | 82  | 63950905 |
| MASTER TL5 35W/835 1SL/40 | 34.7    | 3650              | 3500       | 82  | 71006255 |
| MASTER TL5 35W/840 UNP/40 | 34.7    | 3650              | 4000       | 82  | 61105555 |
| MASTER TL5 35W/840 1SL/40 | 34.7    | 3650              | 4000       | 82  | 63952355 |
| MASTER TL5 35W/840 1SL/20 | 34.7    | 3650              | 4000       | 82  | 63952305 |
| MASTER TL5 35W/865 UNP/40 | 34.7    | 3400              | 6500       | 82  | 61107955 |
| MASTER TL5 35W/865 1SL/40 | 34.7    | 3400              | 6500       | 82  | 71018555 |


# MASTER LEDtube Ultra Output



| Product description      | Wattage | Lamp lumen output | Operation  | Color temp | CRI | EOC      |
|--------------------------|---------|-------------------|------------|------------|-----|----------|
|                          | W       | lm                |            | K          |     | 8718696  |
| MASTER LEDtube 600mm RN* | 9       | 1000              | EM & Mains | 3000       | 83  | 57279500 |
| MASTER LEDtube 600mm RS* | 9       | 1000              | EM & Mains | 3000       | 83  | 46141900 |
| MASTER LEDtube 600mm RN* | 9       | 1050              | EM & Mains | 4000       | 83  | 57281800 |
| MASTER LEDtube 600mm RS* | 9       | 1050              | EM & Mains | 4000       | 83  | 46143300 |
| MASTER LEDtube 600mm RN* | 9       | 1050              | EM & Mains | 6500       | 83  | 57283200 |
| MASTER LEDtube 600mm RS* | 9       | 1050              | EM & Mains | 6500       | 83  | 46145700 |
| MASTER LEDtube 600mm     | 10.5    | 1000              | HF         | 3000       | 83  | 55965900 |
| MASTER LEDtube 600mm     | 10.5    | 1050              | HF         | 4000       | 83  | 55967300 |
| MASTER LEDtube 600mm     | 10.5    | 1050              | HF         | 6500       | 83  | 55969700 |
| MASTER LEDtube 1200mm    | 18      | 2300              | EM & Mains | 3000       | 83  | 46149500 |
| MASTER LEDtube 1200mm    | 18      | 2500              | EM & Mains | 4000       | 83  | 46151800 |
| MASTER LEDtube 1200mm    | 18      | 2500              | EM & Mains | 6500       | 83  | 46155600 |
| MASTER LEDtube 1500mm    | 25      | 3400              | EM & Mains | 3000       | 83  | 46157000 |
| MASTER LEDtube 1500mm    | 25      | 3700              | EM & Mains | 4000       | 83  | 46159400 |
| MASTER LEDtube 1500mm    | 25      | 3700              | EM & Mains | 6500       | 83  | 46163100 |
| MASTER LEDtube 1200mm    | 21      | 2300              | HF         | 3000       | 83  | 55282700 |
| MASTER LEDtube 1200mm    | 21      | 2500              | HF         | 4000       | 83  | 55278000 |
| MASTER LEDtube 1200mm    | 21      | 2500              | HF         | 6500       | 83  | 55280300 |
| MASTER LEDtube 1500mm    | 26      | 3400              | HF         | 3000       | 83  | 55288900 |
| MASTER LEDtube 1500mm    | 26      | 3700              | HF         | 4000       | 83  | 55284100 |
| MASTER LEDtube 1500mm    | 26      | 3700              | HF         | 6500       | 83  | 55286500 |

\* RS = Region Southern Europe / RN = Region Northern Europe

# CoreLine Panel Office Compliant



| Product description              | Wattage | Luminaire lumen output | Color temp | CRI  | EOC      |
|----------------------------------|---------|------------------------|------------|------|----------|
|                                  | W       | lm                     | K          |      | 8718696  |
| RC127V LED34S/840 PSU W60L60 OC  | 41      | 3400                   | 4000       | ≥ 80 | 07088899 |
| RC127V LED34S/830 PSU W60L60 OC  | 41      | 3400                   | 3000       | ≥ 80 | 07089599 |
| RC127V LED34S/840 PSU W30L120 OC | 41      | 3400                   | 4000       | ≥ 80 | 07090199 |
| RC127V LED34S/830 PSU W30L120 OC | 41      | 3400                   | 3000       | ≥ 80 | 07091899 |
| RC127V LED34S/840 PSD W60L60 OC  | 41      | 3400                   | 4000       | ≥ 80 | 07092599 |
| RC127V LED34S/830 PSD W60L60 OC  | 41      | 3400                   | 3000       | ≥ 80 | 07093299 |
| RC127V LED34S/840 PSD W30L120 OC | 41      | 3400                   | 4000       | ≥ 80 | 07094999 |
| RC127V LED34S/830 PSD W30L120 OC | 41      | 3400                   | 3000       | ≥ 80 | 07095699 |
| RC128V LED34S/840 PSD W62L62 OC  | 41      | 3400                   | 4000       | ≥ 80 | 07096399 |
| RC128V LED34S/830 PSD W62L62 OC  | 41      | 3400                   | 3000       | ≥ 80 | 07097099 |

# OccuSwitch Controls




| Product description      | EOC            |
|--------------------------|----------------|
|                          | <b>8718696</b> |
| LRM1011 OS mov det small | 44209800       |

## Corridor

### MASTER PL-C



| Product description    | Wattage | Lamp lumen output | Operation | Color temp | CRI | EOC      |
|------------------------|---------|-------------------|-----------|------------|-----|----------|
|                        | W       | lm                |           | K          |     | 8711500  |
| MASTER PL-C 10W/827/2P | 10      | 600               | EM        | 2700       | 82  | 70681270 |
| MASTER PL-C 10W/830/2P | 10      | 600               | EM        | 3000       | 82  | 70724670 |
| MASTER PL-C 10W/840/2P | 10      | 600               | EM        | 4000       | 82  | 70498670 |
| MASTER PL-C 13W/827/2P | 13      | 900               | EM        | 2700       | 82  | 62081170 |
| MASTER PL-C 13W/830/2P | 13      | 900               | EM        | 3000       | 82  | 62084270 |
| MASTER PL-C 13W/840/2P | 13      | 900               | EM        | 4000       | 82  | 62086670 |
| MASTER PL-C 13W/865/2P | 13      | 845               | EM        | 6500       | 82  |          |
| MASTER PL-C 18W/827/2P | 18      | 1200              | EM        | 2700       | 82  | 62088070 |
| MASTER PL-C 18W/830/2P | 18      | 1200              | EM        | 3000       | 82  | 62091070 |
| MASTER PL-C 18W/840/2P | 18      | 1200              | EM        | 4000       | 82  | 62093470 |
| MASTER PL-C 18W/865/2P | 18      | 1150              | EM        | 6500       | 82  |          |
| MASTER PL-C 26W/827/2P | 26      | 1800              | EM        | 2700       | 82  | 62095870 |
| MASTER PL-C 26W/830/2P | 26      | 1800              | EM        | 3000       | 82  | 62098970 |
| MASTER PL-C 26W/840/2P | 26      | 1800              | EM        | 4000       | 82  | 62100970 |
| MASTER PL-C 26W/865/2P | 26      | 1740              | EM        | 6500       | 82  |          |



| Product description    | Wattage | Lamp lumen output | Operation | Color temp | CRI | EOC      |
|------------------------|---------|-------------------|-----------|------------|-----|----------|
|                        | W       | lm                |           | K          |     | 8711500  |
| MASTER PL-C 10W/827/4P | 10      | 600               | HF        | 2700       | 82  | 62325670 |
| MASTER PL-C 10W/830/4P | 10      | 600               | HF        | 3000       | 82  | 62329470 |
| MASTER PL-C 10W/840/4P | 10      | 600               | HF        | 4000       | 82  | 62330070 |
| MASTER PL-C 13W/827/4P | 13      | 900               | HF        | 2700       | 82  | 62326370 |
| MASTER PL-C 13W/830/4P | 13      | 900               | HF        | 3000       | 82  | 62331770 |
| MASTER PL-C 13W/840/4P | 13      | 900               | HF        | 4000       | 82  | 62332470 |
| MASTER PL-C 18W/827/4P | 18      | 1200              | HF        | 2700       | 82  | 62327070 |
| MASTER PL-C 18W/830/4P | 18      | 1200              | HF        | 3000       | 82  | 62333170 |
| MASTER PL-C 18W/840/4P | 18      | 1200              | HF        | 4000       | 82  | 62334870 |
| MASTER PL-C 26W/827/4P | 26      | 1800              | HF        | 2700       | 82  | 62328770 |
| MASTER PL-C 26W/830/4P | 26      | 1800              | HF        | 3000       | 82  | 62335570 |
| MASTER PL-C 26W/840/4P | 26      | 1800              | HF        | 4000       | 82  | 62336270 |


## CorePro LED PLC



3000/4000



G24d-2 & G24d-3



G24q-2 & G24q-3



ROTATABLE  
(ROT)



NON-  
DIMMABLE



30.000 H



120°  
BEAM ANGLE



A<sup>+</sup>  
EEL

| Product description                | Wattage | Lamp lumen output | Operation | Color temp | CRI | EOC      |
|------------------------------------|---------|-------------------|-----------|------------|-----|----------|
|                                    | W       | lm                |           | K          |     | 8718696  |
| CorePro LED PLC 6.5W 830 2P G24d-2 | 6.5     | 600               | EM        | 3000       | 80  | 54127200 |
| CorePro LED PLC 6.5W 840 2P G24d-2 | 6.5     | 650               | EM        | 4000       | 80  | 54129600 |
| CorePro LED PLC 8.5W 830 2P G24d-3 | 8.5     | 900               | EM        | 3000       | 80  | 54123400 |
| CorePro LED PLC 8.5W 840 2P G24d-3 | 8.5     | 950               | EM        | 4000       | 80  | 54125800 |
| CorePro LED PLC 6.5W 830 4P G24q-2 | 6.5     | 600               | HF        | 3000       | 80  | 54119700 |
| CorePro LED PLC 6.5W 840 4P G24q-2 | 6.5     | 650               | HF        | 4000       | 80  | 54121000 |
| CorePro LED PLC 9W 830 4P G24q-3   | 9.0     | 900               | HF        | 3000       | 80  | 54115900 |
| CorePro LED PLC 9W 840 4P G24q-3   | 9.0     | 950               | HF        | 4000       | 80  | 54117300 |

## CoreLine SlimDownlight



3000/4000



NON-  
DIMMABLE



50.000 H



120°  
BEAM ANGLE



A<sup>+++</sup>  
EEL

| Product description         | Wattage | Luminaire lumen output | Color temp | CRI  | EOC      |
|-----------------------------|---------|------------------------|------------|------|----------|
|                             | W       | lm                     | K          |      | 8718696  |
| DN135B LED10S/830 PSU II WH | 13      | 1000                   | 3000       | ≥ 80 | 07042099 |
| DN135B LED10S/840 PSU II WH | 13      | 1000                   | 4000       | ≥ 80 | 07043799 |
| DN135B LED20S/830 PSU II WH | 28      | 2000                   | 3000       | ≥ 80 | 07044499 |
| DN135B LED20S/840 PSU II WH | 28      | 2000                   | 4000       | ≥ 80 | 07045199 |
| DN135C LED10S/830 PSU II WH | 13      | 1000                   | 3000       | ≥ 80 | 07046899 |
| DN135C LED10S/840 PSU II WH | 13      | 1000                   | 4000       | ≥ 80 | 07047599 |
| DN135C LED20S/830 PSU II WH | 28      | 2000                   | 3000       | ≥ 80 | 07048299 |
| DN135C LED20S/840 PSU II WH | 28      | 2000                   | 4000       | ≥ 80 | 07049999 |

## OccuSwitch Controls



| Product description                | EOC      |
|------------------------------------|----------|
|                                    | 8718696  |
| LRM1011 OS presence detector small | 44209800 |





# Restroom

## LED spot classic



2700



GU10



GU5.3



NON-DIMMABLE



15,000 H



36° BEAM ANGLE



EEL

| Product description                   | Wattage | Lamp lumen output | Color temp | CRI | EOC      |
|---------------------------------------|---------|-------------------|------------|-----|----------|
|                                       | W       | lm                | K          |     | 8718696  |
| CLA LEDspotMV ND 3.1-25W GU10 827 36D | 3.1     | 215               | 2700       | 80  | 58769000 |
| CLA LEDspotMV ND 3.5-35W GU10 827 36D | 3.5     | 260               | 2700       | 80  | 55120200 |
| CLA LEDspotMV ND 5.3-50W GU10 827 36D | 5.3     | 390               | 2700       | 80  | 55118900 |
| CLA LEDspotLV ND 3-20W MR16 827 36D   | 3.0     | 380               | 2700       | 80  | 55114100 |
| CLA LEDspotLV ND 5-35W MR16 827 36D   | 5.0     | 370               | 2700       | 80  | 55110300 |



2700/3000



GU10



GU5.3



DIMMABLE



15,000 H



36° BEAM ANGLE



EEL

| Product description                  | Wattage | Lamp lumen output | Color temp | CRI | EOC      |
|--------------------------------------|---------|-------------------|------------|-----|----------|
|                                      | W       | lm                | K          |     | 8718696  |
| CLA LEDspotMV D 4.4-35W GU10 827 36D | 4.4     | 250               | 2700       | 80  | 56558200 |
| CLA LEDspotMV D 4.4-35W GU10 830 36D | 4.4     | 260               | 3000       | 80  | 58167400 |
| CLA LEDspotMV D 5.5-50W GU10 827 36D | 5.5     | 350               | 2700       | 80  | 56560500 |
| CLA LEDspotMV D 5.5-50W GU10 830 36D | 5.5     | 365               | 3000       | 80  | 58169800 |

## CoreLine Recessed Spot



2700/3000/4000



DIMMABLE



50,000 H



32° BEAM ANGLE



EEL


| Product description             | Wattage | Luminaire lumen output | Color temp | CRI  | EOC      |
|---------------------------------|---------|------------------------|------------|------|----------|
|                                 | W       | lm                     | K          |      | 8718696  |
| RS140B LED6-32-/827 PSR PI6 WH  | 10      | 650                    | 2700       | ≥ 85 | 06897799 |
| RS140B LED6-32-/830 PSR PI6 WH  | 10      | 650                    | 3000       | ≥ 85 | 06898499 |
| RS140B LED6-32-/840 PSR PI6 WH  | 10      | 650                    | 4000       | ≥ 85 | 06899199 |
| RS141B LED6-32-/827 PSR PI6 WH  | 10      | 650                    | 2700       | ≥ 85 | 06903599 |
| RS141B LED6-32-/830 PSR PI6 WH  | 10      | 650                    | 3000       | ≥ 85 | 06904299 |
| RS141B LED6-32-/840 PSR PI6 WH  | 10      | 650                    | 4000       | ≥ 85 | 06905999 |
| RS140B LED6-60-/830 PSR PI6 WH  | 10      | 650                    | 3000       | ≥ 80 | 07125099 |
| RS140B LED6-60-/840 PSR PI6 WH  | 10      | 650                    | 4000       | ≥ 80 | 07126799 |
| RS141B LED12-32-/830 PSR PI6 WH | 16      | 1200                   | 3000       | ≥ 80 | 07127499 |
| RS141B LED12-32-/840 PSR PI6 WH | 16      | 1200                   | 4000       | ≥ 80 | 07128199 |

## OccuSwitch Controls




| Product description                 | EOC      |
|-------------------------------------|----------|
|                                     | 8718696  |
| LRM1032 OS Mov Det Switch 3w WR DIN | 44225800 |

## MASTER TL-D Xtreme




| Product description            | Wattage | Lamp lumen output | Operation | Color temp | CRI | EOC      |
|--------------------------------|---------|-------------------|-----------|------------|-----|----------|
|                                | W       | lm                |           | K          |     | 8711500  |
| MASTER TL-D Xtreme 18W/830 SLV | 18      | 1350              | EM & HF   | 3000       | 82  | 54492640 |
| MASTER TL-D Xtreme 18W/840 SLV | 18      | 1350              | EM & HF   | 4000       | 82  | 54496440 |
| MASTER TL-D Xtreme 18W/865 SLV | 18      | 1250              | EM & HF   | 6500       | 82  | 89275140 |
| MASTER TL-D Xtreme 36W/830 SLV | 36      | 3250              | EM & HF   | 3000       | 82  | 55866440 |
| MASTER TL-D Xtreme 36W/840 SLV | 36      | 3250              | EM & HF   | 4000       | 82  | 55868840 |
| MASTER TL-D Xtreme 36W/865 SLV | 36      | 3150              | EM & HF   | 6500       | 82  | 89277540 |
| MASTER TL-D Xtreme 58W/830 SLV | 58      | 5150              | EM & HF   | 3000       | 82  | 55882440 |
| MASTER TL-D Xtreme 58W/840 SLV | 58      | 5150              | EM & HF   | 4000       | 82  | 55886240 |
| MASTER TL-D Xtreme 58W/865 SLV | 58      | 5000              | EM & HF   | 6500       | 82  | 89279940 |

## CorePro LEDtube EM



| Product description                | Wattage | Lamp lumen output | Operation  | Color temp | CRI | EOC      |
|------------------------------------|---------|-------------------|------------|------------|-----|----------|
|                                    | W       | lm                |            | K          |     | 8718696  |
| CorePro LEDtube 1500mm 20W 840 C G | 20      | 2000              | EM & Mains | 4000       | 80  | 56608400 |
| CorePro LEDtube 1500mm 20W 865 C G | 20      | 2000              | EM & Mains | 6500       | 80  | 56610700 |
| CorePro LEDtube 1200mm 20W 865 C G | 16      | 1600              | EM & Mains | 6500       | 80  | 49281900 |
| CorePro LEDtube 1200mm 20W 865 C G | 16      | 1600              | EM & Mains | 4000       | 80  | 49283300 |

## MASTER LEDtube High Output EM/HF



| Product description              | Wattage | Lamp lumen output | Operation  | Color temp | CRI | EOC 1 pcs (C)*  |
|----------------------------------|---------|-------------------|------------|------------|-----|-----------------|
|                                  | W       | lm                |            | K          |     |                 |
| MASTER LEDtube 1200mm            | 18      | 2000              | EM & Mains | 3000       | 83  | 871869642198700 |
| MASTER LEDtube 1200mm            | 18      | 2100              | EM & Mains | 4000       | 83  | 871869642200700 |
| MASTER LEDtube 1200mm            | 18      | 2100              | EM & Mains | 6500       | 83  | 871869642202100 |
| MASTER LEDtube 1500mm            | 23      | 2900              | EM & Mains | 3000       | 83  | 871829178956700 |
| MASTER LEDtube 1500mm            | 23      | 3100              | EM & Mains | 4000       | 83  | 871829178958100 |
| MASTER LEDtube 1500mm            | 23      | 3100              | EM & Mains | 6500       | 83  | 871829178960400 |
| MASTER LEDtube 1200mm InstantFit | 18      | 2000              | HF         | 3000       | 83  | 871869651456600 |
| MASTER LEDtube 1200mm InstantFit | 18      | 2100              | HF         | 4000       | 83  | 871869647125800 |
| MASTER LEDtube 1200mm InstantFit | 18      | 2100              | HF         | 6500       | 83  | 871869647127200 |
| MASTER LEDtube 1500mm InstantFit | 25      | 2900              | HF         | 3000       | 83  | 871869651458000 |
| MASTER LEDtube 1500mm InstantFit | 25      | 3100              | HF         | 4000       | 83  | 871869640886500 |
| MASTER LEDtube 1500mm InstantFit | 25      | 3100              | HF         | 6500       | 83  | 871869640888900 |



## CoreLine Waterproof



4000/6500



NON-DIMMABLE



50,000 H



240°  
BEAM ANGLE



EEL

| Product description         | Wattage | Luminaire lumen output | Operation | Color temp | CRI  | EOC      |
|-----------------------------|---------|------------------------|-----------|------------|------|----------|
|                             | W       | lm                     |           | K          |      | 8718696  |
| WT120C LED18S/840 PSU L600  | 17      | 1800                   |           | 4000       | ≥ 80 | 84045900 |
| WT120C LED22S/840 PSU L1200 | 20      | 2200                   |           | 4000       | ≥ 80 | 84046600 |
| WT120C LED34S/840 PSU L1500 | 29      | 3400                   |           | 4000       | ≥ 80 | 84047300 |
| WT120C LED40S/840 PSU L1200 | 38      | 4000                   |           | 4000       | ≥ 80 | 84048000 |
| WT120C LED60S/840 PSU L1500 | 57      | 6000                   |           | 4000       | ≥ 80 | 84049700 |

## OccuSwitch Controls



| Product description              | EOC      |
|----------------------------------|----------|
|                                  | 8718696  |
| LRM1040 OS Move Det IP54 240 dgr | 22573700 |

