

PHILIPS

LED lamps classic



Designed to be seen

The perfect mix of classic style
and today's LED efficiency

Looks like incandescent saves like LED

Now you can turn back the clock and recreate that classic look and feel of incandescent lighting with Philips LED lamps classic. A collection of heritage-designed lamps that offer some of today's best energy savings.



Designed to be seen

Philips LED lamps classic recreates incandescent lighting in every way possible. The classic bulb shapes are designed for timeless, decorative appeal. But it's what's inside that makes them so different. We've given our LED energy-saving technology a new twist by arranging the LED to mimic incandescent, so you can create a glowing, warm white light without high energy bills.

Create intimate ambiances

The timeless appeal of Philips LED lamps classic makes them perfect for a wide range of applications:

Application areas

- Create a magical, intimate atmosphere in living rooms
- Add a touch of vintage ambience to restaurants, bars and hotel rooms
- Illuminate hospitals and museums with soothing, warm, white light.



Spot the new classic

A beautiful alternative to halogen

As new ErP legislation comes into effect, mains-voltage halogen lamps will no longer be available for sale. Our LED spots classic are just as iconic and are now made from glass. You'll appreciate the stylish design for its well-known look and feel whether the lamp is switched on or off. Philips LED spots classic are the perfect halogen replacement for high-end applications such as restaurants, hotels or private residences.

The single optic glass spots offer perfect beam, high quality light output with a good color rendering index of CRI80. Available as an MR16 LV and a GU10 MV. They're also a classic choice for their long lifetime and low energy consumption.

LED spot classic G10 and MR16 MV

- Long-lasting replacement for non-dimmable and dimmable spots
- LED replacement for halogens phased out by ErP
- Glass spot with single optics
- Optimized beam angle
- Dimmable versions: 3.2-35W and 5.3-50W
- 15,000 hours lifetime




DimTone
technology
available
NOW

DimTone - the more you dim, the warmer the light

Now all the LED bulbs Clear and Frosted in our portfolio are available with DimTone technology. The unique feature takes dimming to a next level. As the light is dimmed, the color temperature is reduced. This creates a warm, intimate ambience at lower light levels with a same candle-like effect as dimmed halogens or incandescent lamps. So you can create the most elegant and luxurious lighting for hospitality, bar and retail environments.



LED filament technology





Long-lasting energy savings

The real beauty of Philips LED lamps classic is that they use less energy. With 90% energy savings and a long and reliable life time of 1,000 vs 15,000 hours, 15 times longer than incandescent bulbs, you'll save on energy and replacement costs. So you can look forward to hours of beautiful ambience that looks like incandescent and lasts like LED.

up to **90%**
energy saving
15,000
hours lifetime



Incandescent

Since 1879
NO energy saving
1,000 hours lifetime

Halogen

30% energy saving
2,000 hours lifetime

Philips LED lamps classic

Decorative light
Classic design
LED technology

	Equivalent wattage	Equivalent wattage	Equivalent input wattages
Candles	25 W	18 W	2.3 W
Lusters	40 W	28 W	4.3 W
Bulbs	60 W	42 W	7.5 W
Spots		35 W	3.2 W
		50 W	5.3 W

Product specifications

Philips LED bulb classic



Product type	LED	Traditional	Lumen output	Efficacy	Bulb shape	CRI	Color temperature	Dimmable	EOC
CLA LED bulb	W	W	lm	lm/W			K	Yes/No	8718696
6-60W A60 E27 827 CL ND	6	60	806	134	A60	80	2700	No	40100000
6-60W ST64 E27 827 CL ND	6	60	806	134	ST64	80	2700	No	57405800
3.5-40W A60 E27 827 CL ND	3.5	40	470	134	A60	80	2700	No	57399000
3.5-40W ST64 E27 827 CL ND	3.5	40	470	118	ST64	80	2700	No	57403400
7.5-60W A60 E27 827 CL D	7.5	60	806	107	A60	80	2700	Yes	57547500
7.5-60W A60 B22 827 CL D	7.5	60	806	107	A60	80	2700	Yes	57551200
7.5-48W A60 E27 820 GOLD D	7.5	48	600	80	A60	80	2000	Yes	57567300
7.5-48W A60 B22 820 GOLD D	7.5	48	600	80	A60	80	2000	Yes	58741600
7-60W ST64 E27 827 CL D	7	60	806	115	ST64	80	2700	Yes	57569700
7-60W ST64 B22 827 CL D	7	60	806	115	ST64	80	2700	Yes	57581900
7-55W ST64 E27 825 GOLD D	7	55	720	103	ST64	80	2500	Yes	57571000
7-50W ST64 E27 820 GOLD D	7	50	630	90	ST64	80	2000	Yes	57573400
7-50W ST64 B22 820 GOLD D	7	50	630	90	ST64	80	2000	Yes	58108700
5-40W A60 E27 827 CL D	5	40	470	94	A60	80	2700	Yes	57545100
5-40W A60 B22 822 CL D	5	40	470	94	A60	80	2700	Yes	57549900



Philips LED globe classic



Product type	LED	Traditional	Lumen output	Efficacy	Bulb shape	CRI	Color temperature	Dimmable	EOC
CLA LED globe	W	W	lm	lm/W			K	Yes/No	8718696
6-60W G93 E27 827 CL ND	6	60	806	134	G93	80	2700	No	57417100
7-60W G93 E27 827 CL D	7	60	806	115	G93	80	2700	Yes	57575800
7-50W G120 E27 820 GOLD D	7	50	630	90	G120	80	2000	Yes	57577200
7-50W G120 B22 820 GOLD D	7	50	630	90	G120	80	2000	Yes	58743000



Philips LED candle classic



2700



E14



B22



15,000 H



EEL

Product type	LED	Traditional	Lumen output	Efficacy	Bulb shape	CRI	Color temperature	Dimmable	EOC
CLA LED candle	W	W	lm	lm/W			K	Yes/No	8718696
4-40W B35 E14 827 CL ND	4	40	470	118	B35	80	2700	No	58729400
2-25W B35 E14 827 CL ND	2	25	250	125	B35	80	2700	No	57407200
2-25W BA35 E14 827 CL ND	2	25	250	125	BA35	80	2700	No	57409600
2-25W ST35 E14 827 CL ND	2	25	250	125	ST35	80	2700	No	57411900
5-40W B35 B22 827 CL D	5	40	470	94	B35	80	2700	Yes	57563500
5-40W B35 E14 827 CL D	5	40	470	94	B35	80	2700	Yes	57555000
5-40W BA35 E14 827 CL D	5	40	470	94	BA35	80	2700	Yes	57557400
3-25W B35 E14 827 CL D	3	25	300	100	B35	80	2700	Yes	57553600



Philips LED luster classic



2700



E14



E27



B22



15,000 H



EEL

Product type	LED	Traditional	Lumen output	Efficacy	Bulb shape	CRI	Color temperature	Dimmable	EOC
CLA LED luster	W	W	lm	lm/W			K	Yes/No	8718696
4-40W P45 E14 827 CL ND	4	40	470	118	P45	80	2700	No	58725600
4-40W P45 E27 827 CL ND	4	40	470	118	P45	80	2700	No	58727000
2-25W P45 E14 827 CL ND	2	25	250	125	P45	80	2700	No	57413300
2-25W P45 E27 827 CL ND	2	25	250	125	P45	80	2700	No	57415700
5-40W P45 E14 827 CL D	5	40	470	94	P45	80	2700	Yes	57559800
5-40W P45 E27 827 CL D	5	40	470	94	P45	80	2700	Yes	57561100
5-40W P45 B22 827 CL D	5	40	470	94	P45	80	2700	Yes	57565900
3-25W P45 E14 827 CL D	3	25	300	100	P45	80	2700	Yes	58111700
3-25W P45 E27 827 CL D	3	25	300	100	P45	80	2700	Yes	58115500



Philips LED spot classic MV



2200-2700/3000



GU10



15,000 /
25,000 H



EEL



BEAM ANGLE

Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Color temperature	Dimmable	EOC
CLA LED spot	W	W	lm	lm/W	cd	°		K	Yes/No	8718696
CLA LED spot MV 4.6-50W GU10 827 36D ND	4.6	50	355	77	700	36	80	2700	No	59994500
CLA LED spot MV 3.5-35W GU10 827 36D ND	3.5	35	255	73	545	36	80	2700	No	59992100
CLA LED spot MV 5.5-50W GU10 827 36D D	5.5	50	350	64	650	36	80	2700	Yes	56560500
CLA LED spot MV 5.5-50W GU10 830 36D D	5.5	50	365	66	680	36	80	3000	Yes	58169800
CLA LED spot MV 4.4-35W GU10 827 36D D	4.4	35	250	57	500	36	80	2700	Yes	56558200
CLA LED spot MV 4.4-35W GU10 830 36D D	4.4	35	260	59	520	36	80	3000	Yes	58167400
CLA LED spot MV 3.1-25W GU10 827 36D ND	3.1	25	215	69	470	36	80	2700	No	58769000
MAS LEDspot MV CLA 5-50W GU10 36D DimTone	5	50	345	69	600	36	80	2700-2200	Yes	66762000
MAS LEDspot MV CLA 4.5-35W GU10 36D DimTone	4.5	35	245	61	450	36	80	2700-2200	Yes	66764400

To find out more about Philips LED lamps classic go to www.philips.com/masterledlamps

