



CorePro LED tube

600, 1200 &
1500 mm




Made
from
glass

The most affordable switch

Now CorePro LED tube offer even better value with the new glass housing. Plus we have improved the energy consumption from 80 to 100 lm/W to make them more efficient. A simple, retrofit replacement, the 600mm, 1200mm and 1500mm CorePro LED tube offer low energy consumption with instant savings. Perfect for basic applications that demand an affordable solution.

**Now
available
in HF!**



240°
beam angle

- ✓ Uniform light spread for car parks, storage rooms, warehouses
- ✗ Not for high lux applications like offices or industry

CorePro LED tube



4000 / 6500



G13



NON-DIMMABLE



FRAGILE
600 - 1200 mm



30,000 H



EEL



BEAM ANGLE



DIMENSIONS

589 1198 1498

Product type	LED	Lumen output	Operation	Beam angle	CRI	Color temperature	EOC 1 pcs (C)
CorePro LED tube (EM)*	W	lm		°		K	8718696
600mm 8W 840 C G	8	800	EM & Mains	240	80	4000	49277200
600mm 8W 865 C G	8	800	EM & Mains	240	80	6500	49279600
1200mm 16W 840 C G	16	1600	EM & Mains	240	80	4000	49281900
1200mm 16W 865 C G	16	1600	EM & Mains	240	80	6500	49283300
1500mm 20W 840 C G	20	2000	EM & Mains	240	80	4000	56608400
1500mm 20W 865 C G	20	2000	EM & Mains	240	80	6500	56610700
CorePro LED tube (HF)	W	lm		°		K	8718696
600mm 9W840 T8 G InstantFit	9	800	HF	240	80	4000	65217600
600mm 9W865 T8 G InstantFit	9	800	HF	240	80	6500	65219000
1200mm 15W 840 T8 G InstantFit	15	1600	HF	240	83	4000	58127800
1200mm 15W 865 T8 G InstantFit	15	1600	HF	240	83	6500	58129200
1500mm 20W 840 T8 G InstantFit	20	2000	HF	240	83	4000	59203800
1500mm 20W 865 T8 G InstantFit	20	2000	HF	240	83	6500	59205200

*) incl. EMP

