

The Philips logo is displayed in a bold, blue, sans-serif font. It is positioned within a white rectangular area that has a curved bottom edge, which is set against a dark red background that also curves at the bottom.

Trade lighting

# Every light the office needs

Whether it's LED, conventional  
luminaires or controls, we've got the  
right installation solution for offices.



Find the right light  
**for every  
kind of office**



Today's offices are bright, flexible spaces that offer more exciting lighting possibilities than ever before. With light you can connect the whole office environment. From open plan offices that energize and inspire, to corridors, restrooms and parking areas that feel safe and secure.

But office lighting isn't just about providing the right light levels to perform tasks safely and effectively. Your customers will also be looking for ways to reduce their energy and maintenance bills, as well as the cost of the lighting installation itself.

Our solutions let you approach office lighting from four different angles. From high quality conventional solutions to sophisticated controls that are smart, sustainable and ultra-efficient. So with Philips, you have every light the office needs.



Relamping

Option

## Conventional lamp

With fluorescent tri-phosphor technology, our conventional lamp **upgrades** offer high quality light and a long to extremely long and reliable lifetime.

Option

## LED lamp

You can improve existing luminaire installations quickly and simply by **replacing** conventional lamps with energy-efficient LEDs.



Renovation

Option

## LED luminaire

For **renovations** or new installations, our one-to-one replacements are an energy-saving alternative to existing luminaires.

Option

## Lighting control

Add lighting controls to LED luminaires and you can create a **smarter lighting** solution.

# Choosing the right light

We've made it easy to compare different lighting solutions depending on when and where they'll be used in the office. So whether they need an upgrade, replacement, renovation or smart solution, you can offer your customers the right office light every time.



**Open plan office**



**Corridor**



**Restroom**



**Parking**

## Conventional

## LED lamp



MASTER TL5 High Efficiency



MASTER LEDtube 600-1200-1500 mm



MASTER PL-C



CorePro LED PLC



LED spot classic



MASTER TL-D Xtreme



CorePro LEDtube

## LED luminaire

## Lighting control



CoreLine Panel OC



OccuSwitch Presence Detector LRM1011



CoreLine SlimDownlight



OccuSwitch Presence Detector LRM1011



CoreLine Recessed Spot (UPDATED)



OccuSwitch Movement Detector LRM1032



CoreLine Waterproof



OccuSwitch Movement Detector LRM1040





# Open plan office





Option

## Conventional lamp

### MASTER TL5 High Efficiency

- › Lamp efficacies up to 104 lm/W
- › Low energy consumption
- › Constant lumen level, excellent lumen maintenance
- › Good color rendering
- › Choice out of 6 color temperatures



Option

## LED lamp

### MASTER LEDtube Ultra Output T8 1200 and 1500 mm

- › Fluorescent TL-D replacement
- › Ultra output of 2300 lm up to 3700 lm
- › High quality light with outstanding lamp efficiency of 148 lm/W
- › High light output designed for ergonomic norms
- › Available in 1200 and 1500 mm lengths
- › One blue stripe for EM & Mains control gear
- › Two blue stripes for HF control gear

### MASTER LEDtube 600 mm

- › Up to 1050 lumens light output
- › Choice of color temperatures: 3000K, 4000K, 6500K
- › One blue stripe for EM & Mains control gear
- › Two blue stripes for HF control gear



new





## Option LED luminaire

### CoreLine Panel OC

- › Surface-of-light panel design
- › 50,000 hours lifetime
- › 3400 lumens light output
- › Unified Glare Rating (UGR) =18 (square design); UGR<19 (rectangular)
- › Saves up to 40% energy compared to functional TL-D luminaires






Option

## Lighting control

### OccuSwitch Presence Detector LRM1011

- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m<sup>2</sup>
- › Detachable mains connector
- › Separate Weiland cable for hassle-free installation



Application bundle

Save up to  
**30%**

more energy -  
add a presence  
detector to your  
luminaires





# Corridor





Option

## Conventional lamp

### MASTER PL-C

- › Efficient, compact fluorescent lamp
- › Optimum light performance
- › Choice out of 4 color temperatures
- › 2 pin with instant starter for electromagnetic gear
- › 4 pin for HF control gear
- › 4 pins enables dimming down to 10%
- › 600, 900, 1200 and 1800 lumen at 10, 13, 18 and 26W



Option

## LED lamp

### CorePro LED PLC

- › Retrofit LED upgrade for downlighting
- › Incredible energy savings
- › 30,000 hours lifetime, less maintenance
- › Fits neatly into existing fixtures
- › Similar PLC form-factor - no building or modification work
- › The range includes both 2-pin (EM) and 4-pin (HF) lamps options.



new



Option

## LED luminaire

### CoreLine SlimDownlight

- › Ultra-thin, recessed LED downlight
- › One-to-one replacement for conventional luminaires
- › Saves up to 40% energy compared to conventional CFLY luminaires
- › 50,000 hours lifetime
- › 'Surface of light' for a high-end look
- › Extremely small build-in depth (<50 mm) fits more ceiling types





Option

## Lighting control

### OccuSwitch Presence Detector LRM1011

- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m<sup>2</sup>
- › Detachable mains connector
- › Separate Weiland cable for hassle-free installation





# Restroom



## Option LED lamp

### LED spot classic G10 and MR16

- › Long-lasting replacement for non-dimmable and dimmable spots
- › Iconic glass spot with single optic, no shades in the beam
- › LED replacement for halogens phased out by ErP
- › Dimmable versions: GU10 3.2-35W and 5.3-50W
- › 15,000 hours lifetime





Option  
LED luminaire



**CoreLine Recessed Spot**

- › Designed to replace halogen luminaires
- › Saves 80% energy compared to conventional halogen luminaires
- › 50,000 hours lifetime, 15x halogen
- › Slim design (60mm) fits in most types of ceiling
- › Compatible with almost all wall-mounted dimmers

Fast fit  
with push-in  
connectors



Option  
Lighting control

**OccuSwitch Movement Detector LRM1032**


- › Light switch with built-in movement detector
- › Switches lights off when room is vacated
- › Saves up to 30% on electricity
- › Covers 20 - 25 m2
- › Detachable mains connector
- › Separate Wieland cable for hassle-free installation



Application bundle  
Save up to  
**50%**  
more energy -  
add a movement  
detector to your  
luminaires



# Parking







Option

## Conventional lamp

### MASTER TL-D Xtreme

- › Extremely long lifetime up to 90.000 hrs - 10 years of operation
- › Lower maintenance costs
- › Fewer early failures
- › Less waste and disposal costs
- › Easy switch from spot to group replacement



Option

## LED lamp

### MASTER LEDtube High Output EM/HF

- › An affordable LED solution
- › Minimizes overall lighting costs
- › Retrofit replacement on EM and HF ballast (Instant Fit) installations
- › Available in 1200 mm and 1500 mm lengths for EM and HF gear



### CorePro LEDtube EM

- › An affordable LED solution
- › Minimizes overall lighting costs
- › Retrofit replacement on electromagnetic (EM) ballast installations
- › Available in 1200 mm and 1500 mm lengths
- › Beam angle of 240°



NEW



240° beam angle

- ✓ Uniform light spread for car parks, storage rooms, warehouses
- ✗ Not for high lux applications like offices or industry



## Option LED luminaire

### CoreLine Waterproof

- › Direct replacement for conventional waterproof luminaires (18 to 58 W TL-D)
- › Same light performance, installation flexibility and length
- › Reliable integrated LED technology
- › 50,000 hours lifetime
- › Maintenance-free installation



Saves  
**50%**  
energy  
compared  
with TL-D



## Option Lighting control

### Movement detector LRM1040

- › Designed for outdoor or indoor use (IP54)
- › Adjustable light sensor prevents switch on in daylight
- › Wall, corner or ceiling mounting
- › Cover 12m range over 240°




Application bundle  
Save up to  
**70%**  
more energy -  
add a movement  
detector to your  
luminaires



For a longer  
lifetime, turn  
lighting off when  
not required

# Calculate **Total Cost of Ownership**



Every business is keen to reduce energy, maintenance and operating costs to meet tight budgets and environmental targets. Understanding the total costs of a lighting installation over its whole life time can help to sell the right lighting choice. Our quick comparison tool includes energy consumption, maintenance costs and carbon footprint. So you can instantly see the Total Cost of Ownership (TCO) and show your clients how much they can save.

Just follow these four simple steps:

- 1** Go to the link for the product TCO calculator  
LEDlamps  
[www.philips.com/masterledlamps](http://www.philips.com/masterledlamps)  
[www.philips.com/coreproledlamps](http://www.philips.com/coreproledlamps)  
LEDtubes  
[www.philips.com/LEDtube](http://www.philips.com/LEDtube)  
Coreline  
[www.philips.com/coreline](http://www.philips.com/coreline)  
Application bundles  
[www.philips.com/applicationbundles](http://www.philips.com/applicationbundles)
- 2** Follow the steps on screen
- 3** Complete your project details
- 4** The online tool automatically calculates the TCO

# Specifications

## Open plan office

### MASTER TL5 High Efficiency



  
2700/3000/3500/  
4000/5000/6500



G5



DIMMABLE



24,000 H



EEL

Product description	Wattage	Lamp lumen output	Color temp	CRI	EOC
	W	lm	K		8711500
MASTER TL5 14W/827 1SL/40	13.7	1350	2700	82	64102155
MASTER TL5 14W/830 UNP/40	13.7	1350	3000	82	61063855
MASTER TL5 14W/830 1SL/40	13.7	1350	3000	82	63938755
MASTER TL5 14W/830 1SL/20	13.7	1350	3000	82	63938705
MASTER TL5 14W/835 1SL/40	13.7	1350	3500	82	70765955
MASTER TL5 14W/840 UNP/40	13.7	1350	4000	82	61066955
MASTER TL5 14W/840 1SL/40	13.7	1350	4000	82	63940055
MASTER TL5 14W/840 1SL/20	13.7	1350	4000	82	63940005
MASTER TL5 14W/865 UNP/40	13.7	1250	6500	82	61068355
MASTER TL5 14W/865 1SL/40	13.7	1250	6500	82	71009355
MASTER TL5 21W/827 1SL/40	20.7	2100	2700	82	64320955
MASTER TL5 21W/830 UNP/40	20.7	2100	3000	82	61070655
MASTER TL5 21W/830 1SL/40	20.7	2100	3000	82	63942455
MASTER TL5 21W/830 1SL/20	20.7	2100	3000	82	63942405
MASTER TL5 21W/840 UNP/40	20.7	2100	4000	82	61072055
MASTER TL5 21W/840 1SL/40	20.7	2100	4000	82	63944855
MASTER TL5 21W/840 1SL/20	20.7	2100	4000	82	63944805
MASTER TL5 21W/865 UNP/40	20.7	1950	6500	82	61077555
MASTER TL5 21W/865 1SL/40	20.7	1950	6500	82	71011655
MASTER TL5 28W/827 1SL/40	27.8	2900	2700	82	64322355
MASTER TL5 28W/830 UNP/40	27.8	2900	3000	82	61081255
MASTER TL5 28W/830 1SL/40	27.8	2900	3000	82	63946255
MASTER TL5 28W/830 1SL/20	27.8	2900	3000	82	63946205
MASTER TL5 28W/835 1SL/40	27.8	2900	3500	82	71004855
MASTER TL5 28W/840 UNP/40	27.8	2900	4000	82	61090455
MASTER TL5 28W/840 1SL/40	27.8	2900	4000	82	63948655
MASTER TL5 28W/840 1SL/20	27.8	2900	4000	82	63948605
MASTER TL5 28W/850 1SL/40	27.8	2775	5000	82	26020855
MASTER TL5 28W/865 UNP/40	27.8	2700	6500	82	61092855
MASTER TL5 28W/865 1SL/40	27.8	2700	6500	82	71015455
MASTER TL5 35W/827 1SL/40	34.7	3650	2700	82	64324755
MASTER TL5 35W/830 UNP/40	34.7	3650	3000	82	61103155
MASTER TL5 35W/830 1SL/40	34.7	3650	3000	82	63950955
MASTER TL5 35W/830 1SL/20	34.7	3650	3000	82	63950905
MASTER TL5 35W/835 1SL/40	34.7	3650	3500	82	71006255
MASTER TL5 35W/840 UNP/40	34.7	3650	4000	82	61105555
MASTER TL5 35W/840 1SL/40	34.7	3650	4000	82	63952355
MASTER TL5 35W/840 1SL/20	34.7	3650	4000	82	63952305
MASTER TL5 35W/865 UNP/40	34.7	3400	6500	82	61107955
MASTER TL5 35W/865 1SL/40	34.7	3400	6500	82	71018555


## MASTER LEDtube Ultra Output



Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8718696
MASTER LEDtube 600mm RN*	9	1000	EM & Mains	3000	83	57279500
MASTER LEDtube 600mm RS*	9	1000	EM & Mains	3000	83	46141900
MASTER LEDtube 600mm RN*	9	1050	EM & Mains	4000	83	57281800
MASTER LEDtube 600mm RS*	9	1050	EM & Mains	4000	83	46143300
MASTER LEDtube 600mm RN*	9	1050	EM & Mains	6500	83	57283200
MASTER LEDtube 600mm RS*	9	1050	EM & Mains	6500	83	46145700
MASTER LEDtube 600mm	10.5	1000	HF	3000	83	55965900
MASTER LEDtube 600mm	10.5	1050	HF	4000	83	55967300
MASTER LEDtube 600mm	10.5	1050	HF	6500	83	55969700
MASTER LEDtube 1200mm	18	2300	EM & Mains	3000	83	46149500
MASTER LEDtube 1200mm	18	2500	EM & Mains	4000	83	46151800
MASTER LEDtube 1200mm	18	2500	EM & Mains	6500	83	46155600
MASTER LEDtube 1500mm	25	3400	EM & Mains	3000	83	46157000
MASTER LEDtube 1500mm	25	3700	EM & Mains	4000	83	46159400
MASTER LEDtube 1500mm	25	3700	EM & Mains	6500	83	46163100
MASTER LEDtube 1200mm	21	2300	HF	3000	83	55282700
MASTER LEDtube 1200mm	21	2500	HF	4000	83	55278000
MASTER LEDtube 1200mm	21	2500	HF	6500	83	55280300
MASTER LEDtube 1500mm	26	3400	HF	3000	83	55288900
MASTER LEDtube 1500mm	26	3700	HF	4000	83	55284100
MASTER LEDtube 1500mm	26	3700	HF	6500	83	55286500

\* RS = Region Southern Europe / RN = Region Northern Europe

## CoreLine Panel Office Compliant



Product description	Wattage	Luminaire lumen output	Color temp	CRI	EOC
	W	lm	K		8718696
RC127V LED34S/840 PSU W60L60 OC	41	3400	4000	≥ 80	07088899
RC127V LED34S/830 PSU W60L60 OC	41	3400	3000	≥ 80	07089599
RC127V LED34S/840 PSU W30L120 OC	41	3400	4000	≥ 80	07090199
RC127V LED34S/830 PSU W30L120 OC	41	3400	3000	≥ 80	07091899
RC127V LED34S/840 PSD W60L60 OC	41	3400	4000	≥ 80	07092599
RC127V LED34S/830 PSD W60L60 OC	41	3400	3000	≥ 80	07093299
RC127V LED34S/840 PSD W30L120 OC	41	3400	4000	≥ 80	07094999
RC127V LED34S/830 PSD W30L120 OC	41	3400	3000	≥ 80	07095699
RC128V LED34S/840 PSD W62L62 OC	41	3400	4000	≥ 80	07096399
RC128V LED34S/830 PSD W62L62 OC	41	3400	3000	≥ 80	07097099

# OccuSwitch Controls




Product description	EOC
	<b>8718696</b>
LRM1011 OS mov det small	44209800

## Corridor

### MASTER PL-C



Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8711500
MASTER PL-C 10W/827/2P	10	600	EM	2700	82	70681270
MASTER PL-C 10W/830/2P	10	600	EM	3000	82	70724670
MASTER PL-C 10W/840/2P	10	600	EM	4000	82	70498670
MASTER PL-C 13W/827/2P	13	900	EM	2700	82	62081170
MASTER PL-C 13W/830/2P	13	900	EM	3000	82	62084270
MASTER PL-C 13W/840/2P	13	900	EM	4000	82	62086670
MASTER PL-C 13W/865/2P	13	845	EM	6500	82	
MASTER PL-C 18W/827/2P	18	1200	EM	2700	82	62088070
MASTER PL-C 18W/830/2P	18	1200	EM	3000	82	62091070
MASTER PL-C 18W/840/2P	18	1200	EM	4000	82	62093470
MASTER PL-C 18W/865/2P	18	1150	EM	6500	82	
MASTER PL-C 26W/827/2P	26	1800	EM	2700	82	62095870
MASTER PL-C 26W/830/2P	26	1800	EM	3000	82	62098970
MASTER PL-C 26W/840/2P	26	1800	EM	4000	82	62100970
MASTER PL-C 26W/865/2P	26	1740	EM	6500	82	




Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8711500
MASTER PL-C 10W/827/4P	10	600	HF	2700	82	62325670
MASTER PL-C 10W/830/4P	10	600	HF	3000	82	62329470
MASTER PL-C 10W/840/4P	10	600	HF	4000	82	62330070
MASTER PL-C 13W/827/4P	13	900	HF	2700	82	62326370
MASTER PL-C 13W/830/4P	13	900	HF	3000	82	62331770
MASTER PL-C 13W/840/4P	13	900	HF	4000	82	62332470
MASTER PL-C 18W/827/4P	18	1200	HF	2700	82	62327070
MASTER PL-C 18W/830/4P	18	1200	HF	3000	82	62333170
MASTER PL-C 18W/840/4P	18	1200	HF	4000	82	62334870
MASTER PL-C 26W/827/4P	26	1800	HF	2700	82	62328770
MASTER PL-C 26W/830/4P	26	1800	HF	3000	82	62335570
MASTER PL-C 26W/840/4P	26	1800	HF	4000	82	62336270

## CorePro LED PLC



Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8718696
CorePro LED PLC 6.5W 830 2P G24d-2	6.5	600	EM	3000	80	54127200
CorePro LED PLC 6.5W 840 2P G24d-2	6.5	650	EM	4000	80	54129600
CorePro LED PLC 8.5W 830 2P G24d-3	8.5	900	EM	3000	80	54123400
CorePro LED PLC 8.5W 840 2P G24d-3	8.5	950	EM	4000	80	54125800
CorePro LED PLC 6.5W 830 4P G24q-2	6.5	600	HF	3000	80	54119700
CorePro LED PLC 6.5W 840 4P G24q-2	6.5	650	HF	4000	80	54121000
CorePro LED PLC 9W 830 4P G24q-3	9.0	900	HF	3000	80	54115900
CorePro LED PLC 9W 840 4P G24q-3	9.0	950	HF	4000	80	54117300

## CoreLine SlimDownlight



Product description	Wattage	Luminaire lumen output	Color temp	CRI	EOC
	W	lm	K		8718696
DN135B LED10S/830 PSU II WH	13	1000	3000	≥ 80	07042099
DN135B LED10S/840 PSU II WH	13	1000	4000	≥ 80	07043799
DN135B LED20S/830 PSU II WH	28	2000	3000	≥ 80	07044499
DN135B LED20S/840 PSU II WH	28	2000	4000	≥ 80	07045199
DN135C LED10S/830 PSU II WH	13	1000	3000	≥ 80	07046899
DN135C LED10S/840 PSU II WH	13	1000	4000	≥ 80	07047599
DN135C LED20S/830 PSU II WH	28	2000	3000	≥ 80	07048299
DN135C LED20S/840 PSU II WH	28	2000	4000	≥ 80	07049999

## OccuSwitch Controls



Product description	EOC
	8718696
LRM1011 OS presence detector small	44209800





# Restroom

## LED spot classic



2700



GU10



GU5.3



NON-DIMMABLE



15,000 H



36° BEAM ANGLE



EEL

Product description	Wattage	Lamp lumen output	Color temp	CRI	EOC
	W	lm	K		8718696
CLA LEDspotMV ND 3.1-25W GU10 827 36D	3.1	215	2700	80	58769000
CLA LEDspotMV ND 3.5-35W GU10 827 36D	3.5	260	2700	80	55120200
CLA LEDspotMV ND 5.3-50W GU10 827 36D	5.3	390	2700	80	55118900
CLA LEDspotLV ND 3-20W MR16 827 36D	3.0	380	2700	80	55114100
CLA LEDspotLV ND 5-35W MR16 827 36D	5.0	370	2700	80	55110300



2700/3000



GU10



GU5.3



DIMMABLE



15,000 H



36° BEAM ANGLE



EEL

Product description	Wattage	Lamp lumen output	Color temp	CRI	EOC
	W	lm	K		8718696
CLA LEDspotMV D 4.4-35W GU10 827 36D	4.4	250	2700	80	56558200
CLA LEDspotMV D 4.4-35W GU10 830 36D	4.4	260	3000	80	58167400
CLA LEDspotMV D 5.5-50W GU10 827 36D	5.5	350	2700	80	56560500
CLA LEDspotMV D 5.5-50W GU10 830 36D	5.5	365	3000	80	58169800

## CoreLine Recessed Spot



2700/3000/4000



DIMMABLE



50,000 H



32° 60° BEAM ANGLE



EEL


Product description	Wattage	Luminaire lumen output	Color temp	CRI	EOC
	W	lm	K		8718696
RS140B LED6-32-/827 PSR PI6 WH	10	650	2700	≥ 85	06897799
RS140B LED6-32-/830 PSR PI6 WH	10	650	3000	≥ 85	06898499
RS140B LED6-32-/840 PSR PI6 WH	10	650	4000	≥ 85	06899199
RS141B LED6-32-/827 PSR PI6 WH	10	650	2700	≥ 85	06903599
RS141B LED6-32-/830 PSR PI6 WH	10	650	3000	≥ 85	06904299
RS141B LED6-32-/840 PSR PI6 WH	10	650	4000	≥ 85	06905999
RS140B LED6-60-/830 PSR PI6 WH	10	650	3000	≥ 80	07125099
RS140B LED6-60-/840 PSR PI6 WH	10	650	4000	≥ 80	07126799
RS141B LED12-32-/830 PSR PI6 WH	16	1200	3000	≥ 80	07127499
RS141B LED12-32-/840 PSR PI6 WH	16	1200	4000	≥ 80	07128199

## OccuSwitch Controls



Product description	EOC
	8718696
LRM1032 OS Mov Det Switch 3w WR DIN	44225800

## MASTER TL-D Xtreme




Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8711500
MASTER TL-D Xtreme 18W/830 SLV	18	1350	EM & HF	3000	82	54492640
MASTER TL-D Xtreme 18W/840 SLV	18	1350	EM & HF	4000	82	54496440
MASTER TL-D Xtreme 18W/865 SLV	18	1250	EM & HF	6500	82	89275140
MASTER TL-D Xtreme 36W/830 SLV	36	3250	EM & HF	3000	82	55866440
MASTER TL-D Xtreme 36W/840 SLV	36	3250	EM & HF	4000	82	55868840
MASTER TL-D Xtreme 36W/865 SLV	36	3150	EM & HF	6500	82	89277540
MASTER TL-D Xtreme 58W/830 SLV	58	5150	EM & HF	3000	82	55882440
MASTER TL-D Xtreme 58W/840 SLV	58	5150	EM & HF	4000	82	55886240
MASTER TL-D Xtreme 58W/865 SLV	58	5000	EM & HF	6500	82	89279940

## CorePro LEDtube EM



Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8718696
CorePro LEDtube 1500mm 20W 840 C G	20	2000	EM & Mains	4000	80	56608400
CorePro LEDtube 1500mm 20W 865 C G	20	2000	EM & Mains	6500	80	56610700
CorePro LEDtube 1200mm 20W 865 C G	16	1600	EM & Mains	6500	80	49281900
CorePro LEDtube 1200mm 20W 865 C G	16	1600	EM & Mains	4000	80	49283300

## MASTER LEDtube High Output EM/HF



Product description	Wattage	Lamp lumen output	Operation	Color temp	CRI	EOC 1 pcs (C)*
	W	lm		K		
MASTER LEDtube 1200mm	18	2000	EM & Mains	3000	83	871869642198700
MASTER LEDtube 1200mm	18	2100	EM & Mains	4000	83	871869642200700
MASTER LEDtube 1200mm	18	2100	EM & Mains	6500	83	871869642202100
MASTER LEDtube 1500mm	23	2900	EM & Mains	3000	83	871829178956700
MASTER LEDtube 1500mm	23	3100	EM & Mains	4000	83	871829178958100
MASTER LEDtube 1500mm	23	3100	EM & Mains	6500	83	871829178960400
MASTER LEDtube 1200mm InstantFit	18	2000	HF	3000	83	871869651456600
MASTER LEDtube 1200mm InstantFit	18	2100	HF	4000	83	871869647125800
MASTER LEDtube 1200mm InstantFit	18	2100	HF	6500	83	871869647127200
MASTER LEDtube 1500mm InstantFit	25	2900	HF	3000	83	871869651458000
MASTER LEDtube 1500mm InstantFit	25	3100	HF	4000	83	871869640886500
MASTER LEDtube 1500mm InstantFit	25	3100	HF	6500	83	871869640888900



## CoreLine Waterproof



4000/6500



NON-DIMMABLE



50,000 H



240°  
BEAM ANGLE



EEL

Product description	Wattage	Luminaire lumen output	Operation	Color temp	CRI	EOC
	W	lm		K		8718696
WT120C LED18S/840 PSU L600	17	1800		4000	≥ 80	84045900
WT120C LED22S/840 PSU L1200	20	2200		4000	≥ 80	84046600
WT120C LED34S/840 PSU L1500	29	3400		4000	≥ 80	84047300
WT120C LED40S/840 PSU L1200	38	4000		4000	≥ 80	84048000
WT120C LED60S/840 PSU L1500	57	6000		4000	≥ 80	84049700

## OccuSwitch Controls



Product description	EOC
	8718696
LRM1040 OS Move Det IP54 240 dgr	22573700

