

PHILIPS

Showline

SL SUNLED 10



Wash lights

SL SUNLED 10

The Showline SL SUNLED 10 has ten cells of fixed white LEDs to deliver a blended wash of warm white light. Similar to the traditional and popular halogen strip light effect, the SUNLED 10 offers reduced power consumption, low heat output, and minimal maintenance. A tungsten mimic option shifts the color temperature as the luminaire dims, providing the distinctive warm tungsten feel at lower light levels. The SL SUNLED 10 can easily replace the halogen striplight effect in your designs without compromising the look and feel of your production.

Silent passive cooling ideal for studio environments. Multiple mounting points allows innovative hanging positions.

Product data



Features and benefits

- Delivers 6000 lumens of output.
- 15° beam angle.
- Up to ten zones of LED control.
- Low power consumption - 150W maximum.
- Simple cost effective MR16 strip light replacement.
- Multiple mounting points allows for a variety of rigging positions.
- Rugged construction.
- Configure remotely via RDM, or locally through a simple Showline LCD menu system.
- DMX512-A control via 5 pin XLRs.
- Comprehensive Showline LCD menu system.
- Two year limited warranty.


Source	Fixed white LED
Qty of LED cells	10
Lumen output (max.)	6000
Color temperature	2700K
CRI	80
Beam angle	15°
Tilt	–
Controls	DMX512-A / RDM, local control
Dimming control	Electronic 16-bit
Pixel / zone control	1 / 2 / 5 / 10
DMX modes	8-bit, 16-bit
Macro effects	Pre-set chases
Color mixing	–
Color calibration	No
Software updates	Via PEGASUS
Accessories	–
Operating voltage	100-240VAC, 50/60Hz
Wattage (max.)	150W
IP rating	IP20
Cooling	Silent convection cooling
Cooling control	–
Operating temperature	-20-40°C
Mounting position	Any
Finish	Black
Construction	Metal
Dimensions L x H x W	1082 x 146 x 130mm (42.6 x 5.75 x 5.12in)
Hanging centers	545mm (21.5in)
Weight	8.8kg (19.4lb)
Warranty	2 years

Product data

Philips Showline SL SUNLED 10

Color temp	CRI	Wattage	Beam	Overall dimensions W x H x D	Weight	Order Code
2700K	80	150W	15°	1082 x 146 x 130mm (42.6 x 5.75 x 5.12in)	8.8kg (19.4lb)	88-095-5662-76

Dimensional drawing





© Philips Lighting Holding B.V. 2017. All rights reserved. Philips reserves the right to make changes in specification and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

philips.com/showline

04/2017

Data subject to change. All measurements quoted primarily in millimeters.