

VLZ Wash



Intelligent lights – washes **VLZ Wash**

The Philips Vari-Lite VLZ Wash is a dedicated wash luminaire utilizing the latest high output LED light engine and a familiar CMY-CTO color system to produce stunning colors. The dual fixed color wheel with linear control gives access to Vari-Lite colors and split color combinations. Color shake and color wheel spin control have also been added to the mix. All of this is bundled into a luminaire that produces a staggering 25,000 lumens projected from a large 155mm (6") lens.

In addition to the wide zoom range, Beam–Shaping control can be achieved via 3 different systems used independently of each other; a lenticular lens can change the beam from round to oblong; 4 different beam softness grades are achievable using the beam softening control; a set of internal barndoors shape the beam even further.

The combination of the color and beam control makes the VLZ Wash the go-to professional moving wash luminaire.

Product data



Feature and benefits

- 25,000 lumen output.
- 155mm large aperture wash lens.
- High ouput white light LED light source engine to maintain constant high output light levels.
- Wide zoom range.
- 16-bit dimmer control with 4 selectable curves.
- Color mixing system CMY + CTO color control.
- 12 fixed color 2 color wheels 6+ open with color shake and wheel spin functions.
- Indexing and rotatable beam shaping system.
- 4 selectable beam edge softness.
- Masking barndoor system with 4 blades frame rotation ±50 degree either side of center.
- Fast, accurate and repeatable movement on all functions.
- Two year limited warranty.


Source	LED			
Qty of LED cells	N/A			
Lamp cap	-			
Lumen output (max.)	25,000			
Wattage	620W			
Color temperature	8000K source, varible CTO			
CRI	>70			
Color mixing	CMY, variable CTO 2x fixed color wheels			
Beam angle	7-50°			
Pan / tilt	540° / 270°			
Controls	DMX512-A / RDM, Art-Net™			
DMX channels	52			
Dimming	Electronic 16-bit			
Macro effects	No			
Accessories	-			
Operating voltage	100-240VAC 50/60Hz			
IP rating	IP20			
Operating temperature	10-45°C			
Construction	Metal frame and engineering plastic covers			
Finish	Black			
Dimensions L x H x W	458 x 316 x 796mm (18 x 12.44 x 31.34in)			
Hanging centers	600mm (23.62in)			
Weight	39.0kg (86lb)			
Warranty	2 years			


Product data


Philips Vari-Lite VLZ Wash


	Wattage	Beam	Overall dimensions W x H x D	Weight	Order Code
Philips Vari-Lite VLZ automated LED Wash, with barndoor system with input power powerCON connector AC100-240V	620W	7-50°	458 x 316 x 796mm (18 x 12.44 x 31.34in)	39kg (86lb)	26-105-0003-00
Luminaire programming kit					PEGASUS

Dimensional drawing











© Philips Lighting Holding B.V. 2017. All rights reserved. Philips reserves the right to make changes in specification and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

www.philips.com/vari-lite

04/2017

Data subject to change. All measurements quoted primarily in millimeters.