

**GREAT LIGHT,  
SOLID DESIGN**

# MAZDA LED SPOTS

## SPOTLIGHT ON STYLE

**A<sup>+</sup>**  
EEI label

**80**  
CRI

**⚡**  
220-240 Vac

**🕒**  
15,000h

**⊗**  
non dimmable



**MZD LED 50W GU10 865  
36D ND 1CT/10**

12NC: **929001259132**  
EAN1: **3139188162648**

**5** WATT **50** WATT **6500 K**  
**380 lm**



**MZD LED 500lm GU10 840  
120D ND 1CT/10**

12NC: **929001358632**  
EAN1: **3139188161696**

**5** WATT **4000 K**  
**500 lm**

Product type	Lamp type	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 50W GU10 827 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001250432	3139188161252
MZD LED 50W GU10 840 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001247032	3139188162662
MZD LED 50W GU10 865 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001259132	3139188162648
MZD LED 50W GU10 WH 60D ND	PAR16	5	60	15000	38	50	50 x 55	929001912232	3139188161276
MZD LED 50W GU10 CW 60D ND	PAR16	5	60	15000	38	50	50 x 55	929001912332	3139188161290
MZD LED 65W GU10 827 36D ND	PAR16	6	36	15000	48	50	50 x 56	929001371132	3139188161634
MZD LED 65W GU10 840 36D ND	PAR16	6	36	15000	44	50	50 x 56	929001371232	3139188161658
MZD LED 350lm GU10 840 120D ND	PAR16	6	120	15000	40	50	50 x 58	929001358532	3139188161672
MZD LED 500lm GU10 827 120D ND	PAR16	6	120	15000	58	50	50 x 56	929001372032	3139188161719
MZD LED 500lm GU10 840 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001358632	3139188161696
MZD LED 500lm GU10 865 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001372132	3139188161733
MZD LED 35W GU5.3 827 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001210932	3139188161832
MZD LED 35W GU5.3 840 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001245932	3139188161856
MZD LED 50W GU5.3 827 12V 36D ND*	MR16	8	36	15000	710	50	50 x 44	929001912632	3139188163287
MZD LED 50W GU5.3 840 12V 36D ND*	MR16	8	36	15000	710	50	50 x 44	929001912732	3139188163263
MZD LED 50W GU5.3 WH 12V 50D ND*	MR16	8	50	15000	700	50	50 x 44	929001912432	3139188161313
MZD LED 50W GU5.3 CW 12V 50D ND*	MR16	8	50	15000	700	50	50 x 44	929001912532	3139188161337

\*Wattage equivalence cannot be claimed as, due to their wide beam (120D) these spots are not directional lamps