

Since
1894

BEAUTIFUL LIGHT, BUILT TO PERFORM

 MAZDA

GREAT LIGHT SOLID DESIGN



4 Indoor
luminaires



8 Outdoor
luminaires




12 Bulbs



16 Candles
& Lustrés



22 Spots



26 Tubes

There's an art to creating a quality lighting scheme that exceeds your customers' expectations - without going over their budget. Now you can master it beautifully with MAZDA's portfolio of LED lamps and MAZDA's recently introduced luminaires.

QUALITY WHEN IT COUNTS

The MAZDA name has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting. From retail and residential projects to commercial and industrial installations, they have been developed to meet the challenging requirements of a wide range of lighting applications.

We've designed our range using the very latest LED technology, from classic bulbs and elegant candles to hand-working tubes and directional spots. The MAZDA portfolio now also offers indoor and outdoor luminaires to meet your customer's needs. So you can promise your customers excellent performance and efficiency from their lighting installation, with instant energy savings.

They'll love the light quality too. With a choice of lumens, color temperatures and beam angles, our high quality LED solutions create the perfect ambience for every space. Light that's designed to create a great first impression, with value that lasts.



MASTERING LIGHT SINCE 1894

MAZDA has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting:

- Engineered for performance**
- Up to 35,000 hours reliable lifetime**
- Superb light quality**
- Save up to 85% energy**


MAZDA INDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS



Instant energy savings with MAZDA's range of luminaires.

- Instant energy savings
- 2 years warranty
- 35,000 hours lifetime

INDOOR BATTENS & WALLMOUNTS



NEW

MAZDA BN007C LED32S/840
PSU L1200

12NC: **911401800480**
EAN1: **8710163338040**

1200 mm
IP20



NEW

MAZDA WL007C LED14S/740
PSU OVL WH

12NC: **911401800780**
EAN1: **8710163338071**

IP65 / IK06
Silver trim included




NEW

MAZDA WL007C LED13S/740
PSU RND MDU WH

12NC: **911401800880**
EAN1: **8710163338088**

IP54 / IK06
Silver trim included
Motion sensor

INDOOR WATERPROOF




NEW

MAZDA WT007C LED17S/740
PSU L600

12NC: **911401800980**
EAN1: **8710163338774**

600 mm
IP65 / IK06




NEW

MAZDA WT007C LED34S/740
PSU L1200

12NC: **911401800580**
EAN1: **8710163338057**

1200 mm
IP65 / IK06



NEW

MAZDA WT007C LED54S/740
PSU L1500

12NC: **911401800680**
EAN1: **8710163338064**

1500 mm
IP65 / IK06

MAZDA INDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS



Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
	lm	W	K					
Batten								
NEW	MAZDA BN007C LED32S/840 PSU L1200	3200	32	4000	IP20		I	911401800480 8710163338040
Wallmount								
NEW	MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	4000	IP65 / IK06		II	911401800880 8710163338088
NEW	MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	4000	IP54 / IK06	Yes	II	911401800780 8710163338071
Waterproof								
NEW	MAZDA WT007C LED17S/740 PSU L600	1700	17	4000	IP65 / IK06		II	911401800980 8710163338774
NEW	MAZDA WT007C LED34S/740 PSU L1200	3400	34	4000	IP65 / IK06		II	911401800580 8710163338057
NEW	MAZDA WT007C LED54S/740 PSU L1500	5400	54	4000	IP65 / IK06		II	911401800680 8710163338064

MAZDA OUTDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS

Instant energy savings with MAZDA's range of luminaires.



- Instant energy savings
- 2 years warranty
- 35,000 hours lifetime

OUTDOOR FLOODLIGHTS



MAZDA BVP007
10W 4000K

12NC: **911401737432**
EAN1: **8710163337371**

IP65 / IK06



MAZDA BVP007
20W 4000K

12NC: **911401737442**
EAN1: **8710163337388**

IP65 / IK06



MAZDA BVP007
50W 4000K

12NC: **911401737452**
EAN1: **8710163337395**

IP65 / IK06



MAZDA BVP007
20W 4000K MDU

12NC: **911401741582**
EAN1: **8710163338200**

IP65 / IK06

Motion sensor




MAZDA BVP007
50W 4000K MDU

12NC: **911401741592**
EAN1: **8710163338217**

IP65 / IK06

Motion sensor

MAZDA OUTDOOR LUMINAIRES FOR INSTANT ENERGY SAVINGS



	Product type	Lumen output	Energy consumption	Color temperature	IP / IK	Motion sensor	Safety Class	12NC	EAN1
		lm	W	K					
NEW	MAZDA BVP007 10W 4000K	850	10	4000	IP65 / IK06		I	911401737432	8710163337371
NEW	MAZDA BVP007 20W 4000K	1700	20	4000	IP65 / IK06		I	911401737442	8710163337388
NEW	MAZDA BVP007 50W 4000K	4250	50	4000	IP65 / IK06		I	911401737452	8710163337395
NEW	MAZDA BVP007 20W 4000k MDU	1700	20	4000	IP65 / IK06	Yes	I	911401741582	8710163338200
NEW	MAZDA BVP007 50W 4000k MDU	4250	50	4000	IP65 / IK06	Yes	I	911401741592	8710163338217

MAZDA LED BULBS

INSTANT ENERGY SAVINGS

With MAZDA's range of LED bulbs you can create exactly the right ambience.

- Classic bulb shape
- Frosted or clear finish
- 2700K or 4000K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR BULBS



MZD LED 40W E27 840
A60 ND

12NC: **929001913032**
EAN1: **3139188161436**

6 WATT	40 WATT	4000 K
		500 lm



MZD LED 40W E27 827
A60 ND

12NC: **929001912932**
EAN1: **3139188161412**

6 WATT	40 WATT	2700 K
		470 lm



MZD LED 40W A60 E27
CDL FR ND

12NC: **929001913232**
EAN1: **3139188162266**

6 WATT	40 WATT	6500 K
		470 lm



MZD LED 60W A60 E27
827 FR ND

12NC: **929001913132**
EAN1: **3139188161450**

9 WATT	60 WATT	2700 K
		806 lm



MZD LED 60W A60 B22
WW FR ND RF

12NC: **929001913532**
EAN1: **3139188162969**

9 WATT	60 WATT	2700 K
		806 lm



MZD LED 60W A60 E27
CDL FR ND

12NC: **929001913432**
EAN1: **3139188162327**

9 WATT	60 WATT	6500 K
		806 lm



MZD LED 60W A60 E27
840 FR ND

12NC: **929001913332**
EAN1: **3139188161474**

9 WATT	60 WATT	4000 K
		806 lm



MZD LED 75W A60 E27
827 FR ND

12NC: **929001365532**
EAN1: **3139188161498**

11 WATT	75 WATT	2700 K
		1055 lm



MZD LED 75W A60 E27
840 FR ND

12NC: **929001365632**
EAN1: **3139188161511**

10 WATT	75 WATT	4000 K
		1055 lm



MZD LED 75W A60 E27
865 FR ND

12NC: **929001359132**
EAN1: **3139188162488**

10 WATT	75 WATT	6500 K
		1055 lm

MAZDA LED BULBS INSTANT ENERGY SAVINGS





**MZD LED 100W E27 827
A67 FR ND**

12NC: **929001252932**
EAN1: **3139188161535**

14 **100** **2700 K**
WATT WATT 1521 lm



**MZD LED 100W A60 E27
CDL FR ND**

12NC: **929001359232**
EAN1: **3139188162501**

14 **100** **6500 K**
WATT WATT 1521 lm

80
CRI

220-240 Vac

15,000h

non dimmable

Product type	Energy consumption	Color temperature	Lumen output	12NC	EAN1
		K	lm		
MZD LED 40W E27 840 A60 ND 1CT/6	6	4000	470	929001913032	3139188161436
MZD LED 40W E27 827 A60 ND 1CT/6	6	2700	470	929001912932	3139188161412
MZD LED 40W A60 E27 CDL FR ND 1CT/6 G3	6	6500	470	929001913232	3139188162266
MZD LED 60W A60 E27 827 FR ND 1CT/6 G3	9	2700	806	929001913132	3139188161450
MZD LED 60W A60 B22 WW FR ND RF 1BC G3 1CT/6	9	2700	806	929001913532	3139188162969
MZD LED 60W A60 E27 CDL FR ND 1CT/6 G3	9	6500	806	929001913432	3139188162327
MZD LED 60W A60 E27 840 FR ND 1CT/6 G3	9	4000	806	929001913332	3139188161474
MZD LED 75W A60 E27 827 FR ND 1CT/6 G3	11	2700	1055	929001365532	3139188161498
MZD LED 75W A60 E27 840 FR ND 1CT/6 G3	10	4000	1055	929001365632	3139188161511
MZD LED 75W A60 E27 CDL FR ND 1CT/6 G3	10	6500	1055	929001359132	3139188162488
MZD LED 100W E27 827 A67 FR ND 1CT/6	14	2700	1521	929001252932	3139188161535
MZD LED 100W A60 E27 CDL FR ND 1CT/6 G3	14	6500	1521	929001359232	3139188162501

MAZDA LED CANDLES & LUSTRE DESIGNED FOR ATMOSPHERE

With an elegant design and frosted finish, our LED candles also offer significant energy savings.

- Elegant shape
- Frosted finish
- Warm white light
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR CANDLES & LUSTRES



MZD LED 25W B35 E14
827 CL ND

12NC: **929001253132**
EAN1: **3139188162709**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W E14 827
B35 FR ND

12NC: **929001253032**
EAN1: **3139188161351**

4 25 WATT	2700 K	
		250 lm



MZD LED 25W B35 E14
CW FR ND

12NC: **929001359432**
EAN1: **3139188162549**

3 WATT	25 WATT	4000 K
		250 lm



MZD LED 25W B35 E14
CDL FR ND

12NC: **929001388832**
EAN1: **3139188162563**

3 WATT	25 WATT	6500 K
		250 lm



MZD LED 25W E27 827
P45 FR ND

12NC: **929001253332**
EAN1: **3139188161399**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W E14 827
P45 FR ND

12NC: **929001253232**
EAN1: **3139188161375**

4 WATT	25 WATT	2700 K
		250 lm



MZD LED 25W P45 E14
CW FR ND

12NC: **929001263832**
EAN1: **3139188162822**

4 WATT	25 WATT	4000 K
		250 lm



MZD LED 25W P45 E14
CDL FR ND

12NC: **929001388932**
EAN1: **3139188162587**

3 WATT	25 WATT	6500 K
		250 lm



MZD LED 40W B35 E14
WW FR ND

12NC: **929001253632**
EAN1: **3139188162723**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W B35 E14
CW FR ND

12NC: **929001263732**
EAN1: **3139188162884**

5 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W B35 E14
CDL FR ND

12NC: **929001389032**
EAN1: **3139188162686**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E27
WW FR ND

12NC: **929001253832**
EAN1: **3139188162808**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E14
WW FR ND

12NC: **929001253732**
EAN1: **3139188162785**

6 WATT > **40** WATT **2700 K**
470 lm



MZD LED 40W P45 E27
CW FR ND

12NC: **929001264032**
EAN1: **3139188162860**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E14
CW FR ND

12NC: **929001263932**
EAN1: **3139188162846**

6 WATT > **40** WATT **4000 K**
470 lm



MZD LED 40W P45 E27
CDL FR ND

12NC: **929001389232**
EAN1: **3139188162624**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 40W P45 E14
CDL FR ND

12NC: **929001389132**
EAN1: **3139188162600**

5 WATT > **40** WATT **6500 K**
470 lm



MZD LED 60W B35 E14
827 FR ND

12NC: **929001907632**
EAN1: **3139188163201**

8 WATT **60** WATT **2700 K**
806 lm



MZD LED 60W B35 E14
840 FR ND

12NC: **929001907732**
EAN1: **3139188163225**

8 WATT **60** WATT **4000 K**
806 lm



MZD LED 60W B35 E14
865 FR ND

12NC: **929001907832**
EAN1: **3139188163249**

8 WATT **60** WATT **6500 K**
806 lm

A⁺
EEI label**80**
CRI
220-240 Vac
15,000h
non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 25W B35 E14 827 CL ND 1CT/10	B35	4	15000	2700	250	35 x 106	929001253132	3139188162709
MZD LED 25W E14 827 B35 FR ND 1CT/10	B35	4	15000	2700	250	35 x 106	929001253032	3139188161351
MZD LED 25W B35 E14 CW FR ND 1CT/10 G3	B35	3	15000	4000	250	37 x 109	929001359432	3139188162549
MZD LED 25W B35 E14 CDL FR ND 1CT/10 G3	B35	3	15000	6500	250	37 x 109	929001388832	3139188162563
MZD LED 25W P45 E27 827 CL ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253532	3139188162761
MZD LED 25W P45 E14 827 CL ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253432	3139188162747
MZD LED 25W E27 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253332	3139188161399
MZD LED 25W E14 827 P45 FR ND 1CT/10	P45	4	15000	2700	250	45 x 90	929001253232	3139188161375
MZD LED 25W P45 E14 CW FR ND 1CT/10	P45	4	15000	4000	250	45 x 90	929001263832	3139188162822
MZD LED 25W P45 E14 CDL FR ND 1CT/10 G3	P45	3	15000	6500	250	45 x 82	929001388932	3139188162587

A⁺
EEI label**80**
CRI
220-240 Vac
15,000h
non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 40W B35 E14 WW FR ND 1CT/10	B35	6	15000	2700	470	35 x 106	929001253632	3139188162723
MZD LED 40W B35 E14 CW FR ND 1CT/10	B35	5	15000	4000	470	37 x 109	929001263732	3139188162884
MZD LED 40W B35 E14 CDL FR ND 1CT/10 G3	B35	5	15000	6500	470	37 x 109	929001389032	3139188162686
MZD LED 40W P45 E27 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 90	929001253832	3139188162808
MZD LED 40W P45 E14 WW FR ND 1CT/10	P45	6	15000	2700	470	45 x 90	929001253732	3139188162785
MZD LED 40W P45 E27 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 80	929001264032	3139188162860
MZD LED 40W P45 E14 CW FR ND 1CT/10	P45	6	15000	4000	470	45 x 85	929001263932	3139188162846
MZD LED 40W P45 E27 CDL FR ND 1CT/10 G3	P45	5	15000	6500	470	45 x 77	929001389232	3139188162624
MZD LED 40W P45 E14 CDL FR ND 1CT/10 G3	P45	5	15000	6500	470	45 x 82	929001389132	3139188162600

A⁺

EEI label

80

CRI



220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy consumption	Switch Cycle (times)	Color temperature	Lumen output	Dimensions W x H	12NC	EAN1
				K	lm	mm		
MZD LED 60W B35 E14 827 FR ND 1CT/10	B35	8	15000	2700	806	39 x 114	929001907632	3139188163201
MZD LED 60W B35 E14 840 FR ND 1CT/10	B35	8	15000	4000	806	39 x 114	929001907732	3139188163225
MZD LED 60W B35 E14 865 FR ND 1CT/10 G3	B35	8	15000	6500	806	39 x 114	929001907832	3139188163249

MAZDA LED SPOTS

SPOTLIGHT ON STYLE



Create warm or cool lighting accents with our range of LED spotlights to highlight interior décor or architectural features.

- Direction or wide beam options
- 2700K, 3000K and 4000K, 6500K
- Instant start
- 15,000 hours lifetime
- Save up to 85% energy

INDOOR SPOTS



MZD LED 50W GU10 827
36D ND 1CT/10

12NC: **929001250432**
EAN1: **3139188161252**

5 WATT	50 WATT	2700 K
		345 lm



MZD LED 50W GU10 840
36D ND 1CT/10

12NC: **929001247032**
EAN1: **3139188162662**

5 WATT	50 WATT	4000 K
		380 lm



MZD LED 50W GU10 865
36D ND 1CT/10

12NC: **929001259132**
EAN1: **3139188162648**

5 WATT	50 WATT	6500 K
		380 lm



MZD LED 50W GU10 WH
60D ND 1CT/10

12NC: **929001912232**
EAN1: **3139188161276**

5 WATT	50 WATT	3000 K
		345 lm



MZD LED 50W GU10 CW
60D ND 1CT/10

12NC: **929001186632**
EAN1: **3139188161290**

5 WATT	50 WATT	4000 K
		360 lm



MZD LED 65W GU10 827
36D ND 1CT/10

12NC: **929001371132**
EAN1: **3139188161634**

5.5 WATT	65 WATT	2700 K
		490 lm



MZD LED 65W GU10 840
36D ND 1CT/10

12NC: **929001371232**
EAN1: **3139188161658**

5.5 WATT	65 WATT	4000 K
		500 lm



MZD LED 350lm GU10 840
120D ND 1CT/10

12NC: **929001358532**
EAN1: **3139188161672**

5.5 WATT **4000 K**
350 lm



MZD LED 500lm GU10 827
120D ND 1CT/10

12NC: **929001372032**
EAN1: **3139188161719**

5.5 WATT **2700 K**
500 lm



MZD LED 500lm GU10 840
120D ND 1CT/10

12NC: **929001358632**
EAN1: **3139188161696**

5 WATT **4000 K**
500 lm



MZD LED 500lm GU10 865
120D ND 1CT/10

12NC: **929001372132**
EAN1: **3139188161733**

5 WATT **6500 K**
500 lm



MZD LED 35W GU5.3 827
12V 36D ND 1CT/10

12NC: **929001210932**
EAN1: **3139188161832**

4.5 WATT **35** WATT **2700 K**
345 lm



MZD LED 35W GU5.3 840
12V 36D ND 1CT/10

12NC: **929001245932**
EAN1: **3139188161856**

4.5 WATT **35** WATT **4000 K**
380 lm



MZD LED 50W GU5.3 827
12V 36D ND 1CT/10

12NC: **929001912632**
EAN1: **3139188163287**

7.5 WATT **50** WATT **2700 K**
621 lm



MZD LED 50W GU5.3 840
12V 36D ND 1CT/10

12NC: **929001912732**
EAN1: **33139188163263**

7.5 WATT **50** WATT **4000 K**
621 lm



MZD LED 50W GU5.3 WH
12V 50D ND 1CT/10

12NC: **929001912432**
EAN1: **3139188161313**

7.5 WATT **50** WATT **3000 K**
621 lm



MZD LED 50W GU5.3 CW
12V 50D ND 1CT/10

12NC: **929001912532**
EAN1: **3139188161337**

7.5 WATT **50** WATT **4000 K**
621 lm

*Wattage equivalence cannot be claimed as, due to their wide beam (120D) these spots are not directional lamps

A⁺

EEI label

80

CRI



220-240 Vac



15,000h



non dimmable

Product type	Lamp type	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 50W GU10 827 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001250432	3139188161252
MZD LED 50W GU10 840 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001247032	3139188162662
MZD LED 50W GU10 865 36D ND	PAR16	5	36	15000	38	50	50 x 54	929001259132	3139188162648
MZD LED 50W GU10 WH 60D ND	PAR16	5	60	15000	38	50	50 x 55	929001912232	3139188161276
MZD LED 50W GU10 CW 60D ND	PAR16	5	60	15000	38	50	50 x 55	929001912332	3139188161290
MZD LED 65W GU10 827 36D ND	PAR16	6	36	15000	48	50	50 x 56	929001371132	3139188161634
MZD LED 65W GU10 840 36D ND	PAR16	6	36	15000	44	50	50 x 56	929001371232	3139188161658
MZD LED 350lm GU10 840 120D ND	PAR16	6	120	15000	40	50	50 x 58	929001358532	3139188161672
MZD LED 500lm GU10 827 120D ND	PAR16	6	120	15000	58	50	50 x 56	929001372032	3139188161719
MZD LED 500lm GU10 840 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001358632	3139188161696
MZD LED 500lm GU10 865 120D ND	PAR16	5	120	15000	50	50	50 x 58	929001372132	3139188161733

A⁺

EEI label

80

CRI



220-240 Vac



15,000h



non dimmable


Product type	Lamp type	Energy consumption	Beam angle	Switch Cycle (times)	Input current	Frequency	Dimension W x H	12NC	EAN1
			°		mA	Hz	mm		
MZD LED 35W GU5.3 827 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001210932	3139188161832
MZD LED 35W GU5.3 840 12V 36D ND	MR16	6	36	15000	550	50	50 x 46	929001245932	3139188161856
MZD LED 50W GU5.3 827 12V 36D ND	MR16	8	36	15000	710	50	50 x 44	929001912632	3139188163287
MZD LED 50W GU5.3 840 12V 36D ND	MR16	8	36	15000	710	50	50 x 44	929001912732	3139188163263
MZD LED 50W GU5.3 WH 12V 50D ND	MR16	8	50	15000	700	50	50 x 44	929001912432	3139188161313
MZD LED 50W GU5.3 CW 12V 50D ND	MR16	8	50	15000	700	50	50 x 44	929001912532	3139188161337

MAZDA LED TUBES FOR BRIGHTER LIGHTING

Our LED tubes provide high quality light to illuminate any space.

- 600mm, 1200mm and 1500mm lengths
- 4000K and 6500K
- Instant start
- 25,000 hours lifetime
- Save up to 55% energy


INDOOR TUBES



MZD LEDtube 600mm
8W 840

12NC: **929001855632**
EAN1: **8718696717455**


8 WATT	18 WATT	4000 K
		800 lm



MZD LEDtube 600mm
8W 865

12NC: **929001855732**
EAN1: **8718696717479**


8 WATT	18 WATT	6500 K
		800 lm



MZD LED tube 1200mm
14.5W 840

12NC: **929001855832**
EAN1: **8718696717417**


14.5 WATT	36 WATT	4000 K
		1600 lm



MZD LEDtube 1200mm
14.5W 865

12NC: **929001855932**
EAN1: **8718696717431**


14.5 WATT	36 WATT	6500 K
		1600 lm



MZD LEDtube 1500mm
20W 840

12NC: **929001855432**
EAN1: **8718696717370**

20 WATT	58 WATT	4000 K
		2200 lm



MZD LEDtube 1500mm
20W 865

12NC: **929001855532**
EAN1: **8718696717394**

20 WATT	58 WATT	6000 K
		2200 lm



MZD LED PLC7
5W 840

12NC: **929001879032**
EAN1: **3139188162983**

7.5 WATT	13 WATT	4000 K
		806 lm



MZD LED PLC
7.5W 865

12NC: **929001879132**
EAN1: **3139188163003**

7.5 WATT	13 WATT	6500 K
		806 lm



MZD LED PLC
9W 840

12NC: **929001879332**
EAN1: **3139188163027**

9 WATT	18 WATT	4000 K
		1050 lm



MZD LED PLC
9W 865

12NC: **929001879432**
EAN1: **3139188163041**

9 WATT	18 WATT	6500 K
		1050 lm

MAZDA LED TUBES FOR BRIGHTER LIGHTING



TSHAPES



MZD LED 26-24W E27
830 HB 1CT/6



MZD LED 28-24W E27
840 HB 1CT/6



MZD LED 48-42W E27
830 HB 1CT/6



MZD LED 50-42W E27
840 HB 1CT/6

12NC: **929001937632**
EAN1: **3139188164260**

24 WATT **40** WATT **3000 K**
2600 lm

12NC: **929001937732**
EAN1: **3139188164284**

24 WATT **40** WATT **4000 K**
2800 lm

12NC: **929001938232**
EAN1: **3139188164222**

42 WATT **70** WATT **3000 K**
4800 lm

12NC: **929001938332**
EAN1: **3139188164246**

42 WATT **70** WATT **4000 K**
5000 lm

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⚡
non dimmable

Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LEDtube 600mm 8W 840	Tube	8	38	50/60	604h / 27,80ø	929001855632	87186967174500
MZD LEDtube 600mm 8W 865	Tube	8	38	50/60	604h / 27,80ø	929001855732	871869671747900
MZD LEDtube 1200mm 14.5W 840	Tube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	871869671741700
MZD LEDtube 1200mm 14.5W 865	Tube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	871869671743100
MZD LEDtube 1500mm 20W 840	Tube	20	96	50/60	1514,20h / 27,80ø	929001855432	871869671737000
MZD LEDtube 1500mm 20W 865	Tube	20	96	50/60	1514,20h / 27,80ø	929001855532	871869671739400

A⁺
EEI label

80
CRI

⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⚡
non dimmable

Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LED PLC 7.5W 840 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	3139188162983
MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	3139188163003
MZD LED PLC 9W 840 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	3139188163027
MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	3139188163041

A⁺
EEI label

80
CRI

⚡
220-240 Vac


🕒
15,000h

ON/OFF
50,000x

⚡
non dimmable

Product type	Lamp type	LED	Input current	Frequency	Dimension	12NC	EAN1
		W	mA	Hz	mm		
MZD LED 26-24W E27 830 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	x	3139188164260
MZD LED 28-24W E27 840 HB 1CT/6	T-shape	24	250	50/60	190h / 105ø	x	3139188164284
MZD LED 48-42W E27 830 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	x	3139188164222
MZD LED 50-42W E27 840 HB 1CT/6	T-shape	42	240	50/60	225h / 123ø	x	3139188164246

GREAT LIGHT
SOLID DESIGN





Engineered for performance
Up to 35,000 hours reliable lifetime
Superb light quality
Save up to 85% energy

MAZDA | I.B.R.S. / C.C.R.I. Numéro 10461 | 5600 VB Eindhoven, the Netherlands | WWW.MAZDALIGHTING.COM

© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

 **MAZDA**