

# Product Specification Sheet Accent LED Beamshaper



The Philips Selecon Accent LED Beamshaper delivers accurate shaping of the beam and precise pattern / logo projection.

A sophisticated lighting instrument of timeless appearance.

The Accent LED Beamshaper delivers on Philips Selecon's brand promise for performance (efficient optical system; high quality pattern projections); precision (accurate beam shaping; locking focus adjustments) and simplicity (intuitive operation).

Allen key lock offs and reference scales for all adjustments offers the means to effectively assure the integrity of the original lighting design.

#### **Features**

High quality zoom optical system (24 ° -39 °).

High CRI fixed white delivers excellent colour rendering.

Improved beam control and zoom adjustment.

Reference scales for pan/tilt and zoom adjustments.

Improved gobo installation and projection.

Easy mount E size pattern holder included with every luminaire.

Superior glare control and no light spill.

Four captive shaping shutters with integrated shutter lock system.

Hinged opening body for easy cleaning of lenses.

Multiple/integrated accessory and filter mounting slots – to carry colour filter 50mm round, one of which can be up to 4mm thick..

Engineered from precision aluminium pressure die-castings and injection moulded engineering plastic.

Three year limited warranty.

## Colours



White - PANTONE® 11-4800 - Blanc de Blanc.

### Mounting options

Universal track three circuit track adapter.

Ceiling mount plate, ridged 80mm diameter x 20mm deep.

1.0m cable tail from top of yoke mount spindle. Half coupler for 48/51mm OD pipe.





Ceiling rose mount

ose mount Track Adap



Half Coupler

#### **Control Options**

- -Local Dimming non dimmed mains supply.
- -Dali Dimming non dimmed mains supply.

Dimming performance of LED Sources can vary greatly on different dimming systems. 100% compatibility cannot be guaranteed.

#### Wattage / Power Supply

13W / 220-240V

#### Colour Temperature / Life<sup>1</sup>

Choice of 2700K, 3000K, or 4000K / 50,000hrs

#### CRI<sup>2</sup> / Colour Consistency

95 typical, Within 2-Step MacAdam Ellipse


## **Approvals**



PAGE 1 www.seleconlight.com


## **Physical Data**

Weight: 1.95 kg



## **Performance Data**

# Accent LED BEAMSHAPER 24º-39º:



3000K version

PAGE 2 www.seleconlight.com

#### **Order Codes**

- 2-2700K
- 3 3000 K
- 4 4000 K
- LD Local Dim non-dimmed mains input
- DD Dali Dim non-dimmed mains input (not available with Ceiling Rose, Half Coupler, or Flex mount)
- H 50mm Halfcoupler and 1.0m cable
- C Ceiling Rose
- G Global track adaptor standard option for track mount. Dali or local control
- T Eutrack adaptor non-standard option for track mount. Dali or local control.
- $\label{eq:energy} E-eDali\ Track\ adaptor\ -\ custom\ adaptor\ for\ three\ circuit\ track\ -\ for\ installations\ using\ Dali\ on\ standard\ track\ .$  Please contact your sales representative.
- 01 White
- 03 Black
- P Aust / NZ plug

Family Name	Light Source	Colour Temp	Beam Angle	Control Option	Mounting Option	Paint Finish	Aust/NZ Plug
ACNT	LED	2	BS		Н	01	Р
		3		LD	С	03	
		4		DD*	Т		
					G		
					E		
					F		

 $\label{eq:lem:$ 

#### **Accessories**

Various glass effects and coloured glass can be used with the Accent LED Beamshaper. Please contact your Philips Selecon dealer for full details - www.seleconlight.com/distributors

Pattern size: E Outside diameter: 37.5cm Image area: 28mm

To achieve the best results with your pattern projection:

- always use black matt finish patterns as these reduce internal light reflections.
- for custom / text logos please ensure the design is inside the 28mm diameter area.
- 1. Based on LED Manufacturers IES LM-80-2008
- 2. LED manufacturer tolerance of +-2 on CRI measurements

Philips Selecon reserves the right to change this product specification without notice (October 2015).

PAGE 3 www.seleconlight.com

<sup>\*</sup> DALI Dimming version only available with Track adaptor Mounting (T,G,E)