

# Acclaim 4 Inch 6°-60° Fresnel



The Acclaim 6°-60° Fresnel is a 300W / 575W / 650W general purpose Fresnel (41/4" diameter lens) for theatre, small studio and display lighting applications which produces an adjustable cone of light with a soft edge that is easily blended with adjacent beams to provide even illumination.

#### **Features**

Up to 40% more light output than other Fresnels.

Improved filter life through increased airflow.

Cooler focus operation due to the use of engineering plastics on front (color frame mount) and rear.

Adjustable yoke balance point.

'Swing-down' side door for easy access to lamp or for cleaning.

Lamp life is enhanced through judder-free focus action of the captive lamp/reflector assembly which moves on Teflon-coated bearings.

Heat-insulated rear grab-handle which doubles as handy storage for the 3ft cable length.

New barndoor design, cool to focus maintaining settings through unique hinge tension design.

Focusing is fast and safe using the large rear grab handle, heat protected focus knob and filter holder.

Built Selecon tough from aluminum extrusion and molded engineering plastics – robust, dependable, safe and easy to rig.

Permanently attached integrated safety cable ensures that this important safety requirement is always on hand.

Integral micro-switch provides automatic power disconnection to the fixture when opening to relamp, preventing a student or technician inserting a lamp into an electrically live fixture.

Three year warranty.

#### Lamps

300W FKW

7,800 lumens 200hrs average life

575W Ushio

JCS120V-575WC 300hrs average life

575W Ushio

JCS120V-575WX 1500hrs average life

650W FRK

16,900 lumens 200hrs average life

### Ordering information

12ACFUS Acclaim 4 Inch Fresnel, black

20BDMFBarndoor, 4 way, black15ACSMLens safety mesh20CFMFSpare color frameUSCLAMPSpare US theatrical C-clamp

For connector options please specify the following suffixes when ordering:

-GR NEMA 5-15P Grounded Edison

-GP 20A Stage Pin Plug-GTL NEMA L5-20P Twist-Lock

## **Approvals**

ETL / cETL listed to UL 1573.


# SPECIFICATION SUBMITTAL

CONSULTANT:	PROJECT NAME:	MODEL NUMBER   QUANTITY:
DATE:	PROJECT NUMBER:	APPROVED BY:

www.strandlighting.com www.seleconlight.com

#### Photometric data

Tests conducted using a standard FRK, 650W, 120V lamp.



For Lux please multiply Fc by 10.7

# Physical data

 Weight: 7lb 4oz
 Packed: 8lb

 Carton size: 16 ½" x 8 ¾" x 7"
 Cubic: 0.016

Color frame size: 4 % x 4 %

AC supply cable: 36"

Fixture with integrated safety cable supplied with: 1x color frame, 1x C-clamp, instruction sheet.

#### **North America**

10911 Petal Street Dallas, Texas 75238 Tel: +1 214 647 7880 Fax: +1 214 647 8030

267 5th Ave, 4th Floor New York, NY 10016 Tel: +1 212 213 8219 Fax: +1 212 532 2593

#### **New Zealand**

19-21 Kawana Street Northcote, Auckland 0627 Tel: +64 9 481 0100 Fax: +64 9 481 0101


# **Hong Kong**

Room 6-10 20/F Delta House 3 On Yiu Street Shatin, N.T. Tel: +852 2757 3033 Fax: +852 2757 1767

# **European Service & Distribution Centre**

Marssteden 152 Enschede 7547 TD the Netherlands Tel: +31 53 450 0424 Fax: +31 53 450 0425

110810NA



© Philips Group 2010

All rights reserved.

The Company reserves the right to make any variation in design or construction to the equipment described. E&OE



www.strandlighting.com www.seleconlight.com