


# PHILIPS

## PerfectBeam gen.2 Variable Spot

ST741T



220 V  
240 V

50Hz  
60Hz







LEDs




Ta  
35 °C




	P (W)	IP...	kg
ST512T	25	IP20	1.5




GLOBAL Trac Pro  
Wiring options:



90°








2 note: only if required



3

1d




SV-5  
L-0140

note: inscription at side of LED

4a

4b

Inrush current



MCB	Downlights Max.
B-10 A	57
B-13 A	74
B-16 A	91
C-10 A	57
C-13 A	74
C-16 A	91