

**GREAT LIGHT,
SOLID DESIGN**

MAZDA LED TUBES FOR BRIGHTER LIGHTING

A⁺
EEI label

80
CRI


⚡
220-240 Vac

🕒
25,000h

ON/OFF
50,000x

⊗
non dimmable

	Product type	Lamp type	LED	Input Current	Frequency	Dimension	12NC	EAN1
			W	mA	Hz	mm		
NEW	MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	871869671745500
NEW	MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	871869671747900
NEW	MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	871869671741700
NEW	MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	871869671743100
NEW	MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	871869671737000
NEW	MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	871869671739400
NEW	MZD LED PLC 7.5W 840 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	3139188162983
NEW	MZD LED PLC 7.5W 865 2P G24d 1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	3139188163003
NEW	MZD LED PLC 840 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	3139188163027
NEW	MZD LED PLC 9W 865 2P G24d 1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	3139188163041



**MZD LED tube 1200mm
14.5W 840**

12NC: **929001855832**
EAN1: **8718696717417**

14.5 WATT **36** WATT **4000 K**
1600 lm



**MZD LED PLC
7.5W 865**

12NC: **929001879132**
EAN1: **3139188163003**

7.5 WATT **13** WATT **6500 K**
806 lm