

Requested parameters

Project name	
Colour temperature	Warm White (2018Q1)
Flux	7600 lm @ L80
Requested lumen depreciation	L80
Requested expected lifetime	100 000
Dim option	DYNADIM
Dim regime	24

Solution

Luminaire type	Clearway gen 2
Basic insulation class	Class II
Number of LED	40 LED
System power	Luminaire 58 W Module 0 W Total 58 W (module included)
Consumed power over lifetime	4 263 kWh
Minimal realized flux	7 600
Power Factor (100%)	0.98
Power Factor	no data available
Light Regulation	DYNADIM
Driver Code	R00
Drivers Code Key	18:0:0
Program Code	8VFRUPEYE6CD (https://www.l-tune.net/results/decode?code=8VFRUPEYE6CD)