

Built to last, designed to save

GreenLine range brochure





Total solutions

As the worlds largest lighting company, Philips has the breadth and depth of products and services across all lighting applications to provide total lighting solutions for our customers. Whether you need a simple lamp and ballast switch or are looking to upgrade youe existing road lighting system, parterning with Philips will ensure that you always receive much greater value for your investment.

Our specialst teams would be happy to evaluate your needs by performing an energy benchmark analysis or complete lighting energy audit, so that we can recommend the perfect lighting solution to meet your requirements. We can even provide you with a complete turnkey solution, thereby offering you the ease of a single point of contact, and we are happy to discuss various financial solutions with you. We are committed to providing you with only the best-in-class, energy efficient lighting solutions.



We offer

- Project management
- Turnkey solutions & services covering
 - Lighting design
 - Product supply
 - Testing & commissioning
 - Installation
 - Maintenance
- Lighting energy management scheme including energy audit
- Uplamping solutions
- Assured pay-back
- Finance scheme available



GreenLine Smart

Philips GreenLine Smart luminaire is perfect for secondary roads and pathways. It sports a compact body, which offers a highly efficient lighting solution as compared to fluorescent and CFL street lights.

This is a versatile street light that can be used in various other outdoor applications. The compact size of GreenLine Smart allows it to be used as an outdoor light for periphery lighting. It can be used in and around residential houses, offices, small and medium industries and gated communities.

GreenLine Smart is completely maintenance free, it ensures trouble free operation with use of LED source and electronic driver. Specially designed polycarbonate cover reduces glare, spreads light evenly and is impact resistant. It is completely reliable for Indian conditions as it operates on a wide range of supply voltage. GreenLine Smart also has IP 65 protection with very high ingress protection against dust and water.

GreenLine Smart is an environment friendly product with no mercury content and saves up to 50% energy as compared to conventional fluorescent and CFL street lights.





*Usage of 11 hours per day

High power LEDs

Wider light spread

ETM technology ensures long life



Product Features

Product dimensions

- High pressure die cast Al housing for effective thermal management, sturdiness and excellent corrosion resistance
- Polycarbonate cover provides resistance against impact
- Lumen output of 1650 lm.
- Specially designed cover with prismatic optics to spread light and reduce direct glare
- LED as light source offer very long life as compared to conventional source
- Electronic driver with PF > 0.9
- Wide operating voltage of 100 300V
- Ingress protection of IP 65
- Environmental friendly with no mercury content
- Pre-wired for ease of Installation





Ordering data

Туре	Qty. per box	Dimensions (mm)	Nett weight (Kg.)	Gross weight (Kg.)	Vol (m3)
BRP020 1x10LED	10	410 × 155 × 485	1.0	12.0	0.031

Applications



Pole mounted streetlights for residential streets, parks, gardens, parking areas and small lanes.



Post top mounted outdoor lights for gates



Wall mounted outdoor lights for terraces, car garages, kitchen gardens and balconies.

GreenLine

Philips road lighting luminaire with 24 High power LED and extendable upto 48 High power led, with unique peanut lens to ensure uniform distribution, higher spacing between poles and maintenance free system. With a life class of 50000hrs (At L70) with excellent thermal management.



Salient features

- Luminaire with dedicated street light optics for good uniform lighting
- Pressure die cast LM6 Aluminum housing for sturdiness and better aesthetics
- UV stabilized Polycarbonate cover
- A full length heat resistant Silicon gasket along the perimeter of housing for high ingress protection of IP 65 for complete luminaire
- Suitable for Side entry with pole diameter $\mathbf{28\text{-}40}$ / $\mathbf{48\text{-}60\text{mm}}$ dia
- The luminaire has a built in replaceable drivers
- Modular arrangement ensure freedom



Product dimensions



Technical specifications

Туре	Greenline	Greenline Duo High Power LED		
Light source	High Power LED			
Lumen output	3500lm	7000lm		
Color	Cool white	Cool white		
Nominal voltage	220V-240V AC 50Hz	220V-240V AC 50Hz		
Driver	Integral type	Integral type		
Material, Construction	Housing : Pressure Die-cast LM6 Aluminum	Housing : Pressure Die-cast LM6 Aluminum		
and finish	Optic: Lens	Optic: Lens		
	Philips metallic paint RAL9007	Philips metallic paint RAL9007		
CRI	70	70		
Mounting (OD)	Side entry on standard pole	Side entry on standard pole		
	28-40mm	48-60mm		
Weight	2.4Kg.	6.0Kg.		
Classification	IP 65, Class I	IP 65, Class I		

Ordering data

Туре	Qty. per box	Dimensions (mm)	Nett weight (Kg.)	Gross weight (Kg.)	Vol (m3)
BRP320 2x24LED-HP/CW PSU GR	I	645 x 380 x 150	5.3	6.5	0.037
BRP320 Ix24LED-HP/CW PSU GR	4	520 × 450 × 285	2.4	13.2	0.086

Lighting distribution





- Greenline: Suitable for up-to road width (W) of 7mts with SPACE to HEIGHT ratio of up-to (S/H) = 4 Lighting level: Meets all types of Roads up-to B1 category roads as per IS 1944

- Green Duo: Suitable for up-to road width (W) of 8mts with SPACE to HEIGHT ratio of up-to (S/H) = 4Lighting level: Meets all types of Roads up-to A2 category roads as per IS 1944

Contact nearest Philips office to make optimum design and save maximum energy in your installation / project

North

Philips Electronics India Ltd,

Regional Sales Manager 9th Floor, DLF - 9B,DLF Cyber City DLF Phase 3, Gurgaon 122002 Tel:- 91 124 460 6000 Fax :- 91 124 460 6666 lighting.india@philips.com

West

Philips Electronics India Ltd,

Regional Sales Manager Technopolis Knowledge Park, Mahakali Caves Road, Chakala, Andheri East, Mumbai 400093 Tel :- 91 22 6691 2000 Fax :- 91 22 6691 2389 / 6691 2398 lighting.india@philips.com

Philips Electronics India Ltd,

8th Floor, DLF - 9B, DLF Cyber City DLF phase 3, Gurgaon 122002 Tel :- 91 124 460 6000 Fax :- 91 124 460 6666

Contact customer service executive at 1800 102 2929 (Toll free) 1860 180 1111, 0124- 4291111 "Standard call rates apply"

South

Philips Electronics India Ltd,

Temple Towers, 5th Floor, Old No. 476, New No. 672, Anna Salai, Nandanam, Chennai 600 035 Tel :- 91 45 6650 1000 Fax :- 91 44 6650 1075 lighting.india@philips.com

Philips Electronics India Ltd,

Area Sales Manager Philips Innovation Campus Manyata Tech Park, Nagavara Bengaluru- 560045 Tel : 080-4189 0000 Fax :- 080 6692 9930 lighting.india@philips.com

Philips Electronics India Ltd,

Area Sales Manager 6-3-1109 / 1 / P/103, 3rd Floor, Jewalpawani Towers, Rajbhavan Road, Somajiguda, Hyderabad Tel :- 040 6646 7676 / 4825 Fax :- 040 6678 7974 lighting.india@philips.com

East

Philips Electronics India Ltd,
Regional Sales Manager
7, Justice Chandra Madhab Road,
Kolkata 700 020
Tel :91 33 2486 7621-24
Fax :91 33 2486 8318
lighting.india@philips.com

© 2012 Koninklijke Philips Electronics N.V.



All rights reserved, reproduction, copying, usage, modifying, hiring, renting, public performance, transmission and/or broadcasting in whole or in part is prohibited without the written consent of Philips Design. PHILIPS and the Philips shield are registered trademarks or Koninklijke Philips Electronics N.V.

URL : www.lighting.philips.co.in