


Ordering 12NC	9290 014 17506
Brand Name	Xitanium
Description	Xitanium 50W 1.2A 44V
Model Number	X050C120V050FNP2AI
Input Voltage	220 - 240V
Input Frequency	50/60 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified

Output Power (W)	Output Voltage (V dc)	Output Current (mA)	Efficiency at Max Load (%)	Max Case Temp (°C)	Input Current (Arms)	Max Input Power (W)	Inrush Current (Apk/50%-µs)	THD @ Max Load (%)	Power Factor @Max Load	Surge Protection (KV) Diff/Com	Weight (Kg)	Envir. Protection Rating
22 -50	18 - 44	1200	240V	75	240V	57	240V	≤ 10 @Max Load	≥ 0.95	1.8 / 2	0.4	Dry & Damp
			87.5		0.27		23/280					

Wire Diagram



Input and output use lead-wires.
Lead-Wires are 18AWG 105C / 600V
Solid Copper

Lead Length
Standard lead length is 165mm (±10mm)
on all wires outside the can
EARTH lead length is 185mm (±10mm)
outside the can

Enclosure



	(mm)
Case Length	104.4
Case Width	68.4
Case Height	32
Mounting Length	94.5
Mounting Width	58

Ordering 12NC	9290 014 17506
Brand Name	Xitanium
Description	Xitanium 50W 1.2A 44V
Model Number	X050C120V050FNP2AI
Input Voltage	220 - 240V
Input Frequency	50/60 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified


PHILIPS

XITANIUM™

50W 1.2A 44V

Model No: X050C120V050FNP2AI

IS 15885
(Part 2/Sec 13)



R-67000191


1.2A

P_n : 57W	P_{out} : 50W
U_n : 240V _{rms}	I_{out} : 1.2Adc
I_n : 0.25A _{ac,max}	U_{out} : 18-44Vdc
f_n : 50Hz	U_{OCV} : 60Vdc _{max}
PF : 0.9C	t_c : 0...+50°C; t_c max: 75°C

For indoor use only

SELV
Equivalent

MADE IN INDIA



• t_c

Product Data	
Full product code	9290 014 17506
Full product name	Xitanium 50W 1.2A 240V P2
Net weight per piece	400 gms
Dimming	None (FIXED)
Ambient Temp. Range	0C to +50C
Line Voltage (AC Nominal)	220 - 240V +/-10%
Line Voltage (AC Operating Range)	120 - 277V
Line Current	0.27A @ 240V
Line Frequency	50 Hz
Life at Tc 65 drgree C	50000 hrs (nom.)
Application	Indoor - Potted Driver
Tc - Max	75 ⁰ C
Inrush Current	23Apk @ 240V
Max. Driver number on MCB 16A (Type B)	19 (max.)
Input Over Voltage	Can Survive input Voltage Stress of 320V for 48 hours Can Survive input Voltage Stress of 350V for 2 hours
LED Current Tolerance	+/- 7%of Imax
Earth Leakage Current	0.7 mA Pk (max)
Output Current Ripple	10% (ripple = pk / avg.)
THD Total	≤ 10% @ Full Load @ 240V Supply
P.F. at Max. Load	≥ 0.95
Galvanic Isolation	Input - Output Isolated (Isolation 3.75 KV)
Protection	Short Circuit and Open Circuit Protection for LED + and LED -
Standby Power	≤4W

Ordering 12NC	9290 014 17506
Brand Name	Xitanium
Description	Xitanium 50W 1.2A 44V
Model Number	X050C120V050FNP2AI
Input Voltage	220 - 240V
Input Frequency	50/60 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified

Installation & Application Notes :

Section I - Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure or fixed to an indoor LED Luminaire.
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105°C rating or higher

Section II - Performance

- 2.1 LED Driver has a rated lifetime of 50,000 hours @ $T_c \leq 75^\circ\text{C}$
- 2.2 LED Driver tolerates sustained open circuit and short circuit output conditions without damage
- 2.3 LED Driver maximum allowable case temperature is 75°C max. - see product label for measurement location
- 2.4 LED Driver complies with the requirements of IS 15885 (Part 2 / Sec 13)

ELECTRICAL RATINGS :

Model	Input, 50/60 Hz		Output (nominal)		
	V	A	V DC	A DC	Watts
Xitanium 50W 1.2A 44V	220 - 240	0.27	18 - 44	1.2	50

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVES USE) :

Section III - Conditions of acceptability

When installed in the end-use equipment, the following are among the considerations to be made :

- 3.1 The equipment shall be installed in compliance with the enclosure, mounting, spacing, casualty and segregation requirements of the ultimate application.
- 3.2 The driver case must be grounded in the end-use application.
- 3.3 The driver is suitable for use in indoor lighting locations.
- 3.4 When the drivers are installed in the end-use application, the case temperature should not exceed the temperature limits specified in the following table:


Model	Input Voltage, Hz	Max Case @ TC , °C
Xitanium 50W 1.2A 44V	220 - 240 , 50/60	75

- 3.5 The leakage current test should be repeated in the end device.


Model	Input Voltage, Hz	Leakage Current
Xitanium 50W 1.2A 44V	220 - 240 , 50/60	0.7mA max.

Ordering 12NC	9290 014 17506
Brand Name	Xitanium
Description	Xitanium 50W 1.2A 44V
Model Number	X050C120V050FNP2AI
Input Voltage	220 - 240V
Input Frequency	50/60 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified

Power Factor vs Output Power :




Inrush Current info :



Vin	Ipeak	T (@50% of Ipeak)
240 Vrms	23A	280 μ s

THD vs Load Power :



Failure rate info based upon field called rate data:
 < 0.2% per 1 Khr @ \leq T case-Life 75°C

Revised 11/24/2016

Philips Lighting India Ltd
 9B, DLF 9th Floor
 DLF Cyber City, DLF Phase III
 Gurgaon 122002
 India