

# Service Manual




HPK150

**Cabana (Philips)**



[Return  
to  
Index](#)

# PHILIPS



Data subject to change

Number	Service 12nc	Description
1	992200110303	HPK150 PLASTIC WIRING HOUSING CABANA (1
2	992200110419	HPK150 BAJONET RING
3	910502597018	ZPK150 GC (Glass Cover including clips, gasket& safety rope) (2
4	910502597118	GPK150 R (Reflector) (2
5	910502597218	ZPK150 MB (Mounting Bracket) (2
All types	Lampholder	BJB 29404.8001.00 Lampholder E40 ø 70x85 (3
HPI/HPL250W 230V	Ballast	ELT VMI 25/23-3-P 250W 230V ELT code: 5112411
HPI/HPL250W 230V	Ignitor	ELT AH-002-D Sin-Tue-Ara ELT code: 3210137 (only for HPI, HPL no Ignitor)
HPI/HPL250W 240V	Ballast	ELT VMI 25/24-3-P 250W 240V ELT code : 5112251
HPI/HPL250W 240V	Ignitor	ELT AH-002-D Sin-Tue-Ara ELT code: 3210137 (only for HPI, HPL no Ignitor)
HPI/HPL400W 230V	Ballast	ELT VMI 40/23-3-P 400W 230V ELT code: 5112425
HPI/HPL400W 230V	Ignitor	ELT AH-002-D Sin-Tue-Ara ELT code: 3210137 (only for HPI, HPL no Ignitor)
HPI/HPL400W 240V	Ballast	ELT VMI 40/24-2-P 400W 240V ELT code: 5112261
HPI/HPL400W 240V	Ignitor	ELT AH-002-D Sin-Tue-Ara ELT code: 3210137 (only for HPI, HPL no Ignitor)
SON250W 230V&240V	Ballast	Philips BSN250L427ITS 12nc: 9137 002 24427
SON250W 230V&240V	Ignitor	Philips SN58T15S 12nc: 9137 001 37566
SON400W 230V	Ballast	ELT VSI 40/23-3T-D-P 400W 230V ELT code: 6112366
SON400W 230V	Ignitor	ELT AVS-100-DP Sin-Tue-Ara ELT code: 3210519
SON400W 240V	Ballast	ELT VSI 40/23-3T-G-P 400W 240V ELT code: 6112365
SON400W 240V	Ignitor	ELT AVS-100-DP Sin-Tue-Ara ELT code: 3210519
Auxillary version	Driver AUX version	Vossloh AS1000 K A10

(1 Housing is made in PA66 (Nylon) Fiber Glass 25%

(2 Commercially available

(3 Cabana has only 1 type of lampholder which is available at wholesaler or directly at BJB