

# Service Manual

2KS070 & 3KS070

## Koffer 1 70




2KS070




3KS070

[Back to Index](#)

# PHILIPS





Number	Service 12nc	Description
1	992200111131	2KS070 PRISMATIC COVER PMMA WITH GASKET
1	992200111132	2KS070 PRISMATIC COVER PC WITH GASKET
1	992200111133	2KS070 FROSTED COVER PMMA WITH GASKET
1	992200111134	2KS070 FROSTED COVER PC WITH GASKET
2	992200111135	1KK150/3KK150 MAST FIXATION SCREW ASSY
3	992200111136	2KS-/3KS070 FELT GASKET
4	992200110907	REDUCTION PIECE, DIAMETER 76/60mm
5	992200111138	2KS-/3KS070 OPENER FOR POWER UNIT (plastic)
6	992200111139	2KS-/3KS070, 1KH100 SOCKET CLASS I
7	992200111140	2KS-/3KS070, 1KH100 PLUG CLASS I
6	992200111141	2KS-/3KS070, 1KH100 SOCKET CLASS II
7	992200111142	2KS-/3KS070, 1KH100 PLUG CLASS II
no picture	992200111143	3KS070 COVER-PLATE, NOT STRUCTURED, LOW BEAM SKIRT
no picture	992200111145	3KS070 FLAT SCREEN PC WITH GASKET
8**	992200111146	2KS-/3KS070 POWER UNIT 1xHPL 80/125W **
8**	992200111147	2KS-/3KS070 POWER UNIT 1xHPL 125W **
8**	992200111148	2KS-/3KS070 POWER UNIT 1xSON 50/70W-E **
8**	992200111149	2KS-/3KS070 POWER UNIT 2xPL-S 11W **
8**	992200111150	2KS-/3KS070 POWER UNIT 1xPL-T 32W EVG / HF
8**	992200111151	2KS-/3KS070 POWER UNIT 2xPL-L 18W **
8**	992200111152	2KS-/3KS070 POWER UNIT 1xHPL 50/80W **
8**	992200111153	2KS-/3KS070 POWER UNIT 1xSON 70/50W **
8**	992200111255	2-/3KS070 POWERUNIT 1xSON50/70W IC II F

\*\* The power unit contains: main unit, ballast, lampholder, ignitor, wire with plug.

[Back to Index](#)

# Service Manual

2KS070 & 3KS070

Koffer 1 70







2KS070



3KS070

[Back to Index](#)

# PHILIPS



Number	Service 12nc	Description
1	992200111131	2KS070 PRISMATIC COVER PMMA WITH GASKET
1	992200111132	2KS070 PRISMATIC COVER PC WITH GASKET
1	992200111133	2KS070 FROSTED COVER PMMA WITH GASKET
1	992200111134	2KS070 FROSTED COVER PC WITH GASKET
2	992200111135	1KK150/3KK150 MAST FIXATION SCREW ASSY
3	992200111136	2KS-/3KS070 FELT GASKET
4	992200110907	REDUCTION PIECE, DIAMETER 76/60mm
5	992200111138	2KS-/3KS070 OPENER FOR POWER UNIT (plastic)
6	992200111139	2KS-/3KS070, 1KH100 SOCKET CLASS I
7	992200111140	2KS-/3KS070, 1KH100 PLUG CLASS I
6	992200111141	2KS-/3KS070, 1KH100 SOCKET CLASS II
7	992200111142	2KS-/3KS070, 1KH100 PLUG CLASS II
no picture	992200111143	3KS070 COVER-PLATE, NOT STRUCTURED, LOW BEAM SKIRT
no picture	992200111145	3KS070 FLAT SCREEN PC WITH GASKET
8**	992200111146	2KS-/3KS070 POWER UNIT 1xHPL 80/125W **
8**	992200111147	2KS-/3KS070 POWER UNIT 1xHPL 125W **
8**	992200111148	2KS-/3KS070 POWER UNIT 1xSON 50/70W-E **
8**	992200111149	2KS-/3KS070 POWER UNIT 2xPL-S 11W **
8**	992200111150	2KS-/3KS070 POWER UNIT 1xPL-T 32W EVG / HF
8**	992200111151	2KS-/3KS070 POWER UNIT 2xPL-L 18W **
8**	992200111152	2KS-/3KS070 POWER UNIT 1xHPL 50/80W **
8**	992200111153	2KS-/3KS070 POWER UNIT 1xSON 70/50W **
8**	992200111255	2-/3KS070 POWERUNIT 1xSON50/70W IC II F

\*\* The power unit contains: main unit, ballast, lampholder, ignitor, wire with plug.

[Back to Index](#)