



Service Manual

MCS241 & MRS241 & MCS244 & MRS244
LCS242 & LRS242 & QCS243 & QRS243

EFix Projector Micro (Philips)



MCS241
CDM-Tm Baseplate



MRS241
CDM-Tm 3C



MCS244
CDM-Rm Baseplate



MRS244
CDM-Rm 3C

[Return
to
Index](#)

PHILIPS



**LCS242 Dichroic
Halogen Baseplate**



**RS242 Dichroic
Halogen 3C**




**QCS243 PAR
Halogen Baseplate**




**QRS243 PAR
Halogen 3C**


[Return
to
Index](#)




1a



1b



2



3

Number	Service 12nc	Description
1a	992200111410	MCS241/MRS241 REFLECTOR 12 DEGREES
1b	992200111411	MCS241/MRS241 REFLECTOR 36 DEGREES
2	992200111412	MCS241/MRS241 FRONTGLASS INCLUDING RING
3	992200111413	MCS241&244/LCS242/QCS243 BASEPLATE BRACKET

[Return to Index](#)

Lampholders used



E27 Lampholders made of porcelain, one-piece

Type: 62310

Item number: 102624

Lamp base:	E27
Material:	Porcelain
Colour:	White
Style:	One-piece
Fixing:	Fixing holes for screws M4
Connection:	Screw terminal 0,5-2,5 mm
Earth terminal:	No
T-Marking:	270
For Cover caps:	Yes
Nominal rating:	4/250/5KV
Safety catch:	No

Unit: 150 pcs.



914499997330 MASTERC CDM-Tm Mini 35W/930 PGJ5 KIT/12

Ballasts used

913700601466 HID-PV m 1x020/S mCDM LPF 220-240V

913700611866 HID-PV m 1x035/S CDM HPF 220-240V

[Return
to
Index](#)

