


Field Service Manual

MVF 401 range, 1000W version




MVF 401 range, 1000W version
Medium optic
Wide optic

This is the service manual of the
above mentioned luminaires.

Field Service Manual

MVF 401 range, 1000W version

3222 609 27861
10/02
Data subject to change



Item	Ordering number	Description
1	9965 000 05761	Aluminium frame incl. safety net
2a	9965 000 05770	Frontglass downlight (see drawing A)
2b	9965 000 05762	Frontglass uplight (see drawing B)
3a	9965 000 05763	Front reflector assy medium
3b	9965 000 05764	Front reflector assy wide
4	9965 000 05041	Adjustment part incl. washer and cap
5	9965 000 05042	Gasket rear house
6a	9965 000 05765	Rear reflector medium
6b	9965 000 05766	Rear reflector wide
7	9965 000 05049	Microswitch
8	9965 000 05050	Lamp support set ¹⁾
9	9965 000 05052	Assy lamp connection ²⁾
10	9965 000 05053	Assy clip rear house ³⁾
11	9965 000 05054	Wiring set
12	9965 000 05055	Alu terminal box with wiring in tube
13	5322 447 92403	Cover terminal box + gasket
14	5322 447 92405	Alu box empty
15	9965 000 05768	Serie ignitor mono

1) Set = left + right.
2) Single connector.
3) Single clip.