


Service Manual

MVP504
OptiFlood



[Back to
Index](#)

PHILIPS



Number	Service 12nc	Description
1	992200110285	MVP504 CLOSING CLIP
2a	992200110286	MVP504 LAMPHOLDER&BRACKET ASSYMETRIC COSMOPOLIS
2b	992200110287	MVP504 LAMPHOLDER&BRACKET E27 ASYMMETRIC
2c	992200110288	MVP504 LAMPHOLDER&BRACKET CDM-TD 150W
2d	992200110289	MVP504 LAMPHOLDER&BRACKET CDM-TD 70W
3	992200110290	MVP504 REFLECTOR ASSYMETRIC
4	992200110291	MVP504 GLASS COVER
5	992200110292	MVP504 GLASS GASKET
6	992200110293	MVP504 FRAME GASKET
7a	992200110294	MVP504 WIREGUARD FRAME ASSY UNPAINTED
7b	992200110295	MVP504 WIREGUARD FRAME ASSY 10714

Data subject to change

[Back to](#)
[Index](#)

Ballast and ignitor info MVP504

SON50W - Class 1 Versions

ballast

913700255700 CB1 SON50 230-240 BSN50L427ITS

Ignitor

913700139400 AMORCEUR SN 57T15 COURT

SON/CDO 70W - Class 1 Versions

ballast

913700255900 CB1 SON70 230-240 BA BSN70L427ITS

Ignitor

913700256500 SN 58T15 220-240V 50/60Hz/

CDM 70W - Class 1 Versions

913700256500 CB1 CDM70 230-240 BA BMH70L427ITS

Ignitor

913700256500 SN 58T15 220-240V 50/60Hz/

SON50W - Class 2 Versions

ballast

242254900182 CB1 SON50-70 230 RI OMBS70-50 A201D

Ignitor

242254944332 IG1 SON35-70 230 SU ZRM 2 ES-B

SON/CDO 70W - Class 2 Versions

ballast

913700269200 CB1 SON70 230-240 RI BSN70L327 TS R

Ignitor

242254944332 IG1 SON35-70 230 SU ZRM 2 ES-B

Electronic ballast types - All Versions

913700614066 HID-PV C 150 /S CDM 220-240V 50/60Hz

913700652966 HID-PV C 70 /S CDM 220-240V 50/60Hz

913700652766 HID-PV C 35 /S CDM 220-240V 50/60Hz

913700657366 HID-DV 1-10V 70 /S CDO 220-240V 50/60Hz

913700657466 HID-DV 1-10V 70 /S SON 220-240V 50/60Hz

Cosmopolis 45/60/90 - All Versions

913700635100 HID-PV 45 CPO-TW Extreme Tc 80

913700635000 HID-PV 60 CPO-TW Xtreme Tc 80

913700635200 HID-DV LS-6 Xt 60 /S CPO-TW Xtrem Tc 80

913700635300 HID-DV LS-8 Xt 60 /S CPO-TW Xtrem Tc 80

913700635400 HID-DV LS-10 Xt 60 /S CPO-TW Xtrem Tc 80

913700642272 HID-PV Xt 90 /S CPO-TW 220-240V 50/60Hz

913700642300 HID-DV LS-6 Xt 90 /S CPO-TW 220-240

913700642400 HID-DV LS-8 Xt 90 /S CPO-TW 220-240

913700642500 HID-DV LS-10 Xt 90 /S CPO-TW 220-240

Data subject to change

[Back to](#)
[Index](#)