

BALASTRO ELECTRÓNICO 2x24 W T5 120 V -277V

Encendido Rapido - Programado
Circuito Serie

NI520, ICN2S2473M

Tipo de lámpara	No. de lámparas	Watt lámparas	Temp. de arranque (°F/°C)	Volts	Corriente de línea (A rcm)	Potencia de línea (W Watt)	THD (Máx.)	Factor de Potencia
F24T5/HO	1	24	0/-18	120-277	0.23/0.10 A	27	10	0.98
F24T5/HO	2	24	0/-18	120-277	0.44/0.19 A	52	10	0.98
F39T57HO	1	39	0/-18	120-277	0.34/0.15 A	40	10	0.98
FC12T5	1	40	0/-18	120-277	0.34/0.15 A	40	10	0.98
FC9T5	1	22	0/-18	120-277	0.23/0.10 A	27	10	0.98
FC9T5	2	22	0/-18	120-277	0.44/0.19 A	52	10	0.98
FT24W/2G11	1	24	0/-18	120-277	0.23/0.10 A	27	10	0.98
FT24W/2G11	2	24	0/-18	120-277	0.44/0.19 A	52	10	0.98
FT36W/2G11	1	36	0/-18	120-277	0.29/0.13 A	34	10	0.98
FT40W/2G11/RS	1	40	0/-18	120-277	0.40/0.17 A	47	10	0.98





DIAGRAMA DE CONEXIÓN



Longitud (L)	Ancho (W)	Alto (H)	Montaje (M)
--------------	-----------	----------	-------------

42.4 cm	3.0 cm	1.0 cm	41.5 cm
---------	--------	--------	---------

16.70"	1.18"	1.00"	16.34"
--------	-------	-------	--------

NOM

Philips Lighting Electronics North America - Mexico
 Av. de la Palma, No. 6 Piso 2 Col. San Fernando, La Herradura, C.P. 52760, Huixquilucan, Edo. de México
 Tel: 5269-9316, Fax: 5269-9032
 lumisistemas@philips.com

www.lumisistemas.com

**PHILIPS
ADVANCE**